


MY2H, Mechanical Joint Rodless Cylinder, High Precision Guide, w/High Load Shock Absorber, Series H

MY2H25TFG-400H

Datasheet

General series information

- Series H: w/High Load Shock Absorber.




Rodless cylinder mechanically joint with adjustable cushion

Standard specifications

Guide Suffix	High Precision Guide 1 Shaft
Bore Size	25 mm
Port Thread	TF [G (Ø25 & 40)]
Stroke	400
Stroke Adjusting Unit	H (Left: w/High Load Shock Absorber; Right: w/High Load Shock Absorber)
Auto Switch	No Switch
Lead Wire or Prewired Connector	0.5m (Or None in the Case of No Switch)
Number	2 pcs. (Or None in the Case of No Switch)
Made to Order	None
Pressure medium	Air
Maximum temperature of pressure medium	60 °C
Minimum temperature of pressure medium	5 °C
Maximum operating pressure	0.8 MPa
Minimum operating pressure	0.1 MPa
Proof pressure	1.2 MPa
Maximum ambient temperature with magnet	60 °C
Minimum ambient temperature with magnet	5 °C
Conform to the European RoHS Directive	Conform
Number of pneumatic connections	4 pcs.
Pneumatic input connection	G 1/8
Pneumatic exhaust connection	G 1/8
Mode of operation of drive	Double acting

Theoretical cylinder force, advance stroke (at 0.5 MPa)	245 N
Maximum piston speed	1500 mm/s
Type of cushioning	Air Cushion
Minimum piston speed	100 mm/s
Lubrication	Non-lube
Weight	4.350 Kg



Additional information

Catalogue

[MY2-Bb_EU.pdf](#)

Operation manuals

[OM_MY2_OM0011QEN.pdf](#)