

## RENOCLEAN 269

Water dilutable cleaner & degreaser

### Description

RENOCLEAN 269 is a low viscosity straw coloured fluid designed for use, when diluted with water, as a cost effective general cleaner and degreaser for multi-metal components, and as a barrelling fluid in certain applications.

### Application

For cleaning applications, it is designed for use at temperatures above 55°C, it is very low foaming and inhibits rusting of ferrous components. This product is nitrite and phosphate free.

The product is formulated for use at 3-5%.

As a degreaser, application is usually with automatic spray systems operating above 55°C.

For barrelling applications the fluid is used at ambient temperatures.

Drying is not normally necessary due to the superior anti-corrosion properties.

### Advantages/Benefits

- Low foaming potential
- Mineral oil, boron, phosphate and nitrite free
- Protects against rust
- Does not emulsify oils and greases - allows them to be removed by skimming from surface, helping to extend the fluid life

### Skin Protection

To maintain a healthy skin condition when using cleaning materials within your particular working environment, FUCHS recommend the use of **Velvetone Hand Protect** cream before commencing work. At the end of the day, after thorough cleansing, recondition the skin using **Velvetone Hand Care Conditioning** cream.



February 2014 GDUK Page 1 of 2

## CHARACTERISTICS (Concentrate): RENOCLEAN 269

Characteristics	Unit	Test Method
Appearance	Straw fluid	
Odour characteristics	Mild, fatty	
Specific gravity at 15.6°C	1.025	IP160
Oil content	Nil	
Boron content	Nil	
Nitrite content	Nil	

## CHARACTERISTICS (Emulsion): RENOCLEAN 269

pH value at 2%	10.5	
Corrosion filterchip	%	>2.0 break point IP287
Foaming	Very low	
Temperature stability	Normal, avoid frost	
Shelf life	12 months when stored in original container	
Refractometer correction factor	3.6	

*Note: Refractometer Reading x Correction Factor = Actual Concentration*

## FUCHS Spray Cleaners

✓ ✓ ✓ \* = Best    ✓ ✓ ✓ = Excellent    ✓ ✓ = Good    ✓ = Not advised

Metal Type	Product	Cleaning	Low Temp	High Pressure	Corrosion Prevention
FERROUS	RENOCLEAN S 237 BF	✓ ✓ ✓ *	✓ ✓ ✓	✓ ✓ ✓	✓ ✓ ✓
	RENOCLEAN 269	✓ ✓	✓	✓ ✓	✓ ✓
MULTI	RENOCLEAN MS 215 NF UK	✓ ✓ ✓	✓ ✓ ✓	✓ ✓ ✓	✓ ✓ ✓
	RENOCLEAN MS 214 F	✓ ✓ ✓	✓ ✓ ✓	✓	✓ ✓ ✓
ALUMINIUM	RENOCLEAN MS 215 NF UK	✓ ✓	✓ ✓ ✓	✓ ✓ ✓	✓ ✓ ✓
	RENOCLEAN MSO 3004	✓ ✓ ✓ *	✓ ✓	✓ ✓ ✓	✓ ✓ ✓