



Energy & Power > Power Systems Connectors > Mechanical Connectors > Shear Bolt Connectors up to 35 kV



Mechanical Connector Product Type: **Shear Bolt Connector**

Installation Technology: **Shear Bolt**

Voltage Class: **≤ 35 kV**

Compatible Conductor Material: **Aluminum, Copper**

Compatible Conductor Range: **600 – 1000 AWG/kcmil**

[All Shear Bolt Connectors up to 35 kV \(14\)](#)

Features

Product Type Features

Installation Technology	Shear Bolt
-------------------------	------------

Configuration Features

Visual Inspection	Yes
-------------------	-----

Electrical Characteristics

Voltage Class	≤ 35 kV
---------------	---------

Body Features

Compatible Conductor Material	Aluminum, Copper
-------------------------------	------------------

Dimensions

Compatible Conductor Range	600 – 1000 AWG/kcmil
Compatible Conductor Cross-Section Range	304 – 507 mm²

Operation/Application

Mechanical Connector Product Type	Shear Bolt Connector
-----------------------------------	----------------------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Product Availability

--	--



Product Availability	Americas, Australia, New Zealand & Pacific Islands
----------------------	--

Other

Conductor Gauge Type	AWG
----------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (1.5% in 74023549) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

ASBS-600-1000

English

Datasheets & Catalog Pages

ALUMINUM SHEAR BOLT SPLICE ASBS CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English