

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Type 2 surge protection plug for VAL-SPP base element, thermally monitored, optical red/green status indicator.

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466685
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	CL138Z
GTIN	4063151860165
Weight per piece (including packing)	52.8 g
Weight per piece (excluding packing)	49 g
Country of origin	DE

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Technical data

Product properties

Product type	Replacement plug
Product family	VAL-SPP
IEC test classification	II
	T2
EN type	T2
IEC power supply system	TN-C
	TN-S
	TT
Type	Male
Number of positions	1
Surge protection fault message	optical

Insulation characteristics

Overvoltage category	III
Pollution degree	3


Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
-------------------------	---------------

Connection data

Connection method	pluggable
-------------------	-----------

Dimensions

Dimensional drawing	
Width	17.5 mm
Height	54.2 mm
Depth	61.5 mm
Horizontal pitch	1 Div.

Material specifications

Color	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
Material group	I
Housing material	PA 6.6-FR 20 % GF

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Protective circuit

Mode of protection	L-N
	L-PEN
Direction of action	1L-N/PE
Nominal voltage U_N	240 V AC $\pm 10\%$ (TN-C, TN-S)
	240 V AC $\pm 10\%$ (TT)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous voltage U_C	275 V AC
Residual current I_{PE}	≤ 0.4 mA
Standby power consumption P_C	≤ 120 mVA
Nominal discharge current I_n (8/20) μ s	20 kA
Maximum discharge current I_{max} (8/20) μ s	40 kA
Short-circuit current rating I_{SCCR}	50 kA
Voltage protection level U_p	≤ 1.35 kV
Residual voltage U_{res}	≤ 1.35 kV (at I_n)
	≤ 1.1 kV (at 10 kA)
	≤ 1 kV (at 5 kA)
	≤ 0.9 kV (at 3 kA)
TOV behavior at U_T	350 V AC (5 s / withstand mode)
	460 V AC (120 min / safe failure mode)
Response time t_A	≤ 25 ns
Max. backup fuse with branch wiring	315 A (gG)

Additional technical data

Short-circuit current rating I_{SCCR}	100 kA
---	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Standards and regulations

Standards/specifications	IEC 61643-11
Note	2011
Standards/specifications	EN 61643-11
Note	2012 + A11:2018

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Mounting

Mounting type	on base element
---------------	-----------------

VAL-SPP-T2-275-P - Type 2 surge protection plug


1466685

<https://www.phoenixcontact.com/in/products/1466685>



Drawings

Dimensional drawing



Circuit diagram



VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1466685>



IECEE CB Scheme

Approval ID: NL-109184

CCA

Approval ID: NTR NL-8052



KEMA-KEUR

Approval ID: 71-138153 REV.2

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Classifications

ECLASS

ECLASS-11.0	27130890
ECLASS-13.0	27171292

ETIM

ETIM 9.0	EC002496
----------	----------

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685

<https://www.phoenixcontact.com/in/products/1466685>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

VAL-SPP-T2-275-P - Type 2 surge protection plug



1466685


<https://www.phoenixcontact.com/in/products/1466685>

Accessories

VAL-SPP-T2-BE-3+1-UT - Type 2 surge protection base element

1466705

<https://www.phoenixcontact.com/in/products/1466705>




Base element for type 2/Class II arresters from the VALVETRAB SPP product family. Version for 3-phase power supply networks with separate N and PE (5-conductor system: L1, L2, L3, N, PE).

VAL-SPP-T2-BE-1+1-UT - Type 2 surge protection base element

1466703

<https://www.phoenixcontact.com/in/products/1466703>



Base element for type 2 arresters from the VAL-SPP product family. Version for 1-phase power supplies with separate cable routing of N and PE.

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in