

41472 ✓ ACTIVE


TE Internal #: 41472

Closed Ring Tongue Terminal, 20 – 16 AWG, #8 / M4 Stud, 3.96 mm [.156 in] Stud Diameter, Open Barrel, Straight, Tin Plating, Uninsulated

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: **Closed Ring Tongue Terminal**

Wire Size: **1021 – 2582 CMA**

Stud Size: **#8, M4**

Features

Product Type Features

Shape Description	Circular/Oval
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	.319 g
----------------	--------

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel



Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.1 in
Wire Size	1021 – 2582 CMA
Stud Diameter	3.96 mm [.156 in]
Tongue Thickness	.76 mm [.03 in]
Product Length	11.94 mm [.47 in]
Barrel Inside Diameter	2.03 mm, 2.92 mm [.08 in] [.115 in]
Compatible Insulation Diameter (Max)	3.43 mm [.135 in]
Compatible Insulation Diameter Range	2.54 – 3.43 mm [.1 – .135 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	25000
Packaging Method	Strip/Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC

Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 61764-1
RING CRIMP 20-16 AWG BR



KIT
REPRESENTATION ONLY

TE Part # 7-2150461-7
OCEAN_2.0_SPARE_PART_KIT-120F155F



TE Part # 2150461-2
OCEAN_2.0_Applicator-E-120F155F-REA




TE Part # 2150461-1
OCEAN_2.0_Applicator-E-120F155F-REM

Customers Also Bought



TE Part #41532
250 FASTON FLAG REC 18-12 AWG TPBR




TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals



TE Part #63137-1
250 FASOTN FLAG REC 20-16 AWG TPBZ




TE Part #40723
RING 138(3.50 MM) TERMINAL18-14 AWG TPBR




TE Part #350969-1
MR GRND PIN 26-18 PTPPHBZ



TE Part #63971-1
250 FASTON TAB TPBR



TE Part #325069
TERMINAL,SOLIS FLAG R 16-14 8



TE Part #53425-1
TERMINAL,PIDG PVF2 R 12-10 10



Documents

Product Drawings

RING TERMINAL 20-16 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_41472_P_c-41472-p.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_41472_P_c-41472-p.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_41472_P_c-41472-p.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English