



tesa® Anti-Slip Tape Fluorescent

Product Information

BNR 55580, 55629

Product Description

The reflecting tesa® anti slip tape provides security and safety by reducing the danger of slipping. It is often attached to staircases, ramps or ladders.

Product Features

- Extremely strong and durable fluorescent tape
- Very strong adhesion
- Glows in the dark up to 20 minutes
- Hand-tearable
- Resistant to water, temperature, UV and cleaning agents

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- Type of adhesive acrylic

Properties/Performance Values

• Abrasion resistance	yes	• Material	PVC
• Adhesive strength	High adhesion	• Residue-free removability	no
• Applicationfield	Home, Hall, Garage, Bathroom	• Reusable	no
• Area of use	Indoor	• Solvent free	yes
• Batteries included	no	• Spare part service	no
• Batteries required	no	• Suitable surfaces	Tiles, Most plastics, Plaster, Steel, Stone, Metal
• Fluorescent	yes	• Temperature resistance	yes
• Hand tearability	yes	• Temperature resistance max.	50 °C
• Hazard material	no	• Temperature resistance min.	0 °C



tesa® Anti-Slip Tape Fluorescent

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?cp=NaN>