




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Insulation Boots & Sleeves



Insulation Boot & Sleeve Product Type: **Insulation Boot**

Terminal Orientation: **Flag**

Compatible Insulation Diameter (Max): **3.3 mm**

Primary Product Material: **Nylon 66**

Primary Product Color: **Natural**

Features

Product Type Features

Insulation Boot & Sleeve Product Type	Insulation Boot
---------------------------------------	-----------------

Configuration Features

Number of Positions	1
---------------------	---

Body Features

Primary Product Material	Nylon 66
Primary Product Color	Natural

Contact Features

Accepts Terminal Style	Receptacle
Terminal Orientation	Flag

Dimensions

Compatible Insulation Diameter (Max)	3.3 mm
--------------------------------------	--------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features



Packaging Quantity	2000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | **POD-LOK 187**



Insulation Boots & Sleeves(1)



Quick Disconnects(3)

Customers Also Bought




TE Part #CAT-P842-187045
POD LOK: Flag, Receptacle Assembly, Tin Plated, 0.187 inch



TE Part #794617-4
4POS,MICRO MNL,RCPT HSG




TE Part #8-1879335-6
CPF 0603 165R 1% 50PPM 1K RL



TE Part #52772-1
TERMINAL,BUDG SPR SPD 12-10



TE Part #2-2329328-2
PB ON/OFF HC RED M1 TERM IP68



TE Part #2317947-1
POD-LOK 250 FLAG BACKCOVER NYLON NAT



TE Part #1-104482-3
30 SHORT PT RCPT HSG DR .100CL



TE Part #165019
PG SPADE



TE Part #60938-2
250 FASTON REC 18-14 AWG TPBR

Documents

Product Drawings

POD-LOK 187 FLAG BACKCOVER NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2317947-2_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2317947-2_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2317947-2_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[pod-lok_receptacles_qrg](#)

English

Product Specifications

[Application Specification](#)

English