


## FEATURES

- **High Chemical Resistance:** Suitable for use with a wide range of chemicals, enhancing durability.
- **Temperature Range of -20 °C to 140 °C:** Ensures performance in both cold and hot environments.
- **Shore A Hardness of 90 to 95:** Provides a balance of flexibility and strength for effective sealing.
- **Compliance with Multiple Standards:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance.
- **Made from Fluoroelastomer and Viton:** Offers superior resistance to heat and aggressive chemicals.

## RS PRO Black O-Ring Seal, Shore A 90 to 95

RS Stock No: 731-340



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in various industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene and Viton, it offers excellent resistance to chemicals and extreme temperatures. Ideal for use in demanding environments, this O-Ring ensures optimal performance and longevity.

## General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

## Mechanical Specifications

Inside Diameter	145.72 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	150.96 mm
Thickness	2.62 mm

## Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

## Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

