

Power Cutter XGT®

CE001G

40Vmax X2 • 355 mm • 5 300 min⁻¹

Powerful XGT® Battery powered Power Cutter with two 40Vmax batteries.

Powerful and lightweight cordless power cutter with 355 mm blade for professional construction. Brushless motor. Water connection as standard.



XGT 80Vmax **BL** MOTOR **AFT**

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	2 x 40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	5300 min ⁻¹
Max. Depth of Cut	127 mm
Bore Size (Arbor Diameter)	20 / 25,4 mm
Disc Diameter	355 mm
Electronic brake	✓
Vibration Level, Concrete Cutting	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Concrete Cutting	1,5 m/s ²
Sound Power Level (L _{WA})	120 dB(A)
Sound Pressure Level (L _{pA})	109 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

E-12996

Diamond Wheel 25.4 x 355mm



B-13275

Diamond wheel 350 mm, Comet, Wet



B-54053

Diamond wheel 350 mm, Nebula, Dry



B-55348

Vacuum Brazed Rescue Diamond



E-12790-5

Cut-off wheel, 355 x 4,3 x 25,4 mm,



Other

[User manual](#)

[Parts drawing](#)