


Product datasheet

Specifications



locating dowels 3,8xd8/d5,5 - 20 pieces

VW33MF020LD01

EAN Code: 3606485219981

Main

Range of product	Lexium linear motion
Product or component type	Adaptor
Accessory / separate part category	Maintenance accessories

Complementary

Product compatibility	PAS 41 linear axis, outer dimension : 40 x 40 mm PAS 42 linear axis, outer dimension : 60 x 60 mm CAS 41 linear axis, outer dimension : 40 x 40 mm CAS 42 linear axis, outer dimension : 60 x 60 mm CAS 30 cantilever axis, outer dimension : 70 x 28 mm CAS 31 cantilever axis, outer dimension : 80 x 30 mm
Range compatibility	Lexium CAS Lexium PAS

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	12.8 cm
Package 1 Length	18.8 cm
Package 1 Weight	92 g
Unit Type of Package 2	S04
Number of Units in Package 2	18
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	2.42 kg

Logistical informations

Country of origin	DE
-------------------	----

Contractual warranty

Warranty (in months)	18
----------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
PVC free	Yes

Use Longer


Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No

Dimensions Drawings

Dimensions



Dimensions in mm

ØD1	ØD2
5.5	8 h6

Dimensions in in.

ØD1	ØD2
0.22	0.31 h6