




**Part Number :** [395321005](#)

**Product Description :** 5.08mm Pitch Eurostyle Right-Angle PCB Header, 5 Circuits

**Series Number :** 39532

**Status :** Active

**Product Category :** Terminal Blocks and Barrier Strip



---

## Documents & Resources

### Drawings

[395321005\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

### Specifications

[PS-39500-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |  |
|--------------------|--|
| GADSL/IMDS         | Not Relevant   |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant   |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21   |
| REACH SVHC         | Not Contained per D(2025)4165-DC<br>(25 June 2025)   |
| EU RoHS            | Compliant per EU 2015/863  |

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | Terminal Blocks and Barrier Strip                         |
| Series         | 39532   |
| Description    | 5.08mm Pitch Eurostyle Right-Angle PCB Header, 5 Circuits |
| Application    | Wire-to-Board   |
| Component Type | PCB Header  |
| Product Name   | Eurostyle Pluggable                                       |
| Type           | PCB Terminal Blocks and Connectors                        |
| UPC            | 822350506564  |

### Agency

|    |        |
|----|--------|
| UL | E48521 |
|----|--------|

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 15.0A |
| Voltage - Maximum             | 300V  |

### Physical

|                    |   |
|--------------------|---|
| Circuits (Loaded)  | 5 |
| Circuits (maximum) | 5 |

|                               |                |
|-------------------------------|----------------|
| Color - Resin                 | Black          |
| Entry Angle                   | N/A            |
| Lock to Mating Part           | Yes            |
| Net Weight                    | 2.320/g        |
| Number of Rows                | 1              |
| Orientation                   | Horizontal     |
| Panel Mount                   | No             |
| PCB Thickness - Recommended   | 3.18mm         |
| PC Tail Length                | 5.08mm         |
| Pitch - Mating Interface      | 5.08mm         |
| Pitch - Termination Interface | 5.08mm         |
| Polarized to Mating Part      | Yes            |
| Shrouded                      | Closed Ends    |
| Stackable                     | No             |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size (AWG)               | N/A            |

---

## Mates With / Use With

### Mates with Part(s)

| Description                             | Part Number                               |
|---|---|
| 5.08mm Pitch Eurostyle Horizontal Plugs | <u><a href="#">39530</a></u>              |
| 5.08mm Pitch Eurostyle Vertical Plugs   | <u><a href="#">39533</a></u>              |
| Mates With                              | Most 5.08mm Pitch Industry Standard Plugs |