

## FEATURES

- **LED Display:** Provides clear visibility of settings and temperature for precise control
- **Dual Output:** Allows for simultaneous operation of two soldering tools, increasing efficiency
- **Wide Input Voltage Range:** Compatible with 110 to 230 V, suitable for international use
- **High Power Rating of 70W:** Ensures rapid heating and consistent performance
- **Maximum Temperature of 500°C:** Capable of handling a variety of soldering tasks
- **Type G and Type E Plug Options:** Offers flexibility for use in different regions

## RS PRO LED Soldering Station, 70W 500°C

RS Stock No: 631-069



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO LED Soldering Station is designed for precision soldering tasks, offering reliable performance with a power rating of 70W. It supports a wide input voltage range from 110 to 230 V, making it versatile for various work environments. The station is ideal for both professional and hobbyist applications, providing consistent heat for effective soldering.

### General Specifications

Display Type	LED
Number of Outputs	2
Product Type	Soldering Station
Soldering Tip Temperature	500 °C
Tasks Supported	Soldering

### Protection Category

ESD Safe	No
----------	----

### Electrical Specifications

Input Voltage	110-230 V
Plug Type	Type G - British 3-Pin, Type E - France-2 Round Pin
Power Rating	70 W

### Approvals

Standards/Approvals	CE, UKCA
---------------------	----------

