

# Direct Drive Oil Free *fiac*



LEONARDO



ECU

Also available  
as 110 Volt



FX95



FX250

## Key Features

- Automatic stop/start controls - requires minimum supervision
- All 230V models are supplied with 13 amp plug and cable - ready for use
- Motor overload protection and air receivers to 09/105 CE ensures maximum user protection
- Lightweight with carry handles or wheels, makes this range of compressors convenient and easy to use
- 12 months warranty

Order Code	Model	HP	Tank Litres	Displacement CFM	Max Pressure PSI	Motor Pump RPM	Weight Kg	Electrical Phase	Dimensions mm LxWxH
1027990000	LEONARDO	1.0	6	3.7	116	1450	17	1	430 x 187 x 450
1028010000	ECU	1.5	6	7.3	116	2850	16	1	410 x 187 x 450
1218010000	FX95	1.5	24	6.0	116	2850	27	1	650 x 315 x 630
1369430000	FX250	2.0	50	8.4	116	2850	46	1	845 x 320 x 665