



SEE SHEET 2		
FOR CONTACT & BRACKET DIMENSION DETAILS	S	

THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE

BASIS FOR THE MANUFACTURE OR SALE OF

APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

DATE:

P. JENKINS

08/22/2011

SPECIFICATIONS:

ELECTRICAL:

ELECTRICAL:	
INSULATOR RESISTANCE:	5 GOhms MIN.
WORKING VOLTAGE:	250V
OPERATING TEMPERATURE:	-55°C TO +125°C
POWER CONTACT RESISTANCE:	2.0 mOhms MAX.
POWER CONTACT AMPERAGE:	SEE P/N KEY
MECHANICAL:	
CONTACT INSERTION FORCE:	4.5 Kg MAX.
CONTACT SEPARATION FORCE:	0.3 Kg MIN.
MATERIALS:	
CONTACTS:	COPPER ALLOY, GO
INSULATOR:	PBT UL94V-0 RATED

SHELL: BRACKET: BOARD LOCK: COPPER ALLOY, GOLD FLASH PBT UL94V-0 RATED 230°C PROCESS TEMP. NICKEL PLATED STEEL NICKEL PLATED STEEL NICKEL PLATED BRASS

684M3W3103LYYY

00 = 40 AMP POWER // NO BRACKET // STANDARD PCB TAILS -46 = 40 AMP POWER // #4-40 BRACKET // STANDARD PCB TAILS 62 = 40 AMP POWER // #4-40 BRACKET // 2.22mm PCB TAILS

1 = GOLD FLASH -

_	UNITS = inches [mm] DO NOT SCALE FROM DRAWING			
	NorComp	SCALE: NTS	SHEET OF 1 2	REV 7
NorComp		DWG NO. 684M3W3103L461		

ROMS COMPLIANT THESE DRAWINGS AND SPECIFICATIONS ARE

M	
IØ.	



