




Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Headers



Sealable: No

Shielded: Yes

PCB Mount Orientation: Horizontal

Number of Positions: 1

Connector Mounting Type: Board Mount

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Mixed & Hybrid Connector	No
Sealable	No

Configuration Features

PCB Mount Orientation	Horizontal
Number of Positions	1

Electrical Characteristics

Impedance	50 Ω
Operating Voltage	60 VDC

Signal Characteristics

Operating Frequency Range	0 – 6000 MHz
---------------------------	--------------

Body Features

PCB Retention Feature Plating Material	Tin
--	-----



Body Material	PA6T GF30
Connector & Keying Code	C

Contact Features

Outer Contact Plating Material	Tin (Sn)
RF Connector Center Contact Plating Material	Other
Contact Mating Area Plating Material	Gold (Au)
Center Contact	With
Contact Type	Pin
Mating Pin Diameter	.5 mm[.02 in]

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

PCB Mount Retention	With
Mating Retention	With
PCB Mount Retention Type	Boardlock
Connector Mounting Type	Board Mount

Housing Features

Housing Color	Blue
---------------	------

Dimensions

Product Width	10.4 mm[.409 in]
Product Length	19.5 mm[.768 in]
Connector Height	13.8 mm[.543 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Assembly Process Feature	Board Standoff
Shielded	Yes
Circuit Application	Signal

Industry Standards

Compatible With Agency/Standards Products	USCAR
---	-------

Other



Dielectric Material	PCT
---------------------	-----

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2474533-1
ADAPTER, SMA F TO FAKRA F, NO
HOUSING, 6GHZ



TE Part # 1452584-3
1 WAY PLUG CONN FAKRA2



TE Part # 2474535-1
ADAPTER, SMA F TO FAKRA F W H,
STR, 6GHZ

Also in the Series | [FAKRA RF Connector System](#)




Automotive Connector Caps & Covers (2)



Automotive Terminals(28)



Connector Contacts(1)



Data Connectivity Housings(430)



Power Contacts(1)



RF Contacts(6)

Customers Also Bought



TE Part #2322610-2
12POS,TAB0.63X0.63,HDR ASSY, 90DEG,SLDR



TE Part #1-2295321-6
RITS CONN. SOCKET ASSY 6P RED TIN



TE Part #2291392-1
MALE ASM, 1 POS, R/A, PCB, FAKRA



TE Part #2291364-2
4POS,PIN DIA 0.6,HEADER ASSY, CODE B



TE Part #2291392-3
MALE ASM, 1 POS, R/A, PCB, FAKRA




TE Part #2322610-1
12POS,TAB0.63X0.63,HDR ASSY, 90DEG,SLDR



TE Part #2321709-1
4POS,TAB2.8X0.8,HDR ASSY,180DEG, SLDR



TE Part #CAT-SIGH262
Signal Header



TE Part #1563308-2
24POS, MIXED,PIN HSG,ASSY

Documents



Product Drawings

Jack Assy, RA, Panel Mount, PCB, FAKRA

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2209201-3_B_c-2209201-3-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2209201-3_B_c-2209201-3-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2209201-3_B_c-2209201-3-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English