


SAUTER CS 50-3P1

KERN

4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement



Category

Brand	Sauter
Product category	Measuring cell
Product group	Load/force measuring cell
Product family	CS P1

Measuring System

Weighing capacity [Max]	50 kg
Measuring range force [Max] (N)	500 N
Load cell - characteristic value - nominal	2 mV/V
Load cell OIML class	C3
Load cell connection	4-wire
Power supply + Colour	red
Power supply - Colour	black
Signal + Colour	green
Signal - Colour	white
Load cell - Resolution (verifiable)	3000 e
Load cell - Dead load [Min] (%)	0%
Measuring applications	force mass
Directions of force	tension compression
Load cell - Y-value	10000
Load cell - Input resistance - nominal	350 Ω
Load cell - Output resistance - nominal	351 Ω
Load cell - Recommended excitation voltage [Min]	5 V
Load cell - Recommended excitation voltage [Max]	12 V

Load cell - Isolation resistance - [Min]	500 M Ω
Load cell - Combined error	0,02%
Safe overload	150%
Ultimate overload	300%

Functions

IP protection - complete device	IP67
---------------------------------	------

Construction

Material	steel, nickel-plated
Design	"S" shaped cell
Dimension (W×D×H)	50,8×76,2×14,5 mm
Cable length	3 m
Mounting - force application	Threaded hole M8
Mounting - force dissipation	Threaded hole M8

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration (compressive force)	963-261V
Article number for DAkkS calibration (tensile force)	963-161V
Article number for DAkkS calibration (tensile force/ compressive force)	963-361V

Product information

GTIN/EAN number	4045761221567
Trade number	90249000
REACH classification	no prohibited substances

Packing & Shipping

Shipping method	Parcel service
Delivery time	1 d
Dimensions packaging (W×D×H)	185×155×60 mm
Net weight approx.	0,60 kg
Gross weight approx.	0,70 kg
Shipping volume weight	0,3 kg

SAUTER CS 50-3P1

KERN

4-wire "S" measuring cell made of nickel-plated steel for force and mass measurement

Pictograms

STANDARD



OPTION

