



Brand of NTN corporation

## Technical data

### UKT217H

Bearing units




Grey cast housing, radial insert ball bearing with adapter sleeve, seal with slinger

### KIT CONTENT

UK217G2H, T217

### VISUAL (S)



### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>A - Housing width</b>	73 mm
<b>A1 - Width of location slot</b>	30 mm
<b>A2</b>	54 mm
<b>B1 - Overall width Inner Ring</b>	82 mm
<b>d - Shaft diameter</b>	75 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
 S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
 SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>d1 - Outer dia of eccent. Lock. collar / nut of adapter sleeve</b>	110 mm
<b>G - Grease fitting</b>	M10x1
<b>H - Housing length, width or diameter</b>	198 mm
<b>H1 - Distance between location slots</b>	173 mm
<b>H2 - Housing height / width</b>	124 mm
<b>L - Housing length</b>	260 mm
<b>L1 - Distance attachment end face to bearing centerline</b>	162 mm
<b>L2 - Thickness of attachment end</b>	29 mm
<b>L3 - Length of guidance slot/face</b>	157 mm
<b>N - Mounting hole dimension</b>	48 mm
<b>N1 - Length of attachment slot</b>	38 mm
<b>N2 - Height of attachment slot</b>	73 mm
<b>s1 - Distance nut to middle of bearing raceway</b>	40 mm

### PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	83200000 mN
<b>C0 - Static load rating</b>	63800000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

### OTHER FEATURES

<b>Mass</b>	11,23 kg
<b>Adapter sleeve designation</b>	H2317

