

# Eaton 019455

Catalog Number: 019455

Eaton xEffect K-Type Terminal Enclosures Switch- & Controlgear Enclosure. Connection terminal, 630A, 1p, round/round

General specifications



Product Name	Catalog Number
Eaton xEffect K-Type Terminal Enclosures Switch- & Controlgear Enclosure	019455
	EAN
	4015080194552
Product Length/Depth	Product Height
125 mm	140 mm
Product Width	Product Weight
240 mm	1.967 kg
Compliances	
RoHS conform	

## Product specifications

### Used with

Accessory panel building  
General switchboard accessory

### Special features

Conversion kits for strip terminal in cable connection available separately  
Terminal covers available separately  
Including labels for terminal marking U, V, W - X, Y, Z - L1, L2, L3 - T1, T2, T3 - PE, N, PEN, protective earth (ground) symbol  
Relationship of rated operational current -terminal capacity to IEC/EN 60439, VDE 0660 Part 500 or EN 50021  
Outer terminal for round or sectoral conductor, other side for Cu strip

### Type

Accessory panel building  
General switchboard accessory

### Features

Contact safe

### Accessory/spare part type

Terminals, 160 – 1000 A  
Terminations

### Connection type

Clamp  
Screwing

### Number of poles

Single-pole

### Rated operation current (Ie)

630 A

## Resources

### Catalogs

[eaton-panel-building-accessories-catalog-ca008008en-en-us.pdf](#)

### Declarations of conformity

[eaton-xeffect-k-type-terminals-declaration-of-conformity-en-us.pdf](#)

DA-DC-03\_K95\_K150\_K240\_K2x240\_K3x185

### Drawings

[eaton-control-panels-xeffect-k-type-terminal-3d-drawing.eps](#)

### Installation instructions

IL015110ZU

IL0609

### mCAD model

[eaton-K2X240\\_1\\_BR-3d-model.stp](#)

[eaton-K2X240\\_1\\_BR-drawing.dwg](#)

### System overview

[eaton-control-panels-terminals-xeffect-k-type-terminal-explosion-drawing-002.eps](#)

Mounting method

Screw

Suitable for

Useful for stranded conductors

Nominal current

630 A

Number of connections (Less Than 6 mm squared)

0

Number of connections (Less Than AWG 6)

0

Number of connections (Greater Than 25 mm squared)

2

Number of connections (Greater Than 250 kcmil)

0

Number of connections (10 mm squared)

0

Number of connections (16 mm squared)

0

Number of connections (25 mm squared)

0

Number of connections (250 kcmil)

0

Number of connections (AWG 2)

0

Number of connections (AWG 4)

0

Number of connections (AWG 4/0)

0

Number of connections (AWG 6)

0

Number of connections (total)

2

Rated insulation voltage (Ui)

1000 VAC

Number of outputs

2

Terminal capacity (aluminum cable)

150 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x)

95 mm<sup>2</sup> - 185 mm<sup>2</sup> (2x)

Terminal capacity (conductor)

18 mm x 4 mm

Terminal capacity (copper/aluminum cable)

50 mm<sup>2</sup> - 240 mm<sup>2</sup> (2x)

150 mm<sup>2</sup> - 300 mm<sup>2</sup> (1x)

Conductor cross section, input - max

240 mm<sup>2</sup>

Conductor cross section, output - min

70 mm<sup>2</sup>

Conductor cross section, input - min

70 mm<sup>2</sup>

Conductor cross section, input AWG - min

0 mm<sup>2</sup>

Conductor cross section, input AWG - max

500 mm<sup>2</sup>

Conductor cross section, output - max

240 mm<sup>2</sup>

Conductor cross section, output AWG - max

500 mm<sup>2</sup>

Conductor cross section, output AWG - min

2 mm<sup>2</sup>

Number of inputs

2