


CATALOG

Wiring ducts, floor boxes and trunking

Easily allows for organization,
pulling and separation of cables



ABB's broad offering of wire & cable management solutions is designed to deliver the most effective, reliable and long lasting support for your cabling needs for various applications. When strength, reliability and performance are required, knowledgeable professionals turn to ABB for wire & cable management solutions.

Table of contents

004 –015	Introduction
016 –022	Applications
023 –031	Floor boxes
032 –038	Mini-trunking
039 –046	Feeder and cable trunking
047 –055	Wiring ducts
056 –145	Industrial cable tray
146 –155	Support systems for industrial trunking
156 –179	Technical details and assembly instructions
180 –222	Overall dimensions
223 –238	Appendix - Product ID index

Introduction

Trunking systems for residential, commercial and industrial installations


ABB's plastic and metal trunking systems include several different product types designed to provide more and more specific installation solutions.

ABB's offer for distribution applications includes devices and equipment for managing electricity end-users and optimizing safety and comfort at home, in offices, shops, etc. Now ABB's product range is even more comprehensive and allows to design "state-of-the-art" technology solutions. In this respect, wiring and trunking products are fundamental instruments to ensure high safety standards and meet certain exterior design requirements for installations. This category includes different product families with different technical details, construction materials, and intended use.

Self-adhesive mini-trunking is available in two versions: Without cover, to connect single press-cables for antenna, phone, and electric circuits; With hinged cover, to facilitate cable routing during installation.

Equipped mini-trunking, available both with standard cover and with adhering cover (removable with the help of a tool), this product can be used as both cable retainer and equipment retainer (switch/socket boxes, cell phone towers, etc.) and can be wall- or ceiling-mounted.

Cable and equipment retainer made of thermoplastic material. Several different models available for a wide range of applications. You can choose the type of trunking that best fits your application. Wide range of accessories available. All the trunking in this product line can be wall- or ceiling-mounted using anchors. Cable and equipment retainer trunking versions available, which can be equipped with separators to isolate the various circuits in telephone, computer, and emergency installations, etc.



Wiring ducts are made of HALOGEN-FREE thermoplastic material. They allow fast and simple wiring and are extremely space-efficient.

Metal trunking and trays for industrial use include trunking made of Galvanized metal and hot dip metal Galvanized after fabrication according to CEI 7.6 and BS 729 and cable ladders for maritime applications. This product line includes all necessary accessories for the most complex in-plant applications, in addition to a comprehensive and versatile solutions for trunking suspension.

Steel wire cable trays, for industrial use are an innovative and reliable solution for power distribution. They are particularly fit for industrial, maritime, and commercial applications requiring a fast and flexible installation of trunking systems. The trays are made of robust but light and easy-to-handle steel wire. They can be quickly and safely cut, bent, curved and assembled into different configurations even after installation.

ABB's comprehensive experience in designing and manufacturing trunking systems for plastic and metal cables and ducts allows us to offer a full product line able to meet any specific needs of designers and installers. High production and quality control standards ensure full compliance to even the most stringent functional and visual appearance requirements. ABB's trunking systems can be used for residential and commercial applications, such as the renovation and extension of existing buildings.



Introduction

Wiring ducts: a comprehensive offer, an efficient the job

The totally new range of ABB wiring ducts also includes products for specific applications.



The top profile of the ribs of all the wiring ducts has been redesigned to make the cover easier to open and close and to make sure that it snaps on even more safely thanks to its new rounded shape that makes wiring operations easier. If you need more room for cables, six new 100-mm high ducts are now available on 25, 40, 60, 80, 100 and 150-mm bases, in addition to the traditional ones with heights from between 17 and 80 mm.

The new wiring ducts with standard easurements of 50 x 50 mm and 100 x 60 mm with circular lateral knockouts, on the other hand, have been designed for the branch connection of rigid and corrugated conduits in specific applications, such as in the lift sector.

The best solution for connecting panels and doors with compass opening mechanisms, and in general, for all applications where cables are subject to bending and twisting, is the new flexible duct in thermoplastic material available in

seven sizes, that can be bent or twisted without breaking. Made in thermoplastic, ABB SACE wiring ducts are used in electrical consumer units, in applications with a rated voltage of up to 1000 V in alternating current and 1500 V in direct current.

In all installation contexts, they stand out for their high installation speed as they can be snapped onto the Fix-O-rapid – the accessory specially designed for fastening onto DIN rails and mounting plates.



Introduction

Advantages in daily jobs

ABB's cable trunking systems combine strength and versatility, thus ensuring perfect tightness and streamlining wiring operations.

The different sizes and resistance of the ribs in ABB wiring ducts ensure repeated splaying during wiring while still making it possible to eliminate the rib, breaking it cleanly and neatly using the special knockout. The knockouts on the base of the walls also make it possible to cut the edge itself when creating branch connections. Controlled splaying of the sides of the wiring duct also ensures that the cover is sealed perfectly even in vertical sections and in high temperatures. In particular in the 80 and 100-mm high versions, special cable holder mouldings located halfway along the straight section of the ribs further reinforce the structure. The out of phase, slightly inward-angled design of the ribs, in the flexible wiring ducts, makes it easy to insert and extract cables, while the fact that there is no cover makes it possible to monitor their position constantly. These wiring ducts can be fastened with screws and rivets or with pre-mounted bi-adhesive tape that sticks strongly to steel.



Introduction

Halogen free thermoplastic trunking for maximum safety

ABB has produced a new version of its trunking to satisfy higher safety standards, including in the range its new wiring ducts in halogen free thermoplastic in compliance with VDE 0472 Part 815 Standard.


ABB has always attached maximum importance to safety and we aim at enhancing our offer to include more and more solutions that help construct protected plants and environments. To be able to meet even the most stringent safety standards, ABB trunking product line includes a number of products particularly fit for the wiring needs in dangerous areas, such as areas at risk of fire. We are referring to halogen-free thermoplastic wiring ducts, which can be considered as the optimum solution for all those environments where safety is an absolute "must".

These products are made of HALOGEN-FREE thermoplastic material compliant with VDE 0472, Part 815. The material is insulating, anti-shock and self-extinguishing (according to UL 94 V0). It can also resist to extreme temperatures and flame up to 850 °C (glow wire test) according to IEC 695-2-1.

Available in Color Grey RAL 7035 with 8/2 mm and 4/6 mm guides. The halogen free thermoplastic wiring ducts have the same strength and ease of use of the others products in this line, but offer extended advantages in terms of structural features.

For example, their material is ideal in case of fire: during the first four minutes from a fire outbreak it is dramatically important that the opacity of fumes is as low as possible to allow the involved persons to leave the hazardous areas. This HALOGEN-FREE material, in addition to preventing fire propagations, releases almost fully non-toxic gases and low-opacity fumes, thus facilitating the evacuation.

HALOGEN-FREE thermoplastic cable ducts are ideal for use in a wide range of environments and conditions. For instance, in malls, movie theaters, theaters, schools, congress centers, areas with special safety requirements (such as underground zones, subway stations, bank vaults), various types of industrial plants (petrochemical, off-shore platforms, power plants) and, more generally, in applications involving switchboards.



Introduction

Metal cable trunking

The metal cable trunking manufactured by ABB solve a variety of commercial and industrial wiring needs regardless of the environment.

Trays, ladders and wire trays are all available to meet any kind of cable management applications.

Sendzimir or **electro-galvanized, hot dip galvanized** and **stainless steel** options are there to protect and carry the cables in any kind of environment; for example, where there are high concentrations of humidity or salinity, where acids are used or when very thick or large quantities of cables are required (such as in the petrochemical and iron and steel industries, power stations and underground or maritime installations), in food & beverage applications.

The particular profile and the very thick metal sheet used also give excellent mechanical properties. Easy to mount, practical, safe and equipped with snap-on covers, the ABB metal cable trunking can be fastened to the ceiling or to the wall, making it possible, thanks to the wide range of accessories, to satisfy any kind of installation needs.

ABB's metal trays are designed to streamline installers' daily work and they meet all the technical and safety requirements to this purpose.



Introduction

Brief outline

Plastic trunking

Type

Self-adhesive mini-trunking
Length 2 m

Equipped mini-trunking
Length 2 m

IP40 feeder trunking
Length 2 m



1SLC80015F0001



1SLC80016F0001



1SLC80017F0001

Color, Product ID, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
Without cover				With standard cover				(B)	43002	40	40
(B)	41010	7,5	7	(B)	41080	20	10	(E)	03042		
	41015	10	9		41081			(B)	43003	60	
	41020	12	11		41083	30		(E)	03043		
With hinged cover					41084			(B)	43004	80	
(B)	41040	4,5	9	(B)	41110	15	17	(E)	03044		
	41050	12,5		(B)	41091	30		(E)	03045		
	41055	17	17		41092	40		(B)	43006	120	
				(B)	41 117	25	30	(E)	03045		
				With adhering cover				(B)	43013	60	60
				(B)	41101	20	10	(E)	03053		
					41102			(B)	43014	80	
				(B)	41103	30		(E)	03054		
					41104			(B)	43015	100	
				(B)	41106	40		(E)	03055		
				(B)	41111	15	17	(E)	03056		
				(B)	41113	30		(B)	43017	150	
					41114			(E)	03057		
				(B)	41115	40		(B)	43018	200	
					41116	60		(E)	03058		
				(B)		60	30	(B)	43025	100	80
								(E)	03065		
								(E)	03066		
								(B)	43027	150	
								(E)	03067		
								(B)	43028	200	
								(E)	03068		

Color	B) RAL 9016 white	B) RAL 9016 white	(B) RAL 9016 white (E) RAL 7030 grey
Quality mark	–	IMQ	IMQ
Field of application	Residential	Residential	Residential and commercial
Branch connection accessories	Yes	Yes	Yes
Accessories for equipment	–	Yes, external	Yes, external
Reference	Page 33	Page 35	Page 40

IP40 feeder & cable trunking
Length 2 m



1SLC80018F0001

Color	Product ID	Base (mm)	Height (mm)
(B)	43085	100	40
(B)	43086	120	
(B)	43095	100	60
(B)	43097	150	
(B)	43098	200	
(B)	43105	150	80
(B)	43106	200	

B) RAL 9016 white

IMQ

Residential and commercial

Yes

Yes, external

Page 42

Introduction

Brief outline

Plastic trunking

Halogen free thermoplastic wiring ducts Length 2 m



1SLC80023F0001



1SLC80023F0001

Wiring ducts with vertical slots 8/12 Length 2 m



1SLC80024F0001

Color, Product ID, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
8/12 mm slots				4/6 mm slots				(G)	05019	15	17
(G)	1SL9019A00	15	17	(G)	1SL9119A00	15	17		05033	25	30
	1SL9033A00	25	30		1SL9133A00	25	30		05035	40	
	1SL9035A00	40			1SL9135A00	40			05037	60	
	1SL9037A00	60			1SL9137A00	60			05043	25	40
	1SL9043A00	25	40		1SL9143A00	25	40		05045	40	
	1SL9045A00	40			1SL9145A00	40			05047	60	
	1SL9047A00	60			1SL9147A00	60			05049	80	
	1SL9049A00	80			1SL9149A00	80			05051	100	
	1SL9051A00	100			1SL9151A00	100			05053	120	
	1SL9053A00	120			1SL9153A00	120			05063	25	60
	1SL9063A00	25	60		1SL9163A00	25	60		05065	40	
	1SL9065A00	40			1SL9165A00	40			05067	60	
	1SL9067A00	60			1SL9167A00	60			05069	80	
	1SL9069A00	80			1SL9169A00	80			05071	100	
	1SL9071A00	100			1SL9171A00	100			05073	120	
	1SL9073A00	120			1SL9173A00	120			05083	25	80
	1SL9083A00	25	80		1SL9183A00	25	80		05085	40	
	1SL9085A00	40			1SL9185A00	40			05087	60	
	1SL9087A00	60			1SL9187A00	60			05089	80	
	1SL9089A00	80			1SL9189A00	80			05091	100	
	1SL9091A00	100			1SL9191A00	100			05093	120	
	1SL9093A00	120			1SL9193A00	120			05094	25	100
	1SL9095A00	40	100						05095	40	
	1SL9096A00	60	100						05096	60	
	1SL9097A00	80	100						05097	80	
	1SL9098A00	100	100						05098	100	
									05099	150	

Color	(G) RAL 7035 grey	(G) RAL 7035 grey	(G) RAL 7030 grey
Quality mark	-	-	Vari
Field of application	Industrial	Industrial	Industrial
Branch connection accessories	Yes	No	No
Accessories for equipment	No	No	No
Reference	Page 48	Page 49	Page 51

Wiring ducts with vertical slots 4/6 wiring ducts
Length 2 m Length 50 cm

Wiring ducts with circular knockouts
Length 2 m



1SLC80025F0001



1SLC80026F0001



1SLC80027F0001

Color, code, dimensions

Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)	Color	Product ID	Base (mm)	Height (mm)
(G)	05119	15	17	(F)	05400	12,5	12,5	(E)	05330	50	50
	05133	25	30		05402	16	16	(E)	05331	100	60
	05135	40			05405	20	20				
	05137	60			05410	25	25				
	05143	25	40		05415	30	30				
	05145	40			05420	40	40				
	05147	60			05425	50	50				
	05149	80									
	05151	100									
	05153	120									
	05163	25	60								
	05165	40									
	05167	60									
	05169	80									
	05171	100									
	05173	120									
	05183	25	80								
	05185	40									
	05187	60									
	05189	80									
	05191	100									
	05193	120									
	05194	25	100								
	05195	40									
	05196	60									
	05197	80									
	05198	100									
	05199	150									

(G) RAL 7030 grey

(F) RAL 7040 grey

(E) RAL 7030 grey

Vari

Industrial

No

No

Page 51/52

Industrial

No

No

Page 54

Industrial

No

No


Page 55

Introduction

Brief outline

Cable tray, wire basket and metal trunking

Type



Color, Product ID, dimensions

Color	Product ID	Base (mm)	Color	Product ID	Base (mm)	Color	Product ID	Base (mm)	Color	Product ID	Base (mm)	Color	Product ID	Base Height (mm)
(GAC)	1SL9822A00	75	(GAC)	1SL9844A00	75	(GAC)	1SL9868A00	75	-	-	75	IP 20 punched feeders trunking		
(EG)	PF35X75EZ		(EG)	PF50X75EZ		(EG)	PF75X75EZ		-	-		(Z)	06312	100 50
(GAC)	1SL9823A00	100	(GAC)	1SL9845A00	100	(GAC)	1SL9869A00	100	(GAC)	1SL9923A00	100		06313	150
(EG)	PF35X100EZ		(EG)	PF50X100EZ		(EG)	PF75X100EZ		(EG)	PF100X100EZ			06314	200
(GAC)	1SL9824A00	150	(GAC)	1SL9870A00	150	(GAC)	1SL9870A00	150	(GAC)	1SL9924A00	150		06315	300
(EG)	PF35X150EZ		(EG)	PF50X150EZ		(EG)	PF75X150EZ		(EG)	PF100X150EZ			06316	400
(GAC)	1SL9825A00	200	(GAC)	1SL9847A00	200	(GAC)	1SL9871A00	200	(GAC)	1SL9925A00	200		06317	500
(EG)	PF35X200EZ		(EG)	PF50X200EZ		(EG)	PF75X200EZ		(EG)	PF100X200EZ		IP 40 feeders trunking		
(GAC)	1SL9826A00	300	(GAC)	1SL9848A00	300	(GAC)	1SL9872A00	300	(GAC)	1SL9926A00	300	(Z)	06332	100 50
(EG)	PF35X300EZ		(EG)	PF50X300EZ		(EG)	PF75X300EZ		(EG)	PF100X300EZ			06333	150
(X304)	PF35X75X		(GAC)	1SL9849A00	400	(GAC)	1SL9873A00	400	(GAC)	1SL9927A00	400		06334	200
(X304)	PF35X100X		(EG)	PF50X400EZ		(EG)	PF75X400EZ		(EG)	PF100X400EZ			06335	300
(X304)	PF35X150X		(GAC)	1SL9850A00	500	(GAC)	1SL9874A00	500	(GAC)	1SL9928A00	500		06336	400
(X304)	PF35X200X		(EG)	PF50X500EZ		(EG)	PF75X500EZ		(EG)	PF100X500EZ			06337	500
(X304)	PF35X300X		(X304)	PF50X75X		(X304)	PF75X75X		-	-				
			(X304)	PF50X100X		(X304)	PF75X100X		(X304)	PF100X100X				
			(X304)	PF50X150X		(X304)	PF75X150X		(X304)	PF100X150X				
			(X304)	PF50X200X		(X304)	PF75X200X		(X304)	PF100X200X				
			(X304)	PF50X300X		(X304)	PF75X300X		(X304)	PF100X300X				
			(X304)	PF50X400X		(X304)	PF75X400X		(X304)	PF100X400X				
			(X304)	PF50X500X		(X304)	PF75X500X		(X304)	PF100X500X				

Color	(GAC) Hot dip Galvanized after fabrication, (EG) Electrogalvanized, (X304) Stainless steel			(Z) Sendzimir
Quality mark	-	-	-	IMQ
Field of application	Industrial/Commercial	Industrial/Commercial	Industrial/Commercial	Industrial/Commercial
Branch connection accessories	Yes	Yes	Yes	Yes
Reference	Page 57	Page 57	Page 58	Page 63

Type	Cable ladders H 60 - 100 - 130 Length 2 m	Closed base cable trays H 60 - 100 - 130 Length 2 m	Perforated base cable trays H 60 - 100 - 130 Length 2 m
Sendzimir trunking H 75 Length 1/2/3 m			
	1SLC80033F0001	1SLC80302F0001	1SLC80303F0001

Color, Product ID, dimensions

Color	Product ID Length 1 m	Product ID Length 2 m	Product ID Length 3 m	Base Height (mm)	Base Height (mm)	Color	Product ID (mm)	Base Height (mm)	Color	Product ID (mm)	Base Height (mm)	Color	Product ID (mm)	Base Height (mm)			
IP 20 punched feeders trunking						(GAC)	09400	100	60	GAC)	06800	100	60	(GAC)	06824	100	60
(Z)		07171	07181	75	75		09401	200		06801	200		06825	200			
		07172	07182	100			09402	300		06802	300		06826	300			
		07173	07183	150			09403	400		06803	400		06827	400			
		07174	07184	200			09404	500		06804	500		06828	500			
		07175	07185	300			09405	600		06805	600		06829	600			
		07176	07186	400		(GAC)	09410	100	100	GAC)	06808	100	100	(GAC)	06830	100	100
		07177	07187	500			09411	200		06809	200		06831	200			
With hinged cover							09412	300		06810	300		06832	300			
(Z)	07111	07121	07131	75	75		09413	400		06811	400		06833	400			
(RAL 7035)	1SL7141A00	1SL7151A00	1SL7161A00				09414	500		06812	500		06834	500			
(BLU)	08401	08411	08421				09415	600		06813	600		06835	600			
(Z)	07112	07122	07132	100	75	(GAC)	09420	100	130	GAC)	06816	100	130	(GAC)	06838	100	130
(H)	1SL7142A00	1SL7152A00	1SL7162A00				09421	200		06817	200		06839	200			
(BLU)	08402	08412	08422				09422	300		06818	300		06840	300			
(Z)	07113	07123	07133	150	75		09423	400		06819	400		06841	400			
(RAL 7035)	1SL7143A00	1SL7153A00	1SL7163A00				09424	500		06820	500		06842	500			
(BLU)	08403	08413	08423				09425	600		06821	600		06843	600			
(Z)	07114	07124	07134	200	75												
(RAL 7035)	1SL7144A00	1SL7154A00	1SL7164A00														
(BLU)	08404	08414	08424														
(Z)	07115	07125	07135	300	75												
(RAL 7035)	1SL7145A00	1SL7155A00	1SL7165A00														
(BLU)	08405	08415	08425														
(Z)		07126	07136	400	75												
(Z)		07127	07137	500	75												

(Z) Sendzimir (RAL 7035) RAL 7035 grey (BLU) Bright blue	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(GAC) Hot dip Galvanized after fabrication	(EG) Electrogalvanization
-	-	-	-	-
Industrial	Industrial	Industrial	Industrial	Industrial
Yes	Yes	Yes	Yes	Yes
Page 72	Page 72	Pages 99/107/115	Pages 125/131/139	Pages 125/131/139

Applications

Value proposition

During the last few years residential, work and public spaces have undergone many transformations which have given them more technological features.

The quick evolution of new electronic and IT devices which are available on the market has highlighted the need for flexible electric networks and plants, which can easily be adapted to changes. In this new context, the systems for sight trunking of the electric plant represent the ideal solution for the various installation requirements of the “residential” sector.

The possibility to offer a complete system that can solve all distribution-related problems is the main strength of ABB plastic trunking systems.

ABB plastic trunking systems



Cost effective

Trunking installation does not require building works and, as a consequence, it costs less than other installation systems for electric plants.



Flexibility

The availability of many elements, which are perfectly compatible, allows you to perform an almost infinite range of possible enlargements and changes with very few activities



Time effective

The possibility for wall installation, also by means of a both sides adhesive tape, makes the installation easier and reduces the installation time.

**Wiring possibility for electric plants and data transfer networks**

In those areas where there are cables (for energy, telematics, IT, etc.), plastic trunking allows you to install extremely versatile plants that integrate into one single element the distribution of the different networks.

**Safety**

Due to the fact that it is used for hiding cables, trunking guarantees the adequate safety level for the electric plant.

Application possibilities

ABB plastic trunking systems can have multiple applications. The idea that the electric plant is a purely technical element to be hidden does not apply any more: when some components, such as circuit-breakers, acquire an own aesthetic value, trunking themselves become elements to be inserted harmonically into the environment, as real furniture pieces.

One possible use is the creation of a distribution system that uses different elements and that exploits, at a compositional level, the differences and the contrasts offered by the different types of plastic trunking.


Another possibility is represented by the use of plastic trunking as single elements harmonised with some furniture elements.

In the following pages there are some practical examples for using ABB trunking systems in different spaces and situations.

Applications

Plastic trunking systems with interface elements

Example of application in cellars



The problem

In cellars the electric plant distribution must take into account the different uses of these spaces and the different needs to be fulfilled. Lights, sockets, switches, sensors, emergency lights and any other type of electric devices must be installed so that they can easily be reached.

The solution proposed by ABB

ABB plastic trunking represent the ideal solution for this application: easy to install and economical, they offer the possibility to create a flexible and appealing distribution system of the electric plant.





ABB components

In the illustrated solution a grey feeder trunking 150x60 (art. 03057) has been used as a horizontal upright; from this trunking, in vertical direction, originate grey feeder trunking 100x60 (art. 03055) which are connected to the upright by means of a tee branch (art. 03528). Switch-socket boxes with interaxis 83.5 mm (art. 03724) and the relevant finishing plates (art. 03755) are installed on the trunking. For the lighting point a grey minitrunking 15x17 (art. 01160) has been used, originating from a junction box (art. 03687).

Applications


Plastic trunking systems with interface elements

Example of application in fairs, galleries and exhibitions



The problem

In those spaces where temporary outfitting is required, it is necessary to have adequate electric distribution that allows easy connection activities of mobile elements to the fixed structures.




The solution proposed by ABB

Using ABB plastic trunking, a very flexible electric distribution system can be created. The wide variety of the available elements allows for different installation solutions.

ABB components


The drawing shows a wall-mounted cable trunking 100x60 (art. 43095) with end caps (art. 43404). Switch-socket boxes (art. 03724) and finishing plates for three devices (art. 43744) are installed on it.



Applications

Plastic trunking systems with interface elements

Example of application for covered balconies and terraces



The problem

In particular environments such as covered balconies and terraces, very often there is the problem of how to install an electric distribution system that completely fulfils all installation needs and at the same time is perfectly integrated in the context.

The solution proposed by ABB

ABB plastic trunking represent a good solution to this problem. As many linear elements are available, it is possible to mask the double insulated cable passage and to create a complete and capillary electric distribution plant.





ABB components

Equipped mini-trunking with adhering cover 30x17 (art. 41113) have been used for the cable passage. Wall elements are connected with ceiling elements by means of the suitable wall/ceiling flat tee branch (art. 41913). Various accessories can be installed to complete the system: flat tee branch (art. 41313); end cap (art. 41613); adjustable flat corner (art. 41213), etc.

Applications

Integrated plastic trunking systems

Example of application for elements to be installed under shelves or under wall-cupboards



The problem

The increasingly widespread use of household appliances and electric appliances in studies, bedrooms and kitchens implies the necessity to have an electric distribution plant that is perfectly harmonised with the environment and that can fulfil the various requirements of these spaces (not only the electric distribution, but also lighting and the possibility to be integrated with other accessories).

The solution proposed by ABB

ABB plastic trunking solve this problem in a functional way: they can be installed under shelves or under wallcupboards and guarantee the necessary flexibility and user friendliness.




ABB components

The drawing shows a wall-mounted cable trunking 100x60 (art. 43095) with end caps (art. 43404). Switch-socket boxes (art. 03724) and finishing plates for three devices (art. 43744) are installed on it.

Applications

Plastic trunking systems in workspace applications

Example of application for desks, benches and reading rooms



The problem

The fitting of work stations in an office as well as in school laboratories or in reading rooms of libraries or museums requires that the project foresees a great number of functional enlargements; in particular it is necessary to provide for the integration of additional electronic devices (ex. new peripheral units/ laptops) without having to change the fittings on the occasion of each change in the organisation of the services that can be accessed from the same work stations.

The solution proposed by ABB

If the desk is equipped with a trunking system, it is possible, when needed, to increase the number and type of connections (electric circuits, telephone devices, data transmission, etc.) just by adding switch-socket boxes, connection boxes and other elements that increase the usage possibilities and, at the same time, respect the choices made during the planning phase.




ABB components

In the illustrated solution a cable trunking 150x60 (art. 43097) with separator (art. 43631) has been installed on the wall touching the desk for dividing current and data circuits. Then two switch-socket boxes (art. 03724) with finishing plate (art. 43745) have been installed, for a total of six installed devices.

Floor boxes for underfloor distribution

a safe and convenient choice

Electrical distribution with underfloor channel systems is a practical and advantageous installation solution, used in particular in the service industry in which premises are frequently reorganized and require a number of services connected alongside the electrical distribution (telephone, data processing, automatic control of installations, and auxiliary services).

In offices, shops, and in general in situations where space is restricted, traditional or raised floors can be suitably equipped to accommodate a versatile electrical distribution network, improving the convenience and appearance of the premises.

ABB offers advanced underfloor distribution systems which satisfy the ever-increasing requirements of protection and connectivity by means of floor boxes, junction and distribution boxes.

The compatibility with the devices of the Chiara series permits complete freedom of personalization, as regards capacity (2 to 7 Chiara modules) and aesthetic finish, to suit the requirements of the installation environment.



Undernet concealed floor boxes

The Undernet concealed floor boxes are designed to contain up to 20 wiring units and devices in installations for both traditional and raised floors: the level of protection between the Undernet boxes and the floor corresponds to IP52.



Concept surface-mounted floor boxes

The ABB Concept floor boxes offer safety and reliability. Each of the two sides of the floor box can accommodate up to 4 modular wiring units, making it possible to mount a differential magnetothermal protection alongside any type of socket.

They can also accommodate sockets for telephone, data processing, and auxiliary services; an internal separator divides the different networks. The design is attractive and the snap-on cover makes fitting easier.

- 01 Floor box with cable lid
- 02 Recessed metal box



— 01





— 02



Undernet floor boxes

Concealed floor boxes



Undernet concealed floor boxes

Product IDs

Undernet floor box for 10/12 and 16/20 devices

	Product ID	Order code	Description	Dimensions WxHxD (mm)/Cut-out	Pack/Packaging No. of pieces
 1SLC006120F0001	10/12 devices				
	10902	M109020000	5 mm cable lid	300x100x235/275x211	1
	10903	M109030000	Stainless steel lid	300x100x235/275x211	1
	Each floor box can be fitted with 2 additional supports available as accessories (not supplied with the product) to accommodate up to 12 devices.				
	16/20 devices				
	10900	M109000000	5 m cable lid	300x100x310/275x287	1
	10901	M109010000	Stainless steel lid	300x100x310/275x287	1


Each floor box can be fitted with 4 supports available as accessories (not supplied with the product) to accommodate up to 20 devices.

Universal supports and supports for ABB devices

	Product ID	Order code	Description	Number of devices	Pack/Packaging No. of pieces
 1SLC006121F0001	Floor box for 10/12 devices				
	10918	M109180000	Universal (center distance 83.5 mm)	3	6/24
	10919	M109190000	Universal (center distance 108 mm)	4	6/24
	10920	M109200000	Universal (center distance 132 mm)	5	6/24
	10922	M109220000	Vimar Plana wiring accessories	6	6/24
 1SLC006122F0001	Floor box for 16/20 devices				
	10910	M109100000	Universal (center distance 83.5 mm)	3	6/24
	10923	M109230000	Vimar Plana wiring accessories	5	6/24
The universal supports must be provided with a frame and finishing plate suited to the type of device to be installed.					
 1SLC006122F0001	Floor box for 10/12 ABB devices				
	2CSK1626CH	2CSK1626CH	Chiara 6 wiring unit support for Undernet floor box 10 902-10 903		1/12
 1SLC006122F0001	Floor box for 16/20 ABB devices				
	2CSK1625CH	2CSK1625CH	Chiara 5 wiring unit support for Undernet floor box 10 900-10 901		1/12

The supports for the Chiara devices are supplied with the finishing plates.
To use Mylos devices order the universal supports.

Metal recessed boxes for traditional floors

	Product ID	Order code	Description	Dimensions WxHxD (mm)	Pack/Packaging No. of pieces
 1SLC006192F0001	Floor box for 10 devices				
	10930	M109300000	Recessed box for 10/12 devices	305x105x230	1
	Floor box for 16 devices				
	10931	M109310000	Recessed box for 16/20 devices	310x105x305	1

For installation of the Undernet floor boxes in traditional floors.

Concept floor boxes

Surface-mounted floor boxes



Concept floor boxes

Product IDs



Concept surface-mounted floor boxes

Product IDs

Concept floor box

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
10501	M105010000	155x120x155	Graphite	1/15



For frames and plates with 4 wiring units of all brands with center distance of 108 mm.
Both floor boxes are supplied with a compartment cover.

1SLC006133F0001

For frames and plates with 4 wiring units of all brands with center distance of 108 mm. Both floor boxes are supplied with a compartment cover.

Compartment cover

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
10520	M105200000	155x120x155	Graphite	20/80



1SLC006134F0001

Adaptor for fitting 3 wiring units (center distance 83.5 mm)

Product ID	Order code	Dimensions WxHxD (mm)	Color	Pack/Packaging No. of pieces
10522	M105220000	144x80x10	Graphite	20/80



1SLC006135F0001

Ring nut

Product ID	Order code	Dimensions WxHxD (mm)	Pack/Packaging No. of pieces
10530	M105300000	ø 2" GAS x H 30 mm	20/80
10559	M105590000	ø 2" GAS x H 50 mm	10/40



1SLC006130F0001



1SLC006131F0001


For fixing supports on cable glands of the Scattoplast or equivalent systems.
Overall dimensions 180-185.

Concept surface-mounted floor boxes

Technical details

Concept surface-mounted floor boxes – Technical details

Installation conditions



Raised floor, supply with free cables or flexible conduit/sheath

- No support required: the floor box is fixed to the floor by means of screws or dowels
- It is possible to use supports code 10526, 10527, 10528, or 10529

1SLC006200F0001

Supports

for the installation of the Concept floor box on cable glands of the Scattoplast or equivalent systems, using ring nut code 10 530 or 10559.

	Product ID	Order code	Color	Pack/Packaging No. of pieces
	10526*	M105260000	graphite	6/24
1SLC006137F0001				
	10528**	M105280000	graphite	6/24
1SLC006138F0001				

* With lateral hole for installing two floor boxes side by side (minimum interaxis of the cable glands = 100 mm).

** With central hole (if several floor boxes are installed side by side, the interaxis between the cable glands must be 155 mm).



Mini-trunking

Self-adhesive mini-trunking

Technical details

- Available in two versions:
 - without cover, suitable for snap-on application of single cables (aerial, telephone and electric circuits)
 - with a hinged cover that makes it easier to position the cables during installation
- Color: **RAL 9016 white**
- Plastic, insulating, shock-proof, self extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 960°C, 1760°F (glow wire test) in compliance with IEC 695-2-1 Standard1
- Dimensional stability from -20 to +60°C, -4 to 140°F
- Resistant to acids, oils, and greases
- Standard 2-metre long straight sections
- Easy-to-position self-adhesive base
- Acrylic-base adhesive, resistant to the light and to ageing residential application



Mini-trunking

Self-adhesive mini-trunking

Mini-trunking without cover

	Product ID	Order code	Dimensions WxH (mm)	For cables Ø (mm)	Weight kg/m	Unit/pack - pcs
	41010	M410100000	7,5x7	4-5,5	0,03	176
	41015	M410150000	10x9	6-8	0,04	140
	41020	M410200000	12x11	8-10	0,04	104

1SLC80036F0001

Mini-trunking with hinged cover

	Product ID	Order code	Dimensions WxH (mm)	For cables Ø (mm)	Weight kg/m	Unit/pack - pcs
	41040	M410400000	9x4,5		0,03	224
	41045	M410450000	12,5x7		0,04	100
	41050	M410500000	12,5x12,5		0,08	60
	41055	M410550000	17x17		0,09	32

1SLC80037F0001

Mini-trunking

Equipped mini-trunking

Specifications

- Color: **RAL 9016 white**
- Straight elements made of plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 960°C (glow wire test) in compliance with IEC 60695-2-11 Standard
- Resistant to acids, oils, and greases
- Wall and ceiling mounting, fastening with dowels
- Suitable as feeder and cable trunking (external)
- 2 types of covers: standard and adhering
- **Mounted cover** (except in H 30)
- Accessories common to both types of covers
- Standard 2-metre straight lengths complete with cover
- Ready-made holes on the base for fastening to the wall
- Chiara and other Italian standard wiring accessories can be installed
- Residential application
- Resistance to impacts: 5 joules
- Minimum storage and transport temperature: -15 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Flame-retarding trunking system
- Trunking system without electrical continuity
- Trunking system with electrical insulating properties
- Degree of protection of the case in compliance with EN 60529: IP40 Standard
- Cover can be opened without having to use a special tool
- Trunking system can be mounted protruding from the wall or the ceiling
- Installation system
- Nominal voltage 500V



IMQ mark in compliance
with EN 50085-1 + EN 50085-2-1 Standard



Mini-trunking

Equipped mini-trunking

Mini-trunking with standard cover



	Product ID	Order code	Dimensions WxH (mm)	Compartments	Color	Unit/pack - pcs
1SLC80042F0001	41080	M410800000	20x10 [IMQ]	1	White	96
	41081	M410810000	20x10 [IMQ]	2	White	96
	41083	M410830000	30x10 [IMQ]	1	White	64
	41084	M410840000	30x10 [IMQ]	2	White	64
	41110	M411100000	15x17 [IMQ]	1	White	92
	41091	M410910000	30x17 [IMQ]	1	White	72
	41092	M410920000	40x17 [IMQ]	2	White	48
	41093	M410930000	60x17 [IMQ]	3	White	36
	41117	M411170000	25x30 [IMQ]	1	White	60
	41119	M411190000	40x30 [IMQ]	1	White	40

Mini-trunking with adhering cover*



	Product ID	Order code	Dimensions WxH (mm)	Compartments	Color	Unit/pack - pcs
1SLC80044F0001	41101	M411010000	20x10 [IMQ]	1	White	96
	41102	M411020000	20x10 [IMQ]	2	White	96
	41103	M411030000	30x10 [IMQ]	1	White	64
	41104	M411040000	30x10 [IMQ]	2	White	64
	41106	M411060000	40x10 [IMQ]	2	White	48
	41111	M411110000	15x17 [IMQ]	1	White	92
	41113	M411130000	30x17 [IMQ]	1	White	72
	41114	M411140000	30x17 [IMQ]	2	White	72
	41115	M411150000	40x17 [IMQ]	2	White	48
	41116	M411160000	60x17 [IMQ]	3	White	36
	41120	M411200000	60x30 [IMQ]	3	White	34

* Special tool required for removing covers.

Adjustable flat corner



	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
1SLC80044F0001	41202	M412020000	20x10 [IMQ]	White	40
	41204	M412040000	30x10 [IMQ]	White	40
	41206	M412060000	40x10 [IMQ]	White	40
	41210	M412100000	15x17 [IMQ]	White	40
	41213	M412130000	30x17 [IMQ]	White	40
	41215	M412150000	40x17 [IMQ]	White	40
	41216	M412160000	60x17 [IMQ]	White	20
	41217	M412170000	25x30 [IMQ]	White	40
	41219	M412190000	40x30 [IMQ]	White	20
	41220	M412200000	60x30 [IMQ]	White	10

Overall dimensions pages 186-190.

Mini-trunking

Equipped mini-trunking

Flat tee branch



1SLC80045F0001

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
	41302	M413020000	20x10 [IMQ]	White	40
	41304	M413040000	30x10 [IMQ]	White	40
	41306	M413060000	40x10 [IMQ]	White	40
	41310	M413100000	15x17 [IMQ]	White	40
	41313	M413130000	30x17 [IMQ]	White	40
	41315	M413150000	40x17 [IMQ]	White	40
	41316	M413160000	60x17 [IMQ]	White	20
	41317	M413170000	25x30 [IMQ]	White	40
	41319	M413190000	40x30 [IMQ]	White	20
	41320	M413200000	60x30 [IMQ]	White	40

Adjustable internal corner



1SLC80046F0001

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
	41402	M414020000	20x10 [IMQ]	White	40
	41404	M414040000	30x10 [IMQ]	White	40
	41406	M414060000	40x10 [IMQ]	White	40
	41410	M414100000	15x17 [IMQ]	White	40
	41413	M414130000	30x17 [IMQ]	White	40
	41415	M414150000	40x17 [IMQ]	White	40
	41416	M414160000	60x17 [IMQ]	White	40
	41417	M414170000	25x30 [IMQ]	White	40
	41419	M414190000	40x30 [IMQ]	White	20
	41420	M414200000	60x30 [IMQ]	White	20

Adjustable external corner



1SLC80047F0001

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
	41502	M415020000	20x10 [IMQ]	White	40
	41504	M415040000	30x10 [IMQ]	White	40
	41506	M415060000	40x10 [IMQ]	White	40
	41510	M415100000	15x17 [IMQ]	White	40
	41513	M415130000	30x17 [IMQ]	White	40
	41515	M415150000	40x17 [IMQ]	White	40
	41516	M415160000	60x17 [IMQ]	White	40
	41517	M415170000	25x30 [IMQ]	White	40
	41519	M415190000	40x30 [IMQ]	White	20
	41520	M415200000	60x30 [IMQ]	White	20

Overall dimensions pages 186-190.

Mini-trunking

Equipped mini-trunking

End cap



1SLC80048F0001

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
	41602	M416020000	20x10 [IMQ]	White	40
	41604	M416040000	30x10 [IMQ]	White	40
	41606	M416060000	40x10 [IMQ]	White	40
	41610	M416100000	15x17 [IMQ]	White	40
	41613	M416130000	30x17 [IMQ]	White	40
	41615	M416150000	40x17 [IMQ]	White	40
	41616	M416160000	60x17 [IMQ]	White	40
	41617	M416170000	25x30 [IMQ]	White	40
	41619	M416190000	40x30 [IMQ]	White	40
	41620	M416200000	60x30 [IMQ]	White	40

Flat joint



1SLC80049F0001

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack - pcs
	41702	M417020000	20x10 [IMQ]	White	40
	41704	M417040000	30x10 [IMQ]	White	40
	41706	M417060000	40x10 [IMQ]	White	40
	41710	M417100000	15x17 [IMQ]	White	40
	41713	M417130000	30x17 [IMQ]	White	40
	41715	M417150000	40x17 [IMQ]	White	40
	41716	M417160000	60x17 [IMQ]	White	40
	41717	M417170000	25x30 [IMQ]	White	40
	41719	M417190000	40x30 [IMQ]	White	40
	41720	M41720000	60x30 [IMQ]	White	40

Overall dimensions pages 186-190.

Mini-trunking

Accessories for equipped mini-trunking

Box for flat branch connections – Complete with circuit separator

	Product ID	Order code	Trunking height WxH (mm)	Color	Unit/pack - pcs
 1SLC80051F0001	41800	M418000000	10 – 17 [IMQ]	White	1/60
	41803	M418030000	10 – 17 – 30 [IMQ]	White	1/40

Frame for flush-mounting box – For branch connection with H 10 mm mini-trunking. Attached onto flush-mounting switch-socket box using 2 screws (supplied).

	Product ID	Order code	Description	Color	Unit/pack - pcs
 1SLC80054F0001	41829	M418290000	Inter-axis 83,5 mm	White	1/10

Switch-socket box – Side trimmings for H 10, 17 and 30 mini-trunking.

For fitting a telephone socket on box with 83.5 interaxis use cover supplied separately (art. 42112).

	Product ID	Order code	Description	Color	Unit/pack - pcs
 1SLC80055F0001	Box for 3 devices depth 43 mm				
	41823	M418230000	Inter. 83,5 mm [IMQ]	White	1/28
	Box for 3 devices depth 53 mm				
	41822	M418220000	Inter. 83,5 mm [IMQ]	White	1/24
Box for 4 devices					
	41830	M418300000	Inter. 108 mm [IMQ]	White	1/20

Cover- interaxis 83.5 mm – Attached onto switch-socket box with 2 screws.

	Product ID	Order code	Description	Color	Unit/pack - pcs
 1SLC80056F0001	00059	M000590000	Plain cover [IMQ]	White	20

Feeder and cable trunking

Specifications

- Available in two versions:
 - Feeder trunking
 - Cable trunking
- Colors:
 - **RAL 9016 white**
 - RAL 7030 grey
- Straight elements made of plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0
- Standard and resistant to abnormal heat and fire up to 960°C (glow wire test) in compliance with IEC 60695-2-11 Standard
- Resistant to acids, oils and greases
- Standard 2-metre straight lengths complete with cover
- Wall and ceiling mounting, fastening with dowels
- Ready-made holes on the base for fastening to the wall
- Residential and commercial applications
- Resistance to impacts: 5 joules
- Chiara and other Italian wiring accessories can be installed
- Minimum storage and transport temperature: -15 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Flame-retarding trunking system
- Trunking system without electrical continuity
- Trunking system with electrical insulating properties
- Degree of protection of the case in compliance with EN 60529: IP40 Standard
- Cover can be opened without having to use a special tool
- Trunking system can be mounted protruding from the wall or the ceiling
- Installation system
- Nominal voltage 500V



IMQ mark in compliance
with EN 50085-1 + EN 50085-2-1 Standard



Feeder and cable trunking

Feeder trunking IP40



1SLC80017F0001

Product ID	Order code	Dimensions W (mm)	Color	Pack-m
H 40				
43002	M430020000	40 [IMQ]	White	60
43003	M430030000	60 [IMQ]	White	40
43004	M430040000	80 [IMQ]	White	32
43005	M430050000	100 [IMQ]	White	24
43006	M430060000	120 [IMQ]	White	20
03042	M030420000	40 [IMQ]	Grey	60
03043	M030430000	60 [IMQ]	Grey	40
03044	M030440000	80 [IMQ]	Grey	32
03045	M030450000	100 [IMQ]	Grey	24
03046	M030460000	120 [IMQ]	Grey	20
H 60				
43013	M430130000	60 [IMQ]	White	32
43014	M430140000	80 [IMQ]	White	24
43015	M430150000	100 [IMQ]	White	18
43016	M430160000	120 [IMQ]	White	14
43017	M430170000	150 [IMQ]	White	12
43018	M430180000	200 [IMQ]	White	8
03053	M030530000	60 [IMQ]	Grey	32
03054	M030540000	80 [IMQ]	Grey	24
03055	M030550000	100 [IMQ]	Grey	18
03056	M030560000	120 [IMQ]	Grey	14
03057	M030570000	150 [IMQ]	Grey	12
03058	M030580000	200 [IMQ]	Grey	8
H 80				
43025	M430250000	100 [IMQ]	White	16
43026	M430260000	120 [IMQ]	White	12
43027	M430270000	150 [IMQ]	White	8
43028	M430280000	200 [IMQ]	White	8
03065	M030650000	100 [IMQ]	Grey	16
03066	M030660000	120 [IMQ]	Grey	12
03067	M030670000	150 [IMQ]	Grey	8
03068	M030680000	200 [IMQ]	Grey	8

Overall dimensions pages 189-191.

Feeder and cable trunking

Cable trunking IP40



Product ID	Order code	Dimensions W (mm)	N° of installable separators	Color	Pack-m
H 40					
43085*	M430850000	100 [IMQ]		White	24
43086*	M430860000	120 [IMQ]		White	20
H 60					
43095	M430950000	100 [IMQ]		White	18
43096	M430960000	120 [IMQ]		White	14
43097	M430970000	150 [IMQ]		White	12
43098	M430980000	200 [IMQ]		White	8
H 80					
43105*	M431050000	150 [IMQ]		White	8
43106*	M431060000	200 [IMQ]		White	8

* Each 2-metre bar comes complete with 3 cable retainers.

Flat 90° corner, IP40



Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43152	M431520000	40x40 [IMQ]	White	10/120
43153	M431530000	60x40 [IMQ]	White	10/60
43154	M431540000	80x40 [IMQ]	White	10/30
43155	M431550000	100x40 [IMQ]	White	1/40
43156	M431560000	120x40 [IMQ]	White	1/30
43163	M431630000	60x60 [IMQ]	White	10/40
43164	M431640000	80x60 [IMQ]	White	10/20
43165	M431650000	100x60 [IMQ]	White	1/20
43166	M431660000	120x60 [IMQ]	White	1/20
43167	M431670000	150x60 [IMQ]	White	1/12
43168	M431680000	200x60 [IMQ]	White	1/8
43175	M431750000	100x80 [IMQ]	White	10/20
43176	M431760000	120x80 [IMQ]	White	1/10
43177	M431770000	150x80 [IMQ]	White	1/9
43178	M431780000	200x80 [IMQ]	White	1/6

Overall dimensions pages 189-191.

Feeder and cable trunking

Flat 90° corner, IP40



1SLC80060F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43232	M432320000	40x40 [IMQ]	White	10/60
43233	M432330000	60x40 [IMQ]	White	10/60
43234	M432340000	80x40 [IMQ]	White	10/60
43235	M432350000	100x40 [IMQ]	White	10/30
43236	M432360000	120x40 [IMQ]	White	10/30
43243	M432430000	60x60 [IMQ]	White	10/40
43244	M432440000	80x60 [IMQ]	White	10/30
43245	M432450000	100x60 [IMQ]	White	10/30
43246	M432460000	120x60 [IMQ]	White	10/20
43247	M432470000	150x60 [IMQ]	White	1/8
43248	M432480000	200x60 [IMQ]	White	1/6
43255	M432550000	100x80 [IMQ]	White	10/20
43256	M432560000	120x80 [IMQ]	White	10/20
43257	M432570000	150x80 [IMQ]	White	1/6
43258	M432580000	200x80 [IMQ]	White	1/4

External corner IP40



1SLC80061F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43312	M433120000	40x40 [IMQ]	White	10/60
43313	M433130000	60x40 [IMQ]	White	10/40
43314	M433140000	80x40 [IMQ]	White	10/30
43315	M433150000	100x40 [IMQ]	White	8/16
43316	M433160000	120x40 [IMQ]	White	8/16
43323	M433230000	60x60 [IMQ]	White	10/40
43324	M433240000	80x60 [IMQ]	White	10/30
43325	M433250000	100x60 [IMQ]	White	8/16
43326	M433260000	120x60 [IMQ]	White	8/16
43327	M433270000	150x60 [IMQ]	White	1/6
43328	M433280000	200x60 [IMQ]	White	1/6
43335	M433350000	100x80 [IMQ]	White	8/16
43336	M433360000	120x80 [IMQ]	White	8/16
43337	M433370000	150x80 [IMQ]	White	1/6
43338	M433380000	200x80 [IMQ]	White	1/4

Overall dimensions pages 189-191.

Feeder and cable trunking

Accessories for feeder and cable trunking

End cap IP40



1SLC80062F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43392	M433920000	40x40 [IMQ]	White	20
43393	M433930000	60x40 [IMQ]	White	20
43394	M433940000	80x40 [IMQ]	White	20
43395	M433950000	100x40 [IMQ]	White	20
43396	M433960000	120x40 [IMQ]	White	20
43403	M434030000	60x60 [IMQ]	White	20
43404	M434040000	80x60 [IMQ]	White	20
43405	M434050000	100x60 [IMQ]	White	20
43406	M434060000	120x60 [IMQ]	White	20
43407	M434070000	150x60 [IMQ]	White	20
43408	M434080000	200x60 [IMQ]	White	20
43415	M434150000	100x80 [IMQ]	White	20
43416	M434160000	120x80 [IMQ]	White	20
43417	M434170000	150x80 [IMQ]	White	20
43418	M434180000	200x80 [IMQ]	White	20

Joint cover



1SLC80062F0001

Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
43552	M435520000	40 [IMQ]	White	20
43553	M435530000	60 [IMQ]	White	20
43554	M435540000	80 [IMQ]	White	20
43555	M435550000	100 [IMQ]	White	20
43556	M435560000	120 [IMQ]	White	20
43565	M435650000	150 [IMQ]	White	20
43566	M435660000	200 [IMQ]	White	20

Tee



1SLC80064F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43475	M434750000	40/100 x 40/60 [IMQ]	White	20
43488	M434880000	40/200 x 40/60 [IMQ]	White	10
43498	M434980000	40/200 x 40/60/80 [IMQ]	White	10

Overall dimensions pages 189-191.

Feeder and cable trunking

Accessories for feeder and cable trunking

Junction box*



1SLC80065F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
43681	M436810000	40/100 x 40/60 [IMQ]	White	1/10
43682	M436820000	120/200 x 40/80 [IMQ]	White	1/4

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard.

Switch-socket box interaxis 83.5 mm (3 places)* – For H 60/80



1SLC80066F0001

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
03724	M037240000	Trunking base 80÷200 [IMQ]	Grey	1/20

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard.

Switch-socket box interaxis 108 mm (4 places)* – For H 60/80




037350000

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
03735	M037350000	Trunking base 100÷200	Grey	1/10

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard.

Switch-socket box interaxis 100 mm (6 places)* – For H 60/80



037350000

Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
03736	M037360000	Trunking base 100÷200	Grey	1/10

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard.

Feeder and cable trunking

Accessories for feeder and cable trunking

Equipment support

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03720	M037200000	80÷100 [IMQ]	Grey	10/120

1SLC80070F0001

Equipment support retainer

	Product ID	Order code	Trunking dimensions WxH (mm)	Color	Unit/pack-pcs
	03711	M037110000	100 [IMQ]	Grey	20/120
	03712	M037120000	120 [IMQ]	Grey	20/120
	03713	M037130000	150 [IMQ]	Grey	20/120

1SLC80071F0001

* Switch-socket floor boxes and switch-socket boxes must be installed at a minimum height of 175 mm from the axis at which the socket is inserted at floor level, in compliance with IEC 64-8 standard.

Separator 2000 mm length

	Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
	43630	M436300000	Trunking height 40 [IMQ]	White	metres 100
	43631	M436310000	Trunking height 60 [IMQ]	White	metres 72

1SLC80072F0001

Feeder and cable trunking

Accessories for feeder and cable trunking

Plate for boxes interaxis 83.5 mm



1SLC80074F0001

	Product ID	Order code	Trunking base (mm)	Color	Unit/pack-pcs
	43744	M437440000	80 [IMQ]	White	20/120
	43745	M437450000	100 [IMQ]	White	15/90
	43746	M437460000	120 [IMQ]	White	15/90
	43747	M437470000	150 [IMQ]	White	15/90
	43748	M437480000	200 [IMQ]	White	10/40

Plate for boxes interaxis 108 mm (4 places)



439520000

	Product ID	Order code	Trunking base WxH (mm)	Color	Unit/pack-pcs
	43950	M439500000	100	White	1/10
	43951	M439510000	120	White	1/10
	43952	M439520000	150	White	1/10
	43953	M439530000	200	White	1/10

Plate for boxes interaxis 100 mm (6 places)



439570000

	Product ID	Order code	Trunking base WxH (mm)	Color	Unit/pack-pcs
	43955	M439550000	100	White	1/10
	43956	M439560000	120	White	1/10
	43957	M439570000	150	White	1/10
	43958	M439580000	200	White	1/10

Wiring ducts

Halogen free wiring ducts with vertical slots

Technical details

- Color: **RAL 7035 grey**
- Halogen-free thermoplastic material in compliance with VDE 0472 Part 815 Standard: Br + Cl < 0.2 %, F < 0.1 %
- Smoke toxicity index: 25.78 according to NF X70-100 and NF F16-101 Standards
- Smoke opacity index*: Dm 352.2 (2 mm) VOF4 475.8 (2 mm) in compliance with NF X10-702 Standard (reference NF F16-101)
* In the event of fire, it is extremely important for the smoke opacity level to be as low as possible during the first 4 minutes in order to allow people to move away from the areas of risk
- On the basis of the values obtained during the smoke opacity and toxicity tests, the material falls within class F2 (in compliance with NF F16-101 Standard)
- Insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 850°C (glow wire test) in compliance with IEC 695-2-1 Standard
- Dimensional stability from -40 to +100 °C
- Resistant to acids, oils, and greases
- Absence of burrs, rounded internal edges
- Dimensions and resilience of ribs guarantee repeated splaying during the wiring phase
- Controlled splaying of sides for guaranteeing a perfect seal of the cover in vertical sections and in the case of high temperatures
- Two prearranged trimming lines: one line at the basis of ribs in order to remove them by bending them towards the outside direction and another line at the basis of the wall in order to cut the edge when two connection ducts are used
- Cable holder mouldings halfway along the straight section of the ribs in 80 mm high ducts
- Standard 2-metre length
- **Trunking comply with the EN 50085-2-3 European Standard**
- Fields of application: residential, industrial and commercial
- RoHS Directive compliant
- **EN45545-2-compliant** trunking: 2013 risk class HL3 requirement R22-R23



Halogen free
RoHS compliant

Wiring ducts

Halogen free wiring ducts with vertical slots

Ducts with 8/12 mm slots



	Product ID	Order code	Dimensions WxH (mm)	Unit/pack-m
	1SL9019A00	1SL9019A00	15x17	46
	1SL9033A00	1SL9033A00	25x30	58
	1SL9035A00	1SL9035A00	40x30	38
	1SL9037A00	1SL9037A00	60x30	52
	1SL9043A00	1SL9043A00	25x40	48
	1SL9045A00	1SL9045A00	40x40	30
	1SL9047A00	1SL9047A00	60x40	40
	1SL9049A00	1SL9049A00	80x40	32
	1SL9051A00	1SL9051A00	100x40	24
	1SL9053A00	1SL9053A00	120x40	20
	1SL9063A00	1SL9063A00	25x60	34
	1SL9065A00	1SL9065A00	40x60	22
	1SL9067A00	1SL9067A00	60x60	32
	1SL9069A00	1SL9069A00	80x60	24
	1SL9071A00	1SL9071A00	100x60	20
	1SL9073A00	1SL9073A00	120x60	14
	1SL9083A00	1SL9083A00	25x80	28
	1SL9085A00	1SL9085A00	40x80	36
	1SL9087A00	1SL9087A00	60x80	24
	1SL9089A00	1SL9089A00	80x80	16
	1SL9091A00	1SL9091A00	100x80	16
	1SL9093A00	1SL9093A00	120x80	12
	1SL9095A00	1SL9095A00	40x100	28
	1SL9096A00	1SL9096A00	60x100	20
	1SL9097A00	1SL9097A00	80x100	14
	1SL9098A00	1SL9098A00	100x100	8

Overall dimensions pages 192-194.

Spirals



	Product ID	Order code	Description
	18370	M183700000	Spiral 3x5 Colorless 50 mt pack
	18372	M183720000	Spiral 6x8 Colorless 25 mt pack
	18374	M183740000	Spiral 10x11 Colorless 25 mt pack
	18376	M183760000	Spiral 12x13 Colorless 25 mt pack
	18380	M183800000	Spiral 3x5 self extinguish 50 mt pack
	18382	M183820000	Spiral 6x8 self extinguish 25 mt pack
	18384	M183840000	Spiral 10x11 self extinguish 25 mt pack
	18386	M183860000	Spiral 12x13 self extinguish 25 mt pack

Wiring ducts

Halogen free wiring ducts with vertical slots

Ducts with 4/6 mm slots



	Product ID	Order code	Dimensions WxH (mm)	Unit/pack-m
	1SL9119A00	1SL9119A00	15x17	46
	1SL9133A00	1SL9133A00	25x30	58
	1SL9135A00	1SL9135A00	40x30	38
	1SL9137A00	1SL9137A00	60x30	52
	1SL9143A00	1SL9143A00	25x40	48
	1SL9145A00	1SL9145A00	40x40	30
	1SL9147A00	1SL9147A00	60x40	40
	1SL9149A00	1SL9149A00	80x40	32
	1SL9151A00	1SL9151A00	100x40	24
	1SL9153A00	1SL9153A00	120x40	20
	1SL9163A00	1SL9163A00	25x60	34
	1SL9165A00	1SL9165A00	40x60	22
	1SL9167A00	1SL9167A00	60x60	32
	1SL9169A00	1SL9169A00	80x60	24
	1SL9171A00	1SL9171A00	100x60	20
	1SL9173A00	1SL9173A00	120x60	14
	1SL9183A00	1SL9183A00	25x80	28
	1SL9185A00	1SL9185A00	40x80	36
	1SL9187A00	1SL9187A00	60x80	24
	1SL9189A00	1SL9189A00	80x80	16
	1SL9191A00	1SL9191A00	100x80	16
	1SL9193A00	1SL9193A00	120x80	12

Spare covers



	Product ID	Order code	Description	Unit/pack-m
	1SL5316A00	1SL5316A00	Trunking base 15 mm	2/200
	1SL5317A00	1SL5317A00	Trunking base 25 mm	2/60
	1SL5318A00	1SL5318A00	Trunking base 40 mm	2/40
	1SL5319A00	1SL5319A00	Trunking base 60 mm	2/24
	1SL5320A00	1SL5320A00	Trunking base 80 mm	2/16
	1SL5321A00	1SL5321A00	Trunking base 100 mm	2/48
	1SL5322A00	1SL5322A00	Trunking base 120 mm	2/36

Overall dimensions pages 192-194.

Wiring ducts

Thermoplastic wiring ducts with vertical slots

Technical details

- Color: **RAL 7030 grey**
- Plastic, insulating, shock-proof, self extinguishing material in compliance with UL 94 V0 Standard and resistant to abnormal heat and fire up to 960 °C (glow wire test) in compliance with IEC 695-2-1 Standard
- Minimum storage and transport temperature: -5 °C
- Minimum installation and usage temperature: -15 °C
- Maximum usage temperature: 60 °C
- Resistant to acids, oils, and greases
- No burr, rounded-off inner edges
- New rib profile makes it easy to open and close the cover and guarantees that it clips on more safely
- Designed to snap onto the Fix-O-rapid special accessory, suitable to be fastened both to DIN rail and base plate
- The ribs are cut using a special pressing process (rounding of the edges) producing wiring ducts completely free of burr and rough edges
- The dimensions and resilience of the ribs ensure repeated splaying during cabling
- Installation system
- Controlled splaying of sides to ensure a perfect seal of the cover in the vertical sections and at high temperatures
- Double trimming line, one at the base of the ribs so that they can be removed by bending them outwards and one at the base of the lateral sides so that the edge can be cut when two wiring ducts are branched
- Cable holder mouldings half-way up the straight section of the ribs in 80 and 100-mm high wiring ducts
- Cover can be opened without having to use a special tool
- Can be mounted on horizontal or vertical surfaces even when the cover is on the bottom
- Standard 2-metre length
- Industrial application
- RoHS-Directive compliant
- Trunking compliant with the new European Standard EN 50085-2-3



IMQ mark in compliance with EN 50085-2-3 Standard



RINA Approved



Approved by Canadian Standards Association



Lead free
RoHS compliant



Wiring ducts

Thermoplastic wiring ducts with vertical slots

Wiring duct with 8/12 mm slots



	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
	05019	M050190000	15x17	0,06	46
	05033	M050330000	25x30	0,21	58
	05035	M050350000	40x30	0,27	38
	05037	M050370000	60x30	0,38	52
	05043	M050430000	25x40	0,25	48
	05045	M050450000	40x40	0,31	30
	05047	M050470000	60x40	0,46	40
	05049	M050490000	80x40	0,47	32
	05051	M050510000	100x40	0,55	24
	05053	M050530000	120x40	0,65	20
	05063	M050630000	25x60	0,24	34
	05065	M050650000	40x60	0,34	22
	05067	M050670000	60x60	0,47	32
	05069	M050690000	80x60	0,52	24
	05071	M050710000	100x60	0,59	20
	05073	M050730000	120x60	0,73	14
	05083	M050830000	25x80	0,29	28
	05085	M050850000	40x80	0,38	36
	05087	M050870000	60x80	0,50	24
	05089	M050890000	80x80	0,59	16
	05091	M050910000	100x80	0,68	16
	05093	M050930000	120x80	0,89	12
	05094	M050940000	25x100	0,46	20
	05095	M050950000	40x100	0,53	28
	05096	M050960000	60x100	0,73	20
	05097	M050970000	80x100	0,91	14
	05098	M050980000	100x100	1,06	8
	05099	M050990000	150x100	1,37	8

Wiring duct with 4/6 mm slots



	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
	05119	M051190000	15x17	0,06	46
	05133	M051330000	25x30	0,21	58
	05135	M051350000	40x30	0,27	38
	05137	M051370000	60x30	0,38	52
	05143	M051430000	25x40	0,25	48
	05145	M051450000	40x40	0,31	30
	05147	M051470000	60x40	0,46	40
	05149	M051490000	80x40	0,47	32
	05151	M051510000	100x40	0,55	24
	05153	M051530000	120x40	0,65	20
	05163	M051630000	25x60	0,24	34
	05165	M051650000	40x60	0,34	22
	05167	M051670000	60x60	0,47	32
	05169	M051690000	80x60	0,52	24
	05171	M051710000	100x60	0,59	20
	05173	M051730000	120x60	0,73	14
	05183	M051830000	25x80	0,29	28

Wiring ducts

Thermoplastic wiring ducts with vertical slots

Wiring duct with 4/6 mm slots - continued

	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
 1SLC80150F0001	05185	M051850000	40x80	0,38	36
	05187	M051870000	60x80	0,50	24
	05189	M051890000	80x80	0,59	16
	05191	M051910000	100x80	0,68	16
	05193	M051930000	120x80	0,89	12
	05194	M051940000	25x100	0,46	20
	05195	M051950000	40x100	0,53	28
	05196	M051960000	60x100	0,73	20
	05197	M051970000	80x100	0,91	14
	05198	M051980000	100x100	1,06	8
	05199	M051990000	150x100	1,37	8

Spare covers

	Product ID	Order code	Description	Unit/pack-pcs
 1SLC81045F0001	05300	M053000000	Trunking base 15 mm	2/200
	05302	M053020000	Trunking base 25 mm	2/60
	05304	M053040000	Trunking base 40 mm	2/40
	05306	M053060000	Trunking base 60 mm	2/24
	05308	M053080000	Trunking base 80 mm	2/16
	05310	M053100000	Trunking base 100 mm	2/48
	05312	M053120000	Trunking base 120 mm	2/36
	05314	M053140000	Trunking base 150 mm	2/28

Wiring ducts

Thermoplastic wiring ducts with vertical slots

Duct shears

	Product ID	Order code	Description	Unit/pack-pcs
	05265	M052650000		1

1SLC80156F0001

Rivet fastener

	Product ID	Order code	Description	Unit/pack-pcs
	05266	M052660000	For ø 6mm rivets (Black Color)	1/12
	05268	M052680000	For ø 4mm rivets (Green Color)	1/12

FLCC 9009 verde

Plastic rivet

	Product ID	Order code	Description	Unit/pack-pcs
	05214	M052140000	ø 4 mm	100
	05216	M052160000	ø 6 mm	100

1SLC80158F0001

Plastic rivet

	Product ID	Order code	Description	Unit/pack-pcs
	05224	M052240000	Trunking base 40	100
	05226	M052260000	Trunking base 60	100
	05228	M052280000	Trunking base 80	100
	05230	M052300000	Trunking base 100/120	100

1SLC80159F0001

Plastic label tag

Suitable for wiring ducts with 8/12 mm slots only.

	Product ID	Order code	Description	Unit/pack-pcs
	05240	M052400000		100


1SLC80160F0001

Wiring ducts

Flexible thermoplastic wiring duct

Technical details

- Color: **RAL 7040 grey**
- Plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V2 Standard and resistant to permanent temperature of 80 °C and peaks up to 110 °C in
- Resistant to acids, oils, and greases
- Ribs alternate and angle slightly inwards to make it easier to insert and extract cables
- No covers so that cables can be constantly monitored
- Possibility of fastening using screws and rivets or bi-adhesive tape which sticks strongly to the steel (pre-mounted)
- Suitable for connecting panels and doors with compass opening mechanisms and in general for applications where cabling is subject to bending and twisting
- **Standard 500-mm length**
- Industrial applications



Wiring ducts

Flexible thermoplastic wiring duct

Flexible wiring duct – Slot pitch 7,5/5. Standard length 500 mm.

	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/pcs)	Unit/pack-pcs
 1SLC80024F0001	05400	M054000000	12,5x12,5	0,011	112
	05402	M054020000	16x16	0,014	84
	05405	M054050000	20x20	0,024	112
	05410	M054100000	25x25	0,033	70
	05415	M054150000	30x30	0,044	50
	05420	M054200000	40x40	0,066	50
	05425	M054250000	50x50	0,100	32

Wiring ducts

Thermoplastic wiring duct with circular knockouts

Technical details

- Color: **RAL 7030 grey**
- Plastic, insulating, shock-proof, self-extinguishing material in compliance with UL 94 V0 Standard and resistant to high heat and fire up to 960 °C (glow wire test) in compliance with IEC 695-2-1 Standard
- Dimensional stability from -20 to +60 °C
- Resistant to acids, oils, and greases
- Circular knockouts on sides with alternate diameters of 18 and 23 mm and interaxis of 50 mm
- Ideal solution for branch connection of rigid or corrugated conduits
- Specially designed for specific applications, such as elevators
- Standard 2-metre length
- Industrial applications



Wiring ducts

Thermoplastic wiring duct with circular knockouts

Wiring duct with round holes – Standard 2-metre length.

	Product ID	Order code	Dimensions WxH (mm)	Weight (kg/m)	Unit/pack-m
	05330	M05330	50x50	0,603	36
	05331	M05331	100x60	0,952	18

1SLC80027F0001


Overall dimensions Ppages 192-194.

Industrial cable tray

Steel wire cable tray

Technical details


- Mechanical protection against impacts IK 10 (up to 20 J)
- Classified in "D" class as for the drilling index >30% and in "Z" class as for free base index >90%, in compliance with EN 61537 Standard
- Available in 4 different heights and material finishes:
 - Hot dip galvanization after fabrication
 - Electro-galvanized
 - Stainless steel (AISI 304)
- The universal joint guarantees electrical continuity even in the painted sendzimir finish
- Cable trays can be equipped with couplers, corners, shelves and other products of the ABB metal trunking range
- Applications: industrial, commercial, food & beverage, chemical, oil and marine applications



Industrial cable tray

Steel wire cable tray


Steel wire cable trays H 35 mm



1SLC810009F0001

Product ID	Order code	Description	Finish	Unit/pack-m
1SL9822A00	1SL9822A00	Basket tray W 75 x H 35 x L 3000 mm	GAC	24
1SL9823A00	1SL9823A00	Basket tray W 100 x H 35 x L 3000 mm	GAC	24
1SL9824A00	1SL9824A00	Basket tray W 150 x H 35 x L 3000 mm	GAC	24
1SL9825A00	1SL9825A00	Basket tray W 200 x H 35 x L 3000 mm	GAC	12
1SL9826A00	1SL9826A00	Basket tray W 300 x H 35 x L 3000 mm	GAC	12
PF35X75EZ	7TFP000000R2191	Basket tray W 75 x H 35 x L 3000 mm	EG	24
PF35X100EZ	7TFP000000R2187	Basket tray W 100 x H 35 x L 3000 mm	EG	24
PF35X150EZ	7TFP000000R2188	Basket tray W 150 x H 35 x L 3000 mm	EG	24
PF35X200EZ	7TFP000000R2189	Basket tray W 200 x H 35 x L 3000 mm	EG	12
PF35X300EZ	7TFP000000R2190	Basket tray W 300 x H 35 x L 3000 mm	EG	12
PF35X75X	1SLM001000A0001	Basket tray W 75 x H 35 x L 3000 mm	X304	24
PF35X100X	1SLM001000A0002	Basket tray W 100 x H 35 x L 3000 mm	X304	24
PF35X150X	1SLM001000A0003	Basket tray W 150 x H 35 x L 3000 mm	X304	24
PF35X200X	1SLM001000A0004	Basket tray W 200 x H 35 x L 3000 mm	X304	12
PF35X300X	1SLM001000A0005	Basket tray W 300 x H 35 x L 3000 mm	X304	12

Steel wire cable trays H 50 mm



1SLC810009F0001

Product ID	Order code	Description	Finish	Unit/pack-m
1SL9844A00	1SL9844A00	Basket tray W 75 x H 50 x L 3000 mm	GAC	24
1SL9845A00	1SL9845A00	Basket tray W 100 x H 50 x L 3000 mm	GAC	24
1SL9846A00	1SL9846A00	Basket tray W 150 x H 50 x L 3000 mm	GAC	24
1SL9847A00	1SL9847A00	Basket tray W 200 x H 50 x L 3000 mm	GAC	12
1SL9848A00	1SL9848A00	Basket tray W 300 x H 50 x L 3000 mm	GAC	12
1SL9849A00	1SL9849A00	Basket tray W 400 x H 50 x L 3000 mm	GAC	6
1SL9850A00	1SL9850A00	Basket tray W 500 x H 50 x L 3000 mm	GAC	6
PF50X75EZ	7TFP000000R2198	Basket tray W 75 x H 50 x L 3000 mm	EG	24
PF50X100EZ	7TFP000000R2192	Basket tray W 100 x H 50 x L 3000 mm	EG	24
PF50X150EZ	7TFP000000R2193	Basket tray W 150 x H 50 x L 3000 mm	EG	24
PF50X200EZ	7TFP000000R2194	Basket tray W 200 x H 50 x L 3000 mm	EG	12
PF50X300EZ	7TFP000000R2195	Basket tray W 300 x H 50 x L 3000 mm	EG	12
PF50X400EZ	7TFP000000R2196	Basket tray W 400 x H 50 x L 3000 mm	EG	6
PF50X500EZ	7TFP000000R2197	Basket tray W 500 x H 50 x L 3000 mm	EG	6
PF50X75X	1SLM001000A0006	Basket tray W 75 x H 50 x L 3000 mm	X304	24
PF50X100X	1SLM001000A0007	Basket tray W 100 x H 50 x L 3000 mm	X304	24
PF50X150X	1SLM001000A0008	Basket tray W 150 x H 50 x L 3000 mm	X304	12
PF50X200X	1SLM001000A0009	Basket tray W 200 x H 50 x L 3000 mm	X304	12
PF50X300X	1SLM001000A0010	Basket tray W 300 x H 50 x L 3000 mm	X304	6
PF50X400X	1SLM001000A0011	Basket tray W 400 x H 50 x L 3000 mm	X304	6
PF50X500X	1SLM001000A0012	Basket tray W 500 x H 50 x L 3000 mm	X304	6

GAC = Hot dip galvanized after fabrication.

EG = Electro galvanized.

X304 = Stainless steel.

Overall dimensions pages 195-197.

Industrial cable tray

Steel wire cable tray

Steel wire cable trays H 75 mm



1SLC810009F0001

Product ID	Order code	Description	Finish	Unit/pack-m
1SL9868A00	1SL9868A00	Basket tray W 75 x H 75 x L 3000 mm	GAC	24
1SL9869A00	1SL9869A00	Basket tray W 100 x H 75 x L 3000 mm	GAC	24
1SL9870A00	1SL9870A00	Basket tray W 150 x H 75 x L 3000 mm	GAC	12
1SL9871A00	1SL9871A00	Basket tray W 200 x H 75 x L 3000 mm	GAC	12
1SL9872A00	1SL9872A00	Basket tray W 300 x H 75 x L 3000 mm	GAC	6
1SL9873A00	1SL9873A00	Basket tray W 400 x H 75 x L 3000 mm	GAC	6
1SL9874A00	1SL9874A00	Basket tray W 500 x H 75 x L 3000 mm	GAC	6
PF75X75EZ	7TFP000000R2205	Basket tray W 75 x H 75 x L 3000 mm	EG	24
PF75X100EZ	7TFP000000R2199	Basket tray W 100 x H 75 x L 3000 mm	EG	24
PF75X150EZ	7TFP000000R2961	Basket tray W 150 x H 75 x L 3000 mm	EG	12
PF75X200EZ	7TFP000000R2201	Basket tray W 200 x H 75 x L 3000 mm	EG	12
PF75X300EZ	7TFP000000R2202	Basket tray W 300 x H 75 x L 3000 mm	EG	6
PF75X400EZ	7TFP000000R2203	Basket tray W 400 x H 75 x L 3000 mm	EG	6
PF75X500EZ	7TFP000000R2962	Basket tray W 500 x H 75 x L 3000 mm	EG	6
PF75X75X	1SLM001000A0013	Basket tray W 100 x H100 x L 3000 mm	X304	24
PF75X100X	1SLM001000A0014	Basket tray W 100 x H 75 x L 3000 mm	X304	24
PF75X150X	1SLM001000A0015	Basket tray W 150 x H 75 x L 3000 mm	X304	12
PF75X200X	1SLM001000A0016	Basket tray W 200 x H 75 x L 3000 mm	X304	12
PF75X300X	1SLM001000A0017	Basket tray W 300 x H 75 x L 3000 mm	X304	6
PF75X400X	1SLM001000A0018	Basket tray W 400 x H 75 x L 3000 mm	X304	6
PF75X500X	1SLM001000A0019	Basket tray W 500 x H 75 x L 3000 mm	X304	6

Steel wire cable trays H 100 mm



1SLC810009F0001

Product ID	Order code	Description	Finish	Unit/pack-m
1SL9923A00	1SL9923A00	Basket tray W 100 x H 100 x L 3000 mm	GAC	24
1SL9924A00	1SL9924A00	Basket tray W 150 x H 100 x L 3000 mm	GAC	24
1SL9925A00	1SL9925A00	Basket tray W 200 x H 100 x L 3000 mm	GAC	12
1SL9926A00	1SL9926A00	Basket tray W 300 x H 100 x L 3000 mm	GAC	12
1SL9927A00	1SL9927A00	Basket tray W 400 x H 100 x L 3000 mm	GAC	6
1SL9928A00	1SL9928A00	Basket tray W 500 x H 100 x L 3000 mm	GAC	6
PF100X100EZ	7TFP000000R2182	Basket tray W 100 x H 100 x L 3000 mm	EG	24
PF100X150EZ	7TFP000000R2183	Basket tray W 150 x H 100 x L 3000 mm	EG	24
PF100X200EZ	7TFP000000R2184	Basket tray W 200 x H 100 x L 3000 mm	EG	24
PF100X300EZ	7TFP000000R2185	Basket tray W 300 x H 100 x L 3000 mm	EG	12
PF100X400EZ	7TFP000000R2186	Basket tray W 400 x H 100 x L 3000 mm	EG	12
PF100X500EZ	7TFP000000R2181	Basket tray W 500 x H 100 x L 3000 mm	EG	6
PF100X100X	1SLM001000A0020	Basket tray W 100 x H100 x L 3000 mm	X304	24
PF100X150X	1SLM001000A0021	Basket tray W 150 x H100 x L 3000 mm	X304	12
PF100X200X	1SLM001000A0022	Basket tray W 200 x H100 x L 3000 mm	X304	12
PF100X300X	1SLM001000A0023	Basket tray W 300 x H100 x L 3000 mm	X304	6
PF100X400X	1SLM001000A0024	Basket tray W 400 x H100 x L 3000 mm	X304	6
PF100X500X	1SLM001000A0025	Basket tray W 500 x H100 x L 3000 mm	X304	6

GAC = Hot dip galvanized after fabrication.

EG = Electro galvanized.

X304 = Stainless steel.

Industrial cable tray

Steel wire cable tray

Covers



	Product ID	Order code	Description	Finish	Unit/pack-m
	07241	M07241	Straight element B 75 x L 3000 mm	Z	48
	07242	M07242	Straight element B 100 x L 3000 mm	Z	48
	07243	M07243	Straight element B 150 x L 3000 mm	Z	48
	07244	M07244	Straight element B 200 x L 3000 mm	Z	36
	07245	M07245	Straight element B 300 x L 3000 mm	Z	36
	07246	M07246	Straight element B 400 x L 3000 mm	Z	30
	07247	M07247	Straight element B 500 x L 3000 mm	Z	24
	1SLM001010A0001	1SLM001010A0001	Straight element W 75 x L 1500 mm	X304	24
	1SLM001010A0002	1SLM001010A0002	Straight element W 100 x L 1500 mm	X304	24
	1SLM001010A0003	1SLM001010A0003	Straight element W 150 x L 1500 mm	X304	24
	1SLM001010A0004	1SLM001010A0004	Straight element W 200 x L 1500 mm	X304	18
	1SLM001010A0005	1SLM001010A0005	Straight element W 300 x L 1500 mm	X304	18
	1SLM001010A0006	1SLM001010A0006	Straight element W 400 x L 1500 mm	X304	15
	1SLM001010A0007	1SLM001010A0007	Straight element W 500 x L 1500 mm	X304	12

Straight dividers



	Product ID	Order code	Description	Finish	Unit/pack-m
	1SL9904A00	1SL9904A00	Divider L 2000 mm for cable trays H 35 mm	Z	20
	06652	M06652	Divider L 2000 mm for cable trays H 50 mm	Z	20
	07855	M07855	Divider L 2000 mm for cable trays H 75 mm	Z	20
	M078550002	M078550002	Divider L 2000 mm for cable trays H 100 mm	Z	20
	1SL9876A00	1SL9876A00	Divider L 2000 mm for cable trays H 35 mm	GAC	20
	1SL9877A00	1SL9877A00	Divider L 2000 mm for cable trays H 50 mm	GAC	20
	1SL9878A00	1SL9878A00	Divider L 2000 mm for cable trays H 75 mm	GAC	20
	1SL9878A01	1SL9878A01	Divider L 2000 mm for cable trays H 100 mm	GAC	20
	1SLM001020A0001	1SLM001020A0001	Divider H35 L 1500 mm	X304	15
	1SLM001020A0002	1SLM001020A0002	Divider H50 L 1500 mm	X304	15
	1SLM001020A0003	1SLM001020A0003	Divider H75 L 1500 mm	X304	15
	1SLM001020A0004	1SLM001020A0004	Separatore H100 L 1500 mm	X304	15

Z = Sendzimir.

GAC = Hot dip galvanized after fabrication.




X304 = Stainless steel.

Overall dimensions pages 195-197.

Industrial cable tray

Steel wire cable tray

Joints

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	1SL9879A00	1SL9879A00	Universal joint with screws	EG	10
	1SL9880A00	1SL9880A00	Straight joint	Z	2
1SL9879A00	1SL9881A00	1SL9881A00	Joint for curves with screws	Z	2
	1SL9882A00	1SL9882A00	"T" joint for cable trays W 75 mm	Z	2
1SL9880A00	1SL9883A00	1SL9883A00	Suspension plate	Z	2
	1SL9884A00	1SL9884A00	Connection plate with screws	EG	10
1SL9881A00	1SL9888A00	1SL9888A00	Adapter joint H 50 mm for coupler with sendzimir ducts H 50 mm with screws	Z	2
	1SL9889A00	1SL9889A00	Adapter joint H 75 mm for coupler with sendzimir ducts H 75 mm with screws	Z	2
1SL9882A00	1SLM001020A0005	1SLM001020A0005	Universal joint with screws	X304	10
	1SLM001020A0006	1SLM001020A0006	Straight joint	X304	2
1SLM001020A0007	1SLM001020A0007	1SLM001020A0007	Joint for curves with screws	X304	2
	1SLM001020A0008	1SLM001020A0008	"T" joint for cable trays W 75 & 150mm)	X304	2
1SL9883A00	1SLM001020A0009	1SLM001020A0009	Suspension plate	X304	2
1SL9884A00	1SLM001020A0010	1SLM001020A0010	Connection plate with screws	X304	10
	1SLM001020A0012	1SLM001020A0012	Round head screw M6x16 with nut	X304	100
	1SLM001020A0013	1SLM001020A0013	Round head screw M6x10 with nut	X304	100
1SL9888A00 -1SL9889A00					

Z =Sendzimir.

GAC = Hot dip galvanized after fabrication.

X304 = Stainless steel.

Overall dimensions pages 195-197.

Industrial cable tray

Steel wire cable tray

Accessories for shelves

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	1SL9893A00	1SL9893A00	Fixing element for shelves, with screws	EG	10
	1SLM001020A0011	1SLM001020A0011	Shears	-	1

1SL9893A00

Cross-sections for floor/wall/ceiling fixing

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	1SL9910A00	1SL9910A00	Cross-section L 150 mm for cable trays B 75-100 mm	Z	10
	1SL9911A00	1SL9911A00	Cross-section L 200 mm for cable trayse B 150 mm	Z	10
	1SL9912A00	1SL9912A00	Cross-section L 250 mm for cable trays B 200 mm	Z	10
	1SL9913A00	1SL9913A00	Cross-section L 350 mm for cable trays B 300 mm	Z	10
	1SL9914A00	1SL9914A00	Cross-section L 450 mm for cable trays B 400 mm	Z	10
	1SL9915A00	1SL9915A00	Cross-section L 550 mm for cable trays B 500 mm	Z	10
	1SL9916A00	1SL9916A00	Cross-section L 650 mm	Z	10

FLCM9148d

Accessories

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	1SL9890A00	1SL9890A00	Sliding plate for cable exit	Z	1
	1SL9891A00	1SL9891A00	Support for connection boxes	Z	1
	1SL9892A00	1SL9892A00	Support for corrugated pipes	Z	1
	1SL9902A00	1SL9902A00	Shears	-	1
	1SLM001020A0014	1SLM001020A0014	Sliding plate for cable exit	X304	1
	1SLM001020A0015	1SLM001020A0015	Support for connection boxes	X304	1
	1SLM001020A0016	1SLM001020A0016	Support for corrugated pipes	X304	1

1SLC810018F0001

1SLC810019F0001

1SLC810020F0001

1SLC810024F0001

Z = Sendzimir.
EG = Electro galvanized.
X304 = Stainless steel.

Industrial cable tray

Sendzimir trunking H 50

Technical details

- Degree of protection IP20 (punched) and IP40 (degree of protection refers to trunking with mounted cover)
- Produced in hot dip Galvanized sendzimir steel plate
- UNI EN 10327 Z200
- Standard height 50 mm
- Special method used to punch the trunking totally eliminates burr, guaranteeing maximum safety for the cables and the operator
- All corners and branch connections have a wide curving angle (125 mm)
- Accessories are assembled using a mechanical system that requires no welding
- A mechanical joint system guarantees electrical continuity
- Industrial applications
- Suspension systems: page 160



IMQ mark in compliance
with CEI 23-31+V1 Standard



Industrial cable tray

Sendzimir trunking H 50

Punched cable trunking IP20*

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80198F0001	06312	M06312	100	3000	Galvanized	36
	06313	M06313	150	3000	Galvanized	36
	06314	M06314	200	3000	Galvanized	18
	06315	M06315	300	3000	Galvanized	18
	06315	M06315	400	3000	Galvanized	18
	06317	M06317	500	3000	Galvanized	18

* Degree of protection refers to feeders with mounted cover.

Cable trunking IP40*

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80199F0001	06332	M06332	100	3000	Galvanized	36
	06333	M06333	150	3000	Galvanized	36
	06334	M06334	200	3000	Galvanized	18
	06335	M06335	300	3000	Galvanized	18
	06336	M06336	400	3000	Galvanized	18
	06337	M06337	500	3000	Galvanized	18

* Degree of protection refers to feeders with mounted cover.

Cover for cable trunking IP20 and IP40

	Product ID	Order code	Trunking base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80200F0001	07242	M07242	100	3000	Galvanized	36
	07243	M07243	150	3000	Galvanized	36
	07244	M07244	200	3000	Galvanized	18
	07245	M07245	300	3000	Galvanized	18
	07246	M07246	400	3000	Galvanized	18
	07247	M07247	500	3000	Galvanized	18

90° flat corner

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80201F0001	Base				
	06352	M06352	100	Galvanized	8
	06353	M06353	150	Galvanized	8
	06354	M06354	200	Galvanized	4
	06355	M06355	300	Galvanized	4
	06356	M06356	400	Galvanized	2
	06357	M06357	500	Galvanized	2
	Cover				
	06362	M06362	100	Galvanized	8
	06362	M06362	150	Galvanized	8
	06364	M06364	200	Galvanized	4
	06365	M06365	300	Galvanized	4
	06366	M06366	400	Galvanized	2
06366	M06366	500	Galvanized	2	

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 198-211.

Industrial cable tray

Sendzimir trunking H 50

45° horizontal corner



1SLC80202F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	Base				
	06372	M06372	100	Galvanized	8
	06373	M06373	150	Galvanized	4
	06374	M06374	200	Galvanized	4
	06375	M06375	300	Galvanized	4
	06376	M06376	400	Galvanized	2
	06357	M06357	500	Galvanized	2
	Cover				
	06382	M06382	100	Galvanized	8
	06383	M06383	150	Galvanized	4
	06384	M06384	200	Galvanized	4
	06385	M06385	300	Galvanized	4
	06386	M06386	400	Galvanized	2
	06387	M06387	500	Galvanized	2

Horizontal tee



1SLC80203F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	Base				
	06392	M06392	100	Galvanized	4
	06393	M06393	150	Galvanized	4
	06394	M06394	200	Galvanized	4
	06395	M06395	300	Galvanized	2
	06396	M06396	400	Galvanized	2
	06397	M06397	500	Galvanized	2
	Cover				
	06402	M06402	100	Galvanized	4
	06403	M06403	150	Galvanized	4
	06404	M06404	200	Galvanized	4
	06405	M06405	300	Galvanized	2
	06406	M06406	400	Galvanized	2
	06407	M06407	500	Galvanized	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 198-211.

Industrial cable tray

Sendzimir trunking H 50

Horizontal cross



1SLC80204F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06412	M06412	100	Galvanized	4
06413	M06413	150	Galvanized	4
06414	M06414	200	Galvanized	2
06415	M06415	300	Galvanized	2
06416	M06416	400	Galvanized	2
06417	M06417	500	Galvanized	2
Cover				
06422	M06422	100	Galvanized	4
06423	M06423	150	Galvanized	4
06424	M06424	200	Galvanized	2
06425	M06425	300	Galvanized	2
06426	M06426	400	Galvanized	2
06427	M06427	500	Galvanized	2

90° vertical inside bend



1SLC80205F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06462	M06462	100	Galvanized	6
06463	M06463	150	Galvanized	4
06464	M06464	200	Galvanized	4
06465	M06465	300	Galvanized	4
06466	M06466	400	Galvanized	2
06467	M06467	500	Galvanized	2
Cover				
06472	M06472	100	Galvanized	6
06473	M06473	150	Galvanized	4
06474	M06474	200	Galvanized	4
06475	M06475	300	Galvanized	4
06476	M06476	400	Galvanized	2
06477	M06477	500	Galvanized	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 198-211.

Industrial cable tray

Sendzimir trunking H 50

45° vertical inside bend



1SLC80206F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06482	M06482	100	Galvanized	6
06483	M06483	150	Galvanized	4
06484	M06484	200	Galvanized	3
06485	M06485	300	Galvanized	2
06486	M06486	400	Galvanized	2
06487	M06487	500	Galvanized	2
Cover				
06492	M06492	100	Galvanized	6
06493	M06493	150	Galvanized	4
06494	M06494	200	Galvanized	3
06495	M06495	300	Galvanized	2
06496	M06496	400	Galvanized	2
06497	M06497	500	Galvanized	2

90° vertical outside bend



1SLC80207F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
Base				
06502	M06502	100	Galvanized	6
06503	M06503	150	Galvanized	4
06504	M06504	200	Galvanized	4
06505	M06505	300	Galvanized	2
06506	M06506	400	Galvanized	2
06507	M06507	500	Galvanized	2
Cover				
06512	M06512	100	Galvanized	6
06513	M06513	150	Galvanized	4
06514	M06514	200	Galvanized	4
06515	M06515	300	Galvanized	2
06516	M06516	400	Galvanized	2
06517	M06517	500	Galvanized	2

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions page 198-211.

Industrial cable tray

Sendzimir trunking H 50

45° vertical outside bend



1SLC80208F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	Base				
	06522	M06522	100	Galvanized	6
	06523	M06523	150	Galvanized	4
	06524	M06524	200	Galvanized	3
	06525	M06525	300	Galvanized	2
	06526	M06526	400	Galvanized	2
	06527	M06527	500	Galvanized	2
	Cover				
	06532	M06532	100	Galvanized	6
	06533	M06533	150	Galvanized	4
	06534	M06534	200	Galvanized	3
	06535	M06535	300	Galvanized	2
	06536	M06536	400	Galvanized	2
	06537	M06537	500	Galvanized	2

End cap



1SLC80209F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06542	M06542	100	Galvanized	4
	06543	M06543	150	Galvanized	4
	06544	M06544	200	Galvanized	4
	06545	M06545	300	Galvanized	4
	06546	M06546	400	Galvanized	4
	06547	M06547	500	Galvanized	4

Left 90° vertical outside bend – Complete with cover.



1SLC80210F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06562	M06562	100	Galvanized	2
	06563	M06563	150	Galvanized	2
	06564	M06564	200	Galvanized	2
	06565	M06565	300	Galvanized	2
	06566	M06566	400	Galvanized	1
	06567	M06567	500	Galvanized	1

Except in specifically indicated cases, the accessories cover must be ordered separately.

Overall dimensions pages 198-211.

Industrial cable tray

Sendzimir trunking H 50

Right 90° vertical outside bend – Complete with base.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80211F0001	06572	M06572	100	Galvanized	2
	06573	M06573	150	Galvanized	2
	06574	M06574	200	Galvanized	2
	06575	M06575	300	Galvanized	2
	06576	M06576	400	Galvanized	1
	06577	M06577	500	Galvanized	1

Vertical tee corner with level gradient – Complete with base.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80212F0001	06582	M06582	100	Galvanized	3
	06583	M06583	150	Galvanized	2
	06584	M06584	200	Galvanized	2
	06585	M06585	300	Galvanized	2
	06586	M06586	400	Galvanized	1
	06587	M06587	500	Galvanized	1

90° vertical outside bend

	Product ID	Order code	Reduction from (mm)	Finish	Unit/pack-pcs
 1SLC80213F0001	Left reducer				
	06602	M06602	50	Galvanized	4
	06603	M06603	100	Galvanized	4
	06604	M06604	150	Galvanized	4
	06605	M06605	200	Galvanized	4
 1SLC80213F0001	Right reducer				
	06612	M06612	50	Galvanized	4
	06613	M06613	100	Galvanized	4
	06614	M06614	150	Galvanized	4
	06615	M06615	200	Galvanized	4

Integral mechanical joint – Guarantees electric continuity. Complete with screws and nuts.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80214F0001	06632	M06632	100	Galvanized	48
	06633	M06633	150	Galvanized	36
	06634	M06634	200	Galvanized	24
	06635	M06635	300	Galvanized	24
	06636	M06636	400	Galvanized	8
	06637	M06637	500	Galvanized	8

Mechanical joint for trunking – Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
 1SLC80215F0001	06642	M06642	180		30

Industrial cable tray

Sendzimir trunking H 50

Mechanical joint for accessories – Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06643	M06643	80		30
1SLC80216F0001					

Adjustable vertical joint – Guarantees electric continuity. Every joint supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06644	M06644			10
1SLC80217F0001					

Flange for fastening to switchboard – Supplied with 2 plates, screws and nuts.

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06646	M06646		Galvanized	25
1SLC80218F0001					

Galvanized divider profile

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	06652	M06652	2000	Galvanized	20
1SLC80219F0001					

Screw and nut

	Product ID	Order code	Description	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	100
1SLC80220F0001				

Earth staple

	Product ID	Order code	Description	Unit/pack-pcs
	07850	M07850	Staple complete with 2 M6x10 screws	50
1SLC80220F0001				

Overall dimensions pages 198-211.

Industrial cable tray


Sendzimir trunking H 75

Technical details

- Degree of protection IP20 (punched) and IP40 (solid); using special accessories the degree of protection of the IP40 trunking can be increased to IP44 (the degree of protection refers to trunking with mounted cover)
- Colors:
 - Galvanized
 - RAL 7035 grey
 - bright blue
- Fabricated in hot dip Galvanized sendzimir steel plate UNI EN 10327 Z200
- Painted with thermosetting, epoxy-polyester powders; average thickness 70-80 micron, after fabrication in hot dip sendzimir galvanized plate
- Standard height 75 mm
- Special method used to punch the trunking totally eliminates burrs, guaranteeing maximum safety for the cables and the operator
- All corners and branch connections have a wide curving angle (125 mm)
- Accessories are assembled using a mechanical system that requires no welding
- A mechanical joint system guarantees electrical continuity
- In the version with cover all accessories are supplied in the following Colors:
 - Galvanized
 - RAL 7035 grey
 - bright blue
- Accessories without cover are available in the Galvanized version
- On request galvanized trunking and accessories can be supplied varnished
- Industrial applications
- Suspension systems: page 160



IMQ mark in compliance
with CEI 23-31+V1 Standard



Industrial cable tray

Sendzimir trunking H 75

Galvanized metal trunking H 75 – IP40*



1SLC80222F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	07111	M07111	75	1000	Galvanized	8
	07112	M07112	100	1000	Galvanized	8
	07113	M07113	150	1000	Galvanized	8
	07114	M07114	200	1000	Galvanized	6
	07115	M07115	300	1000	Galvanized	6
	07121	M07121	75	2000	Galvanized	16
	07122	M07122	100	2000	Galvanized	16
	07123	M07123	150	2000	Galvanized	16
	07124	M07124	200	2000	Galvanized	12
	07125	M07125	300	2000	Galvanized	12
	07126	M07126	400	2000	Galvanized	12
	07127	M07127	500	2000	Galvanized	8
	07131	M07131	75	3000	Galvanized	24
	07132	M07132	100	3000	Galvanized	24
	07133	M07133	150	3000	Galvanized	24
	07134	M07134	200	3000	Galvanized	18
	07135	M07135	300	3000	Galvanized	18
	07136	M07136	400	3000	Galvanized	18
	07137	M07137	500	3000	Galvanized	12

* Degree of protection IP40 refers to trunking with mounted cover.

Metal trunking painted in RAL 7035 grey H 75 – IP40*



1SLC80223F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	1SL7141A00	1SL7141A00	75	1000	RAL 7035 grey	4
	1SL7142A00	1SL7142A00	100	1000	RAL 7035 grey	4
	1SL7143A00	1SL7143A00	150	1000	RAL 7035 grey	4
	1SL7144A00	1SL7144A00	200	1000	RAL 7035 grey	2
	1SL7145A00	1SL7145A00	300	1000	RAL 7035 grey	2
	1SL7151A00	1SL7151A00	75	2000	RAL 7035 grey	8
	1SL7152A00	1SL7152A00	100	2000	RAL 7035 grey	8
	1SL7153A00	1SL7153A00	150	2000	RAL 7035 grey	8
	1SL7154A00	1SL7154A00	200	2000	RAL 7035 grey	4
	1SL7155A00	1SL7155A00	300	2000	RAL 7035 grey	4
	1SL7161A00	1SL7161A00	75	3000	RAL 7035 grey	12
	1SL7162A00	1SL7162A00	100	3000	RAL 7035 grey	12
	1SL7163A00	1SL7163A00	150	3000	RAL 7035 grey	12
	1SL7164A00	1SL7164A00	200	3000	RAL 7035 grey	6
	1SL7165A00	1SL7165A00	300	3000	RAL 7035 grey	6

* Degree of protection IP40 refers to trunking with mounted cover.

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Metal trunking painted in blue H 75 – IP40*



1SLC80224F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	08401	M08401	75	1000	Bright blue	4
	08402	M08402	100	1000	Bright blue	4
	08403	M08403	150	1000	Bright blue	4
	08404	M08404	200	1000	Bright blue	2
	08405	M08405	300	1000	Bright blue	2
	08411	M08411	75	2000	Bright blue	8
	08412	M08412	100	2000	Bright blue	8
	08413	M08413	150	2000	Bright blue	8
	08414	M08414	200	2000	Bright blue	4
	08415	M08415	300	2000	Bright blue	4
	08421	M08421	75	3000	Bright blue	12
	08422	M08422	100	3000	Bright blue	12
	08423	M08423	150	3000	Bright blue	12
	08424	M08424	200	3000	Bright blue	6
	08425	M08425	300	3000	Bright blue	6

* Degree of protection IP40 refers to trunking with mounted cover.

Galvanized metal trunking H 75 – IP40*



1SLC80031F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	07171	M07171	75	2000	Galvanized	16
	07172	M07172	100	2000	Galvanized	16
	07173	M07173	150	2000	Galvanized	16
	07174	M07174	200	2000	Galvanized	12
	07175	M07175	300	2000	Galvanized	12
	07176	M07176	400	2000	Galvanized	12
	07177	M07177	500	2000	Galvanized	8
	07181	M07181	75	3000	Galvanized	24
	07182	M07182	100	3000	Galvanized	24
	07183	M07183	150	3000	Galvanized	24
	07184	M07184	200	3000	Galvanized	18
	07185	M07185	300	3000	Galvanized	18
	07186	M07186	400	3000	Galvanized	18
	07187	M07187	500	3000	Galvanized	12

* Degree of protection IP40 refers to trunking with mounted cover.

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Cover galvanized IP40/IP20



1SLC80225F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	07221	M07221	75	1000	Galvanized	16
	07222	M07222	100	1000	Galvanized	16
	07223	M07223	150	1000	Galvanized	16
	07224	M07224	200	1000	Galvanized	12
	07225	M07225	300	1000	Galvanized	12
	07231	M07231	75	2000	Galvanized	32
	07232	M07232	100	2000	Galvanized	32
	07233	M07233	150	2000	Galvanized	32
	07234	M07234	200	2000	Galvanized	24
	07235	M07235	300	2000	Galvanized	24
	07236	M07236	400	2000	Galvanized	20
	07237	M07237	500	2000	Galvanized	16
	07241	M07241	75	3000	Galvanized	48
	07242	M07242	100	3000	Galvanized	48
	07243	M07243	150	3000	Galvanized	48
	07244	M07244	200	3000	Galvanized	36
	07245	M07245	300	3000	Galvanized	36
	07246	M07246	400	3000	Galvanized	30
	07247	M07247	500	3000	Galvanized	24

Cover painted Sendzimir RAL 7035 grey IP40



1SLC80226F0001

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
	1SL7261A00	1SL7261A00	75	1000	RAL 7035 grey	12
	1SL7262A00	1SL7262A00	100	1000	RAL 7035 grey	12
	1SL7263A00	1SL7263A00	150	1000	RAL 7035 grey	12
	1SL7264A00	1SL7264A00	200	1000	RAL 7035 grey	6
	1SL7265A00	1SL7265A00	300	1000	RAL 7035 grey	6
	1SL7271A00	1SL7271A00	75	2000	RAL 7035 grey	24
	1SL7272A00	1SL7272A00	100	2000	RAL 7035 grey	24
	1SL7273A00	1SL7273A00	150	2000	RAL 7035 grey	24
	1SL7274A00	1SL7274A00	200	2000	RAL 7035 grey	12
	1SL7275A00	1SL7275A00	300	2000	RAL 7035 grey	12
	1SL7281A00	1SL7281A00	75	3000	RAL 7035 grey	36
	1SL7282A00	1SL7282A00	100	3000	RAL 7035 grey	36
	1SL7283A00	1SL7283A00	150	3000	RAL 7035 grey	36
	1SL7284A00	1SL7284A00	200	3000	RAL 7035 grey	18
	1SL7285A00	1SL7285A00	300	3000	RAL 7035 grey	18

* Degree of protection IP40 refers to trunking with mounted cover.

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Cover painted in bright blue H 75 – IP40*

	Product ID	Order code	Base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80227F0001	08431	M08431	75	1000	Bright blue	12
	08432	M08432	100	1000	Bright blue	12
	08433	M08433	150	1000	Bright blue	12
	08434	M08434	200	1000	Bright blue	6
	08435	M08435	300	1000	Bright blue	6
	08441	M08441	75	2000	Bright blue	24
	08442	M08442	100	2000	Bright blue	24
	08443	M08443	150	2000	Bright blue	24
	08444	M08444	200	2000	Bright blue	12
	08445	M08445	300	2000	Bright blue	12
	08451	M08451	75	3000	Bright blue	36
	08452	M08452	100	3000	Bright blue	36
	08453	M08453	150	3000	Bright blue	36
	08454	M08454	200	3000	Bright blue	18
	08455	M08455	300	3000	Bright blue	18

Plastic hinge for cover

	Product ID	Order code	Unit/pack-pcs
 1SLC80228F0001	07854	M07854	20

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

D45° horizontal bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80202F0001	07311	M07311	75	Galvanized	8
	07312	M07312	100	Galvanized	8
	07313	M07313	150	Galvanized	4
	07314	M07314	200	Galvanized	4
	07315	M07315	300	Galvanized	4
	07316	M07316	400	Galvanized	2
	07317	M07317	500	Galvanized	2
	1SL7321A00	1SL7321A00	75	RAL 7035 grey	8
	1SL7322A00	1SL7322A00	100	RAL 7035 grey	8
	1SL7323A00	1SL7323A00	150	RAL 7035 grey	4
1SL7324A00	1SL7324A00	200	RAL 7035 grey	4	
1SL7325A00	1SL7325A00	300	RAL 7035 grey	4	
08501	M08501	75	Bright blue	8	
08502	M08502	100	Bright blue	8	
08503	M08503	150	Bright blue	4	
08504	M08504	200	Bright blue	4	
08505	M08505	300	Bright blue	4	

D45° horizontal bend complete with cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80202F0001	17311	M17311	75	Galvanized	8
	17312	M17312	100	Galvanized	8
	17313	M17313	150	Galvanized	4
	17314	M17314	200	Galvanized	4
	17315	M17315	300	Galvanized	4
	17316	M17316	400	Galvanized	2
	17317	M17317	500	Galvanized	2

Cover for 45° horizontal bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80202F0001	06381	M06381	75	Galvanized	8
	06382	M06382	100	Galvanized	8
	06383	M06383	150	Galvanized	8
	06384	M06384	200	Galvanized	4
	06385	M06385	300	Galvanized	4
	06386	M06386	400	Galvanized	2
	06387	M06387	500	Galvanized	2

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

90° horizontal bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80201F0001	07291	M07291	75	Galvanized	8
	07292	M07292	100	Galvanized	8
	07293	M07293	150	Galvanized	8
	07294	M07294	200	Galvanized	4
	07295	M07295	300	Galvanized	4
	07296	M07296	400	Galvanized	2
	07297	M07297	500	Galvanized	2
	1SL7301A00	1SL7301A00	75	RAL 7035 grey	8
	1SL7302A00	1SL7302A00	100	RAL 7035 grey	8
	1SL7303A00	1SL7303A00	150	RAL 7035 grey	8
	1SL7304A00	1SL7304A00	200	RAL 7035 grey	4
	1SL7305A00	1SL7305A00	300	RAL 7035 grey	4
	08511	M08511	75	Bright blue	8
	08512	M08512	100	Bright blue	8
	08513	M08513	150	Bright blue	8
	08514	M08514	200	Bright blue	4
08515	M08515	300	Bright blue	4	

90° horizontal bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80201F0001	17291	M17291	75	Galvanized	8
	17292	M17292	100	Galvanized	8
	17293	M17293	150	Galvanized	8
	17294	M17294	200	Galvanized	4
	17295	M17295	300	Galvanized	4
	17296	M17296	400	Galvanized	2
	17297	M17297	500	Galvanized	2

Cover for 90° horizontal bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80201F0001	06361	M06361	75	Galvanized	8
	06362	M06362	100	Galvanized	8
	06363	M06363	150	Galvanized	4
	06364	M06364	200	Galvanized	4
	06365	M06365	300	Galvanized	4
	06366	M06366	400	Galvanized	2
	06367	M06367	500	Galvanized	2

Industrial cable tray

Sendzimir trunking H 75

Horizontal tee corner complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80203F0001	07351	M07351	75	Galvanized	4
	07352	M07352	100	Galvanized	4
	07353	M07353	150	Galvanized	4
	07354	M07354	200	Galvanized	4
	07355	M07355	300	Galvanized	2
	07356	M07356	400	Galvanized	2
	07357	M07357	500	Galvanized	2
	1SL7361A00	1SL7361A00	75	RAL 7035 grey	4
	1SL7362A00	1SL7362A00	100	RAL 7035 grey	4
	1SL7363A00	1SL7363A00	150	RAL 7035 grey	4
	1SL7364A00	1SL7364A00	200	RAL 7035 grey	4
	1SL7365A00	1SL7365A00	300	RAL 7035 grey	2
	08521	M08521	75	Bright blue	4
	08522	M08522	100	Bright blue	4
	08523	M08523	150	Bright blue	4
	08524	M08524	200	Bright blue	4
	08525	M08525	300	Bright blue	2

Horizontal tee corner without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80203F0001	17351	M17351	75	Galvanized	4
	17352	M17352	100	Galvanized	4
	17353	M17353	150	Galvanized	4
	17354	M17354	200	Galvanized	4
	17355	M17355	300	Galvanized	2
	17356	M17356	400	Galvanized	2
	17357	M17357	500	Galvanized	2

Cover for horizontal tee corner

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80203F0001	06401	M06401	75	Galvanized	4
	06402	M06402	100	Galvanized	4
	06403	M06403	150	Galvanized	4
	06404	M06404	200	Galvanized	4
	06405	M06405	300	Galvanized	2
	06406	M06406	400	Galvanized	2
	06407	M06407	500	Galvanized	2

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Horizontal tee corner with reducer and cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07710	M07710	100/75	Galvanized	4
	07711	M07711	150/75	Galvanized	4
	07712	M07712	150/100	Galvanized	4
	07713	M07713	200/75	Galvanized	4
	07714	M07714	200/100	Galvanized	4
	07715	M07715	200/150	Galvanized	4
	07716	M07716	300/75	Galvanized	2
	07717	M07717	300/100	Galvanized	2
	07718	M07718	300/150	Galvanized	2
	07719	M07719	300/200	Galvanized	2
	1SL7720A00	1SL7720A00	100/75	RAL 7035 grey	4
	1SL7721A00	1SL7721A00	150/75	RAL 7035 grey	4
	1SL7722A00	1SL7722A00	150/100	RAL 7035 grey	4
	1SL7723A00	1SL7723A00	200/75	RAL 7035 grey	4
	1SL7724A00	1SL7724A00	200/100	RAL 7035 grey	4
	1SL7725A00	1SL7725A00	200/150	RAL 7035 grey	4
	1SL7726A00	1SL7726A00	300/75	RAL 7035 grey	2
	1SL7727A00	1SL7727A00	300/100	RAL 7035 grey	2
	1SL7728A00	1SL7728A00	300/150	RAL 7035 grey	2
1SL7729A00	1SL7729A00	300/200	RAL 7035 grey	2	
08660	M08660	100/75	Bright blue	4	
08661	M08661	150/75	Bright blue	4	
08662	M08662	150/100	Bright blue	4	
08663	M08663	200/75	Bright blue	4	
08664	M08664	200/100	Bright blue	4	
08665	M08665	200/150	Bright blue	4	
08666	M08666	300/75	Bright blue	2	
08667	M08667	300/100	Bright blue	2	
08668	M08668	300/150	Bright blue	2	
08669	M08669	300/200	Bright blue	2	

Lateral tee corner and cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	M999120000	M999120000	75	Galvanized	4
	M999130000	M999130000	100	Galvanized	4
	M999140000	M999140000	150	Galvanized	4
	M999150000	M999150000	200	Galvanized	4
	M999160000	M999160000	300	Galvanized	2
	M999170000	M999170000	400	Galvanized	2
	M999180000	M999180000	500	Galvanized	2

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Horizontal tee corner with reducer without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80203F0001	17710	M17710	100/75	Galvanized	4
	17711	M17711	150/75	Galvanized	4
	17712	M17712	150/100	Galvanized	4
	17713	M17713	200/75	Galvanized	4
	17714	M17714	200/100	Galvanized	4
	17715	M17715	200/150	Galvanized	4
	17716	M17716	300/75	Galvanized	2
	17717	M17717	300/100	Galvanized	2
	17718	M17718	300/150	Galvanized	2
	17719	M17719	300/200	Galvanized	2

Cover for horizontal tee corner with reducer

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80203F0001	27710	M27710	100/75	Galvanized	4
	27711	M27711	150/75	Galvanized	4
	27712	M27712	150/100	Galvanized	4
	27713	M27713	200/75	Galvanized	4
	27714	M27714	200/100	Galvanized	4
	27715	M27715	200/150	Galvanized	4
	27716	M27716	300/75	Galvanized	2
	27717	M27717	300/100	Galvanized	2
	27718	M27718	300/150	Galvanized	2
	27719	M27719	300/200	Galvanized	2

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

Horizontal cross complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80204F0001	07371	M07371	75	Galvanized	4
	07372	M07372	100	Galvanized	4
	07373	M07373	150	Galvanized	4
	07374	M07374	200	Galvanized	2
	07375	M07375	300	Galvanized	2
	07376	M07376	400	Galvanized	2
	07377	M07377	500	Galvanized	2
	1SL7381A00	1SL7381A00	75	RAL 7035 grey	4
	1SL7382A00	1SL7382A00	100	RAL 7035 grey	4
	1SL7383A00	1SL7383A00	150	RAL 7035 grey	4
	1SL7384A00	1SL7384A00	200	RAL 7035 grey	2
	1SL7385A00	1SL7385A00	300	RAL 7035 grey	2
	08531	M08531	75	Bright blue	4
	08532	M08532	100	Bright blue	4
	08533	M08533	150	Bright blue	4
08534	M08534	200	Bright blue	2	
08535	M08535	300	Bright blue	2	

Horizontal cross without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80204F0001	17371	M17371	75	Galvanized	4
	17372	M17372	100	Galvanized	4
	17373	M17373	150	Galvanized	4
	17374	M17374	200	Galvanized	2
	17375	M17375	300	Galvanized	2
	17376	M17376	400	Galvanized	2
	17377	M17377	500	Galvanized	2

Cover for horizontal cross

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80204F0001	06421	M06421	75	Galvanized	4
	06422	M06422	100	Galvanized	4
	06423	M06423	150	Galvanized	4
	06424	M06424	200	Galvanized	2
	06425	M06425	300	Galvanized	2
	06426	M06426	400	Galvanized	2
	06427	M06427	500	Galvanized	2

Overall dimensions pages 204-211.

Industrial cable tray

Sendzimir trunking H 75

90° vertical inside bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07391	M07391	75	Galvanized	8
	07392	M07392	100	Galvanized	6
	07393	M07393	150	Galvanized	4
	07394	M07394	200	Galvanized	4
	07395	M07395	300	Galvanized	2
	07396	M07396	400	Galvanized	2
	07397	M07397	500	Galvanized	2
	1SL7401A00	1SL7401A00	75	RAL 7035 grey	8
	1SL7402A00	1SL7402A00	100	RAL 7035 grey	6
	1SL7403A00	1SL7403A00	150	RAL 7035 grey	4
1SL7404A00	1SL7404A00	200	RAL 7035 grey	4	
1SL7405A00	1SL7405A00	300	RAL 7035 grey	2	
08541	M08541	75	Bright blue	8	
08542	M08542	100	Bright blue	6	
08543	M08543	150	Bright blue	4	
08544	M08544	200	Bright blue	4	
08545	M08545	300	Bright blue	2	

90° vertical inside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	17391	M17391	75	Galvanized	8
	17392	M17392	100	Galvanized	6
	17393	M17393	150	Galvanized	4
	17394	M17394	200	Galvanized	4
	17395	M17395	300	Galvanized	2
	17396	M17396	400	Galvanized	2
	17397	M17397	500	Galvanized	2
	1SLC80229F0001				

Cover for 90° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	06471	M06471	75	Galvanized	8
	06472	M06472	100	Galvanized	6
	06473	M06473	150	Galvanized	4
	06474	M06474	200	Galvanized	4
	06475	M06475	300	Galvanized	2
	06476	M06476	400	Galvanized	2
	06477	OM06477	500	Galvanized	2
1SLC80230F0001					

Overall dimensions pages 204-211.


Industrial cable tray

Sendzimir trunking H 75

45° vertical inside bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80206F0001</p>	07411	M07411	75	Galvanized	8
	07412	M07412	100	Galvanized	6
	07413	M07413	150	Galvanized	4
	07414	M07414	200	Galvanized	4
	07415	M07415	300	Galvanized	2
	07416	M07416	400	Galvanized	2
	07417	M07417	500	Galvanized	2
	1SL7421A00	1SL7421A00	75	RAL 7035 grey	8
	1SL7422A00	1SL7422A00	100	RAL 7035 grey	6
	1SL7423A00	1SL7423A00	150	RAL 7035 grey	4
	1SL7424A00	1SL7424A00	200	RAL 7035 grey	4
	1SL7425A00	1SL7425A00	300	RAL 7035 grey	2
	08551	M08551	75	Bright blue	8
	08552	M08552	100	Bright blue	6
	08553	M08553	150	Bright blue	4
	08554	M08554	200	Bright blue	4
	08555	M08555	300	Bright blue	2

45° vertical inside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80231F0001</p>	17411	M17411	75	Galvanized	8
	17412	M17412	100	Galvanized	6
	17413	M17413	150	Galvanized	4
	17414	M17414	200	Galvanized	4
	17415	M17415	300	Galvanized	2
	17416	M17416	400	Galvanized	2
	17417	M17417	500	Galvanized	2

Cover for 45° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80232F0001</p>	06491	M06491	75	Galvanized	8
	06492	M06492	100	Galvanized	6
	06493	M06493	150	Galvanized	4
	06494	M06494	200	Galvanized	4
	06495	M06495	300	Galvanized	2
	06496	M06496	400	Galvanized	2
	06497	M06497	500	Galvanized	2

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

90° vertical outside bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80207F0001</p>	07451	M07451	75	Galvanized	8
	07452	M07452	100	Galvanized	6
	07453	M07453	150	Galvanized	4
	07454	M07454	200	Galvanized	4
	07455	M07455	300	Galvanized	2
	07456	M07456	400	Galvanized	2
	07457	M07457	500	Galvanized	2
	1SL7461A00	1SL7461A00	75	RAL 7035 grey	8
	1SL7462A00	1SL7462A00	100	RAL 7035 grey	6
	1SL7463A00	1SL7463A00	150	RAL 7035 grey	4
	1SL7464A00	1SL7464A00	200	RAL 7035 grey	4
	1SL7465A00	1SL7465A00	300	RAL 7035 grey	2
	08561	M08561	75	Bright blue	8
	08562	M08562	100	Bright blue	6
	08563	M08563	150	Bright blue	4
	08564	M08564	200	Bright blue	4
	08565	M08565	300	Bright blue	2

90° vertical outside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80233F0001</p>	17451	M17451	75	Galvanized	8
	17452	M17452	100	Galvanized	6
	17453	M17453	150	Galvanized	4
	17454	M17454	200	Galvanized	4
	17455	M17455	300	Galvanized	2
	17456	M17456	400	Galvanized	2
	17457	M17457	500	Galvanized	2

Cover for 90° vertical outside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 <p>1SLC80234F0001</p>	06511	M06511	75	Galvanized	8
	06512	M06512	100	Galvanized	6
	06513	M06513	150	Galvanized	4
	06514	M06514	200	Galvanized	4
	06515	M06515	300	Galvanized	2
	06516	M06516	400	Galvanized	2
	06517	M06517	500	Galvanized	2

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

45° vertical outside bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80208F0001	07471	M07471	75	Galvanized	8
	07472	M07472	100	Galvanized	6
	07473	M07473	150	Galvanized	4
	07474	M07474	200	Galvanized	4
	07475	M07475	300	Galvanized	2
	07476	M07476	400	Galvanized	2
	07477	M07477	500	Galvanized	2
	1SL7481A00	1SL7481A00	75	RAL 7035 grey	8
	1SL7482A00	1SL7482A00	100	RAL 7035 grey	6
	1SL7483A00	1SL7483A00	150	RAL 7035 grey	4
1SL7484A00	1SL7484A00	200	RAL 7035 grey	4	
1SL7485A00	1SL7485A00	300	RAL 7035 grey	2	
	08571	M08571	75	Bright blue	8
	08572	M08572	100	Bright blue	6
	08573	M08573	150	Bright blue	4
	08574	M08574	200	Bright blue	4
	08575	M08575	300	Bright blue	2

45° vertical outside bend without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80235F0001	17471	M17471	75	Galvanized	8
	17472	M17472	100	Galvanized	6
	17473	M17473	150	Galvanized	4
	17474	M17474	200	Galvanized	4
	17475	M17475	300	Galvanized	2
	17476	M17476	400	Galvanized	2
	17477	M17477	500	Galvanized	2

Cover for 45° vertical inside bend

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80236F0001	06531	M06531	75	Galvanized	8
	06532	M06532	100	Galvanized	6
	06533	M06533	150	Galvanized	4
	06534	M06534	200	Galvanized	4
	06535	M06535	300	Galvanized	2
	06536	M06536	400	Galvanized	2
	06537	M06537	500	Galvanized	2

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

45° vertical outside bend complete with cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80237F0001	07571	M07571	75	Galvanized	4
	07572	M07572	100	Galvanized	4
	07573	M07573	150	Galvanized	4
	07574	M07574	200	Galvanized	4
	07575	M07575	300	Galvanized	4
	07576	M07576	400	Galvanized	4
	07577	M07577	500	Galvanized	4
	1SL7581A00	1SL7581A00	75	RAL 7035 grey	4
	1SL7582A00	1SL7582A00	100	RAL 7035 grey	4
	1SL7583A00	1SL7583A00	150	RAL 7035 grey	4
1SL7584A00	1SL7584A00	200	RAL 7035 grey	4	
1SL7585A00	1SL7585A00	300	RAL 7035 grey	4	
08701	M08701	75	Bright blue	4	
08702	M08702	100	Bright blue	4	
08703	M08703	150	Bright blue	4	
08704	M08704	200	Bright blue	4	
08705	M08705	300	Bright blue	4	

Left 90° vertical outside bend complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80238F0001	07591	M07591	75	Galvanized	4
	07592	M07592	100	Galvanized	3
	07593	M07593	150	Galvanized	2
	07594	M07594	200	Galvanized	2
	07595	M07595	300	Galvanized	2
	07596	M07596	400	Galvanized	1
	07597	M07597	500	Galvanized	1
	1SL7601A00	1SL7601A00	75	RAL 7035 grey	4
	1SL7602A00	1SL7602A00	100	RAL 7035 grey	3
	1SL7603A00	1SL7603A00	150	RAL 7035 grey	2
	1SL7604A00	1SL7604A00	200	RAL 7035 grey	2
	1SL7605A00	1SL7605A00	300	RAL 7035 grey	2
	08611	M08611	75	Bright blue	4
	08612	M08612	100	Bright blue	3
	08613	M08613	150	Bright blue	2
08614	M08614	200	Bright blue	2	
08615	M08615	300	Bright blue	2	

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Right 90° vertical outside bend complete with cover – Complete with cover earth wiring accessories.



1SLC80239F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07611	M07611	75	Galvanized	4
07612	M07612	100	Galvanized	3
07613	M07613	150	Galvanized	2
07614	M07614	200	Galvanized	2
07615	M07615	300	Galvanized	2
07616	M07616	400	Galvanized	1
07617	M07617	500	Galvanized	1
1SL7621A00	1SL7621A00	75	RAL 7035 grey	4
1SL7622A00	1SL7622A00	100	RAL 7035 grey	3
1SL76283A00	1SL76283A00	150	RAL 7035 grey	2
1SL7624A00	1SL7624A00	200	RAL 7035 grey	2
1SL7625A00	1SL7625A00	300	RAL 7035 grey	2
08621	M08621	75	Bright blue	4
08622	M08622	100	Bright blue	3
08623	M08623	150	Bright blue	2
08624	M08624	200	Bright blue	2
08625	M08625	300	Bright blue	2

Vertical tee branch connection without level gradient complete with cover – Complete with cover earth wiring accessories.



1SLC80240F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07651	M07651	75	Galvanized	4
07652	M07652	100	Galvanized	3
07653	M07653	150	Galvanized	2
07654	M07654	200	Galvanized	2
07655	M07655	300	Galvanized	2
07656	M07656	400	Galvanized	1
07657	M07657	500	Galvanized	1
1SL7661A00	1SL7661A00	75	RAL 7035 grey	4
1SL7662A00	1SL7662A00	100	RAL 7035 grey	3
1SL7663A00	1SL7663A00	150	RAL 7035 grey	2
1SL7664A00	1SL7664A00	200	RAL 7035 grey	2
1SL7665A00	1SL7665A00	300	RAL 7035 grey	2
08631	M08631	75	Bright blue	4
08632	M08632	100	Bright blue	3
08633	M08633	150	Bright blue	2
08634	M08634	200	Bright blue	2
08635	M08635	300	Bright blue	2

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Vertical tee branch connection with level gradient complete with cover - Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07691	M07691	75	Galvanized	4
	07692	M07692	100	Galvanized	3
	07693	M07693	150	Galvanized	2
	07694	M07694	200	Galvanized	2
	07695	M07695	300	Galvanized	2
	07696	M07696	400	Galvanized	1
	07697	M07697	500	Galvanized	1
	1SL7701A00	1SL7701A00	75	RAL 7035 grey	4
	1SL7702A00	1SL7702A00	100	RAL 7035 grey	3
	1SL7703A00	1SL7703A00	150	RAL 7035 grey	2
1SL7704A00	1SL7704A00	200	RAL 7035 grey	2	
1SL7705A00	1SL7705A00	300	RAL 7035 grey	2	
08641	M08641	75	Bright blue	4	
08642	M08642	100	Bright blue	3	
08643	M08643	150	Bright blue	2	
08644	M08644	200	Bright blue	2	
08645	M08645	300	Bright blue	2	

1SLC80241F0001

Vertical tee branch connection with reducer and level gradient complete with cover - Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07630	M07630	100/75	Galvanized	3
	07631	M07631	150/75	Galvanized	2
	07632	M07632	150/100	Galvanized	2
	07633	M07633	200/75	Galvanized	2
	07634	M07634	200/100	Galvanized	2
	07635	M07635	200/150	Galvanized	2
	07636	M07636	300/75	Galvanized	2
	07637	M07637	300/100	Galvanized	2
	07638	M07638	300/150	Galvanized	2
	07639	M07639	300/200	Galvanized	2
	1SL7640A00	1SL7640A00	100/75	RAL 7035 grey	3
	1SL7641A00	1SL7641A00	150/75	RAL 7035 grey	2
	1SL7642A00	1SL7642A00	150/100	RAL 7035 grey	2
	1SL7643A00	1SL7643A00	200/75	RAL 7035 grey	2
	1SL7644A00	1SL7644A00	200/100	RAL 7035 grey	2
	1SL7645A00	1SL7645A00	200/150	RAL 7035 grey	2
	1SL7646A00	1SL7646A00	300/75	RAL 7035 grey	2
	1SL7647A00	1SL7647A00	300/100	RAL 7035 grey	2
	1SL7648A00	1SL7648A00	300/150	RAL 7035 grey	2
	1SL7649A00	1SL7649A00	300/200	RAL 7035 grey	2
08650	M08650	100/75	Bright blue	3	
08651	M08651	150/75	Bright blue	2	
08652	M08652	150/100	Bright blue	2	
08653	M08653	200/75	Bright blue	2	
08654	M08654	200/100	Bright blue	2	
08655	M08655	200/150	Bright blue	2	
08656	M08656	300/75	Bright blue	2	
08657	M08657	300/100	Bright blue	2	
08658	M08658	300/150	Bright blue	2	
08659	M08659	300/200	Bright blue	2	

1SLC80242F0001

Industrial cable tray

Sendzimir trunking H 75

Straight reducer complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07512	M07512	100/75	Galvanized	6
	07513	M07513	150/75	Galvanized	6
	07514	M07514	150/100	Galvanized	6
	07516	M07516	200/75	Galvanized	3
	07517	M07517	200/100	Galvanized	3
	07518	M07518	200/150	Galvanized	3
	07519	M07519	300/200	Galvanized	3
	07520	M07520	400/300	Galvanized	2
	07521	M07521	500/400	Galvanized	2
	1SL7522A00	1SL7522A00	100/75	RAL 7035 grey	6
	1SL7523A00	1SL7523A00	150/75	RAL 7035 grey	6
	1SL7524A00	1SL7524A00	150/100	RAL 7035 grey	6
	1SL7526A00	1SL7526A00	200/75	RAL 7035 grey	3
	1SL7527A00	1SL7527A00	200/100	RAL 7035 grey	3
	1SL7528A00	1SL7528A00	200/150	RAL 7035 grey	3
	1SL7529A00	1SL7529A00	300/200	RAL 7035 grey	3
	08581	M08581	100/75	Bright blue	6
	08582	M08582	150/75	Bright blue	6
	08583	M08583	150/100	Bright blue	6
	08584	M08584	200/75	Bright blue	3
08585	M08585	200/100	Bright blue	3	
08586	M08586	200/150	Bright blue	3	
08587	M08587	300/200	Bright blue	3	

Straight reducer without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	17512	M17512	100/75	Galvanized	6
	17513	M17513	150/75	Galvanized	6
	17514	M17514	150/100	Galvanized	6
	17516	M17516	200/75	Galvanized	3
	17517	M17517	200/100	Galvanized	3
	17518	M17518	200/150	Galvanized	3
	17519	M17519	300/200	Galvanized	3
	17520	M17520	400/300	Galvanized	2
	17521	M17521	500/400	Galvanized	2

Cover for straight reducer

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	27512	M27512	100/75	Galvanized	6
	27513	M27513	150/75	Galvanized	6
	27514	M27514	150/100	Galvanized	6
	27516	M27516	200/75	Galvanized	3
	27517	M27517	200/100	Galvanized	3
	27518	M27518	200/150	Galvanized	3
	27519	M27519	300/200	Galvanized	3
	27520	M27520	400/300	Galvanized	2
	27521	M27521	500/400	Galvanized	2

Industrial cable tray

Sendzimir trunking H 75

Left reducer complete with cover – Complete with cover earth wiring accessories.

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80246F0001	07532	M07532	100/75	Galvanized	6
	07533	M07533	150/75	Galvanized	6
	07534	M07534	150/100	Galvanized	6
	07536	M07536	200/75	Galvanized	3
	07537	M07537	200/100	Galvanized	3
	07538	M07538	200/150	Galvanized	3
	07539	M07539	300/200	Galvanized	3
	07540	M07540	400/300	Galvanized	2
	07541	M07541	500/400	Galvanized	2
	1SL7542A00	1SL7542A00	100/75	RAL 7035 grey	6
1SL7543A00	1SL7543A00	150/75	RAL 7035 grey	6	
1SL7544A00	1SL7544A00	150/100	RAL 7035 grey	6	
1SL7546A00	1SL7546A00	200/75	RAL 7035 grey	3	
1SL7547A00	1SL7547A00	200/100	RAL 7035 grey	3	
1SL7548A00	1SL7548A00	200/150	RAL 7035 grey	3	
1SL7549A00	1SL7549A00	300/200	RAL 7035 grey	3	
08591	M08591	100/75	Bright blue	6	
08592	M08592	150/75	Bright blue	6	
08593	M08593	150/100	Bright blue	6	
08594	M08594	200/75	Bright blue	3	
08595	M08595	200/100	Bright blue	3	
08596	M08596	200/150	Bright blue	3	
08597	M08597	300/200	Bright blue	3	

Left reducer without cover

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80247F0001	17532	M17532	100/75	Galvanized	6
	17533	M17533	150/75	Galvanized	6
	17534	M17534	150/100	Galvanized	6
	17536	M17536	200/75	Galvanized	3
	17537	M17537	200/100	Galvanized	3
	17538	M17538	200/150	Galvanized	3
	17539	M17539	300/200	Galvanized	3
	17540	M17540	400/300	Galvanized	2
	17541	M17541	500/400	Galvanized	2

Cover for left reducer

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80248F0001	27532	M27532	100/75	Galvanized	6
	27533	M27533	150/75	Galvanized	6
	27534	M27534	150/100	Galvanized	6
	27536	M27536	200/75	Galvanized	3
	27537	M27537	200/100	Galvanized	3
	27538	M27538	200/150	Galvanized	3
	27539	M27539	300/200	Galvanized	3
	27540	M27540	400/300	Galvanized	2
	27541	M27541	500/400	Galvanized	2

Industrial cable tray

Sendzimir trunking H 75

Right reducer complete with cover



1SLC80249F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07552	M07552	100/75	Galvanized	6
07553	M07553	150/75	Galvanized	6
07554	M07554	150/100	Galvanized	6
07556	M07556	200/75	Galvanized	3
07557	M07557	200/100	Galvanized	3
07558	M07558	200/150	Galvanized	3
07559	M07559	300/200	Galvanized	3
07560	M07560	400/300	Galvanized	2
07561	M07561	500/400	Galvanized	2
1SL7562A00	1SL7562A00	100/75	RAL 7035 grey	6
1SL7563A00	1SL7563A00	150/75	RAL 7035 grey	6
1SL7564A00	1SL7564A00	150/100	RAL 7035 grey	6
1SL7566A00	1SL7566A00	200/75	RAL 7035 grey	3
1SL7567A00	1SL7567A00	200/100	RAL 7035 grey	3
1SL7568A00	1SL7568A00	200/150	RAL 7035 grey	3
1SL7569A00	1SL7569A00	300/200	RAL 7035 grey	3
08601	M08601	100/75	Bright blue	6
08602	M08602	150/75	Bright blue	6
08603	M08603	150/100	Bright blue	6
08604	M08604	200/75	Bright blue	3
08605	M08605	200/100	Bright blue	3
08606	M08606	200/150	Bright blue	3
08607	M08607	300/200	Bright blue	3

Right reducer without cover



1SLC80250F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
17552	M17552	100/75	Galvanized	6
17553	M17553	150/75	Galvanized	6
17554	M17554	150/100	Galvanized	6
17556	M17556	200/75	Galvanized	3
17557	M17557	200/100	Galvanized	3
17558	M17558	200/150	Galvanized	3
17559	M17559	300/200	Galvanized	3
17560	M17560	400/300	Galvanized	2
17561	M17561	500/400	Galvanized	2

Cover for straight reducer



1SLC80251F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
27552	M27552	100/75	Galvanized	6
27553	M27553	150/75	Galvanized	6
27554	M27554	150/100	Galvanized	6
27556	M27556	200/75	Galvanized	3
27557	M27557	200/100	Galvanized	3
27558	M27558	200/150	Galvanized	3
27559	M27559	300/200	Galvanized	3
27560	M27560	400/300	Galvanized	2
27561	M27561	500/400	Galvanized	2

Industrial cable tray

Sendzimir trunking H 75

Straight inversion elements – Complete with cover earth wiring accessories.



1SLC80252F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07731	M07731	75	Galvanized	24
	07732	M07732	100	Galvanized	24
	07733	M07733	150	Galvanized	12
	07734	M07734	200	Galvanized	12
	07735	M07735	300	Galvanized	6
	07736	M07736	400	Galvanized	4
	07737	M07737	500	Galvanized	4
	1SL7741A00	1SL7741A00	75	RAL 7035 grey	24
	1SL7742A00	1SL7742A00	100	RAL 7035 grey	24
	1SL7743A00	1SL7743A00	150	RAL 7035 grey	12
	1SL7744A00	1SL7744A00	200	RAL 7035 grey	12
	1SL7745A00	1SL7745A00	300	RAL 7035 grey	6
	08711	M08711	75	Bright blue	24
	08712	M08712	100	Bright blue	24
	08713	M08713	150	Bright blue	12
	08714	M08714	200	Bright blue	12
	08715	M08715	300	Bright blue	6

Coupler flange for fastening to switchboard



1SLC80252F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07791	M07791	75	Galvanized	4
	07792	M07792	100	Galvanized	4
	07793	M07793	150	Galvanized	4
	07794	M07794	200	Galvanized	4
	07795	M07795	300	Galvanized	4
	07796	M07796	400	Galvanized	4
	07797	M07797	500	Galvanized	4
	1SL7801A00	1SL7801A00	75	RAL 7035 grey	4
	1SL7802A00	1SL7802A00	100	RAL 7035 grey	4
	1SL7803A00	1SL7803A00	150	RAL 7035 grey	4
	1SL7804A00	1SL7804A00	200	RAL 7035 grey	4
	1SL7805A00	1SL7805A00	300	RAL 7035 grey	4
	08741	M08741	75	Bright blue	4
	08742	M08742	100	Bright blue	4
	08743	M08743	150	Bright blue	4
	08744	M08744	200	Bright blue	4
	08745	M08745	300	Bright blue	4

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Wall flange



1SLC80254F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07811	M07811	75	Galvanized	4
07812	M07812	100	Galvanized	4
07813	M07813	150	Galvanized	4
07814	M07814	200	Galvanized	4
07815	M07815	300	Galvanized	4
07816	M07816	400	Galvanized	4
07817	M07817	500	Galvanized	4
1SL7821A00	1SL7821A00	75	RAL 7035 grey	4
1SL7822A00	1SL7822A00	100	RAL 7035 grey	4
1SL7823A00	1SL7823A00	150	RAL 7035 grey	4
1SL7824A00	1SL7824A00	200	RAL 7035 grey	4
1SL7825A00	1SL7825A00	300	RAL 7035 grey	4
08751	M08751	75	Bright blue	4
08752	M08752	100	Bright blue	4
08753	M08753	150	Bright blue	4
08754	M08754	200	Bright blue	4
08755	M08755	300	Bright blue	4

Mechanical integral joint – Guarantees electric continuity. Complete with screws and nuts. Width 80 mm.



1SLC80214F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07831	M07831	75	Galvanized	48
07832	M07832	100	Galvanized	48
07833	M07833	150	Galvanized	36
07834	M07834	200	Galvanized	24
07836	M07836	300	Galvanized	24
07836	M07836	400	Galvanized	8
07837	M07837	500	Galvanized	8

Retainer for integral joints – Snaps onto integral joint. Width 48 mm.



1SLC80255F0001

Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
07838	M07838	75	Galvanized	48
07839	M07839	100	Galvanized	48
07840	M07840	150	Galvanized	36
07842	M07842	200	Galvanized	24
07844	M07844	300	Galvanized	24
07846	M07846	400	Galvanized	8
07847	M07847	500	Galvanized	8

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Mechanical joint – Guarantees electric continuity. Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLC80215F0001  1SLC80216F0001	07829	M07829	Width 80 mm	Galvanized	50

Vertical joint fixed at 90° – Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLC80256F0001	07841	M07841		Galvanized	25

Vertical adjustable joint – Every joint is supplied with 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLC80257F0001	07843	M07843		Galvanized	10

Coupler for left reducer

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
 1SLC80258F0001	07750	M07750	50	Galvanized	4
	07752	M07752	100	Galvanized	4
	07753	M07753	150	Galvanized	4
	07754	M07754	200	Galvanized	4
	1SL7760A00	1SL7760A00	50	RAL 7035 grey	4
	1SL7762A00	1SL7762A00	100	RAL 7035 grey	4
	1SL7763A00	1SL7763A00	150	RAL 7035 grey	4
	1SL7764A00	1SL7764A00	200	RAL 7035 grey	4
	08721	M08721	50	Bright blue	4
	08722	M08722	100	Bright blue	4
	08723	M08723	150	Bright blue	4
	08724	M08724	200	Bright blue	4

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Coupler for right reducer

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
 1SLC80258F0001	07770	M07770	50	Galvanized	4
	07772	M07772	100	Galvanized	4
	07773	M07773	150	Galvanized	4
	07774	M07774	200	Galvanized	4
	1SL7780A00	1SL7780A00	50	RAL 7035 grey	4
	1SL7782A00	1SL7782A00	100	RAL 7035 grey	4
	1SL7783A00	1SL7783A00	150	RAL 7035 grey	4
	1SL7784A00	1SL7784A00	200	RAL 7035 grey	4
	08731	M08731	50	Bright blue	4
	08732	M08732	100	Bright blue	4
	08733	M08733	150	Bright blue	4
	08734	M08734	200	Bright blue	4

Overall dimensions pages 247 - 253.

Joint IP44 – Must be used with every joint. Complete with all the elements required for mounting (see page 205).

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
 1SLC80259F0001	07866	M07866	75	Galvanized	12
	07867	M07867	100	Galvanized	12
	07868	M07868	150	Galvanized	12
	07869	M07869	200	Galvanized	8
	07870	M07870	300	Galvanized	8
	07998	M07998	400	Galvanized	4
	07999	M07999	500	Galvanized	4
	1SL7861A00	1SL7861A00	75	RAL 7035 grey	12
	1SL7862A00	1SL7862A00	100	RAL 7035 grey	12
	1SL7863A00	1SL7863A00	150	RAL 7035 grey	12
	1SL7864A00	1SL7864A00	200	RAL 7035 grey	8
	1SL7865A00	1SL7865A00	300	RAL 7035 grey	8
	08761	M08761	75	Bright blue	12
	08762	M08762	100	Bright blue	12
	08763	M08763	150	Bright blue	12
	08764	M08764	200	Bright blue	8
	08765	M08765	300	Bright blue	8

Clip

	Product ID	Order code	Description	Unit/pack-pcs
 1SLC80261F0001	07890	M07890		20

Fixed between the cover and the trunking to increase the pressure of the seal and to obtain IP44 (one clip every metre) degree of protection.

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Coupler flange for fastening to IP44 switchboards



1SLC80262F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07430	M07430	75	Galvanized	24
	07431	M07431	100	Galvanized	4
	07432	M07432	150	Galvanized	4
	07433	M07433	200	Galvanized	4
	07434	M07434	300	Galvanized	4
	07435	M07435	400	Galvanized	2
	07436	M07436	500	Galvanized	2
	1SL7440A00	1SL7440A00	75	RAL 7035 grey	24
	1SL7441A00	1SL7441A00	100	RAL 7035 grey	24
	1SL7442A00	1SL7442A00	150	RAL 7035 grey	4
	1SL7443A00	1SL7443A00	200	RAL 7035 grey	4
	1SL7444A00	1SL7444A00	300	RAL 7035 grey	4
	08746	M08746	75	Bright blue	24
	08747	M08747	100	Bright blue	24
	08748	M08748	150	Bright blue	12
	08749	M08749	200	Bright blue	12
	08750	M08750	300	Bright blue	6

End cap IP44 – Complete with all elements required for mounting.



1SLC80263F0001

	Product ID	Order code	For trunking base (mm)	Finish	Unit/pack-pcs
	07886	M07886	75	Galvanized	4
	07887	M07887	100	Galvanized	4
	07889	M07889	150	Galvanized	4
	07896	M07896	200	Galvanized	4
	07897	M07897	300	Galvanized	4
	07898	M07898	400	Galvanized	4
	07899	M07899	500	Galvanized	4
	1SL7881A00	1SL7881A00	75	RAL 7035 grey	4
	1SL7882A00	1SL7882A00	100	RAL 7035 grey	4
	1SL7883A00	1SL7883A00	150	RAL 7035 grey	4
	1SL7884A00	1SL7884A00	200	RAL 7035 grey	4
	1SL7885A00	1SL7885A00	300	RAL 7035 grey	4
	08781	M08781	75	Bright blue	4
	08782	M08782	100	Bright blue	4
	08783	M08783	150	Bright blue	4
	08784	M08784	200	Bright blue	4
	08785	M08785	300	Bright blue	4

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Self-adhesive seal

	Product ID	Order code	Material	Unit/pack-m
	07888	M07888	Neoprene	20

1SLC80265F0001

To attach onto the trunking cover and accessories cover (dim. 2x7 mm).

Divider

	Product ID	Order code	Material	Length (mm)	Unit/pack-m
	44040	M44040	Plastic *	2000	52
	07855	M07855	Galvanized metal **	2000	20

1SLC80266F0001

* Snaps on using art. 07 852. ** Fastens onto the base of the trunking using screws or adhesive.

Fastening element – For plastic dividers and cable ties.

	Product ID	Order code	Material	Unit/pack-pcs
	07852	M07852	Techno-polymer	20

1SLC80267F0001

Fastens onto the base of trunking or cable trays with 2 screws.

Branch connection coupler – Complete with seal for IP44 degree of protection.

	Product ID	Order code	Description	Unit/pack-pcs
	07845	M07845		10

1SLC80268F0001

For installing consumer units or boxes to the base of trunking.

Inner panel

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	07755	M07755	For boxes IP55	Galvanized	4
	07756	M07756	For boxes IP55	Galvanized	4
	07757	M07757	For boxes IP55	Galvanized	4
	07758	M07758	For boxes IP55	Galvanized	4

1SLC80270F0001

Overall dimensions pages 204-215.

Industrial cable tray

Sendzimir trunking H 75

Galvanized DIN rails for branch connection boxes

	Product ID	Order code	Type	For boxes Dimensions WxHxP (mm)	Unit/pack-pcs
 1SLC80271F0001	07765	M07765	Symmetrical	200x200x120	10
	07766	M07766	Symmetrical	300x300x120	10
	07767	M07767	Symmetrical	400x400x120	10
	07768	M07768	Symmetrical	600x600x120	10
	07775	M07775	Asymmetrical	200x200x120	10
	07776	M07776	Asymmetrical	300x300x120	10
	07777	M07777	Asymmetrical	400x400x120	10
	07778	M07778	Asymmetrical	600x600x120	10

Screw and nut

	Product ID	Order code	Description	Unit/pack-pcs
 1SLC80220F0001	07848	M07848	Round-headed M6x10 screw with nut	100

Earth staple

	Product ID	Order code	Description	Unit/pack-pcs
 1SLC80220F0001	07850	M07850	Staple complete with 2 M6x10 screws	50

Hinges

	Product ID	Order code	Description	Unit/pack-pcs
 1SLC80272F0001	07779	M07779		20

To hinge the cover of branch connection boxes

Paints


	Product ID	Order code	Finish	Weight (kg)
 1SLC80272F0001	1SL7856A00	1SL7856A00	RAL 7035 grey	0.5
	08799	M08799	Bright blue	0.5
	06095	M06095	RAL 9016 white	0.25

Industrial cable tray

Cable ladders H 60

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 60 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable ladder strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 60

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80033F0001	09400	M09400	100	3000	GAC	3
	09401	M09401	200	3000	GAC	3
	09402	M09402	300	3000	GAC	3
	09403	M09403	400	3000	GAC	3
	09404	M09404	500	3000	GAC	3
	09405	M09405	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
 1SLC80275F0001	09440	M09440	100	GAC	1
	09441	M09441	200	GAC	1
	09442	M09442	300	GAC	1
	09443	M09443	400	GAC	1
	09444	M09444	500	GAC	1
	09445	M09445	600	GAC	1
Cover					
 1SLC80276F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80277F0001	Base				
	09480	M09480	100	GAC	1
	09481	M09481	200	GAC	1
	09482	M09482	300	GAC	1
	09483	M09483	400	GAC	1
	09484	M09484	500	GAC	1
	09485	M09485	600	GAC	1
 1SLC80278F0001	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80279F0001	Base				
	09520	M09520	100	GAC	1
	09521	M09521	200	GAC	1
	09522	M09522	300	GAC	1
	09523	M09523	400	GAC	1
	09524	M09524	500	GAC	1
	09525	M09525	600	GAC	1
 1SLC80280F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80281F0001	Base				
	09560	M09560	100	GAC	1
	09561	M09561	200	GAC	1
	09562	M09562	300	GAC	1
	09563	M09563	400	GAC	1
	09564	M09564	500	GAC	1
	09565	M09565	600	GAC	1
 1SLC80282F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

Vertical inside and outside bend adjustable from 0° to 90°

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	09600	M09600	100	GAC	1
	09601	M09601	200	GAC	1
	09602	M09602	300	GAC	1
	09603	M09603	400	GAC	1
	09604	M09604	500	GAC	1
	09605	M09605	600	GAC	1

1SLC80283F0001

Use straight covers for covering

90° vertical inside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09962	M09962	100	GAC	1
	09963	M09963	200	GAC	1
	09964	M09964	300	GAC	1
	09965	M09965	400	GAC	1
	09966	M09966	500	GAC	1
	09967	M09967	600	GAC	1
	Cover				
	09920	M09920	100	GAC	1
	09921	M09921	200	GAC	1
	09922	M09922	300	GAC	1
	09923	M09923	400	GAC	1
	09924	M09924	500	GAC	1
	09925	M09925	600	GAC	1

1SLC80284F0001

1SLC80285F0001

90° vertical outside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09980	M09980	100	GAC	1
	09981	M09981	200	GAC	1
	09982	M09982	300	GAC	1
	09983	M09983	400	GAC	1
	09984	M09984	500	GAC	1
	09985	M09985	600	GAC	1
	Cover				
	09941	M09941	100	GAC	1
	09942	M09942	200	GAC	1
	09943	M09943	300	GAC	1
	09944	M09944	400	GAC	1
	09945	M09945	500	GAC	1
	09946	M09946	600	GAC	1

1SLC80286F0001

1SLC80287F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80288F0001	Base				
	09640	M09640	200/100	GAC	1
	09641	M09641	300/100	GAC	1
	09642	M09642	300/200	GAC	1
	09643	M09643	400/200	GAC	1
	09644	M09644	400/300	GAC	1
	09645	M09645	500/300	GAC	1
	09646	M09646	500/400	GAC	1
	09647	M09647	600/400	GAC	1
	09648	M09648	600/500	GAC	1
 1SLC80289F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80290F0001	Base				
	09680	M09680	200/100	GAC	1
	09681	M09681	300/100	GAC	1
	09682	M09682	300/200	GAC	1
	09683	M09683	400/200	GAC	1
	09684	M09684	400/300	GAC	1
	09685	M09685	500/300	GAC	1
	09686	M09686	500/400	GAC	1
	09687	M09687	600/400	GAC	1
	09688	M09688	600/500	GAC	1
 1SLC80291F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
 1SLC80292F0001	09720	M09720	200/100	GAC	1
	09721	M09721	300/100	GAC	1
	09722	M09722	300/200	GAC	1
	09723	M09723	400/200	GAC	1
	09724	M09724	400/300	GAC	1
	09725	M09725	500/300	GAC	1
	09726	M09726	500/400	GAC	1
	09727	M09727	600/400	GAC	1
	09728	M09728	600/500	GAC	1
	Cover				
 1SLC80293F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

Couplers – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09760	M09760	Straight	GAC	1/20
	09761	M09761	Horizontal adjustable	GAC	1/20
	09762	M09762	Vertical adjustable	GAC	1/10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09800	M09800	50	GAC	1
	09801	M09801	100	GAC	1
	09802	M09802	200	GAC	1

1SLC80295F0001

Metal divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	09900	M09900	1500	GAC	2/10

1SLC80296F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 60

Square and cover spacer



15LC80297F0001

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09903	M09903	Spacer for cover H 50 mm	GAC	1/20
	09904	M09904	Square for fastening brackets – inner	GAC	1/50
	09905	M09905	Square for fastening brackets – outer	GAC	1/50

Fastening components



15LC80298F0001

	Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	GAC	100
	07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
	07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100


For fastening squares and spacers and for earth connections.

Industrial cable tray

Cable ladders H 100

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 100 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable ladder strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 100

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80033F0001	09410	M09410	100	3000	GAC	3
	09411	M09411	200	3000	GAC	3
	09412	M09412	300	3000	GAC	3
	09413	M09413	400	3000	GAC	3
	09414	M09414	500	3000	GAC	3
	09415	M09415	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
 1SLC80275F0001	09450	M09450	100	GAC	1
	09451	M09451	200	GAC	1
	09452	M09452	300	GAC	1
	09453	M09453	400	GAC	1
	09454	M09454	500	GAC	1
	09455	M09455	600	GAC	1
Cover					
 1SLC80276F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80277F0001	Base				
	09490	M09490	100	GAC	1
	09491	M09491	200	GAC	1
	09492	M09492	300	GAC	1
	09493	M09493	400	GAC	1
	09494	M09494	500	GAC	1
	09495	M09495	600	GAC	1
 1SLC80278F0001	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80279F0001	Base				
	09530	M09530	100	GAC	1
	09531	M09531	200	GAC	1
	09532	M09532	300	GAC	1
	09533	M09533	400	GAC	1
	09534	M09534	500	GAC	1
	09535	M09535	600	GAC	1
 1SLC80280F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80281F0001	Base				
	09570	M09570	100	GAC	1
	09571	M09571	200	GAC	1
	09572	M09572	300	GAC	1
	09573	M09573	400	GAC	1
	09574	M09574	500	GAC	1
	09575	M09575	600	GAC	1
 1SLC80282F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

Vertical inside and outside bend adjustable from 0° to 90°

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	09610	M09610	100	GAC	1
	09611	M09611	200	GAC	1
	09612	M09612	300	GAC	1
	09613	M09613	400	GAC	1
	09614	M09614	500	GAC	1
	09615	M09615	600	GAC	1

1SLC80283F0001

Use straight covers for covering.

90° vertical inside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09968	M09968	100	GAC	1
	09969	M09969	200	GAC	1
	09970	M09970	300	GAC	1
	09971	M09971	400	GAC	1
	09972	M09972	500	GAC	1
	09973	M09973	600	GAC	1
	Cover				
	09927	M09927	100	GAC	1
	09928	M09928	200	GAC	1
	09929	M09929	300	GAC	1
	09930	M09930	400	GAC	1
	09931	M09931	500	GAC	1
09932	M09932	600	GAC	1	

1SLC80284F0001

1SLC80285F0001

90° vertical outside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09986	M09986	100	GAC	1
	09987	M09987	200	GAC	1
	09988	M09988	300	GAC	1
	09989	M09989	400	GAC	1
	09990	M09990	500	GAC	1
	09991	M09991	600	GAC	1
	Cover				
	09948	M09948	100	GAC	1
	09949	M09949	200	GAC	1
	09950	M09950	300	GAC	1
	09951	M09951	400	GAC	1
	09952	M09952	500	GAC	1
09953	M09953	600	GAC	1	

1SLC80286F0001

1SLC80287F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80288F0001	Base				
	09650	M09650	200/100	GAC	1
	09651	M09651	300/100	GAC	1
	09652	M09652	300/200	GAC	1
	09653	M09653	400/200	GAC	1
	09654	M09654	400/300	GAC	1
	09655	M09655	500/300	GAC	1
	09656	M09656	500/400	GAC	1
	09657	M09657	600/400	GAC	1
	09658	M09658	600/500	GAC	1
 1SLC80289F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80290F0001	Base				
	09690	M09690	200/100	GAC	1
	09691	M09691	300/100	GAC	1
	09692	M09692	300/200	GAC	1
	09693	M09693	400/200	GAC	1
	09694	M09694	400/300	GAC	1
	09695	M09695	500/300	GAC	1
	09696	M09696	500/400	GAC	1
	09697	M09697	600/400	GAC	1
	09698	M09698	600/500	GAC	1
 1SLC80291F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
 1SLC80292F0001	09730	M09730	200/100	GAC	1
	09731	M09731	300/100	GAC	1
	09732	M09732	300/200	GAC	1
	09733	M09733	400/200	GAC	1
	09734	M09734	400/300	GAC	1
	09735	M09735	500/300	GAC	1
	09736	M09736	500/400	GAC	1
	09737	M09737	600/400	GAC	1
	09738	M09738	600/500	GAC	1
Cover					
 1SLC80293F0001	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

Couplers – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09763	M09763	Coupler	GAC	1/20
	09764	M09764	Horizontal adjustable coupler	GAC	1/20
	09765	M09765	Vertical adjustable coupler	GAC	1/10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09803	M09803	50	GAC	1
	09804	M09804	100	GAC	1
	09805	M09805	200	GAC	1

1SLC80295F0001

Divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-pcs
	09901	M09901	1500	GAC	9

1SLC80296F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 100

Square and cover spacer



1SLC80297F0001

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09904	M09904	Square for fastening brackets – inner	GAC	1/50
09905	M09905	Square for fastening brackets – outer	GAC	1/50

Fastening components



1SLC80298F0001

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100


For fastening squares and spacers and for earth connections.

Industrial cable tray

Cable ladders H 130

Technical details

- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 130 mm
- Standard thickness 1.5 mm and, on request, also available in 2 mm thickness
- **Retainer interaxis 300 mm**
- The profile is moulded in a special way to make the cable tray strong and resistant to bending and twisting
- All corners and branch connections have a wide curving angle (standard 300 mm)
- Products manufactured on automatic CNC (Computerised Numeric Control) profiling plant; with robotic welding
- Products are easy to mount, practical and safe and cables are well ventilated
- Special versions of cable ladders can be supplied on request
- Industrial applications



Industrial cable tray

Cable ladders H 130

Cable ladder

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-pcs
 1SLC80033F0001	09420	M09420	100	3000	GAC	3
	09421	M09421	200	3000	GAC	3
	09422	M09422	300	3000	GAC	3
	09423	M09423	400	3000	GAC	3
	09424	M09424	500	3000	GAC	3
	09425	M09425	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-pcs
 1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs	
 1SLC80275F0001	Base					
	09460	M09460	100	GAC	1	
	09461	M09461	200	GAC	1	
	09462	M09462	300	GAC	1	
	09463	M09463	400	GAC	1	
	09464	M09464	500	GAC	1	
 1SLC80276F0001	Cover					
	09470	M09470	100	GAC	1	
	09471	M09471	200	GAC	1	
	09472	M09472	300	GAC	1	
	09473	M09473	400	GAC	1	
	09474	M09474	500	GAC	1	
	09475	M09475	600	GAC	1	

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80277F0001	Base				
	09500	M09500	100	GAC	1
	09501	M09501	200	GAC	1
	09502	M09502	300	GAC	1
	09503	M09503	400	GAC	1
	09504	M09504	500	GAC	1
	09505	M09505	600	GAC	1
 1SLC80278F0001	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80279F0001	Base				
	09540	M09540	100	GAC	1
	09541	M09541	200	GAC	1
	09542	M09542	300	GAC	1
	09543	M09543	400	GAC	1
	09544	M09544	500	GAC	1
	09545	M09545	600	GAC	1
 1SLC80280F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80281F0001	Base				
	09580	M09580	100	GAC	1
	09581	M09581	200	GAC	1
	09582	M09582	300	GAC	1
	09583	M09583	400	GAC	1
	09584	M09584	500	GAC	1
	09585	M09585	600	GAC	1
 1SLC80282F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

Vertical inside and outside bend adjustable from 0° to 90°

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	09620	M09620	100	GAC	1
	09621	M09621	200	GAC	1
	09622	M09622	300	GAC	1
	09623	M09623	400	GAC	1
	09624	M09624	500	GAC	1
	09625	M09625	600	GAC	1

1SLC80283F0001

Use straight covers for covering.

90° vertical inside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09974	M09974	100	GAC	1
	09975	M09975	200	GAC	1
	09976	M09976	300	GAC	1
	09976	M09976	400	GAC	1
	09978	M09978	500	GAC	1
09979	M09979	600	GAC	1	
	Cover				
	09934	M09934	100	GAC	1
	09935	M09935	200	GAC	1
	09936	M09936	300	GAC	1
	09937	M09937	400	GAC	1
	09938	M09938	500	GAC	1
09939	M09939	600	GAC	1	

1SLC80284F0001

1SLC80285F0001

90° vertical outside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	09992	M09992	100	GAC	1
	09993	M09993	200	GAC	1
	09994	M09994	300	GAC	1
	09995	M09995	400	GAC	1
	09996	M09996	500	GAC	1
09997	M09997	600	GAC	1	
	Cover				
	09955	M09955	100	GAC	1
	09956	M09956	200	GAC	1
	09957	M09957	300	GAC	1
	09958	M09958	400	GAC	1
	09959	M09959	500	GAC	1
09960	M09960	600	GAC	1	

1SLC80286F0001

1SLC80287F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80288F0001	Base				
	09660	M09660	200/100	GAC	1
	09661	M09661	300/100	GAC	1
	09662	M09662	300/200	GAC	1
	09663	M09663	400/200	GAC	1
	09664	M09664	400/300	GAC	1
	09665	M09665	500/300	GAC	1
	09666	M09666	500/400	GAC	1
	09667	M09667	600/400	GAC	1
09668	M09668	600/500	GAC	1	
 1SLC80289F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80290F0001	Base				
	09700	M09700	200/100	GAC	1
	09701	M09701	300/100	GAC	1
	09702	M09702	300/200	GAC	1
	09703	M09703	400/200	GAC	1
	09704	M09704	400/300	GAC	1
	09705	M09705	500/300	GAC	1
	09706	M09706	500/400	GAC	1
	09707	M09707	600/400	GAC	1
09708	M09708	600/500	GAC	1	
 1SLC80291F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80292F0001	Base				
	09740	M09740	200/100	GAC	1
	09741	M09741	300/100	GAC	1
	09742	M09742	300/200	GAC	1
	09743	M09743	400/200	GAC	1
	09744	M09744	400/300	GAC	1
	09745	M09745	500/300	GAC	1
	09746	M09746	500/400	GAC	1
	09747	M09747	600/400	GAC	1
	09748	M09748	600/500	GAC	1
 1SLC80293F0001	Cover				
	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

Coupler – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09766	M09766	Coupler	GAC	1/20
	09767	M09767	Horizontal adjustable	GAC	1/20
	09768	M09768	Vertical adjustable	GAC	1/10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09806	M09806	50	GAC	1
	09807	M09807	100	GAC	1
	09808	M09808	200	GAC	1

1SLC80295F0001

Divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09902	M09902	1500	GAC	2/10

1SLC80296F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Cable ladders H 130

Square and cover spacer



1SLC80297F0001

Product ID	Order code	Description	Finish	Unit/pack-pcs
09903	M09903	Spacer for cover H 50 mm	GAC	1/20
09904	M09904	Square for fastening brackets – inner	GAC	1/50
09905	M09905	Square for fastening brackets – outer	GAC	1/50

Fastening components



1SLC80298F0001

Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
07848	M07848	Round-headed M6x10 screw with nut	GAC	100
07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100
07819	M07819	Hexagonal-headed M10x20 screw with nut	GAC	100

For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 60

Technical details

- IP40 degree of protection with closed base and IP20 with punched base (the grade of protection refers to trays with mounted cover)
- Produced in EN 10111 DD11 MAC carbon steel hot dip Galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 60 mm
- Standard thickness 1.2 mm and, on request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- Considerable mechanical capacity thanks to the special moulding of the profile
- All corners and branch connections have a wide curving angle (standard 300 mm) and different curvatures are available on request
- Products are easy to mount, practical and safe
- Industrial applications



Industrial cable tray

Closed/punched base cable trays H 60


Solid bottom cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
	06800	M06800	100	3000	GAC	3
	06801	M06801	200	3000	GAC	3
	06802	M06802	300	3000	GAC	3
	06803	M06803	400	3000	GAC	3
	06804	M06804	500	3000	GAC	3
	1SLC80302F0001	06805	M06805	600	3000	GAC

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
	06824	M06824	100	3000	GAC	3
	06825	M06825	200	3000	GAC	3
	06826	M06826	300	3000	GAC	3
	06827	M06827	400	3000	GAC	3
	06828	M06828	500	3000	GAC	3
	1SLC80303F0001	06829	M06829	600	3000	GAC

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	1SLC80274F0001	09435	M09435	600	15000	GAC

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
	06858	M06858	100	GAC	1
	06859	M06859	200	GAC	1
	06860	M06860	300	GAC	1
	06861	M06861	400	GAC	1
	06862	M06862	500	GAC	1
	1SLC80275F0001	06863	M06863	600	GAC
Cover					
	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	1SLC80276F0001	09475	M09475	600	GAC

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80306F0001	Base				
	06874	M06874	100	GAC	1
	06875	M06875	200	GAC	1
	06876	M06876	300	GAC	1
	06877	M06877	400	GAC	1
	06878	M06878	500	GAC	1
	06879	M06879	600	GAC	1
 1SLC80307F0001	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80308F0001	Base				
	06896	M06896	100	GAC	1
	06897	M06897	200	GAC	1
	06898	M06898	300	GAC	1
	06999	M06999	400	GAC	1
	07000	M07000	500	GAC	1
	07001	M07001	600	GAC	1
 1SLC80309F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80281F0001	Base				
	07021	M07021	100	GAC	1
	07022	M07022	200	GAC	1
	07023	M07023	300	GAC	1
	07024	M07024	400	GAC	1
	07025	M07025	500	GAC	1
	07026	M07026	600	GAC	1
 1SLC80311F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

Vertical inside and outside bend adjustable from 0° to 90°



1SLC80312F0001


Use straight covers for covering.

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	07046	M07046	100	GAC	1
	07047	M07047	200	GAC	1
	07048	M07048	300	GAC	1
	07049	M07049	400	GAC	1
	07050	M07050	500	GAC	1
	07051	M07051	600	GAC	1

90° vertical inside bend



1SLC80313F0001



1SLC80314F0001

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
	06900	M06900	100	GAC	1
	06901	M06901	200	GAC	1
	06902	M06902	300	GAC	1
	06903	M06903	400	GAC	1
	06904	M06904	500	GAC	1
	06905	M06905	600	GAC	1
Cover					
	09920	M09920	100	GAC	1
	09921	M09921	200	GAC	1
	09922	M09922	300	GAC	1
	09923	M09923	400	GAC	1
	09924	M09924	500	GAC	1
	09925	M09925	600	GAC	1

90° vertical outside bend



1SLC80286F0001



1SLC80316F0001

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
	06924	M06924	100	GAC	1
	06925	M06925	200	GAC	1
	06926	M06926	300	GAC	1
	06927	M06927	400	GAC	1
	06928	M06928	500	GAC	1
	06929	M06929	600	GAC	1
Cover					
	09941	M09941	100	GAC	1
	09942	M09942	200	GAC	1
	09943	M09943	300	GAC	1
	09944	M09944	400	GAC	1
	09945	M09945	500	GAC	1
	09946	M09946	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80317F0001	Base				
	06700	M06700	200/100	GAC	1
	06701	M06701	300/100	GAC	1
	06702	M06702	300/200	GAC	1
	06703	M06703	400/200	GAC	1
	06704	M06704	400/300	GAC	1
	06705	M06705	500/300	GAC	1
	06706	M06706	500/400	GAC	1
	06707	M06707	600/400	GAC	1
	06708	M06708	600/500	GAC	1
 1SLC80318F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80319F0001	Base				
	06730	M06730	200/100	GAC	1
	06731	M06731	300/100	GAC	1
	06732	M06732	300/200	GAC	1
	06733	M06733	400/200	GAC	1
	06734	M06734	400/300	GAC	1
	06735	M06735	500/300	GAC	1
	06736	M06736	500/400	GAC	1
	06737	M06737	600/400	GAC	1
	06738	M06738	600/500	GAC	1
 1SLC80320F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80321F0001	Base				
	06760	M06760	200/100	GAC	1
	06761	M06761	300/100	GAC	1
	06762	M06762	300/200	GAC	1
	06763	M06763	400/200	GAC	1
	06764	M06764	400/300	GAC	1
	06765	M06765	500/300	GAC	1
	06766	M06766	500/400	GAC	1
	06767	M06767	600/400	GAC	1
	06768	M06768	600/500	GAC	1
 1SLC80322F0001	Cover				
	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

Coupler – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09760	M09760	Coupler	GAC	1/20
	09761	M09761	Horizontal adjustable joint	GAC	1/20
	09762	M09762	Vertical adjustable joint	GAC	1/10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09800	M09800	50	GAC	1
	09801	M09801	100	GAC	1
	09802	M09802	200	GAC	1

1SLC80295F0001

Divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09910	M09910	1500	GAC	9

1SLC80296F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 60

Square and cover spacer



1SLC80297F0001

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09903	M09903	Spacer for cover H 50 mm	GAC	1/20
	09905	M09905	Square for fastening brackets – outer	GAC	1/50

Fastening components



1SLC80298F0001

	Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	GAC	100
	07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100


For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 100

Technical details

- IP40 degree of protection with closed base and IP20 with punched base
- Produced in EN 10111 DD11 MAC carbon steel hot dip galvanized after fabrication in compliance with
- UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 100 mm
- Standard thickness 1.2 mm and, upon request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- All corners and branch connections have a wide curving angle (standard 300 mm) and variations are available on request
- Products are easy to mount, practical and safe
- Industrial applications




Industrial cable tray

Closed/punched base cable trays H 100

Closed base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80302F0001	06808	M06808	100	3000	GAC	3
	06809	M06809	200	3000	GAC	3
	06810	M06810	300	3000	GAC	3
	06811	M06811	400	3000	GAC	3
	06812	M06812	500	3000	GAC	3
	06813	M06813	600	3000	GAC	3

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80303F0001	06830	M06830	100	15000	GAC	3
	06831	M06831	200	15000	GAC	3
	06832	M06832	300	15000	GAC	3
	06833	M06833	400	15000	GAC	3
	06834	M06834	500	15000	GAC	3
	06835	M06835	600	15000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
 1SLC80304F0001	06850	M06850	100	GAC	1
	06851	M06851	200	GAC	1
	06852	M06852	300	GAC	1
	06853	M06853	400	GAC	1
	06854	M06854	500	GAC	1
	06855	M06855	600	GAC	1
Cover					
 1SLC80305 F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80306F0001	Base				
	06882	M06882	100	GAC	1
	06883	M06883	200	GAC	1
	06884	M06884	300	GAC	1
	06885	M06885	400	GAC	1
	06886	M06886	500	GAC	1
	06887	M06887	600	GAC	1
	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80308F0001	Base				
	07005	M07005	100	GAC	1
	07006	M07006	200	GAC	1
	07007	M07007	300	GAC	1
	07008	M07008	400	GAC	1
	07009	M07009	500	GAC	1
 1SLC80309F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80310F0001	Base				
	07030	M07030	100	GAC	1
	07031	M07031	200	GAC	1
	07032	M07032	300	GAC	1
	07033	M07033	400	GAC	1
	07034	M07034	500	GAC	1
 1SLC80311F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

Vertical inside and outside bend adjustable from 0° to 90°

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	07055	M07055	100	GAC	1
	07056	M07056	200	GAC	1
	07057	M07057	300	GAC	1
	07058	M07058	400	GAC	1
	07059	M07059	500	GAC	1
	07060	M07060	600	GAC	1

1SLC80312F0001

Use straight covers for covering.

90° vertical inside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	06908	M06908	100	GAC	1
	06909	M06909	200	GAC	1
	06910	M06910	300	GAC	1
	06911	M06911	400	GAC	1
	06912	M06912	500	GAC	1
	06913	M06913	600	GAC	1
	Cover				
	09927	M09927	100	GAC	1
	09928	M09928	200	GAC	1
	09929	M09929	300	GAC	1
	09930	M09930	400	GAC	1
	09931	M09931	500	GAC	1
09932	M09932	600	GAC	1	

90° vertical outside bend

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
	Base				
	06932	M06932	100	GAC	1
	06933	M06933	200	GAC	1
	06934	M06934	300	GAC	1
	06935	M06935	400	GAC	1
	06936	M06936	500	GAC	1
	06937	M06937	600	GAC	1
	Cover				
	09948	M09948	100	GAC	1
	09949	M09949	200	GAC	1
	09950	M09950	300	GAC	1
	09951	M09951	400	GAC	1
	09952	M09952	500	GAC	1
09953	M09953	600	GAC	1	

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80317F0001	Base				
	06709	M06709	200/100	GAC	1
	06710	M06710	300/100	GAC	1
	06711	M06711	300/200	GAC	1
	06712	M06712	400/200	GAC	1
	06713	M06713	400/300	GAC	1
	06714	M06714	500/300	GAC	1
	06715	M06715	500/400	GAC	1
	06716	M06716	600/400	GAC	1
	06717	M06717	600/500	GAC	1
 1SLC80318F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80319F0001	Base				
	06739	M06739	200/100	GAC	1
	06740	M06740	300/100	GAC	1
	06741	M06741	300/200	GAC	1
	06742	M06742	400/200	GAC	1
	06743	M06743	400/300	GAC	1
	06744	M06744	500/300	GAC	1
	06745	M06745	500/400	GAC	1
	06746	M06746	600/400	GAC	1
	06747	M06747	600/500	GAC	1
 1SLC80320F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80321F0001	Base				
	06769	M06769	200/100	GAC	1
	06770	M06770	300/100	GAC	1
	06771	M06771	300/200	GAC	1
	06772	M06772	400/200	GAC	1
	06773	M06773	400/300	GAC	1
	06774	M06774	500/300	GAC	1
	06775	M06775	500/400	GAC	1
	06776	M06776	600/400	GAC	1
	06777	M06777	600/500	GAC	1
 1SLC80322F0001	Cover				
	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

Coupler – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09763	M09763	Coupler	GAC	20
	09764	M09764	Horizontal adjustable joint	GAC	20
	09765	M09765	Vertical adjustable joint	GAC	10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09803	M09803	50	GAC	1
	09804	M09804	100	GAC	1
	09805	M09805	200	GAC	1

1SLC80295F0001

Divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09911	M09911	1500	GAC	9

1SLC80296F0001

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 100

Square and cover spacer



15LC80297F0001

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09903	M09903	Spacer for cover H 50 mm	GAC	1/20
	09905	M09905	Square for fastening brackets – outer	GAC	1/50

Fastening components



15LC80298F0001

	Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	GAC	100
	07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100


For fastening squares and spacers and for earth connections.

Industrial cable tray

Closed/punched base cable trays H 130

Technical details

- IP40 degree of protection with closed base and IP20 with punched base (the grade of protection refers to trays with mounted cover)
- Produced in EN 10111 DD11 MAC carbon steel hot dip galvanized after fabrication in compliance with UNI E 14.07.000.0 Standard project complying with CEI 7-6 Standard and BS 729
- Standard length 3 metres
- Standard height 130 mm
- Standard thickness 1.2 mm and, upon request, also available in 1.5 and 2 mm thickness
- Resistance to atmospheric and chemical (water, saline solutions, acids and mineral and oil bases) agents
- Considerable mechanical capacity thanks to the special moulding of the profile
- Other dimensions available upon request
- Products are easy to mount, practical and safe
- Industrial applications



Industrial cable tray

Closed/punched base cable trays H 130


Solid base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80302F0001	06816	M06816	100	3000	GAC	3
	06817	M06817	200	3000	GAC	3
	06818	M06818	300	3000	GAC	3
	06819	M06819	400	3000	GAC	3
	06820	M06820	500	3000	GAC	3
	06821	M06821	600	3000	GAC	3

Punched base cable tray

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80303F0001	06838	M06838	100	3000	GAC	3
	06839	M06839	200	3000	GAC	3
	06840	M06840	300	3000	GAC	3
	06842	M06842	400	3000	GAC	3
	06842	M06842	500	3000	GAC	3
	06843	M06843	600	3000	GAC	3

Snap-on cover

	Product ID	Order code	Cable ladder base (mm)	Length (mm)	Finish	Unit/pack-m
 1SLC80274F0001	09430	M09430	100	15000	GAC	3
	09431	M09431	200	15000	GAC	3
	09432	M09432	300	15000	GAC	3
	09433	M09433	400	15000	GAC	3
	09434	M09434	500	15000	GAC	3
	09435	M09435	600	15000	GAC	3

90° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base					
 1SLC80304F0001	06866	M06866	100	GAC	1
	06867	M06867	200	GAC	1
	06868	M06868	300	GAC	1
	06869	M06869	400	GAC	1
	06870	M06870	500	GAC	1
	06871	M06871	600	GAC	1
	Cover				
 1SLC80305F0001	09470	M09470	100	GAC	1
	09471	M09471	200	GAC	1
	09472	M09472	300	GAC	1
	09473	M09473	400	GAC	1
	09474	M09474	500	GAC	1
	09475	M09475	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

45° horizontal corner

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80306F0001	Base				
	06890	M06890	100	GAC	1
	06891	M06891	200	GAC	1
	06892	M06892	300	GAC	1
	06893	M06893	400	GAC	1
	06894	M06894	500	GAC	1
	06895	M06895	600	GAC	1
 1SLC80307F0001	Cover				
	09510	M09510	100	GAC	1
	09511	M09511	200	GAC	1
	09512	M09512	300	GAC	1
	09513	M09513	400	GAC	1
	09514	M09514	500	GAC	1
	09515	M09515	600	GAC	1

Horizontal tee

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80308F0001	Base				
	07013	M07013	100	GAC	1
	07014	M07014	200	GAC	1
	07015	M07015	300	GAC	1
	07016	M07016	400	GAC	1
	07017	M07017	500	GAC	1
	07018	M07018	600	GAC	1
 1SLC80309F0001	Cover				
	09550	M09550	100	GAC	1
	09551	M09551	200	GAC	1
	09552	M09552	300	GAC	1
	09553	M09553	400	GAC	1
	09554	M09554	500	GAC	1
	09555	M09555	600	GAC	1

Horizontal cross

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80310F0001	Base				
	07038	M07038	100	GAC	1
	07039	M07039	200	GAC	1
	07040	M07040	300	GAC	1
	07041	M07041	400	GAC	1
	07042	M07042	500	GAC	1
	07043	M07043	600	GAC	1
 1SLC80311F0001	Cover				
	09590	M09590	100	GAC	1
	09591	M09591	200	GAC	1
	09592	M09592	300	GAC	1
	09593	M09593	400	GAC	1
	09594	M09594	500	GAC	1
	09595	M09595	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

Vertical inside and outside bend adjustable from 0° to 90°



1SLC80312F0001


Use straight covers for covering.

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
07063	M07063	100	GAC	1
07064	M07064	200	GAC	1
07065	M07065	300	GAC	1
07066	M07066	400	GAC	1
07067	M07067	500	GAC	1
07068	M07068	600	GAC	1

90° vertical inside bend



1SLC80313F0001



1SLC80314F0001

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
06916	M06916	100	GAC	1
06917	M06917	200	GAC	1
06918	M06918	300	GAC	1
06919	M06919	400	GAC	1
06920	M06920	500	GAC	1
06921	M06921	600	GAC	1
Cover				
09934	M09934	100	GAC	1
09935	M09935	200	GAC	1
09936	M09936	300	GAC	1
09937	M09937	400	GAC	1
09938	M09938	500	GAC	1
09939	M09939	600	GAC	1

90° vertical outside bend



1SLC80315F0001



1SLC80316F0001

Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
Base				
06940	M06940	100	GAC	1
06941	M06941	200	GAC	1
06942	M06942	300	GAC	1
06943	M06943	400	GAC	1
06944	M06944	500	GAC	1
06945	M06945	600	GAC	1
Cover				
09955	M09955	100	GAC	1
09956	M09956	200	GAC	1
09957	M09957	300	GAC	1
09958	M09958	400	GAC	1
09959	M09959	500	GAC	1
09960	M09960	600	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

Straight reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80317F0001	Base				
	06718	M06718	200/100	GAC	1
	06719	M06719	300/100	GAC	1
	06720	M06720	300/200	GAC	1
	06721	M06721	400/200	GAC	1
	06722	M06722	400/300	GAC	1
	06723	M06723	500/300	GAC	1
	06724	M06724	500/400	GAC	1
	06725	M06725	600/400	GAC	1
	06726	M06726	600/500	GAC	1
 1SLC80318F0001	Cover				
	09670	M09670	200/100	GAC	1
	09671	M09671	300/100	GAC	1
	09672	M09672	300/200	GAC	1
	09673	M09673	400/200	GAC	1
	09674	M09674	400/300	GAC	1
	09675	M09675	500/300	GAC	1
	09676	M09676	500/400	GAC	1
	09677	M09677	600/400	GAC	1
	09678	M09678	600/500	GAC	1

Left reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80319F0001	Base				
	06748	M06748	200/100	GAC	1
	06749	M06749	300/100	GAC	1
	06750	M06750	300/200	GAC	1
	06751	M06751	400/200	GAC	1
	06752	M06752	400/300	GAC	1
	06753	M06753	500/300	GAC	1
	06754	M06754	500/400	GAC	1
	06755	M06755	600/400	GAC	1
	06756	M06756	600/500	GAC	1
 1SLC80320F0001	Cover				
	09710	M09710	200/100	GAC	1
	09711	M09711	300/100	GAC	1
	09712	M09712	300/200	GAC	1
	09713	M09713	400/200	GAC	1
	09714	M09714	400/300	GAC	1
	09715	M09715	500/300	GAC	1
	09716	M09716	500/400	GAC	1
	09717	M09717	600/400	GAC	1
	09718	M09718	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

Right reducer

	Product ID	Order code	Cable ladder base (mm)	Finish	Unit/pack-pcs
 1SLC80321F0001	Base				
	06778	M06778	200/100	GAC	1
	06779	M06779	300/100	GAC	1
	06780	M06780	300/200	GAC	1
	06781	M06781	400/200	GAC	1
	06782	M06782	400/300	GAC	1
	06783	M06783	500/300	GAC	1
	06784	M06784	500/400	GAC	1
	06785	M06785	600/400	GAC	1
	06786	M06786	600/500	GAC	1
 1SLC80322F0001	Cover				
	09750	M09750	200/100	GAC	1
	09751	M09751	300/100	GAC	1
	09752	M09752	300/200	GAC	1
	09753	M09753	400/200	GAC	1
	09754	M09754	400/300	GAC	1
	09755	M09755	500/300	GAC	1
	09756	M09756	500/400	GAC	1
	09757	M09757	600/400	GAC	1
	09758	M09758	600/500	GAC	1

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

Coupler – Includes 2 plates complete with screws and nuts.

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09766	M09766	Coupler	GAC	1/20
	09767	M09767	Horizontal adjustable joint	GAC	1/20
	09768	M09768	Vertical adjustable joint	GAC	1/10

1SLC80294F0001

Couplers for left and right reduction

	Product ID	Order code	For reductions of (mm)	Finish	Unit/pack-pcs
	09806	M09806	50	GAC	1
	09807	M09807	100	GAC	1
	09808	M09808	200	GAC	1

1SLC80295F0001

Divider

	Product ID	Order code	Length (mm)	Finish	Unit/pack-m
	09912	M09912	1500	GAC	2/10

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 212-216.

Industrial cable tray

Closed/punched base cable trays H 130

Square and cover spacer



1SLC80297F0001

	Product ID	Order code	Description	Finish	Unit/pack-pcs
	09903	M09903	Spacer for cover H 50 mm	GAC	20
	09905	M09905	Square for fastening brackets – outer	GAC	50

Fastening components



1SLC80298F0001

	Product ID	Order code	Description (mm)	Finish	Unit/pack-pcs
	07848	M07848	Round-headed M6x10 screw with nut	GAC	100
	07818	M07818	Hexagonal-headed M8x16 screw with nut	GAC	100


For fastening squares and spacers and for earth connections.

Support systems for industrial trunking

Support elements

Technical details



- Colors:
 - Galvanized
 - RAL 7035 grey
 - Bright blue
- Produced in hot dip Galvanized sendzimir steel plate and in hot dip Galvanized after fabrication steel plate, in compliance with UNI E 14.07.000.0 Standard
- Painted with thermosetting, epoxy-polyester powders; average thickness 70-80 micron, after fabrication on hot dip Galvanized plate
- Complete range of accessories for suspension and anchorage specially designed to be modular and highly versatile
- Industrial application



Support systems for industrial trunking

Support elements

Galvanized bracket – Can be fixed directly to the wall or on the “C” profile art. 07992, 07993 and 08861 using plate art. 07995.

	Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/ pack-pcs
 1SLC80326F0001	07901	M07901	75	Sendzimir Galvanized	600	40
	07902	M07902	100	Sendzimir Galvanized	600	30
	07903	M07903	150	Sendzimir Galvanized	600	30
	07904	M07904	200	Sendzimir Galvanized	650	20
	07905	M07905	300	Sendzimir Galvanized	650	20
	07906	M07906	400	Hot dip Galvanized after fabrication	900	10
	07907	M07907	500	Hot dip Galvanized after fabrication	1100	10
 1SL7911A00 1SL7912A00 1SL7913A00 1SL7914A00 1SL7915A00 1SL7916A00 1SL7917A00	1SL7911A00	1SL7911A00	75	RAL 7035 grey	600	40
	1SL7912A00	1SL7912A00	100	RAL 7035 grey	600	30
	1SL7913A00	1SL7913A00	150	RAL 7035 grey	600	30
	1SL7914A00	1SL7914A00	200	RAL 7035 grey	650	20
	1SL7915A00	1SL7915A00	300	RAL 7035 grey	650	20
	1SL7916A00	1SL7916A00	400	RAL 7035 grey	900	10
	1SL7917A00	1SL7917A00	500	RAL 7035 grey	1100	10
 08801 08802 08803 08804 08805 08806 08807	08801	M08801	75	Bright blue	600	40
	08802	M08802	100	Bright blue	600	30
	08803	M08803	150	Bright blue	600	30
	08804	M08804	200	Bright blue	650	20
	08805	M08805	300	Bright blue	650	20
	08806	M08806	400	Bright blue	900	10
	08807	M08807	500	Bright blue	1100	10
 1SLM001020A0020 1SLM001020A0021 1SLM001020A0022 1SLM001020A0023 1SLM001020A0024 1SLM001020A0025	1SLM001020A0020	1SLM001020A0020	75/100	Stainless steel	600	30
	1SLM001020A0021	1SLM001020A0021	150	Stainless steel	600	30
	1SLM001020A0022	1SLM001020A0022	200	Stainless steel	650	20
	1SLM001020A0023	1SLM001020A0023	300	Stainless steel	650	20
	1SLM001020A0024	1SLM001020A0024	400	Stainless steel	900	10
1SLM001020A0025	1SLM001020A0025	500	Stainless steel	1100	10	

N.B.: You can position the trunking without dropping it using the tongue.

Chair bracket – Can be used with “C” profile art. 07992, 07993 or 08861.

	Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/ pack-pcs
 07908 07909 1SL7918A00 1SL7919A00 08811 08812	07908	M07908	75/100/150	Sendzimir Galvanized	600	10
	07909	M07909	200/300	Sendzimir Galvanized	650	10
	1SL7918A00	1SL7918A00	75/100/150	RAL 7035 grey	600	10
	1SL7919A00	1SL7919A00	200/300	RAL 7035 grey	650	10
	08811	M08811	75/100/150	Bright blue	600	10
	08812	M08812	200/300	Bright blue	650	10

1SLC80328F0001

Overall dimensions pages 217-222.

Support systems for industrial trunking

Support elements

Light pressed bracket (sendzimir galvanized) – Can be used with profile art. 07960.

	Product ID	Order code	Trunking base (mm)	Finish	Capacity (N)	Unit/pack-pcs
 1SLC80329F0001	07671	M07671	75	Galvanized	1000	10
	07672	M07672	100	Galvanized	1000	10
	07673	M07673	150	Galvanized	750	10
	07674	M07674	200	Galvanized	600	10
	07675	M07675	300	Galvanized	450	10
	07676	M07676	400	Galvanized	400	5
	07677	M07677	500	Galvanized	300	5
	1SL7681A00	1SL7681A00	75	RAL 7035 grey	1000	10
	1SL7682A00	1SL7682A00	100	RAL 7035 grey	1000	10
	1SL7683A00	1SL7683A00	150	RAL 7035 grey	750	10
1SL7684A00	1SL7684A00	200	RAL 7035 grey	600	10	
1SL7685A00	1SL7685A00	300	RAL 7035 grey	450	10	
1SL7686A00	1SL7686A00	400	RAL 7035 grey	400	5	
1SL7687A00	1SL7687A00	500	RAL 7035 grey	300	5	
08881	M08881	75	Bright blue	1000	10	
08882	M08882	100	Bright blue	1000	10	
08883	M08883	150	Bright blue	750	10	
08884	M08884	200	Bright blue	600	10	
08885	M08885	300	Bright blue	450	10	
08886	M08886	400	Bright blue	400	5	
08887	M08887	500	Bright blue	300	5	

Heavy bracket (hot dip galvanized after fabrication) – Can be used directly to the wall or with profile art. 07956 and anchoring screws art. 07851.

	Product ID	Order code	Trunkingbase (mm)	Finish	Capacity (N)	Unit/pack-pcs
 1SLC80330F0001	07785	M07785	75/100/150	GAC	1800	30
	07786	M07786	200	GAC	1800	20
	07787	M07787	300	GAC	1800	20
	07788	M07788	400	GAC	2000	10
	07789	M07789	500	GAC	2000	10
	07790	M07790	600	GAC	2000	10

Alfen profile bracket (hot dip galvanized after fabrication) – Can be used with profile art. 07956 and anchorage screws art. 07851.

	Product ID	Order code	Trunkingbase (mm)	Finish	Capacity (N)	Unit/pack-pcs
 1SLC80331F0001	09770	M09770	150	GAC	2000	1
	09771	M09771	250	GAC	1700	1
	09772	M09772	350	GAC	1500	1
	09773	M09773	450	GAC	1300	1
	09774*	M09774*	550	GAC	2500	1
	09775*	M09775*	650	GAC	2200	1
	09776*	M09776*	750	GAC	2500	1
	09777*	M09777*	850	GAC	2400	1
	09778*	M09778*	950	GAC	2300	1
	09779*	M09779*	1050	GAC	2200	1

* Reinforced bracket.

GAC = Hot dip galvanized after fabrication.

Overall dimensions pages 217-222.

Support systems for industrial trunking

Support elements

Cross piece for fastening to the ceiling



1SLC80332F0001

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07941	M07941	75	Galvanized	40
07942	M07942	100	Galvanized	30
07943	M07943	150	Galvanized	30
07944	M07944	200	Galvanized	20
07945	M07945	300	Galvanized	20
1SL7951A00	1SL7951A00	75	RAL 7035 grey	40
1SL7952A00	1SL7952A00	100	RAL 7035 grey	30
1SL7953A00	1SL7953A00	150	RAL 7035 grey	30
1SL7954A00	1SL7954A00	200	RAL 7035 grey	20
1SL7955A00	1SL7955A00	300	RAL 7035 grey	20
08831	M08831	75	Bright blue	40
08832	M08832	100	Bright blue	30
08833	M08833	150	Bright blue	30
08834	M08834	200	Bright blue	20
08835	M08835	300	Bright blue	20

Support for suspension



1SLC80333F0001

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07961	M07961	75	Galvanized	40
07962	M07962	100	Galvanized	30
07963	M07963	150	Galvanized	30
07964	M07964	200	Galvanized	20
07965	M07965	300	Galvanized	20
1SL7971A00	1SL7971A00	75	RAL 7035 grey	40
1SL7972A00	1SL7972A00	100	RAL 7035 grey	30
1SL7973A00	1SL7973A00	150	RAL 7035 grey	30
1SL7974A00	1SL7974A00	200	RAL 7035 grey	20
1SL7975A00	1SL7975A00	300	RAL 7035 grey	20
08841	M08841	75	Bright blue	40
08842	M08842	100	Bright blue	30
08843	M08843	150	Bright blue	30
08844	M08844	200	Bright blue	20
08845	M08845	300	Bright blue	20

Overall dimensions pages 217-222.

Support systems for industrial trunking

Support elements

Cross piece with conduit-tightening collar Ø 22 mm



1SLC80334F0001

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07921	M07921	75	Galvanized	40
07922	M07922	100	Galvanized	30
07923	M07923	150	Galvanized	30
07924	M07924	200	Galvanized	20
07925	M07925	300	Galvanized	20
1SL7931A00	1SL7931A00	75	RAL 7035 grey	40
1SL7932A00	1SL7932A00	100	RAL 7035 grey	30
1SL7933A00	1SL7933A00	150	RAL 7035 grey	30
1SL7934A00	1SL7934A00	200	RAL 7035 grey	20
1SL7935A00	1SL7935A00	300	RAL 7035 grey	20
08821	M08821	75	Bright blue	40
08822	M08822	100	Bright blue	30
08823	M08823	150	Bright blue	30
08824	M08824	200	Bright blue	20
08825	M08825	300	Bright blue	20

Plate with conduit-tightening collar Ø 22 mm – Suitable for ceiling suspension and branch connection.



1SLC80335F0001

Product ID	Order code	Trunking base (mm)	Finish	Unit/pack-pcs
07978	M07978	For conduit with Ø 22 mm	Galvanized	40
1SL7979A00	1SL7979A00	For conduit with Ø 22 mm	RAL 7035 grey	40
08854	M08854	For conduit with Ø 22 mm	Bright blue	40

Conduit Ø 22 mm – For suspension or branch connection: 3-metre bars.



1SLC80336F0001



Product ID	Order code	Description	Finish	Unit/pack-pcs
07982	M07982	Conduit Ø 22 mm	Galvanized	10 bars
1SL7983A00	1SL7983A00	Conduit Ø 22 mm	RAL 7035 grey	10 bars
08862	M08862	Conduit Ø 22 mm	Bright blue	10 bars

Overall dimensions pages 222-223.

Support systems for industrial trunking

Support elements

Profile for suspensions

	Product ID	Order code	Dimensions (mm)	Length (mm)	Description	Finish	Unit/ pack-pcs
	1SL9895A00	1SL9895A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm perforated	Sendzimir	6
	07956	M07956	41x41x2,5	2000	Anchor screw profile 41x41x2000mm perforated	Hot dip galvanized	4
	1SL9896A00	1SL9896A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm plain cover	Hot dip galvanized	6
	07926	M07926	41x41x2,5	2000	Anchor screw profile 41x41x2000mm plain cover	Hot dip galvanized	4
	1SL9897A00	1SL9897A00	41x41x2,5	3000	Anchor screw profile 41x41x3000mm plain cover	Hot dip galvanized	6
	07927	M07927	82x41x2,5	2000	Anchor screw profile 82x41x2000mm plain cover	Hot dip galvanized	2
	07957	M07957	40x28x2	2000	"L" punched profile 40x28x2000	Sendzimir	10
	1SL7947A00	1SL7947A00	40x28x2	2000	"L" punched profile 40x28x2000	RAL 7035 grey	10
	08863	M08863	40x28x2	2000	"L" punched profile 40x28x2000	Bright blue	10
	07958	M07958	40x28x2	2000	"U" punched profile 40x28x2000	Sendzimir	4
	1SL7948A00	1SL7948A00	40x28x2	2000	"U" punched profile 40x28x2000	RAL 7035 grey	4
	08864	M08864	40x28x2	2000	"U" punched profile 40x28x2000	Bright blue	4
	07959	M07959	56x36x3	2000	"U" punched profile 56x36x2000	Hot dip galvanized	4
	07992*	M07992*	44x25x2	2000	"C" punched profile 44x25x2000	Sendzimir	4
	1SL7993A00*	1SL7993A00*	44x25x2	2000	"C" punched profile 44x25x2000	RAL 7035 grey	4
	08861*	M08861*	44x25x2	2000	"C" punched profile 44x25x2000	Bright blue	4
	1SLM001020A0026	1SLM001020A0026	44x29x2	2000	"U" punched profile 44x29x2000	Stainless steel	4

* Use plate art. 07995 for fastening brackets.

Tip of the shelf (nut included) – To be used in combination with "U" punched profile 40x29x20 00 (Product ID: 1SLM001020A0026).

	Product ID	Order code	Trunking base (mm)	Finish	Unit/ pack-pcs
	1SLM001020A0017	1SLM001020A0017	75/100	X304	1
	1SLM001020A0018	1SLM001020A0018	150	X304	1
	1SLM001020A0019	1SLM001020A0019	200	X304	1

1SLM001020A0017

Note: You can position the trunking without dropping it using the tongue.

Light pressed bracket profile – Length 1000 mm.

	Product ID	Order code	Dimensions (mm)	Description	Finish	Unit/ pack-pcs
	07960	M07960	60x20x2	Light bracket profile	Galvanized	10

1SLC80338F0001

Overall dimensions pages 178 & 179.

Support systems for industrial trunking

Support elements

Punched profile for suspensions

Product ID	Order code	Description	Type	Shape	Blocking
1SL9895A00	1SL9895A00	Anchor screw profile 41x41x3000 mm perforated Sendzimir	Z		Anchor
07956	M07956	Anchor screw profile 41x41x2000 mm perforated hot dip galvanized	GAC		Anchor
1SL9896A00	1SL9896A00	Anchor screw profile 41x41x3000 mm perforated hot dip galvanized	GAC		Anchor
07926	M07926	Anchor screw profile 41x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
1SL9897A00	1SL9897A00	Anchor screw profile 41x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
07927	M07927	Anchor screw double profile 82x41x2000 mm plain cover hot dip galvanized	GAC		Anchor
07957	M07957	"L" punched profile 40x28x2000 Sendzimir	Z		Profile screw
1SL7947A00	1SL7947A00	"L" punched profile 40x28x2000 RAL 7035 grey	RAL 7035		Profile screw
08863	M08863	"L" punched profile 40x28x2000 Bright blue	BLU		Profile screw
07958	M07958	"U" punched profile 40x28x2000 Sendzimir	RAL 7035		Profile screw
1SL7948A00	1SL7948A00	"U" punched profile 40x28x2000 RAL 7035 grey	RAL 7035		Profile screw
08864	M08864	"U" punched profile 40x28x2000 Bright blue	BLU		Profile screw
07959	M07959	"U" punched profile 56x36x2000 hot dip galvanized	GAC		Profile screw
07992	M07992	"C" punched profile 44x25x2000 Sendzimir	Z		Blocking plate
1SL7993A00	1SL7993A00	"C" punched profile 44x25x2000 RAL 7035 grey	RAL 7035		Blocking plate
08825	M08825	"C" punched profile 44x25x2000 Bright blue	BLU		Blocking plate

Legend:

Z	= Galvanized
GAC	= Hot dip galvanized after fabrication
BLU	= Bright blue
RAL 7035	= Grey RAL 7035
EG	= Electro galvanized

Overall dimensions pages 178-179.

Support systems for industrial trunking

Support elements

Ceiling anchorage plate

	Product ID	Order code	Description	Color	Unit/pack-pcs
	07986	M07986	Single plate 44x25x2 a C hot dip galvanized	GAC	20
	1SL7987A00	1SL7987A00	Single plate 44x25x2 a C RAL 7035	RAL 7035	20
	08851	M08851	Single plate 44x25x2 a C blu	BLU	20
1SLC80340F0001	07988	M07988	Double plate 44x25x2 a C Hot dip galvanized	GAC	10
	1SL7989A00	1SL7989A00	Double plate 44x25x2 a C RAL 7035	RAL 7035	10
	08852	M08852	Double plate 44x25x2 a C blu	BLU	10
	07984	M07984	Single plate 41x41x2,5 Galvanized	GAC	20
	07949	M07949	Double plate 41x41x2,5 Galvanized	GAC	20
	07990	M07990	Adjustable plate 44x25x2 a C Galvanized	Z	20
1SLC80342F0001	1SL7991A00	1SL7991A00	Adjustable plate 44x25x2 a C RAL 7035	RAL 7035	20
	08853	M08853	Adjustable plate 44x25x2 a C blu	BLU	20
	07985	M07985	Adjustable heavy plate 41x41x2,5 Galvanized	GAC	10
	1SLM001020A0027	1SLM001020A0027	Adjustable plate for profile 1SLM001020A0026	X304	20
	1SLC80342F0001				
	1SLC80343F0001				

GAC = Hot dip galvanized after fabrication.
X304 = Stainless steel.

Overall dimensions pages 178-179.

Punched bar – In 20-metre roll.

	Product ID	Order code	Dimensions BxD (mm)	Color	Unit/pack - m
	07996	M07996	40x1,2	Hot dip galvanized	20
	07997	M07997	20x1	Hot dip galvanized	20
1SLC80344F0001					

Flat punched profile – Length 2 m.

	Product ID	Order code	Dimensions BxD (mm)	Color	Unit/pack - m
	07966	M07966	30x3	Hot dip galvanized	20
	1SLC80345F0001				

Overall dimensions page 222.

Support systems for industrial trunking

Support elements

Horizontal punched fastening plate – Thickness 4 mm.



	Product ID	Order code	Description	Length (mm)	Color	Unit/pack-pcs
	07437	M07437	Plate with 1 hole	40	Hot dip galvanized	25
	07967	M07967	Plate with 2 holes	75	Hot dip galvanized	25
	07976	M07976	Plate with 3 holes	115	Hot dip galvanized	10
	07968	M07968	Plate with 4 holes	155	Hot dip galvanized	10

1SLC80344F0001

Horizontal punched fastening plate – Thickness 4 mm.



	Product ID	Order code	Description	Color	Unit/pack-pcs
	07969	M07969	Plate with 2 holes	Hot dip galvanized	25
	07977	M07977	Plate with 3 holes	Hot dip galvanized	10
	07970	M07970	Plate with 4 holes	Hot dip galvanized	10

1SLC80347F0001

Horizontal 90°, tee and cross punched fastening plate – Thickness 4 mm.



	Product ID	Order code	Description	Color	Unit/pack-pcs
	07980	M07980	90° plate	Hot dip galvanized	10
	07981	M07981	Tee plate	Hot dip galvanized	10
	07438	M07438	Cross plate	Hot dip galvanized	10

1SLC80348F0001

Overall dimensions pages 219-220.

Horizontal 90°, tee and cross punched fastening plate – Thickness 4 mm.



	Product ID	Order code	Description	Color	Unit/pack-pcs
	07849	M07849	Round-headed M8x16 screw complete with nut and washer	Electrolytic Galvanized	100
	07818	M07818	Hexagonal-headed M8x16 screw complete with nut and washer	Electrolytic Galvanized	100
	07819	M07819	Hexagonal-headed M10x20 screw complete with nut and washer	Electrolytic Galvanized	100
	07439	M07439	M6 nut in cage	Electrolytic Galvanized	100
	07853	M07853	M6 nut in cage	Electrolytic Galvanized	100

1SLC80349F0001

Overall dimensions pages 177.

Support systems for industrial trunking

Support elements

Anchor screws

	Product ID	Order code	Description	Color	Unit/pack-pcs
 1SLC80350F0001	07448	M07448	M8x30 male screw with nut	Electrolytic Galvanized	50
	07851	M07851	M10x30 male screw with nut	Electrolytic Galvanized	50
	07826	M07826	M8 female screw	Electrolytic Galvanized	50
	07827	M07827	M10 female screw	Electrolytic Galvanized	50
	07828	M07828	M8 female screw with spring	Electrolytic Galvanized	50
	07830	M07830	M10 female screw with spring	Electrolytic Galvanized	50

Fixing elements

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLC80339F0001	07995*	M07995	Blocking plate	ElectroGalvanized (EG)	50

* Blocking plate to be used within the "C" punched profile (art. 07992, 07993 & 08861) for shelf fixing.

Thread rod (ATR) – 1-metre length.

	Product ID	Order code	Description	Color	Unit/pack-pcs
 1SLC80351F0001	07806	M07806	M8 bar	Electrolytic Galvanized	10
	07807	M07807	M10 bar	Electrolytic Galvanized	10
	1SLM001020A0028	1SLM001020A0028	M8 bar	Stainless steel	10

Coupler

	Product ID	Order code	Description	Color	Unit/pack-pcs
 1SLC80351F0001	07808	M07808	M8 sleeve	Electrolytic Galvanized	50
	07809	M07809	M10 sleeve	Electrolytic Galvanized	50
	1SLM001020A0029	1SLM001020A0029	M8 sleeve	Stainless steel	50

Wall supports

	Product ID	Order code	Description	Finish	Unit/pack-pcs
 1SLM001020A0030	1SLM001020A0030	1SLM001020A0030	Wall support for H35 wire trays	Stainless steel	4
	1SLM001020A0031	1SLM001020A0031	Wall support for H50 & H75 wire trays	Stainless steel	6
 1SLM001020A0031					





Technical details and assembly instructions

IK degrees of protection and self-extinguishing tests

Degrees of mechanical shock protection IK conforming to CEI EN 50102 Standard

IK	Shock energy (Joule)	IK	Shock energy (Joule)
00	not protected	06	1 Joule
01	0,15 Joules	07	2 Joules
02	0,2 Joules	08	5 Joules
03	0,35 Joules	09	10 Joules
04	0,5 Joules	10	20 Joules
05	0,7 Joules		

Self-extinguishing degrees of protection

Test	Test equipment	Compliance to standards	Purpose of the test	Results of the test	Test conditions		
					Heat source	Duration of test	Characteristic elements
UL (UNDERWRITERS' LABORATORIES)	 <p>1SLC80062F0901</p>	UL 94 IEC 60695-2-11	A classification is given to the various types of behaviour that the materials may have following contact with the Bunsen flame	V0 if the test specimen burns for less than 5 seconds before going out. V1 if it burns for less than 25 seconds V2 if it burns for less than 25 seconds, dripping glowing material HB if it burns for more than 25 seconds (horizontal test specimen with a maximum burning speed of 38mm per minute) Can be assimilated with ASTM D-635	Bunsen burner flame	Flame applied for 10 seconds and for two consecutive times	Duration of combustion
GLOW-WIRE TEST	 <p>1SLC80063F0901</p>	IEC 60695-2-11	Simulates the types of thermal stress that may be produced by the sources of heat or ignition (glowing elements or overcharged resistors for short periods) in order to assess the danger of fire using this simulation	Any manifestation of a flame must stop within 30 seconds of removing the glow-wire. TEST TEMPERATURES 650 °C 750 °C 850 °C 960 °C	Glow-wire 4 mm in diameter	Wire applied for 30 seconds	Time it takes the flame to extinguish

Technical details and assembly instructions

IP degrees of protection

Protection against the penetration of solid bodies

1st digit	Brief description	Full description
0	Unprotected	No particular protection is provided
1	Protected against solid bodies larger than 50 mm	It must be impossible for a large surface area, for example, the hand, to penetrate (voluntary protection is not provided, however) or solid bodies larger than 50 mm in diameter
2	Protected against solid bodies larger than 12 mm	It must be impossible for the fingers or similar objects with a maximum length of 80 mm or solid bodies with a diameter greater than 12 mm to penetrate
3	Protected against solid bodies larger than 2.5 mm	It must be impossible for tools, wires, etc. with a diameter or thickness greater than 2.5 mm or solid bodies with a diameter greater than 2.5 mm to penetrate
4	Protected against solid bodies larger than 1.0 mm	It must be impossible for wires, or plates with a thickness greater than 1.0 mm or solid bodies with a diameter greater than 1.0 mm to penetrate
5	Dust proof	Not totally dust proof, but the quantity that penetrates is not such to prevent the material from functioning well
6	Totally dust proof	No dust can penetrate


Protection against water penetration

2nd digit	Brief description	Full description
0	Unprotected	No particular protection is provided
1	Protected against drops of water	Vertically-falling drops of water must not cause damage
2	Protected against drops of water falling with a maximum angle of 15°	Vertically-falling drops of water will not cause damage when angled at a maximum of 15° from vertical
3	Rain proof	Rain water falling from a direction creating a maximum angle of 60° from vertical must not cause damage
4	Protected against sprays of water	Water sprayed onto the covering from any direction must not cause damage
5	Protected against jets of water	Water projected with a nozzle from any direction must not cause damage
6	Protected against waves	In the case of waves or powerful water jets must not penetrate the covering in harmful quantities
7	Protected against the effects of temporary immersion	Harmful quantities of water must not penetrate inside the immersed covering in specific conditions of pressure or duration
8	Protected against the effects of continuous immersion	The material is suitable to remain constantly immersed in water in the conditions specified by the manufacturer


Technical details and assembly instructions

Assembly instructions for steel wire cable trays

Straight sections with hardware



Detail A



Q.ty art. 1SL9879A00




Bridge (mm)	Position 1	Position 2
75	2	0
100	2	0
150	2	0
200	2	1
300	2	1
400	2	2
500	2	2

The specific profile of the staple allows, after having tightened the screws to have earth continuity without using earthing terminals. To ensure this it is necessary that the minimum torque to be applied is of 6 N m.


Technical details and assembly instructions

Assembly instructions for steel wire cable trays


Assembly instructions for bends and T-fittings



If you straighten the joint, it can be used for reductions (see relevant examples)





If you bend the joint by 90° it can be used for "T" branch connections at 90° on trunking measure P=100-200-300-400-500 mm



Technical details and assembly instructions

Assembly instructions for steel wire cable trays


Adapter joints for sendzimir accessories 1SL9888A00 - 1SL9889A00




Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Fastening clips

Metal clip





Plastic rapid clip



Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Large-radius bends with constant pitch



For cable trays B = 75-100-150-200-400-500 mm



B (mm)	1SL9879A00	1SL9881A00
75	–	2
100	1	1
150	2	1
200	3	1
300	See table on the right	
400	6	1
500	7	1

B (mm)	1SL9879A00
300	5

Cutting schemes for the preparation of bends





B (mm)	Minimum R (mm)
75	182
100	125
150	157
200	232
300	355
400	483
500	607

Technical details and assembly instructions

Assembly instructions for steel wire cable trays

90° bends




Splice kits for bend

B (mm)	1SL9879A00
75	1
100	2
150	2
200	2
300	3
400	4
500	4

Splice kits for bend

B (mm)	1SL9883A00	07818
75	2	1
100	2	1
150	2	2
200	4	2
300	4	3
400	6	4
500	6	5

Cuts required by fitting type and wire basket dimensions




No. of "X" units to be cut

B (mm)	W
75	1
100	1
150	2
200	2
300	3
400	4
500	5


Technical details and assembly instructions

Assembly instructions for steel wire cable trays – T-Fitting with straight or reducing fitting

For cable trays B = 100-200-300-400-500 mm



For cable trays B = 75-150 mm




Fitting types

A - Straight fitting


B - Reducer

C - Straight fitting
B = 75 mm


D - Reducer for
B = 75 mm



1SL9881A00
90° bent




1SL9879A00




1SL9884A00

1SL9882A00



1SL9881A00

Cuts required by fitting type and wire basket dimensions





No. of "X" units to be cut

B (mm)	W	Y
75	1	2
100	1	2
150	2	3
200	2	3
300	3	4
400	4	5
500	5	6



Technical details and assembly instructions

Assembly instructions for steel wire cable trays – T-Fitting with straight or reducing fitting


For 50 mm reducers (ex. 50/100) and 100 mm (ex. 500/400)



For 75 mm reducers (ex. 150/75), 150 mm (ex. 300/150) and 200 mm (ex. 400/200)




Cut required




Technical details and assembly instructions

Assembly instructions for steel wire cable trays


Wire Basket H 35 mm



Wire Basket H 50 mm




Wire Basket H 75 mm




Technical details and assembly instructions

Assembly instructions for steel wire cable trays – Covers and dividers

Covers




Dividers



Technical details and assembly instructions


Assembly instructions for steel wire cable trays




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket


Installation with cross-sections – Wall-mounting



Installation with cross-sections – Ceiling-mounting




Installation with cross-sections – Floor-mounting




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Installation with light-duty brackets – Wall-mounting



Installation with light-duty brackets – Ceiling-mounting




Note. Suggested installation only.

Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Installation with medium-duty brackets – Wall-mounting




Note. Suggested installation only.

Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Installation with heavy-duty brackets – Wall-mounting




Note. Suggested installation only.


Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire basket

Preparation of a heavy-duty system




Cable tray fixing on ALFEN profile




Technical details and assembly instructions

Mounting examples – Suspension systems for steel wire W.B.

Preparation of a heavy-duty system



Cable tray fixing on ALFEN profile




Technical details and assembly instructions

Mounting examples – Sendzimir trunkings H 75

- IP44 joint
- IP44 end cap
- Cover with seal
- Clip hooks (art. 07 890) fixed at 1 meter intervals


Mounting system for IP44 trunking




Technical details and assembly instructions

Mounting examples – Hot dip galvanised after production cable trays


Mounting a cable ladder on heavy brackets




Mounting a cable ladder on Alfen brackets




Straight joint of a cable closed/punched base art. 09 760-09 763-09 766




Scheme for fixing a cable ladder on heavy brackets



Scheme for fixing a cable ladder on Alfen profile brackets



Instructions for mounting vertical inside/vertical outside rider articulated corner of cable ladder





- Fix the articulate joints "1" - "2" to the cable ladder with the appropriate roundheaded screws "3" and nuts "4".
- Connect the vertical inside/vertical outside rider articulated corner "5" to the articulated joint using, as a pin, hexagonal head screws M8x16 "6" and the relevant nut "7".
- Block the corner to the joint with the hexagonal head screws M6x12 "8" and nut M6 "4".
- In the same way connect the two vertical inside/vertical outside rider articulated corners "5" one to the other


Technical details and assembly instructions


Guide to selecting suspension systems for industrial trunking

Guide to selecting suspension systems for trunkings and cable trays

Mounting example 1	1 Base plates	2 Profiles "U" punched	3 Brackets	4 Fastening components Plates - profiles
	07984	07956	07785 - 07786 - 07787	Screw 07849 with nut
		07926	07788 - 07789 - 07790	Screw 07818 with nut
		1SL9895A00	09770 - 09771 - 09772	Screw 07448 with nut
		1SL9896A00	09773 - 09774 - 09775	
		1SL9897A00	09776 - 09777 - 09778	
				09779

Mounting example 2	1 Base plates	2 Profiles "C" punched	3 Brackets	4 Fastening components Plates - profiles
	07988 - 1SL7989A00	07992 - 1SL7993A00	07901 - 07902 - 07903	Screw 07849 with nut
	08852	08861	07904 - 07905 - 07906	Screw 07818 with nut
			07907 - 1SL7911A00	
			1SL7912A00 - 1SL7912A00	Brackets - profiles
			1SL7914A00 - 1SL7915A00	Blocking plate 07995
			1SL7916A00 - 1SL7917A00	
			08901 - 08902 - 08903	
			08904 - 08905 - 08906	
			08907	

Mounting example 3	1 Base plates	2 Profiles "C" punched	3 Brackets	4 Fastening components Plates - profiles
	07986 - 1SL7987A00	07992 - 1SL7993A00	07901 - 07902 - 07903	Screw 07849 with nut
	08851	08861	07904 - 07905 - 07906	Screw 07818 with nut
			07907 - 1SL7911A00	
			1SL7912A00 - 1SL7912A00	Brackets - profiles
			1SL7914A00 - 1SL7915A00	Blocking plate 07995
			1SL7916A00 - 1SL7917A00	
			08901 - 08902 - 08903	
			08904 - 08905 - 08906	
			08907	

Mounting example 4	1 Base plates	2 Profiles "U" punched	3 Brackets	4 Fastening components Plates - profiles
	07949	0927	07785 - 07786 - 07787	-
	With bolts for attaching profile		07788 - 07789 - 07790	
			09770 - 09771 - 09772	Mensole - profiles
			09773 - 09774 - 09775	Screw 07851 with anchorage nut
			09776 - 09777 - 09778	
				09779

Technical details and assembly instructions

Guide to selecting suspension systems for industrial trunking

Guide to selecting suspension systems for trunkings and cable trays

Mounting example 1	1 Base plates	2 Profiles	3 Brackets	4 Fastening components	
	07990 - 1SL7991A00 - 08853 With bolts for attaching profile	"C" punched 07992 - 1SL7993A00 - 08861	07901 - 07902 - 07903	Plates - profiles	
			07904 - 07905 - 07906		-
			07907 - 1SL7911A00	Brackets - profiles	
			1SL7912A00 - 1SL7913A00		Blocking plate 07995
			1SL7914A00 - 1SL7915A00		
			1SL7916A00 - 1SL7917A00		
			08901 - 08902 - 08903	-	
			08904 - 08905 - 08906		
			08907		


Mounting example 2	1 Base plates	2 Profiles	3 Brackets	4 Fastening components	
	07985 With bolts for attaching profile	"U" punched 07956 1SL9895A00 1SL9896A00	07785 - 07786 - 07787	Plates - profiles	
			07788 - 07789 - 07790		-
			09770 - 09771 - 09772	Brackets - profiles	
			09773 - 09774 - 09775		Screw 07851 with anchorage nut
			09776 - 09777 - 09778		
			09779		

Mounting example 3	1 Base plates	2 Profiles	3 Brackets	4 Fastening components	
	-	Light-duty 07960	07671 - 07672 - 07673	Plates - profiles	
			07674 - 07675 - 07676		-
			07677 - 1SL7681A00	Brackets - profiles	
			1SL7682A00 - 1SL7683A00		Screw 07818 with nut
			1SL7684A00 - 1SL7685A000		
			1SL7686A00 - 1SL7687A00		
			08 881 - 08 882 - 08 883	-	
			08 884 - 08 885 - 08 886		
			08 887		

Mounting example 4	1 Base plates	2 Profiles	3 Brackets	4 Fastening components	
	07986 - 1SL7987A00 - 08851	"C" punched 07992 - 1SL7993A00 - 08861	07908 - 07909 - 1SL7918A00	Plates - profiles	
			1SL7919A00 - 08811 - 08812		Screw 07849 with nut
				Brackets - profiles	
					Screw 07818 with nut
				-	


Overall dimensions

Undernet concealed floor boxes



Floor box for 10 devices

Product ID	Order code	Dimensions (mm)
10902		275x211
10903		275x211





Floor box for 16 devices

Product ID	Order code	Dimensions (mm)
10900		275x287
10901		275x287

Overall dimensions



Accessories for Undernet concealed floor boxes for 10 devices codes 10902 and 10903



Universal support for 3 modular devices

Product ID	Order code
10918	

All measurements expressed in millimeters.




Universal support for 4 modular devices

Product ID	Order code
10919	

Overall dimensions


Accessories for Undernet concealed floor boxes for 10 devices codes 10902 and 10903



Universal support for 5 modular devices

Product ID	Order code
10920	

All measurements expressed in millimeters.




Metal recessed box for traditional floors, depth 105 mm

Product ID	Order code
10930	

Overall dimensions

Accessories for Undernet concealed floor boxes for 10 devices codes 10900 and 10901




Universal support for 3 devices

Product ID	Order code
10910	

Support for 5 Chiara wiring unit

Product ID	Order code
2CSK1625CH	





Metal recessed box for traditional floors, depth 105 mm

Product ID	Order code
10931	

All measurements expressed in millimeters

Overall dimensions



Concept surface-mounted floor boxes



Floor box

Product ID	Order code
10501	

All measurements expressed in millimeters.





Adaptor for fitting 3 electrical wiring units

Product ID	Order code
10522	



Overall dimensions

Mini-trunking – Self-adhesive mini-trunking



Mini-trunking without cover

Product ID	A	B
41010	7.5	7
41015	10	9
41020	12	11








Mini-trunking with hinged cover

Product ID	A	B
41040	9	4.5
41045	12.5	7
41050	12.5	12.5
41055	17	17

Overall dimensions

Mini-trunking









Mini-trunking H 10 with standard cover

Product ID	Compartment	A
41080	1	20
41081	2	20
41083	1	30
41084	2	30

Mini-trunking H 17 with standard cover

Product ID	Compartment	A
41110	1	15
41091	1	30
41092	2	40
41093	3	60



Mini-trunking H 10 with adhering cover

Product ID	Compartment	A
41101	1	20
41102	2	20
41103	1	30
41104	2	30
41106	2	40

Mini-trunking H 17 with adhering cover


Product ID	Compartment	A
41111	1	15
41113 - 01183	1	30
41114	2	30
41115	2	40
41116	3	60

Mini-trunking H 30 with adhering cover

Product ID	Compartment	A
41120	3	60


Overall dimensions

Mini-trunking




Adjustable flat corner

Product ID	A	B	C	D
41202	36	36	12	20
41204	56	56	12	30
41206	66	66	12	40
41210	31	31	19	15
41213	56	56	19	30
41215	66	66	19	40
41216	86	86	19	60
41217	51	51	32	25
41219	66	66	32	40
41220	86	86	30	60




Flat tee

Product ID	A	B	C	D
41302	45	34	10	20
41304	55	44	10	30
41306	65	54	10	40
41310	40	29	17	15
41313	55	44	17	30
41315	65	54	17	40
41316	85	74	17	60
41317	50	39	30	25
41319	65	54	30	40
41320	85	74	30	60




Adjustable inside corner

Product ID	A	B	C	D
41402	36	36	20	10
41404	36	36	30	10
41406	36	36	40	10
41410	43	43	15	17
41413	43	43	30	17
41415	43	43	40	17
41416	43	43	60	17
41417	55	55	25	30
41419	55	55	40	30
41420	55	55	60	30




Adjustable outside corner

Product ID	A	B	C	D
41502 - 01552 - 01572	37	37	20	10
41504	37	37	30	10
41506	37	37	40	10
41510 - 01560 - 01580	43	43	15	17
41513 - 01563 - 01583	43	43	30	17
41515	43	43	40	17
41516	43	43	60	17
41517	55	55	25	30
41519	55	55	40	30
41520	55	55	60	30



End cap

Product ID	A	B
41602 - 01652 - 01672	11	23
41604	11	33
41606	11	43
41610 - 01660 - 01680	17	15
41613 - 01663 - 01683	17	30
41615	17	40
41616	17	60
41617	30	25
41619	30	40
41620	30	60






Flat joint

Product ID	A	B
41702 - 01752 - 01772	10	20
41704	10	30
41406	10	40
41710 - 01760 - 01780	17	15
41713 - 01763 - 01783	17	30
41715	17	40
41716	17	60
41717	30	25
41719	30	40
41720	30	60

Overall dimensions

Mini-trunking



Box for flat branch connections



Product ID	A	B	C
41800	85	85	26
41803	99	99	33

Frame for flush-mounting box

Product ID
41829


Overall dimensions

Mini-trunking



Switch-socket box

Product ID	A	B	C	I
41823	92	133	43	83.5



Cover


Product ID	A	B	I
00059	92	133	43

Mini-trunking sections and number of devices that can be inserted

Mini-trunking				Mini-trunking Max. no of H07V-K single-pole wires with reduction coefficient = 50% under CEI 64-8						
1 compart.	2 compart.	3 compart.	Order Code	Geometric section of compart. cm ²	Section 1.5 mm ²	Section 2.5 mm ²	Section 4 mm ²	Section 6 mm ²	Max. compatible H07V-K cable for the system Section mm ²	Cross-sections to be used with cables mm ²
	20x10		41081-41102	0.45+0.45	2+2	2+2	1+1	1+1	1.5	22.5+22.5
20x10			41080 41101	1.16	5	4	4	3	1.5	58
30x10			41083-41103	195	15	10	8	5	1.5	97.5
	30x10		41084-41104	0.90+0.90	4+4	3.3	3+3	2+2	1.5	45+45
	40x10		41106	1.31+1.31	6+6	5+5	4+4	3+3	1.5	65.5+65.5
15x17			41080 41111	1.7	8	6	5	4	6	85
30x17			41091 41113	3.70	17	14	12	9	6	185
	40x17		41092-41115	2.33+2.33	10+10	9+9	8+8	6+6	6	116.5+116.5
	60x17		41093-41116	2.4+2.2+2.4	12+10+12	8+7+8	7+6+7	4+3+4	6	120+110+120
25x30			41117	5.12	23	19	17	13	16	256
40x30			41119	9.13	42	35	30	23	16	465.5
	60x30		41120	4.6+4.2+4.6	23+21+23	16+15+16	12+11+12	7+6+7	16	230+210+230


Overall dimensions

Feeder and cable trunking




Feeder and cable

Product ID	A	B
43002	40	40
43003	60	40
43004	80	40
43005	100	40
430066	120	40
43013	60	60
43014	80	60
43015	100	60
43016	120	60
43017	150	60
43018	200	60
43025	100	80
43026	120	80
43027	150	80
43028	200	80




Cable trunking

Product ID	A	B	C
43085	100	40	72
43086	120	40	92
43095	100	60	72
43096	120	60	92
43097	150	60	122
43098	200	60	172
43105	150	80	122
43106	200	80	172




90° flat corner

Product ID	A	B	C	D	E
43152	63	44	44	63	40
43153	83	64	64	83	40
43154	103	84	84	103	40
43155	123	104	104	123	40
43156	143	124	124	143	40
43163	83	64	64	83	60
43164	103	84	84	103	60
43165	123	104	104	123	60
43166	143	124	124	143	60
43167	225	150	150	225	60
43168	275	200	200	275	60
43175	123	104	104	123	80
43176	143	124	124	143	80
43177	225	150	150	225	80
43178	275	200	200	275	80




Inside corner

Product ID	A	B	C	D
43232	60	60	40	44
43233	60	60	40	64
43234	60	60	40	84
43235	60	60	40	104
43236	60	60	40	124
43243	80	80	60	64
43244	80	80	60	84
43245	80	80	60	104
43246	80	80	60	124
43247	195	195	60	150
43248	195	195	60	200
43255	100	100	80	104
43255	100	100	80	124
43255	220	220	80	150
43255	220	220	80	200



Outside corner

Product ID	A	B	C	D
43312	44	75	60	40
43313	64	95	80	40
43314	84	95	80	40
43315	104	115	100	40
43316	124	115	120	40
43323	64	95	80	60
43324	84	95	80	60
43325	104	115	100	60
43326	124	115	100	60
43327	150	200	200	60
43328	200	200	200	60
43335	104	115	100	80
43336	124	115	100	80
43337	150	220	220	80
43338	200	220	220	80









End cap

Product ID	A	D	E
43392	44	42	10
43393	64	42	10
43394	84	42	10
43395	104	42	10
43396	124	42	10
43403	64	62	10
43404	84	62	10
43405	104	62	10
43406	124	62	10
43407	154	62	10
43408	204	62	10
43415	104	82	10
43416	124	82	10
43417	154	82	10
43418	200	82	10

Overall dimensions

Feeder and cable trunking



Tee


Product ID	Trunking height	A	B
43475	40	40/60/80/100	64
43488	60	60/80/100/120/150/200	64
43498	80	100/120/150/200	84

Box for flat branch connections

Product ID	Trunking height	A	B	H
43681	40	121	121	68
43682	60	221	121	85

Switch-socket box

Product ID	Trunking height	A	B	C	D	E
03724	60/80	83.5	97	129	60.5	50
03735	60/80	108	124	155	69	52.5



Product ID	Trunking height
03736	60/80





Trunking sections and number of cables that can be inserted

Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8

Type of trunking	Geometric section of compartment.		Cross-sections to be used with cables							Max. no of H07V-K unipolar wires	
	A	B	1.5 (mm ²)	2.5 (mm ²)	4 (mm ²)	6 (mm ²)	10 (mm ²)	16 (mm ²)	25 (mm ²)		
	40	40	14	74	51	39	23	16	12	7	710
	60	40	20.4	105	51	56	33	23	17	11	1020
	80	40	27.5	143	99	76	44	30	23	14	1375
	100	40	34.4	179	124	95	55	38	28	18	1720
	120	40	41.1	214	148	114	66	45	34	22	2055
	60	60	32	166	115	88	51	35	26	17	1600
	80	60	42.4	220	153	117	68	47	35	22	2120
	100	60	53.6	279	194	148	86	59	44	28	2680
	120	60	62.9	327	227	174	101	69	52	33	3145
	150	60	79.5	413	287	220	128	88	65	42	3975
	200	60	106.8	555	386	295	171	118	88	56	5340
	100	80	72.8	379	263	201	117	80	60	38	3640
	120	80	86.6	450	313	239	139	95	71	46	4330
	150	80	108.8	566	393	301	175	120	89	57	5440
	200	80	149.7	758	526	403	234	161	120	77	7485

Overall dimensions

Feeder and cable trunking



Flat joint and cover

For Trunking Base	A	For Trunking Height	B
40	44	40	30
60	64	60	50
80	84	80	70
100	104		
120	124		
150	154		
200	204		

Equipment support retainer





Product ID	For Trunking Base	A
03711	100	86
03712	120	116
03713	130	136

Overall dimensions

Thermoplastic and halogen free wiring ducts

Thermoplastic and halogen free wiring ducts with 4/6 mm slots

CEI 23-22 Standard applies to plastic wiring ducts and their accessories to be used in the mechanical protection and support of cables in switchboards, in application with a maximum rated voltage of 1000 V in alternate current and 1500 V in direct current. Thermoplastic wiring ducts have obtained the IMQ certification.




Overall dimensions


Thermoplastic and halogen free wiring ducts

Thermoplastic and halogen free wiring ducts with 8/12 mm slots

CEI 23-22 Standard applies to plastic wiring ducts and their accessories to be used in the mechanical protection and support of cables in switchboards, in application with a maximum rated voltage of 1000 V in alternate current and 1500 V in direct current. Thermoplastic wiring ducts have obtained the IMQ certification.




H 100: only thermoplastic material ducts




Overall dimensions

Thermoplastic wiring ducts




Ducts with round holes

Product ID	A	B
05330	50	50
05331	100	60




Plastic rivets and wiring duct bases

Product ID
05214 - 05216 - 05210



Plastic cable retainers

Product ID
05224 - 05226 - 05228 - 05230




Plastic label tag

Product ID
05240

Overall dimensions


Steel wire cable trays

H 35 mm




Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
75x35	73.3	42.9	3000	0.626	1890.7
100x35	98.3	42.9	3000	0.657	2743.2
150x35	148.3	42.9	3000	0.798	4448.2
200x35	198.3	42.9	3000	0.948	6153.2
300x35	298.3	42.9	3000	1.612	9563.2

H 50 mm




Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
75x50	73.3	57.9	3000	0.857	2726.2
100x50	98.3	57.9	3000	0.881	3953.7
150x50	148.3	57.9	3000	1.029	6408.7
200x50	198.3	57.9	3000	1.178	8863.7
300x50	298.3	57.9	3000	1.909	13773.7
400x50	399.1	58.3	3000	2.292	18683.7
500x50	499.1	58.3	3000	2.675	23593.7

H 75 mm



Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
75x75	73.3	82.9	3000	0.906	4118.7
100x75	98.3	82.9	3000	0.931	5971.2
150x75	148.3	82.9	3000	1.079	9676.2
200x75	198.3	82.9	3000	1.227	13381.2
300x75	298.3	82.9	3000	1.958	20791.2
400x75	399.1	83.3	3000	2.341	28201.2
500x75	499.1	83.3	3000	2.724	35611.2

H 100 mm




Rated dimension	A (mm ²)	B (mm ²)	Length (mm ²)	Weight (kg/m)	Usable section (mm ²)
100x100	98.6	108.8	3000	1.525	8100
150x100	148.6	108.8	3000	1.715	13100
200x100	198.6	108.8	3000	1.908	18100
300x100	298.6	108.8	3000	2.292	28100
400x100	398.6	108.8	3000	2.675	38100
500x100	498.6	108.8	3000	3.058	48100

Overall dimensions


Load diagram - basket tray

—
Load diagram H35




- 75
- 100
- 150
- 200
- 300

—
Load diagram H50




- 75
- 100
- 150
- 200
- 300
- 400
- 500

—
Load diagram H75




- 75
- 100
- 150
- 200
- 300
- 400
- 500

—
Load diagram H100




- 75
- 100
- 150
- 200
- 300
- 400
- 500

Overall dimensions
Steel wire cable trays











Overall dimensions

Sendzimir trunking




Overall dimensions

Sendzimir trunking

1		IP40 trunking	26		Straight joint
2		IP20 trunking	27		Integral joint
3		Cover	28		Vertical joint xed at 90°
4		90° horizontal corner	29		Adjustable joint
5		45° horizontal corner	30		Branch connection coupler
6		Horizontal tee	31		Fastening element for separator
7		Horizontal cross	32		Divider
8		90° vertical inside fitting	33		Screw and nut
9		45° vertical inside fitting	34		Earth connection
10		90° vertical outside fitting	35		Branch connection box
11		45° vertical outside fitting	36		Single anchorage plate
12		Straight reducer	37		Double anchorage plate
13		Left reducer	38		Adjustable anchor plate
14		Right reducer	39		“C” prole
15		End cap	40		Blocking plate
16		Left 90° vertical outside fitting	41		Bracket
17		Right 90° vertical outside fitting	42		Trunking retainer spring
18		Vertical horizontal tee	43		Plate with conduit-tightener collar
19		Vertical tee with reduction	44		Conduit for suspensions
20		Horizontal tee with reduction	45		Cross piece with conduit-tightening collar
21		Straight inversion element	46		Cross piece for fastening to the ceiling
22		Left reducing fitting	47		Support for suspensions
23		Right reducing fitting	48		Punched bar
24		Coupler ange for fastening to switchboards	49		Integral sealed joint
25		Wall support	50		Clip

Overall dimensions

Sendzimir trunking H 50



Punched base cable trunking IP20



Width	A	S	Weight (kg/m)
100	3000	0.8	1.32
150	3000	0.8	1.61
200	3000	1.0	2.37
300	3000	1.0	3.12
400	3000	1.2	4.64
500	3000	1.2	5.53

Cable trunking IP40

Width	A	S	Weight (kg/m)
100	3000	0.8	1.39
150	3000	0.8	1.70
200	3000	1.0	2.50
300	3000	1.0	3.29
400	3000	1.2	4.89
500	3000	1.2	5.82


Cable for cable trunking IP20 and IP40

Width	A	S	Weight (kg/m)
100	3000	0.6	0.69
150	3000	0.6	0.92
200	3000	0.6	1.16
300	3000	0.6	2.16
400	3000	0.8	2.79
500	3000	0.8	3.48




90° horizontal corner

Width	A	B
100	265	265
150	315	315
200	365	365
300	465	465
400	565	565
500	665	665




45° horizontal corner

Width	A	B
100	165	227
150	216	263
200	265	298
300	365	369
400	465	440
500	565	510



Horizontal tee

Width	A	B
100	430	265
150	480	315
200	510	365
300	630	465
400	730	565
500	830	665











Horizontal cross

Width	A	B
100	430	430
150	480	480
200	530	530
300	630	630
400	730	730
500	830	830

Overall dimensions

Sendzimir trunking H 50



90° vertical inside fitting

Width	A	B
100	240	240
150	240	240
200	240	240
300	240	240
400	240	240
500	240	240

45° vertical inside fitting



Width	A	B
100	210	140
150	210	140
200	210	140
300	210	140
400	210	140
500	210	140

90° vertical outside fitting

Width	A	B
100	240	240
150	240	240
200	240	240
300	240	240
400	240	240
500	240	240



45° vertical outside fitting

Width	A	B
100	210	140
150	210	140
200	210	140
300	210	140
400	210	140
500	210	140




End cap

Width	B
100	50
150	50
200	50
300	50
400	50
500	50




Left 90° outside fitting

Width	A	B
100	265	370
150	315	370
200	365	370
300	465	370
400	565	370
500	655	370



Right 90° outside fitting

Width	A	B
100	265	370
150	315	370
200	365	370
300	465	370
400	565	370
500	655	370





Vertical tee

Width	A	B
100	430	370
150	470	370
200	530	370
300	630	370
400	730	370
500	830	370



Overall dimensions

Sendzimir trunking H 50





Left reducer

A
50
100
150
200



Right reducer



A
50
100
150
200





Integral splice plate coupler

Width	A
100	98.4
150	148.4
200	198
300	298
400	397.6
500	497.6



Adjustable coupler





Flange for fastening to switchboards



Splice plate coupler for trunkings








Screw, nut and earth staple




Overall dimensions

Sendzimir trunking H 50


Trunking sections and number of cables that can be inserted

Trunking dimensions	Geometric section of compart. cm ²	Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8												Max. compatible H07V-K cable for the system sec. mm ²
		Sec. 6 mm ²	Sec. 10 mm ²	Sec. 16 mm ²	Sec. 25 mm ²	Sec. 35 mm ²	Sec. 50 mm ²	Sec. 70 mm ²	Sec. 95 mm ²	Sec. 120 mm ²	Sec. 150 mm ²	Sec. 185 mm ²	Sec. 240 mm ²	
	62	99	69	50	32	24	19	13	10	8	7	5	4	240
	100	151	103	76	49	38	38	20	16	13	10	8	7	240
	126	202	224	102	65	51	37	27	22	17	14	12	8	240
	189	305	244	154	99	76	57	41	33	27	21	17	13	240
	253	408	281	207	132	103	76	55	44	36	29	23	17	240
	317	510	352	259	166	128	96	69	55	46	36	29	23	240

Diagrams of maximum loads for metal trunkings H 50




- Evenly distributed load (q)
- Trunkings/cable trays resting on two single constraints (A, B)
- Span 2000 mm (L)
- Maximum camber considered at the middle of span (F)
- Ambient temperature 20° C



Overall dimensions

Sendzimir trunking H 75



Punched base cable trunking IP20



Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.6	1.10
100	1000/2000/3000	0.6	1.22
150	1000/2000/3000	0.6	1.46
200	1000/2000/3000	0.8	2.08
300	1000/2000/3000	1.0	3.40
400	1000/2000/3000	1.2	4.84
500	1000/2000/3000	1.2	5.69

Cable trunking IP40

Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.6	1.17
100	1000/2000/3000	0.6	1.30
150	1000/2000/3000	0.6	1.55
200	1000/2000/3000	0.8	2.32
300	1000/2000/3000	1.0	3.76
400	1000/2000/3000	1.2	5.37
500	1000/2000/3000	1.2	6.31


Cable for cable trunking IP20 and IP40

Width	A	C	Weight (kg/m)
75	1000/2000/3000	0.5	0.48
100	1000/2000/3000	0.5	0.57
150	1000/2000/3000	0.5	0.77
200	1000/2000/3000	0.5	0.96
300	1000/2000/3000	0.5	1.35
400	1000/2000/3000	0.8	2.79
500	1000/2000/3000	0.8	3.48




90° horizontal corner

Width	A	B	Weight (kg)
75	240	240	0.94
100	265	265	1.14
150	315	315	1.48
200	365	365	1.86
300	465	465	2.73
400	565	565	3.76
500	665	665	4.95




45° horizontal corner

Width	A	B	Weight (kg)
75	140	210	0.53
100	165	227	0.65
150	215	263	0.82
200	265	298	1.00
300	365	369	1.41
400	465	440	1.78
500	565	510	2.40



Horizontal tee

Width	A	B	Weight (kg)
75	405	240	1.22
100	430	265	1.45
150	480	315	1.83
200	530	365	2.24
300	630	465	3.18
400	730	565	4.28
500	830	665	5.54










Horizontal cross

Width	A	B	Weight (kg)
75	405	405	1.20
100	430	430	2.00
150	480	480	2.41
200	530	530	2.86
300	630	630	3.87
400	730	730	5.04
500	830	830	6.37

Overall dimensions

Sendzimir trunking H 75



90° vertical inside fitting

45° vertical inside fitting

90° vertical outside fitting






45° vertical outside fitting

Width	A	B	Weight (kg)
75	240	240	0.82
100	240	240	1.07
150	240	240	1.26
200	240	240	1.44
300	240	240	1.83
400	240	240	2.19
500	240	240	2.56

Width	A	B	Weight (kg)
75	210	140	0.84
100	210	140	0.96
150	210	140	0.76
200	210	140	0.87
300	210	140	1.11
400	210	140	1.32
500	210	140	1.55

Width	A	B	Weight (kg)
75	240	240	0.84
100	240	240	0.96
150	240	240	1.09
200	240	240	1.22
300	240	240	1.48
400	240	240	1.75
500	240	240	2.05

Width	A	B	Weight (kg)
75	210	140	0.50
100	210	140	0.65
150	210	140	0.76
200	210	140	0.87
300	210	140	1.11
400	210	140	1.32
500	210	140	1.55



Straight reducer

Left reducer

Right reducer



A	B	C	Weight (kg)
100	75	300	1.20
150	75	300	1.25
150	100	300	1.30
200	75	300	1.45
200	100	300	1.51
200	150	300	1.61
300	200	300	2.15
400	300	300	2.55
500	400	300	3.01

A	B	C	Weight (kg)
100	75	300	1.00
150	75	300	1.23
150	100	300	1.27
200	75	300	1.42
200	100	300	1.49
200	150	300	1.57
300	200	300	1.90
400	300	300	2.58
500	400	300	3.05

A	B	C	Weight (kg)
100	75	300	1.00
150	75	300	1.23
150	100	300	1.27
200	75	300	1.42
200	100	300	1.49
200	150	300	1.57
300	200	300	1.90
400	300	300	2.58
500	400	300	3.05



Overall dimensions

Sendzimir trunking H 75





Left 90° outside fitting

Width	A	B	Weight (kg)
75	240	370	1.25
100	265	370	1.48
150	315	370	1.78
200	365	370	2.67
300	465	370	3.20
400	565	370	6.90
500	665	370	9.30





Right 90° outside fitting

Width	A	B	Weight (kg)
75	240	370	1.25
100	265	370	1.48
150	315	370	1.78
200	365	370	2.67
300	465	370	3.20
400	565	370	6.90
500	665	370	9.30





Vertical tee without level gradient

A	Weight (kg)
75	1.50
100	1.75
150	2.11
200	2.37
300	3.02
400	3.74
500	4.47





Vertical tee with level gradient

Width	A	B	Weight (kg)
75	405	370	2.75
100	430	370	2.85
150	480	370	3.25
200	530	370	3.60
300	630	370	4.40
400	730	370	7.43
500	830	370	10.33



Horizontal tee with reduction

A	B	C	D	Weight (kg)
100	75	405	370	2.13
150	75	405	370	2.53
150	100	430	370	2.66
200	75	405	370	2.9
200	100	430	370	3.09
200	150	480	370	3.45
300	75	405	370	3.69
300	100	430	370	3.9
300	150	480	370	4.32
300	200	530	370	4.8







Horizontal tee with reduction

A	B	C	D	Weight (kg)
100	75	407	266	1.7
150	75	407	316	1.97
150	100	432	316	2.08
200	75	407	366	2.26
200	100	432	366	2.40
200	150	482	366	2.69
300	75	407	466	2.80
300	100	432	466	2.96
300	150	482	466	3.40
300	200	532	466	3.76

Overall dimensions

Sendzimir trunking H 75



End cap

A	Weight (kg)
75	0.085
100	0.100
150	0.135
200	0.170
300	0.240
400	0.310
500	0.380


Straight inversion element

Base	X	Y	L
75	75	78.5	0.085
100	100	78.5	0.100
150	150	78.5	0.135
200	200	78.5	0.170
300	300	78.5	0.240
400	400	78.5	0.310
500	500	78.5	0.380

Overall dimensions


Sendzimir trunking H 75

The illustrations below are all related to a width of 75mm, use the tables below to select the correct items for the size required.




Right-hand skew inside bend 90°

Width	Left 90° Vertical Bend	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07591	07241	07131	07731	07829 (3x)
100	07592	07242	07132	07732	07829 (3x)
150	07593	07243	07133	07733	07829 (3x)
200	07594	07244	07134	07734	07829 (3x)
300	07595	07245	07135	07735	07829 (3x)
400	07596	07246	07136	07736	07829 (3x)
500	07597	07247	07137	07737	07829 (3x)




Left-hand skew inside bend 90°

Width	Right 90° Vertical Bend	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07611	07241	07131	07731	07829 (3x)
100	07612	07242	07132	07732	07829 (3x)
150	07613	07243	07133	07733	07829 (3x)
200	07614	07244	07134	07734	07829 (3x)
300	07615	07245	07135	07735	07829 (3x)
400	07616	07246	07136	07736	07829 (3x)
500	07617	07247	07137	07737	07829 (3x)



Inside bend 90° with plane inversion

Width	Vertical Outside Bend 90° H75	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07391	07241	07131	07731	07829 (3x)
100	07392	07242	07132	07732	07829 (3x)
150	07393	07243	07133	07733	07829 (3x)
200	07394	07244	07134	07734	07829 (3x)
300	07395	07245	07135	07735	07829 (3x)
400	07396	07246	07136	07736	07829 (3x)
500	07397	07247	07137	07737	07829 (3x)




Outside bend 90° with plane inversion

Width	Vertical Inside Bend 90° H75	Metal Trunking Cover	Metal Trunking H75 IP40	Straight Inversion H75	Mechanical Joint
75	07451	07241	07131	07731	07829 (3x)
100	07452	07242	07132	07732	07829 (3x)
150	07453	07243	07133	07733	07829 (3x)
200	07454	07244	07134	07734	07829 (3x)
300	07455	07245	07135	07735	07829 (3x)
400	07456	07246	07136	07736	07829 (3x)
500	07457	07247	07137	07737	07829 (3x)


Overall dimensions

Sendzimir trunking H 75




Coupler flange for fastening to switchboards

Width	A	B	Weight (kg)
75	125	93	0.14
100	150	118	0.16
150	200	168	0.18
200	250	218	0.20
300	350	318	0.25
400	450	418	0.32
500	550	518	0.38




Left reducer

A	Weight (kg)
50	0.13
100	0.16
150	0.20
200	0.23




Right reducer

A	Weight (kg)
50	0.13
100	0.16
150	0.20
200	0.23




Wall flange

A	B	C	Weight (kg)
75	145	180	0.45
100	165	200	0.48
150	215	250	0.6
200	265	300	0.73
300	365	400	0.96
400	465	500	1.19
500	565	600	1.41



Integral coupler and retainer



A	Weight (kg)
75	0.24
100	0.34
150	0.50
200	0.68
300	1.02
400	1.36
500	1.70





Coupler

Overall dimensions



Sendzimir trunking H 75





Vertical coupler fixed at 90°




Adjustable coupler



Branch connection coupler



IP44 coupler



Screws and nut

A	B
75	93
100	118
150	168
200	218
300	318
400	418
500	518


Overall dimensions

Sendzimir trunking H 75


Trunking sections and number of cables that can be inserted

Trunking dimensions	Geometric section of compart. cm ²	Max. no of H07V-K unipolar wires with reduction coefficient = 50% under CEI 64-8												Max. compatible H07V-K cable for the system sec. mm ²
		Sec. 6 mm ²	Sec. 10 mm ²	Sec. 16 mm ²	Sec. 25 mm ²	Sec. 35 mm ²	Sec. 50 mm ²	Sec. 70 mm ²	Sec. 95 mm ²	Sec. 120 mm ²	Sec. 150 mm ²	Sec. 185 mm ²	Sec. 240 mm ²	
	54,25	87	60	44	28	22	16	11	9	7	6	5	4	240
	73	117	81	59	38	29	22	16	12	10	8	6	5	240
	110,5	178	122	90	58	45	33	24	19	16	12	10	8	240
	148	238	264	121	77	60	44	32	26	21	17	14	10	240
	223	359	287	182	117	90	67	49	39	32	25	21	16	240
	298	480	331	244	156	121	90	65	52	43	34	28	21	240
	373	601	414	305	196	151	113	82	65	54	43	35	27	240

Diagrams of maximum loads for metal trunkings H 75




- Evenly distributed load (q)
- Trunkings/cable trays resting on two single constraints (A, B)
- Span 2000 mm (L)
- Maximum camber considered at the middle of span (F)
- Ambient temperature 20° C




Overall dimensions

Cable trays-hot dip galvanized after fabrication




Cable ladder

H	B (Working space)
60	40
100	80
130	110




Cover

A	B	Thickness
100	200	1.2
200	300	1.2
300	300	1.2
400	400	1.2
500	400	1.2
600	500	1.2




90° horizontal corner

Width	A	B
100	545	545
200	645	645
300	745	745
400	845	845
500	945	945
600	1045	1045




Right reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600



Straight reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600





Left reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600



Overall dimensions

Cable trays-hot dip galvanized after fabrication





45° horizontal corner

Width	A	B
100	290	530
200	390	601
300	490	672
400	590	742
500	690	813
600	790	884





Horizontal tee

A	B	C
100	545	990
200	645	1090
300	745	1190
400	845	1290
500	945	1390
600	1045	1490





Horizontal cross

A	B	C
100	990	990
200	1090	1090
300	1190	1190
400	1290	1290
500	1390	1390
600	1490	1490






Vertical inside and outside fitting adjustable from 0° to 90°



90° vertical inside fitting

H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7









90° vertical outside fitting

H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7

Overall dimensions

Cable trays-hot dip galvanized after fabrication



Left and right reducing couplers




B	Y
50	180
100	180
200	180

Solid bottom cable tray

H	Thickness
60	1.2
100	1.2
130	1.2

Punched base cable tray

H	Thickness
60	1.2
100	1.2
130	1.2



Cover

A	B	Thickness
100	26.3	1.2
200	26.3	1.2
300	26.3	1.2
400	26.3	1.2
500	26.3	1.2
600	26.3	1.2

90° horizontal corner


Width	A	B
100	545	545
200	645	645
300	745	745
400	845	845
500	945	945
600	1045	1045

45° horizontal corner

Width	A	B
100	290	530
200	390	601
300	490	672
400	590	742
500	690	813
600	790	884


Overall dimensions

Cable trays-hot dip galvanized after fabrication




Horizontal tee

A	B	C
100	545	990
200	645	1090
300	745	1190
400	845	1290
500	945	1390
600	1045	1490




Horizontal cross

A	B	C
100	990	990
200	1090	1090
300	1190	1190
400	1290	1290
500	1390	1390
600	1490	1490




Vertical inside/outside fitting adjustable from 0° to 90°




Straight reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600



Right reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600




Left reducer

A	B	C
100	200	600
100	300	600
200	300	600
200	400	600
300	400	600
300	500	600
400	500	600
400	600	600
500	600	600


Overall dimensions

Cable trays-hot dip galvanized after fabrication



90° vertical inside fitting

H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7








90° vertical outside fitting

H	A	B	C
60	380.7	145	175.7
100	420.7	145	175.7
130	450.7	145	175.7

Overall dimensions

Suspension systems for industrial trunking







Bracket

Product ID	Width	A	B	C	Capacity (N)
07901 - 1SL7911A00 - 08801	75	112	85	115	600
07902 - 1SL7912A00 - 08802	100	137	110	115	600
07903 - 1SL7913A00 - 08803	150	187	160	115	600
07904 - 1SL7914A00 - 08804	200	237	210	115	650
07905 - 1SL7915A00 - 08805	300	337	310	190	650
07906 - 1SL7916A00 - 08806	400	437	410	190	900
07907 - 1SL7917A00 - 08807	500	537	510	190	1100

Chair bracket

Product ID	Width	A	B	C	Capacity (N)
07908 - 1SL7918A00 - 08808	75/100/150	187	160	415	600
07909 - 1SL7919A00 - 08809	200/300	337	310	490	650



Light-duty pressed brackets


Product ID	Width	A	B	Capacity (N)
07671 - 1SL7681A00 - 08881	75	138	100	1000
07672 - 1SL7682A00 - 08882	100	163	100	1000
07673 - 1SL7683A00 - 08883	150	213	100	750
07674 - 1SL7684A00 - 08884	200	266	140	600
07675 - 1SL7685A00 - 08885	300	366	140	450
07676 - 1SL7686A00 - 08886	400	466	180	400
07677 - 1SL7687A00 - 08887	500	566	180	300

Heavy-duty bracket

Product ID	A	B	C	D	E	Capacity (N)
07785	150	120	40	40	40	1800
07786	250	120	40	40	40	1800
07787	350	160	40	40	80	1800
07788	450	160	40	40	80	2000
07789	550	160	40	40	80	2000
07790	650	160	40	40	80	2000

Overall dimensions

Suspension systems for industrial trunking





Alfen profile bracket

Product ID	A	B	C	Capacity (N)
09770	150	-	-	2000
09771	250	-	-	1700
09772	350	-	-	1500
09773	450	-	-	1300
09774	550	214	344	2500
09775	650	314	344	2200
09776	750	214	543	2500
09777	850	314	543	2400
09778	950	414	543	2300
09779	1050	514	543	2200

Cross piece for fastening to the ceiling

Product ID	A	B
07941 - 1SL7951A00 - 08831	106	75
07942 - 1SL7952A00 - 08832	131	100
07943 - 1SL7953A00 - 08833	181	150
07944 - 1SL7954A00 - 08834	231	200
07945 - 1SL7955A00 - 08835	331	300



Support for suspension

Product ID	A	B
07961 - 1SL7971A00 - 08841	103	75
07962 - 1SL7972A00 - 08842	128	100
07963 - 1SL7973A00 - 08843	178	150
07964 - 1SL7974A00 - 08844	228	200
07965 - 1SL7975A00 - 08845	328	300

Cross piece with conduit tightening collar Ø 22 mm

Product ID	A	B
07921 - 1SL7931A00 - 08821	106	75
07922 - 1SL7932A00 - 08822	131	100
07923 - 1SL7933A00 - 08823	181	150
07924 - 1SL7934A00 - 08824	231	200
07925 - 1SL7935A00 - 08825	331	300

Overall dimensions

Suspension systems for industrial trunking







Plate with conduit-tightening collar Ø 22 mm

Product ID
07978 - 1SL7979 - 08854





Conduit Ø 22 mm

Product ID
07982 - 1SL7983 - 08862

Ceiling anchor plate

Product ID	Product ID	Product ID
07986 - 1SL7987A00	07988 - 1SL79897A00	07990 - 1SL79991A00
08851	08852	08853

Flat punched fastening






Product ID
07437

Product ID
07967

Product ID
07976

Product ID
07968









Product ID
07969

Product ID
07977

Product ID
07970

Overall dimensions

Suspension systems for industrial trunking



90°, tee and cross punched fastening plate

Product ID

07980

Product ID





07981

Product ID

07438

Overall dimensions

Suspension systems for industrial trunking



“C” profile for suspension

Product ID

07992 - 1SL7993A00 - 08 861

Blocking plate for “C” profile


Product ID

07995

Galvanized punched bar

Product ID


07996



Light-duty punched bars

Product ID

07997



Horizontal punched profile

Product ID

07966

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
03042	M030420000	42	17357	M17357	77	17518	M17518	88
03043	M030430000	42	17371	M17371	80	17519	M17519	88
03044	M030440000	42	17372	M17372	80	17520	M17520	88
03045	M030450000	42	17373	M17373	80	17521	M17521	88
03046	M030460000	42	17374	M17374	80	17532	M17532	89
03053	M030530000	42	17375	M17375	80	17533	M17533	89
03054	M030540000	42	17376	M17376	80	17534	M17534	89
03055	M030550000	42	17377	M17377	80	17536	M17536	89
03056	M030560000	42	17391	M17391	81	17537	M17537	89
03057	M030570000	42	17392	M17392	81	17538	M17538	89
03058	M030580000	42	17393	M17393	81	17539	M17539	89
03065	M030650000	42	17394	M17394	81	17540	M17540	89
03066	M030660000	42	17395	M17395	81	17541	M17541	89
03067	M030670000	42	17396	M17396	81	17552	M17552	90
03068	M030680000	42	17397	M17397	81	17553	M17553	90
10501	M105010000	29	17357	M17357	79	17554	M17554	90
10520	M105200000	29	17532	M17532	91	17556	M17556	90
10522	M105220000	29	17533	M17533	91	17557	M17557	90
10526	M105260000	30	17534	M17534	91	17558	M17558	90
10528	M105280000	30	17536	M17536	91	17559	M17559	90
10530	M105300000	29	17537	M17537	91	17560	M17560	90
10559	M105590000	29	17538	M17538	91	17561	M17561	90
10900	M109000000	26	17539	M17539	91	17710	M17710	79
10901	M109010000	26	17540	M17540	91	17711	M17711	79
10902	M109020000	26	17541	M17541	91	17712	M17712	79
10903	M109030000	26	17411	M17411	82	17713	M17713	79
10918	M109180000	26	17412	M17412	82	17714	M17714	79
10919	M109190000	26	17413	M17413	82	17715	M17715	79
10920	M109200000	26	17414	M17414	82	17716	M17716	79
10930	M109300000	26	17415	M17415	82	17717	M17717	79
10931	M109310000	26	17416	M17416	82	17718	M17718	79
17291	M17291	76	17417	M17417	82	17719	M17719	79
17292	M17292	76	17451	M17451	83	18370	M183700000	48
17293	M17293	76	17452	M17452	83	18372	M183720000	48
17294	M17294	76	17453	M17453	83	18374	M183740000	48
17295	M17295	76	17454	M17454	83	18376	M183760000	48
17296	M17296	76	17455	M17455	83	18380	M183800000	48
17297	M17297	76	17456	M17456	83	18382	M183820000	48
17311	M17311	75	17457	M17457	83	18384	M183840000	48
17312	M17312	75	17471	M17471	84	18386	M183860000	48
17313	M17313	75	17472	M17472	84	27512	M27512	88
17314	M17314	75	17473	M17473	84	27513	M27513	88
17315	M17315	75	17474	M17474	84	27514	M27514	88
17316	M17316	75	17475	M17475	84	27516	M27516	88
17317	M17317	75	17476	M17476	84	27517	M27517	88
17351	M17351	77	17477	M17477	84	27518	M27518	88
17352	M17352	77	17512	M17512	88	27519	M27519	88
17353	M17353	77	17513	M17513	88	27520	M27520	88
17354	M17354	77	17514	M17514	88	27521	M27521	88
17355	M17355	77	17516	M17516	88	27532	M27532	89
17356	M17356	77	17517	M17517	88	27533	M27533	89

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
27534	M27534	89	41117	M411170000	35	41619	M416190000	37
27536	M27536	89	41119	M411190000	35	41620	M416200000	37
27537	M27537	89	41120	M411200000	35	41702	M417020000	37
27538	M27538	89	41202	M412020000	35	41704	M417040000	37
27539	M27539	89	41204	M412040000	35	41706	M417060000	37
27540	M27540	89	41206	M412060000	35	41710	M417100000	37
27541	M27541	89	41210	M412100000	35	41713	M417130000	37
27552	M27552	90	41213	M412130000	35	41715	M417150000	37
27553	M27553	90	41215	M412150000	35	41716	M417160000	37
27554	M27554	90	41216	M412160000	35	41717	M417170000	37
27556	M27556	90	41217	M412170000	35	41719	M417190000	37
27557	M27557	90	41219	M412190000	35	41720	M417200000	37
27558	M27558	90	41220	M412200000	35	41800	M418000000	38
27559	M27559	90	41302	M413020000	36	41803	M418030000	38
27560	M27560	90	41304	M413040000	36	41822	M418220000	38
27561	M27561	90	41306	M413060000	36	41823	M418230000	38
27710	M27710	79	41310	M413100000	36	41829	M418290000	38
27711	M27711	79	41313	M413130000	36	41830	M418300000	38
27712	M27712	79	41315	M413150000	36	43002	M430020000	40
27713	M27713	79	41316	M413160000	36	43003	M430030000	40
27714	M27714	79	41317	M413170000	36	43004	M430040000	40
27715	M27715	79	41319	M413190000	36	43005	M430050000	40
27716	M27716	79	41320	M413200000	36	43006	M430060000	40
27717	M27717	79	41402	M414020000	36	43013	M430130000	40
27718	M27718	79	41404	M414040000	36	43014	M430140000	40
27719	M27719	79	41406	M414060000	36	43015	M430150000	40
41010	M410100000	33	41410	M414100000	36	43016	M430160000	40
41015	M410150000	33	41413	M414130000	36	43017	M430170000	40
41020	M410200000	33	41415	M414150000	36	43018	M430180000	40
41040	M410400000	33	41416	M414160000	36	43025	M430250000	40
41045	M410450000	35	41417	M414170000	36	43026	M430260000	40
41050	M410500000	33	41419	M414190000	36	43027	M430270000	40
41055	M410550000	33	41420	M414200000	36	43028	M430280000	40
41080	M410800000	35	41502	M415020000	36	43085	M430850000	41
41081	M410810000	35	41504	M415040000	36	43086	M430860000	41
41083	M410830000	35	41506	M415060000	36	43095	M430950000	41
41084	M410840000	35	41510	M415100000	36	43096	M430960000	41
41091	M410910000	35	41513	M415130000	36	43097	M430970000	41
41092	M410920000	35	41515	M415150000	36	43098	M430980000	41
41093	M410930000	35	41516	M415160000	36	43105	M431050000	41
41101	M411010000	35	41517	M415170000	36	43106	M431060000	41
41102	M411020000	35	41519	M415190000	36	43152	M431520000	41
41103	M411030000	35	41520	M415200000	36	43153	M431530000	41
41104	M411040000	35	41602	M416020000	37	43154	M431540000	41
41106	M411060000	35	41604	M416040000	37	43155	M431550000	41
41110	M411100000	35	41606	M416060000	37	43156	M431560000	41
41111	M411110000	35	41610	M416100000	37	43163	M431630000	41
41113	M411130000	35	41613	M416130000	37	43164	M431640000	41
41114	M411140000	35	41615	M416150000	37	43165	M431650000	41
41115	M411150000	35	41616	M416160000	37	43166	M431660000	41
41116	M411160000	35	41617	M416170000	37	43167	M431670000	41

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
43168	M431680000	41	43488	M434880000	43	00097	M000970000	33
43175	M431750000	41	43498	M434980000	43	00098	M000980000	33
43176	M431760000	41	43552	M435520000	43	03042	M030420000	40
43177	M431770000	41	43553	M435530000	43	03043	M030430000	40
43178	M431780000	41	43554	M435540000	43	03044	M030440000	40
43232	M432320000	42	43555	M435550000	43	03045	M030450000	40
43233	M432330000	42	43556	M435560000	43	03046	M030460000	40
43234	M432340000	42	43565	M435650000	43	03053	M030530000	40
43235	M432350000	42	43566	M435660000	43	03054	M030540000	40
43236	M432360000	42	43630	M436300000	47	03055	M030550000	40
43243	M432430000	42	43631	M436310000	47	03056	M030560000	40
43244	M432440000	42	43681	M436810000	44	03057	M030570000	40
43245	M432450000	42	43682	M436820000	44	03058	M030580000	40
43246	M432460000	42	43744	M437440000	46	03065	M030650000	40
43247	M432470000	42	43745	M437450000	46	03066	M030660000	40
43248	M432480000	42	43746	M437460000	46	03067	M030670000	40
43255	M432550000	42	43747	M437470000	46	03068	M030680000	40
43256	M432560000	42	43748	M437480000	46	03711	M037110000	45
43257	M432570000	42	43950	M439500000	46	03712	M037120000	45
43258	M432580000	42	43951	M439510000	46	03713	M037130000	45
43312	M433120000	42	43952	M439520000	46	03720	M037200000	45
43313	M433130000	42	43953	M439530000	46	03724	M037240000	44
43314	M433140000	42	43955	M439550000	46	03735	M037350000	44
43315	M433150000	42	43956	M439560000	46	03736	M037360000	44
43316	M433160000	42	43957	M439570000	46	05019	M050190000	51
43323	M433230000	42	43958	M439580000	46	05033	M050330000	51
43324	M433240000	42	44040	M44040	96	05035	M050350000	51
43325	M433250000	42	00050	M000500000	32	05037	M050370000	51
43326	M433260000	42	00051	M000510000	32	05043	M050430000	51
43327	M433270000	42	00053	M000530000	32	05045	M050450000	51
43328	M433280000	42	00054	M000540000	32	05047	M050470000	51
43335	M433350000	42	00055	M000550000	33	05049	M050490000	51
43336	M433360000	42	00056	M000560000	33	05051	M050510000	51
43337	M433370000	42	00059	M000590000	33	05053	M050530000	51
43338	M433380000	42	00059	M000590000	38	05063	M050630000	51
43392	M433920000	43	00070	M000700000	32	05065	M050650000	51
43393	M433930000	43	00071	M000710000	32	05067	M050670000	51
43394	M433940000	43	00072	M000720000	32	05069	M050690000	51
43395	M433950000	43	00073	M000730000	32	05071	M050710000	51
43396	M433960000	43	00074	M000740000	32	05073	M050730000	51
43403	M434030000	43	00075	M000750000	32	05083	M050830000	51
43404	M434040000	43	00076	M000760000	32	05085	M050850000	51
43405	M434050000	43	00077	M000770000	32	05087	M050870000	51
43406	M434060000	43	00078	M000780000	32	05089	M050890000	51
43407	M434070000	43	00090	M000900000	33	05091	M050910000	51
43408	M434080000	43	00091	M000910000	33	05093	M050930000	51
43415	M434150000	43	00092	M000920000	33	05094	M050940000	51
43416	M434160000	43	00093	M000930000	33	05095	M050950000	51
43417	M434170000	43	00094	M000940000	33	05096	M050960000	51
43418	M434180000	43	00095	M000950000	33	05097	M050970000	51
43475	M434750000	43	00096	M000960000	33	05098	M050980000	51

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
05099	M050990000	51	05402	M054020000	54	06396	M06396	64
05099	M050990000	54	05405	M054050000	54	06397	M06397	64
05119	M051190000	51	05410	M054100000	54	06401	M06401	77
05133	M051330000	51	05415	M054150000	54	06402	M06402	64, 77
05135	M051350000	51	05420	M054200000	54	06403	M06403	64, 77
05137	M051370000	51	05425	M054250000	54	06404	M06404	64, 77
05143	M051430000	51	06095	M06095	97	06405	M06405	64, 77
05145	M051450000	51	06312	M06312	63	06406	M06406	64, 77
05147	M051470000	51	06313	M06313	63	06407	M06407	64, 77
05149	M051490000	51	06314	M06314	63	06412	M06412	65
05151	M051510000	51	06315	M06315	63	06413	M06413	65
05153	M051530000	51	06315	M06315	63	06414	M06414	65
05163	M051630000	51	06317	M06317	63	06415	M06415	65
05165	M051650000	51	06332	M06332	63	06416	M06416	65
05167	M051670000	51	06333	M06333	63	06417	M06417	65
05169	M051690000	51	06334	M06334	63	06421	M06421	80
05171	M051710000	51	06335	M06335	63	06422	M06422	65, 80
05173	M051730000	51	06336	M06336	63	06423	M06423	65, 80
05183	M051830000	51	06337	M06337	63	06424	M06424	65, 80
05185	M051850000	52	06352	M06352	63	06425	M06425	65, 80
05187	M051870000	52	06353	M06353	63	06426	M06426	65, 80
05189	M051890000	52	06354	M06354	63	06427	M06427	65, 80
05191	M051910000	52	06355	M06355	63	06462	M06462	65
05193	M051930000	52	06356	M06356	63	06463	M06463	65
05194	M051940000	52	06357	M06357	63	06464	M06464	65
05195	M051950000	52	06357	M06357	66	06465	M06465	65
05196	M051960000	52	06361	M06361	76	06466	M06466	65
05197	M051970000	52	06362	M06362	65, 76	06467	M06467	65
05198	M051980000	52	06362	M06362	76	06471	M06471	81
05199	M051990000	52	06363	M06363	76	06472	M06472	65, 81
05214	M052140000	53	06364	M06364	65	06473	M06473	67
05216	M052160000	53	06364	M06364	76	06473	M06473	81
05224	M052240000	53	06365	M06365	65, 76	06474	M06474	65, 81
05226	M052260000	53	06366	M06366	65, 76	06475	M06475	65, 81
05228	M052280000	53	06367	M06367	76	06476	M06476	67
05230	M052300000	53	06372	M06372	64	06476	M06476	83
05240	M052400000	53	06373	M06373	64	06477	M06477	65, 81
05265	M052650000	53	06374	M06374	64	06482	M06482	66
05266	M052660000	53	06375	M06375	64	06483	M06483	66
05268	M052680000	53	06376	M06376	64	06484	M06484	66
05300	M053000000	52	06381	M06381	75	06485	M06485	66
05302	M053020000	52	06382	M06382	64, 75	06486	M06486	66
05304	M053040000	52	06383	M06383	64, 75	06487	M06487	66
05306	M053060000	52	06384	M06384	64, 75	06491	M06491	82
05308	M053080000	52	06385	M06385	64, 75	06492	M06492	66, 82
05310	M053100000	52	06386	M06386	64, 75	06493	M06493	66, 82
05312	M053120000	52	06387	M06387	64, 75	06494	M06494	66, 82
05314	M053140000	52	06392	M06392	64	06495	M06495	66, 82
05330	M05330	55	06393	M06393	64	06496	M06496	66, 82
05331	M05331	55	06394	M06394	64	06497	M06497	66, 82
05400	M054000000	54	06395	M06395	64	06502	M06502	66

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
06503	M06503	66	06604	M06604	68	06736	M06736	126
06504	M06504	66	06605	M06605	68	06737	M06737	126
06505	M06505	66	06612	M06612	68	06738	M06738	126
06506	M06506	66	06613	M06613	68	06739	M06739	134
06507	M06507	66	06614	M06614	68	06740	M06740	134
06511	M06511	83	06615	M06615	68	06741	M06741	134
06512	M06512	66, 83	06632	M06632	68	06742	M06742	134
06513	M06513	66, 83	06633	M06633	68	06743	M06743	134
06514	M06514	66, 83	06634	M06634	68	06744	M06744	134
06515	M06515	66, 83	06635	M06635	68	06745	M06745	134
06516	M06516	66, 83	06636	M06636	68	06746	M06746	134
06517	M06517	66, 83	06637	M06637	68	06747	M06747	134
06522	M06522	67	06642	M06642	68	06748	M06748	142
06523	M06523	67	06643	M06643	69	06749	M06749	142
06524	M06524	67	06644	M06644	69	06750	M06750	142
06525	M06525	67	06646	M06646	69	06751	M06751	142
06526	M06526	67	06652	M06652	59	06752	M06752	142
06527	M06527	67	06652	M06652	69	06753	M06753	142
06531	M06531	84	06700	M06700	126	06754	M06754	142
06532	M06532	67, 84	06701	M06701	126	06755	M06755	142
06533	M06533	67, 84	06702	M06702	126	06756	M06756	142
06534	M06534	67, 84	06703	M06703	126	06760	M06760	127
06535	M06535	67, 84	06704	M06704	126	06761	M06761	127
06536	M06536	67, 84	06705	M06705	126	06762	M06762	127
06537	M06537	67, 84	06706	M06706	126	06763	M06763	127
06542	M06542	67	06707	M06707	126	06764	M06764	127
06543	M06543	67	06708	M06708	126	06765	M06765	127
06544	M06544	67	06709	M06709	134	06766	M06766	127
06545	M06545	67	06710	M06710	134	06767	M06767	127
06546	M06546	67	06711	M06711	134	06768	M06768	127
06547	M06547	67	06712	M06712	134	06769	M06769	135
06562	M06562	67	06713	M06713	134	06770	M06770	135
06563	M06563	67	06714	M06714	134	06771	M06771	135
06564	M06564	67	06715	M06715	134	06772	M06772	135
06565	M06565	67	06716	M06716	134	06773	M06773	135
06566	M06566	67	06717	M06717	134	06774	M06774	135
06567	M06567	67	06718	M06718	142	06775	M06775	135
06572	M06572	68	06719	M06719	142	06776	M06776	135
06573	M06573	68	06720	M06720	142	06777	M06777	135
06574	M06574	68	06721	M06721	142	06778	M06778	143
06575	M06575	68	06722	M06722	142	06779	M06779	143
06576	M06576	68	06723	M06723	142	06780	M06780	143
06577	M06577	68	06724	M06724	142	06781	M06781	143
06582	M06582	68	06725	M06725	142	06782	M06782	143
06583	M06583	68	06726	M06726	142	06783	M06783	143
06584	M06584	68	06730	M06730	126	06784	M06784	143
06585	M06585	68	06731	M06731	126	06785	M06785	143
06586	M06586	68	06732	M06732	126	06786	M06786	143
06587	M06587	68	06733	M06733	126	06800	M06800	123
06602	M06602	68	06734	M06734	126	06801	M06801	123
06603	M06603	68	06735	M06735	126	06802	M06802	123

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
06803	M06803	123	06874	M06874	124	06940	M06940	141
06804	M06804	123	06875	M06875	124	06941	M06941	141
06805	M06805	123	06876	M06876	124	06942	M06942	141
06808	M06808	131	06877	M06877	124	06943	M06943	141
06809	M06809	131	06878	M06878	124	06944	M06944	141
06810	M06810	131	06879	M06879	124	06945	M06945	141
06811	M06811	131	06882	M06882	132	06999	M06999	124
06812	M06812	131	06883	M06883	132	07000	M07000	124
06813	M06813	131	06884	M06884	132	07001	M07001	124
06816	M06816	139	06885	M06885	132	07005	M07005	132
06817	M06817	139	06886	M06886	132	07006	M07006	132
06818	M06818	139	06887	M06887	132	07007	M07007	132
06819	M06819	139	06890	M06890	140	07008	M07008	132
06820	M06820	139	06891	M06891	140	07009	M07009	132
06821	M06821	139	06892	M06892	140	07010	M07010	132
06824	M06824	123	06893	M06893	140	07013	M07013	140
06825	M06825	123	06894	M06894	140	07014	M07014	140
06826	M06826	123	06895	M06895	140	07015	M07015	140
06827	M06827	123	06896	M06896	124	07016	M07016	140
06828	M06828	123	06897	M06897	124	07017	M07017	140
06829	M06829	123	06898	M06898	124	07018	M07018	140
06830	M06830	131	06900	M06900	125	07021	M07021	124
06831	M06831	131	06901	M06901	125	07022	M07022	124
06832	M06832	131	06902	M06902	125	07023	M07023	124
06833	M06833	131	06903	M06903	125	07024	M07024	124
06834	M06834	131	06904	M06904	125	07025	M07025	124
06835	M06835	131	06905	M06905	125	07026	M07026	124
06838	M06838	139	06908	M06908	133	07030	M07030	132
06839	M06839	139	06909	M06909	133	07031	M07031	132
06840	M06840	139	06910	M06910	133	07032	M07032	132
06842	M06842	139	06911	M06911	133	07033	M07033	132
06842	M06842	139	06912	M06912	133	07034	M07034	132
06843	M06843	139	06913	M06913	133	07035	M07035	132
06850	M06850	131	06916	M06916	141	07038	M07038	140
06851	M06851	131	06917	M06917	141	07039	M07039	140
06852	M06852	131	06918	M06918	141	07040	M07040	140
06853	M06853	131	06919	M06919	141	07041	M07041	140
06854	M06854	131	06920	M06920	141	07042	M07042	140
06855	M06855	131	06921	M06921	141	07043	M07043	140
06858	M06858	123	06924	M06924	125	07046	M07046	125
06859	M06859	123	06925	M06925	125	07047	M07047	125
06860	M06860	123	06926	M06926	125	07048	M07048	125
06861	M06861	123	06927	M06927	125	07049	M07049	125
06862	M06862	123	06928	M06928	125	07050	M07050	125
06863	M06863	123	06929	M06929	125	07051	M07051	125
06866	M06866	139	06932	M06932	133	07055	M07055	133
06867	M06867	139	06933	M06933	133	07056	M07056	133
06868	M06868	139	06934	M06934	133	07057	M07057	133
06869	M06869	139	06935	M06935	133	07058	M07058	133
06870	M06870	139	06936	M06936	133	07059	M07059	133
06871	M06871	139	06937	M06937	133	07060	M07060	133

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
07063	M07063	141	07241	M07241	59, 73	07432	M07432	95
07064	M07064	141	07242	M07242	59, 63, 73	07433	M07433	95
07065	M07065	141	07243	M07243	59, 63, 73	07434	M07434	95
07066	M07066	141	07244	M07244	59, 63, 73	07435	M07435	95
07067	M07067	141	07245	M07245	59, 63, 73	07436	M07436	95
07068	M07068	141	07246	M07246	59, 63, 73	07437	M07437	154
07111	M07111	71	07247	M07247	59, 63, 73	07438	M07438	154
07112	M07112	71	07291	M07291	76	07439	M07439	154
07113	M07113	71	07292	M07292	76	07448	M07448	155
07114	M07114	71	07293	M07293	76	07451	M07451	83
07115	M07115	71	07294	M07294	76	07452	M07452	83
07121	M07121	71	07295	M07295	76	07453	M07453	83
07122	M07122	71	07296	M07296	76	07454	M07454	83
07123	M07123	71	07297	M07297	76	07455	M07455	83
07124	M07124	71	07311	M07311	75	07456	M07456	83
07125	M07125	71	07312	M07312	75	07457	M07457	83
07126	M07126	71	07313	M07313	75	07471	M07471	84
07127	M07127	71	07314	M07314	75	07472	M07472	84
07131	M07131	71	07315	M07315	75	07473	M07473	84
07132	M07132	71	07316	M07316	75	07474	M07474	84
07133	M07133	71	07317	M07317	75	07475	M07475	84
07134	M07134	71	07351	M07351	77	07476	M07476	84
07135	M07135	71	07352	M07352	77	07477	M07477	84
07136	M07136	71	07353	M07353	77	07512	M07512	88
07137	M07137	71	07354	M07354	77	07513	M07513	88
07171	M07171	72	07355	M07355	77	07514	M07514	88
07172	M07172	72	07356	M07356	77	07516	M07516	88
07173	M07173	72	07357	M07357	77	07517	M07517	88
07174	M07174	72	07371	M07371	82	07518	M07518	88
07175	M07175	72	07372	M07372	82	07519	M07519	88
07176	M07176	72	07373	M07373	82	07520	M07520	88
07177	M07177	72	07374	M07374	82	07521	M07521	88
07181	M07181	72	07375	M07375	82	07532	M07532	89
07182	M07182	72	07376	M07376	82	07533	M07533	89
07183	M07183	72	07377	M07377	82	07534	M07534	89
07184	M07184	72	07391	M07391	81	07536	M07536	89
07185	M07185	72	07392	M07392	81	07537	M07537	89
07186	M07186	72	07393	M07393	81	07538	M07538	89
07187	M07187	72	07394	M07394	81	07539	M07539	89
07221	M07221	73	07395	M07395	81	07540	M07540	89
07222	M07222	73	07396	M07396	81	07541	M07541	89
07223	M07223	73	07397	M07397	81	07552	M07552	90
07224	M07224	73	07411	M07411	82	07553	M07553	90
07225	M07225	73	07412	M07412	82	07554	M07554	90
07231	M07231	73	07413	M07413	82	07556	M07556	90
07232	M07232	73	07414	M07414	82	07557	M07557	90
07233	M07233	73	07415	M07415	82	07558	M07558	90
07234	M07234	73	07416	M07416	82	07559	M07559	90
07235	M07235	73	07417	M07417	82	07560	M07560	90
07236	M07236	73	07430	M07430	95	07561	M07561	90
07237	M07237	73	07431	M07431	95	07571	M07571	85

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
07572	M07572	85	07710	M07710	78	07806	M07806	155
07573	M07573	85	07711	M07711	78	07807	M07807	155
07574	M07574	85	07712	M07712	78	07808	M07808	155
07575	M07575	85	07713	M07713	78	07809	M07809	155
07576	M07576	85	07714	M07714	78	07811	M07811	92
07577	M07577	85	07715	M07715	78	07812	M07812	92
07591	M07591	85	07716	M07716	78	07813	M07813	92
07592	M07592	85	07717	M07717	78	07814	M07814	92
07593	M07593	85	07718	M07718	78	07815	M07815	92
07594	M07594	85	07719	M07719	78	07816	M07816	92
07595	M07595	85	07731	M07731	91	07817	M07817	92
07596	M07596	85	07732	M07732	91	07818	M07818	105, 113, 121, 129, 137, 145, 154
07597	M07597	85	07733	M07733	91	07819	M07819	105, 113, 121, 154
07611	M07611	86	07734	M07734	91	07826	M07826	155
07612	M07612	86	07735	M07735	91	07827	M07827	155
07613	M07613	86	07736	M07736	91	07828	M07828	155
07614	M07614	86	07737	M07737	91	07829	M07829	93
07615	M07615	86	07750	M07750	93	07830	M07830	155
07616	M07616	86	07752	M07752	93	07831	M07831	92
07617	M07617	86	07753	M07753	93	07832	M07832	92
07630	M07630	87	07754	M07754	93	07833	M07833	92
07631	M07631	87	07755	M07755	96	07834	M07834	92
07632	M07632	87	07756	M07756	96	07836	M07836	92
07633	M07633	87	07757	M07757	96	07837	M07837	92
07634	M07634	87	07758	M07758	96	07838	M07838	92
07635	M07635	87	07765	M07765	97	07839	M07839	92
07636	M07636	87	07766	M07766	97	07840	M07840	92
07637	M07637	87	07767	M07767	97	07841	M07841	93
07638	M07638	87	07768	M07768	97	07842	M07842	92
07639	M07639	87	07770	M07770	94	07843	M07843	93
07651	M07651	88	07772	M07772	94	07844	M07844	92
07652	M07652	88	07773	M07773	94	07846	M07846	92
07653	M07653	88	07774	M07774	94	07847	M07847	92
07654	M07654	88	07775	M07775	97	07845	M07845	96
07655	M07655	88	07776	M07776	97	07848	M07848	69, 97, 105, 113, 121, 129, 137, 145
07656	M07656	88	07777	M07777	97	07849	M07849	154
07657	M07657	88	07778	M07778	97	07850	M07850	69, 97
07671	M07671	148	07779	M07779	97	07851	M07851	155
07672	M07672	148	07785	M07785	148	07852	M07852	96
07673	M07673	148	07786	M07786	148	07853	M07853	154
07674	M07674	148	07787	M07787	148	07854	M07854	74
07675	M07675	148	07788	M07788	148	07855	M07855	59, 96
07676	M07676	148	07789	M07789	148	07866	M07866	94
07677	M07677	148	07790	M07790	148	07867	M07867	94
07691	M07691	87	07791	M07791	91	07868	M07868	94
07692	M07692	87	07792	M07792	91	07869	M07869	94
07693	M07693	87	07793	M07793	91	07870	M07870	94
07694	M07694	87	07794	M07794	91	07886	M07886	95
07695	M07695	87	07795	M07795	91	07887	M07887	95
07696	M07696	87	07796	M07796	91			
07697	M07697	87	07797	M07797	91			

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
07888	M07888	96	07985	M07985	153	08522	M08522	77
07889	M07889	95	07986	M07986	153	08523	M08523	77
07890	M07890	94	07988	M07988	153	08524	M08524	77
07896	M07896	95	07990	M07990	153	08525	M08525	77
07897	M07897	95	07992	M07992	153, 152	08531	M08531	80
07898	M07898	95	07995	M07995	155	08532	M08532	80
07899	M07899	95	07996	M07996	153	08533	M08533	80
07901	M07901	147	07997	M07997	153	08534	M08534	80
07902	M07902	147	07998	M07998	94	08535	M08535	80
07903	M07903	147	07999	M07999	94	08541	M08541	83
07904	M07904	147	08401	M08401	72	08542	M08542	83
07905	M07905	147	08402	M08402	72	08543	M08543	83
07906	M07906	147	08403	M08403	72	08544	M08544	83
07907	M07907	147	08404	M08404	72	08545	M08545	83
07908	M07908	147	08405	M08405	72	08551	M08551	82
07909	M07909	149	08411	M08411	72	08552	M08552	82
07921	M07921	150	08412	M08412	72	08553	M08553	82
07922	M07922	150	08413	M08413	72	08554	M08554	82
07923	M07923	150	08414	M08414	72	08555	M08555	82
07924	M07924	150	08415	M08415	72	08561	M08561	83
07925	M07925	150	08421	M08421	72	08562	M08562	83
07926	M07926	76, 152	08422	M08422	72	08563	M08563	83
07927	M07927	76, 152	08423	M08423	72	08564	M08564	83
07941	M07941	149	08424	M08424	72	08565	M08565	83
07942	M07942	149	08425	M08425	72	08571	M08571	86
07943	M07943	149	08431	M08431	74	08572	M08572	86
07944	M07944	149	08432	M08432	74	08573	M08573	86
07945	M07945	149	08433	M08433	74	08574	M08574	86
07949	M07949	153	08434	M08434	74	08575	M08575	86
07956	M07956	151, 152	08435	M08435	74	08581	M08581	88
07957	M07957	151, 152	08441	M08441	74	08582	M08582	88
07958	M07958	151, 152	08442	M08442	74	08583	M08583	88
07959	M07959	151, 152	08443	M08443	74	08584	M08584	88
07960	M07960	151	08444	M08444	74	08585	M08585	88
07961	M07961	149	08445	M08445	74	08586	M08586	88
07962	M07962	149	08451	M08451	74	08587	M08587	88
07963	M07963	149	08452	M08452	74	08591	M08591	89
07964	M07964	149	08453	M08453	74	08592	M08592	89
07965	M07965	149	08454	M08454	74	08593	M08593	89
07966	M07966	153	08455	M08455	74	08594	M08594	89
07967	M07967	154	08501	M08501	75	08595	M08595	89
07968	M07968	154	08502	M08502	75	08596	M08596	89
07969	M07969	154	08503	M08503	75	08597	M08597	89
07970	M07970	154	08504	M08504	75	08601	M08601	90
07976	M07976	154	08505	M08505	75	08602	M08602	90
07977	M07977	154	08511	M08511	76	08603	M08603	90
07978	M07978	150	08512	M08512	76	08604	M08604	90
07980	M07980	154	08513	M08513	76	08605	M08605	90
07981	M07981	154	08514	M08514	76	08606	M08606	90
07982	M07982	150	08515	M08515	76	08607	M08607	90
07984	M07984	153	08521	M08521	77	08611	M08611	85

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
08612	M08612	85	08723	M08723	93	08835	M08835	149
08613	M08613	85	08724	M08724	93	08841	M08841	149
08614	M08614	85	08731	M08731	94	08842	M08842	149
08615	M08615	85	08732	M08732	94	08843	M08843	149
08621	M08621	86	08733	M08733	94	08844	M08844	149
08622	M08622	86	08734	M08734	94	08845	M08845	149
08623	M08623	86	08741	M08741	91	08851	M08851	153
08624	M08624	86	08742	M08742	91	08852	M08852	153
08625	M08625	86	08743	M08743	91	08853	M08853	153
08631	M08631	86	08744	M08744	91	08854	M08854	150
08632	M08632	86	08745	M08745	91	08861	M08861	151
08633	M08633	86	08746	M08746	95	08862	M08862	150
08634	M08634	86	08747	M08747	95	08863	M08863	151, 152
08635	M08635	86	08748	M08748	95	08864	M08864	151, 152
08641	M08641	87	08749	M08749	95	08881	M08881	148
08642	M08642	87	08750	M08750	95	08882	M08882	148
08643	M08643	87	08751	M08751	92	08883	M08883	148
08644	M08644	87	08752	M08752	92	08884	M08884	148
08645	M08645	87	08753	M08753	92	08885	M08885	148
08650	M08650	87	08754	M08754	92	08886	M08886	148
08651	M08651	87	08755	M08755	92	08887	M08887	148
08652	M08652	87	08761	M08761	94	09400	M09400	99
08653	M08653	87	08762	M08762	94	09401	M09401	99
08654	M08654	87	08763	M08763	94	09402	M09402	99
08655	M08655	87	08764	M08764	94	09403	M09403	99
08656	M08656	87	08765	M08765	94	09404	M09404	99
08657	M08657	87	08781	M08781	95	09405	M09405	99
08658	M08658	87	08782	M08782	95	09410	M09410	107
08659	M08659	78	08783	M08783	95	09411	M09411	107
08660	M08660	78	08784	M08784	95	09412	M09412	107
08661	M08661	78	08785	M08785	95	09413	M09413	107
08662	M08662	78	08799	M08799	97	09414	M09414	107
08663	M08663	78	08801	M08801	147	09415	M09415	107
08664	M08664	78	08802	M08802	147	09420	M09420	115
08665	M08665	78	08803	M08803	147	09421	M09421	115
08666	M08666	78	08804	M08804	147	09422	M09422	115
08667	M08667	78	08805	M08805	147	09423	M09423	115
08668	M08668	78	08806	M08806	147	09424	M09424	115
08669	M08669	78	08807	M08807	147	09425	M09425	115
08701	M08701	85	08811	M08811	147	09430	M09430	99
08702	M08702	85	08812	M08812	147	09430	M09430	99, 107, 115, 123, 131, 139
08703	M08703	85	08821	M08821	150	09431	M09431	99, 107, 115, 123, 131, 139
08704	M08704	85	08822	M08822	150	09432	M09432	99, 107, 115, 123, 131, 139
08705	M08705	85	08823	M08823	150	09433	M09433	99, 107, 115, 123, 131, 139
08711	M08711	91	08824	M08824	150	09434	M09434	99, 107, 115, 123, 131, 139
08712	M08712	91	08825	M08825	150			
08713	M08713	91	08825	M08825	152			
08714	M08714	91	08831	M08831	149			
08715	M08715	91	08832	M08832	149			
08721	M08721	93	08833	M08833	149			
08722	M08722	93	08834	M08834	149			

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
09435	M09435	99, 107, 115, 123, 131, 139	09510	M09510	100, 108, 116, 124, 132, 140	09573	M09573	108
09440	M09440	99	09511	M09511	100, 108, 116, 124, 132, 140	09574	M09574	108
09441	M09441	99	09512	M09512	100, 108, 116, 124, 132, 140	09575	M09575	108
09442	M09442	99	09513	M09513	100, 108, 116, 124, 132, 140	09580	M09580	116
09443	M09443	99	09514	M09514	100, 108, 116, 124, 132, 140	09581	M09581	116
09444	M09444	99	09515	M09515	100, 108, 116, 124, 132, 140	09582	M09582	116
09445	M09445	99	09520	M09520	100	09583	M09583	116
09450	M09450	107	09521	M09521	100	09584	M09584	116
09451	M09451	107	09522	M09522	100	09585	M09585	116
09452	M09452	107	09523	M09523	100	09590	M09590	100, 108, 116, 124, 132, 140
09453	M09453	107	09524	M09524	100	09591	M09591	100, 108, 116, 124, 132, 140
09454	M09454	107	09525	M09525	100	09592	M09592	100, 108, 116, 124, 132, 140
09455	M09455	107	09530	M09530	108	09593	M09593	100, 108, 116, 124, 132, 140
09460	M09460	115	09531	M09531	108	09594	M09594	100, 108, 116, 124, 132, 140
09461	M09461	115	09532	M09532	108	09595	M09595	100, 108, 116, 124, 132, 140
09462	M09462	115	09533	M09533	108	09600	M09600	101
09463	M09463	115	09534	M09534	108	09601	M09601	101
09464	M09464	115	09535	M09535	108	09602	M09602	101
09465	M09465	115	09540	M09540	116	09603	M09603	101
09470	M09470	99, 107, 115, 123, 131, 139	09541	M09541	116	09604	M09604	101
09471	M09471	99, 107, 115, 123, 131, 139	09542	M09542	116	09605	M09605	101
09472	M09472	99, 107, 115, 123, 131, 139	09543	M09543	116	09610	M09610	109
09473	M09473	99, 107, 115, 123, 131, 139	09544	M09544	116	09611	M09611	109
09474	M09474	99, 107, 115, 123, 131, 139	09545	M09545	116	09612	M09612	109
09475	M09475	99, 107, 115, 123, 131, 139	09550	M09550	100, 108, 116, 124, 132, 136, 140	09613	M09613	109
09480	M09480	100	09551	M09551	100, 108, 116, 124, 132, 136, 140	09614	M09614	109
09481	M09481	100	09552	M09552	100, 108, 116, 124, 132, 136, 140	09615	M09615	109
09482	M09482	100	09553	M09553	100, 108, 116, 124, 132, 136, 140	09620	M09620	117
09483	M09483	100	09554	M09554	100, 108, 116, 124, 132, 136, 140	09621	M09621	117
09484	M09484	100	09555	M09555	100, 108, 116, 124, 132, 136, 140	09622	M09622	117
09485	M09485	100	09560	M09560	100	09623	M09623	117
09490	M09490	108	09561	M09561	100	09624	M09624	117
09491	M09491	108	09562	M09562	100	09625	M09625	117
09492	M09492	108	09563	M09563	100	09640	M09640	102
09493	M09493	108	09564	M09564	100	09641	M09641	102
09494	M09494	108	09565	M09565	100	09642	M09642	102
09495	M09495	108	09570	M09570	108	09643	M09643	102
09500	M09500	116	09571	M09571	108	09644	M09644	102
09501	M09501	116	09572	M09572	108	09645	M09645	102
09502	M09502	116				09646	M09646	102
09503	M09503	116				09647	M09647	102
09504	M09504	116				09648	M09648	102
09505	M09505	116				09650	M09650	110
						09651	M09651	110
						09652	M09652	110

Appendix

Product ID index

Product ID	Order Code	Page
09653	M09653	110
09654	M09654	110
09655	M09655	110
09656	M09656	110
09657	M09657	110
09658	M09658	110
09660	M09660	118
09661	M09661	118
09662	M09662	118
09663	M09663	118
09664	M09664	118
09665	M09665	118
09666	M09666	118
09667	M09667	118
09668	M09668	118
09670	M09670	102, 110, 118, 126, 134, 142
09671	M09671	102, 110, 118, 126, 134, 142
09672	M09672	102, 110, 118, 126, 134, 142
09673	M09673	102, 110, 118, 126, 134, 142
09674	M09674	102, 110, 118, 126, 134, 142
09675	M09675	102, 110, 118, 126, 134, 142
09676	M09676	102, 110, 118, 126, 134, 142
09677	M09677	102, 110, 118, 126, 134, 142
09678	M09678	102, 110, 118, 126, 134, 142
09680	M09680	102
09681	M09681	102
09682	M09682	102
09683	M09683	102
09684	M09684	102
09685	M09685	102
09686	M09686	102
09687	M09687	102
09688	M09688	102
09690	M09690	110
09691	M09691	110
09692	M09692	110
09693	M09693	110
09694	M09694	110
09695	M09695	110
09696	M09696	110
09697	M09697	110
09698	M09698	110

Product ID	Order Code	Page
09700	M09700	118
09701	M09701	118
09702	M09702	118
09703	M09703	118
09704	M09704	118
09705	M09705	118
09706	M09706	118
09707	M09707	118
09708	M09708	118
09710	M09710	102, 110, 118, 126, 134, 142
09711	M09711	102, 110, 118, 126, 134, 142
09712	M09712	102, 110, 118, 126, 134, 142
09713	M09713	102, 110, 118, 126, 134, 142
09714	M09714	102, 110, 118, 126, 134, 142
09715	M09715	102, 110, 118, 126, 134, 142
09716	M09716	102, 110, 118, 126, 134, 142
09717	M09717	102, 110, 118, 126, 134, 142
09718	M09718	102, 110, 118, 126, 134, 142
09720	M09720	103
09721	M09721	103
09722	M09722	103
09723	M09723	103
09724	M09724	103
09725	M09725	103
09726	M09726	103
09727	M09727	103
09728	M09728	103
09730	M09730	111
09731	M09731	111
09732	M09732	111
09733	M09733	111
09734	M09734	111
09735	M09735	111
09736	M09736	111
09737	M09737	111
09738	M09738	111
09740	M09740	119
09741	M09741	119
09742	M09742	119
09743	M09743	119
09744	M09744	119
09745	M09745	119

Product ID	Order Code	Page
09746	M09746	119
09747	M09747	119
09748	M09748	119
09750	M09750	103, 111, 119, 127, 135, 143
09751	M09751	103, 111, 119, 127, 135, 143
09752	M09752	103, 111, 119, 127, 135, 143
09753	M09753	103, 111, 119, 127, 135, 143
09754	M09754	103, 111, 119, 127, 135, 143
09755	M09755	103, 111, 119, 127, 135, 143
09756	M09756	103, 111, 119, 127, 135, 143
09757	M09757	103, 111, 119, 127, 135, 143
09758	M09758	103, 111, 119, 127, 135, 143
09760	M09760	104, 128
09761	M09761	104, 128
09762	M09762	104, 128
09763	M09763	112, 136
09764	M09764	112, 136
09765	M09765	112, 136
09766	M09766	120, 144
09767	M09767	120, 144
09768	M09768	120, 144
09770	M09770	148
09771	M09771	148
09772	M09772	148
09773	M09773	148
09774	M09774	148
09775	M09775	148
09776	M09776	148
09777	M09777	148
09778	M09778	148
09779	M09779	148
09800	M09800	104, 128
09801	M09801	104, 128
09802	M09802	104, 128
09803	M09803	112, 136
09804	M09804	112, 136
09805	M09805	112, 136
09806	M09806	120, 144
09807	M09807	120, 144
09808	M09808	120, 144
09900	M09900	104
09901	M09901	112

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
09902	M09902	120	09968	M09968	109	1SL7162A00	1SL7162A00	71
09903	M09903	105, 113, 121, 129, 137, 145	09969	M09969	109	1SL7163A00	1SL7163A00	71
09904	M09904	105, 113, 121	09970	M09970	109	1SL7164A00	1SL7164A00	71
09905	M09905	105, 113, 121, 129, 137, 145	09971	M09971	109	1SL7165A00	1SL7165A00	71
09910	M09910	128	09972	M09972	109	1SL7261A00	1SL7261A00	73
09911	M09911	136	09973	M09973	109	1SL7262A00	1SL7262A00	73
09912	M09912	144	09974	M09974	117	1SL7263A00	1SL7263A00	73
09920	M09920	101, 125	09975	M09975	117	1SL7264A00	1SL7264A00	73
09921	M09921	101, 125	09976	M09976	117	1SL7265A00	1SL7265A00	73
09922	M09922	101, 125	09978	M09978	117	1SL7271A00	1SL7271A00	73
09923	M09923	101, 125	09979	M09979	117	1SL7272A00	1SL7272A00	73
09924	M09924	101, 125	09980	M09980	101	1SL7273A00	1SL7273A00	73
09925	M09925	101, 125	09981	M09981	101	1SL7274A00	1SL7274A00	73
09927	M09927	109, 133	09982	M09982	101	1SL7275A00	1SL7275A00	73
09928	M09928	109, 133	09983	M09983	101	1SL7281A00	1SL7281A00	73
09929	M09929	109, 133	09984	M09984	101	1SL7282A00	1SL7282A00	73
09930	M09930	109, 133	09985	M09985	101	1SL7283A00	1SL7283A00	73
09931	M09931	109, 133	09986	M09986	109	1SL7284A00	1SL7284A00	73
09932	M09932	109, 133	09987	M09987	109	1SL7285A00	1SL7285A00	73
09934	M09934	117, 141	09988	M09988	109	1SL7301A00	1SL7301A00	76
09935	M09935	117, 141	09989	M09989	109	1SL7302A00	1SL7302A00	76
09936	M09936	117, 141	09990	M09990	109	1SL7303A00	1SL7303A00	76
09937	M09937	117, 141	09991	M09991	109	1SL7304A00	1SL7304A00	76
09938	M09938	117, 141	09992	M09992	117	1SL7305A00	1SL7305A00	76
09939	M09939	117, 141	09993	M09993	117	1SL7321A00	1SL7321A00	75
09941	M09941	101, 125	09994	M09994	117	1SL7322A00	1SL7322A00	75
09942	M09942	101, 125	09995	M09995	117	1SL7323A00	1SL7323A00	75
09943	M09943	101, 125	09996	M09996	117	1SL7324A00	1SL7324A00	75
09944	M09944	101, 125	09997	M09997	117	1SL7325A00	1SL7325A00	75
09945	M09945	101, 125	1SL0060A00	1SL0060A00	32	1SL7361A00	1SL7361A00	77
09946	M09946	101, 125	1SL0061A00	1SL0061A00	32	1SL7362A00	1SL7362A00	77
09948	M09948	109, 133	1SL0062A00	1SL0062A00	32	1SL7363A00	1SL7363A00	77
09949	M09949	109, 133	1SL0064A00	1SL0064A00	32	1SL7364A00	1SL7364A00	77
09950	M09950	109, 133	1SL5316A00	1SL5316A00	49	1SL7365A00	1SL7365A00	77
09951	M09951	109, 133	1SL5317A00	1SL5317A00	49	1SL7381A00	1SL7381A00	80
09952	M09952	109, 133	1SL5318A00	1SL5318A00	49	1SL7382A00	1SL7382A00	80
09953	M09953	109, 133	1SL5319A00	1SL5319A00	49	1SL7383A00	1SL7383A00	80
09955	M09955	117, 141	1SL5320A00	1SL5320A00	49	1SL7384A00	1SL7384A00	80
09956	M09956	117, 141	1SL5321A00	1SL5321A00	49	1SL7385A00	1SL7385A00	80
09957	M09957	117, 141	1SL5322A00	1SL5322A00	49	1SL7401A00	1SL7401A00	81
09958	M09958	117, 141	1SL7141A00	1SL7141A00	71	1SL7402A00	1SL7402A00	81
09959	M09959	117, 141	1SL7142A00	1SL7142A00	71	1SL7403A00	1SL7403A00	81
09960	M09960	117, 141	1SL7143A00	1SL7143A00	71	1SL7404A00	1SL7404A00	81
09962	M09962	101	1SL7144A00	1SL7144A00	71	1SL7405A00	1SL7405A00	81
09963	M09963	101	1SL7145A00	1SL7145A00	71	1SL7421A00	1SL7421A00	82
09964	M09964	101	1SL7151A00	1SL7151A00	71	1SL7422A00	1SL7422A00	82
09965	M09965	101	1SL7152A00	1SL7152A00	71	1SL7423A00	1SL7423A00	82
09966	M09966	101	1SL7153A00	1SL7153A00	71	1SL7424A00	1SL7424A00	82
09967	M09967	101	1SL7154A00	1SL7154A00	71	1SL7425A00	1SL7425A00	82
			1SL7155A00	1SL7155A00	71	1SL7440A00	1SL7440A00	95
			1SL7161A00	1SL7161A00	71	1SL7441A00	1SL7441A00	95

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
1SL7442A00	1SL7442A00	95	1SL7642A00	1SL7642A00	87	1SL7804A00	1SL7804A00	91
1SL7443A00	1SL7443A00	95	1SL7643A00	1SL7643A00	87	1SL7805A00	1SL7805A00	91
1SL7444A00	1SL7444A00	95	1SL7644A00	1SL7644A00	87	1SL7821A00	1SL7821A00	92
1SL7461A00	1SL7461A00	83	1SL7645A00	1SL7645A00	87	1SL7822A00	1SL7822A00	92
1SL7462A00	1SL7462A00	83	1SL7646A00	1SL7646A00	87	1SL7823A00	1SL7823A00	92
1SL7463A00	1SL7463A00	83	1SL7647A00	1SL7647A00	87	1SL7824A00	1SL7824A00	92
1SL7464A00	1SL7464A00	83	1SL7648A00	1SL7648A00	87	1SL7825A00	1SL7825A00	92
1SL7465A00	1SL7465A00	83	1SL7649A00	1SL7649A00	87	1SL7856A00	1SL7856A00	97
1SL7481A00	1SL7481A00	84	1SL7661A00	1SL7661A00	86	1SL7861A00	1SL7861A00	94
1SL7482A00	1SL7482A00	84	1SL7662A00	1SL7662A00	86	1SL7862A00	1SL7862A00	94
1SL7483A00	1SL7483A00	84	1SL7663A00	1SL7663A00	86	1SL7863A00	1SL7863A00	94
1SL7484A00	1SL7484A00	84	1SL7664A00	1SL7664A00	86	1SL7864A00	1SL7864A00	94
1SL7485A00	1SL7485A00	84	1SL7665A00	1SL7665A00	86	1SL7865A00	1SL7865A00	94
1SL7522A00	1SL7522A00	88	1SL7681A00	1SL7681A00	148	1SL7881A00	1SL7881A00	95
1SL7523A00	1SL7523A00	88	1SL7682A00	1SL7682A00	148	1SL7882A00	1SL7882A00	95
1SL7524A00	1SL7524A00	88	1SL7683A00	1SL7683A00	148	1SL7883A00	1SL7883A00	95
1SL7526A00	1SL7526A00	88	1SL7684A00	1SL7684A00	148	1SL7884A00	1SL7884A00	95
1SL7527A00	1SL7527A00	88	1SL7685A00	1SL7685A00	148	1SL7885A00	1SL7885A00	95
1SL7528A00	1SL7528A00	88	1SL7686A00	1SL7686A00	148	1SL7911A00	1SL7911A00	147
1SL7529A00	1SL7529A00	88	1SL7687A00	1SL7687A00	148	1SL7912A00	1SL7912A00	147
1SL7542A00	1SL7542A00	89	1SL7701A00	1SL7701A00	87	1SL7913A00	1SL7913A00	147
1SL7543A00	1SL7543A00	89	1SL7702A00	1SL7702A00	87	1SL7914A00	1SL7914A00	147
1SL7544A00	1SL7544A00	89	1SL7703A00	1SL7703A00	87	1SL7915A00	1SL7915A00	147
1SL7546A00	1SL7546A00	89	1SL7704A00	1SL7704A00	87	1SL7916A00	1SL7916A00	147
1SL7547A00	1SL7547A00	89	1SL7705A00	1SL7705A00	87	1SL7917A00	1SL7917A00	147
1SL7548A00	1SL7548A00	89	1SL7720A00	1SL7720A00	78	1SL7918A00	1SL7918A00	147
1SL7549A00	1SL7549A00	89	1SL7721A00	1SL7721A00	78	1SL7919A00	1SL7919A00	147
1SL7562A00	1SL7562A00	90	1SL7722A00	1SL7722A00	78	1SL7931A00	1SL7931A00	150
1SL7563A00	1SL7563A00	90	1SL7723A00	1SL7723A00	78	1SL7932A00	1SL7932A00	150
1SL7564A00	1SL7564A00	90	1SL7724A00	1SL7724A00	78	1SL7933A00	1SL7933A00	150
1SL7566A00	1SL7566A00	90	1SL7725A00	1SL7725A00	78	1SL7934A00	1SL7934A00	150
1SL7567A00	1SL7567A00	90	1SL7726A00	1SL7726A00	78	1SL7935A00	1SL7935A00	150
1SL7568A00	1SL7568A00	90	1SL7727A00	1SL7727A00	78	1SL7947A00	1SL7947A00	151
1SL7569A00	1SL7569A00	90	1SL7728A00	1SL7728A00	78	1SL7947A00	1SL7947A00	152
1SL7581A00	1SL7581A00	85	1SL7729A00	1SL7729A00	78	1SL7948A00	1SL7948A00	151
1SL7582A00	1SL7582A00	85	1SL7741A00	1SL7741A00	91	1SL7948A00	1SL7948A00	152
1SL7583A00	1SL7583A00	85	1SL7742A00	1SL7742A00	91	1SL7951A00	1SL7951A00	149
1SL7584A00	1SL7584A00	85	1SL7743A00	1SL7743A00	91	1SL7952A00	1SL7952A00	149
1SL7585A00	1SL7585A00	85	1SL7744A00	1SL7744A00	91	1SL7953A00	1SL7953A00	149
1SL7601A00	1SL7601A00	85	1SL7745A00	1SL7745A00	91	1SL7954A00	1SL7954A00	149
1SL7602A00	1SL7602A00	85	1SL7760A00	1SL7760A00	93	1SL7955A00	1SL7955A00	149
1SL7603A00	1SL7603A00	85	1SL7762A00	1SL7762A00	93	1SL7971A00	1SL7971A00	149
1SL7604A00	1SL7604A00	85	1SL7763A00	1SL7763A00	93	1SL7972A00	1SL7972A00	149
1SL7605A00	1SL7605A00	85	1SL7764A00	1SL7764A00	93	1SL7973A00	1SL7973A00	149
1SL7621A00	1SL7621A00	86	1SL7780A00	1SL7780A00	94	1SL7974A00	1SL7974A00	149
1SL7622A00	1SL7622A00	86	1SL7782A00	1SL7782A00	94	1SL7975A00	1SL7975A00	149
1SL7624A00	1SL7624A00	86	1SL7783A00	1SL7783A00	94	1SL7979A00	1SL7979A00	150
1SL7625A00	1SL7625A00	88	1SL7784A00	1SL7784A00	94	1SL7983A00	1SL7983A00	150
1SL76283A00	1SL76283A00	86	1SL7801A00	1SL7801A00	91	1SL7987A00	1SL7987A00	153
1SL7640A00	1SL7640A00	87	1SL7802A00	1SL7802A00	91	1SL7989A00	1SL7989A00	153
1SL7641A00	1SL7641A00	87	1SL7803A00	1SL7803A00	91	1SL7991A00	1SL7991A00	153

Product ID	Order Code	Page	Product ID	Order Code	Page	Product ID	Order Code	Page
1SL7993A00	1SL7993A00	151	1SL9823A00	1SL9823A00	57	1SL9928A00	1SL9928A00	58
1SL7993A00	1SL7993A00	152	1SL9824A00	1SL9824A00	57	1SLM001010A0001	1SLM001010A0001	59
1SL9019A00	1SL9019A00	48	1SL9825A00	1SL9825A00	57	1SLM001010A0002	1SLM001010A0002	59
1SL9033A00	1SL9033A00	48	1SL9826A00	1SL9826A00	57	1SLM001010A0003	1SLM001010A0003	59
1SL9035A00	1SL9035A00	48	1SL9844A00	1SL9844A00	57	1SLM001010A0004	1SLM001010A0004	59
1SL9037A00	1SL9037A00	48	1SL9845A00	1SL9845A00	57	1SLM001010A0005	1SLM001010A0005	59
1SL9043A00	1SL9043A00	48	1SL9846A00	1SL9846A00	57	1SLM001010A0006	1SLM001010A0006	59
1SL9045A00	1SL9045A00	48	1SL9847A00	1SL9847A00	57	1SLM001010A0007	1SLM001010A0007	59
1SL9047A00	1SL9047A00	48	1SL9848A00	1SL9848A00	57	1SLM001020A0001	1SLM001020A0001	59
1SL9049A00	1SL9049A00	48	1SL9849A00	1SL9849A00	57	1SLM001020A0002	1SLM001020A0002	59
1SL9051A00	1SL9051A00	48	1SL9850A00	1SL9850A00	57	1SLM001020A0003	1SLM001020A0003	59
1SL9053A00	1SL9053A00	48	1SL9868A00	1SL9868A00	58	1SLM001020A0004	1SLM001020A0004	59
1SL9063A00	1SL9063A00	48	1SL9869A00	1SL9869A00	58	1SLM001020A0005	1SLM001020A0005	60
1SL9065A00	1SL9065A00	48	1SL9870A00	1SL9870A00	58	1SLM001020A0006	1SLM001020A0006	60
1SL9067A00	1SL9067A00	48	1SL9871A00	1SL9871A00	58	1SLM001020A0007	1SLM001020A0007	60
1SL9069A00	1SL9069A00	48	1SL9872A00	1SL9872A00	58	1SLM001020A0008	1SLM001020A0008	60
1SL9071A00	1SL9071A00	48	1SL9873A00	1SL9873A00	58	1SLM001020A0009	1SLM001020A0009	60
1SL9073A00	1SL9073A00	48	1SL9874A00	1SL9874A00	58	1SLM001020A0010	1SLM001020A0010	60
1SL9083A00	1SL9083A00	48	1SL9876A00	1SL9876A00	59	1SLM001020A0011	1SLM001020A0011	61
1SL9085A00	1SL9085A00	48	1SL9877A00	1SL9877A00	59	1SLM001020A0012	1SLM001020A0012	60
1SL9087A00	1SL9087A00	48	1SL9878A00	1SL9878A00	59	1SLM001020A0013	1SLM001020A0013	60
1SL9089A00	1SL9089A00	48	1SL9878A01	1SL9878A01	59	1SLM001020A0014	1SLM001020A0014	61
1SL9091A00	1SL9091A00	48	1SL9879A00	1SL9879A00	60	1SLM001020A0015	1SLM001020A0015	61
1SL9093A00	1SL9093A00	48	1SL9880A00	1SL9880A00	60	1SLM001020A0016	1SLM001020A0016	61
1SL9095A00	1SL9095A00	48	1SL9881A00	1SL9881A00	60	1SLM001020A0017	1SLM001020A0017	151
1SL9096A00	1SL9096A00	48	1SL9882A00	1SL9882A00	60	1SLM001020A0018	1SLM001020A0018	151
1SL9097A00	1SL9097A00	48	1SL9883A00	1SL9883A00	60	1SLM001020A0019	1SLM001020A0019	151
1SL9098A00	1SL9098A00	48	1SL9884A00	1SL9884A00	60	1SLM001020A0020	1SLM001020A0020	147
1SL9119A00	1SL9119A00	49	1SL9888A00	1SL9888A00	60	1SLM001020A0021	1SLM001020A0021	147
1SL9133A00	1SL9133A00	49	1SL9889A00	1SL9889A00	60	1SLM001020A0022	1SLM001020A0022	147
1SL9135A00	1SL9135A00	49	1SL9890A00	1SL9890A00	61	1SLM001020A0023	1SLM001020A0023	147
1SL9137A00	1SL9137A00	49	1SL9891A00	1SL9891A00	61	1SLM001020A0024	1SLM001020A0024	147
1SL9143A00	1SL9143A00	49	1SL9892A00	1SL9892A00	61	1SLM001020A0025	1SLM001020A0025	147
1SL9145A00	1SL9145A00	49	1SL9893A00	1SL9893A00	61	1SLM001020A0026	1SLM001020A0026	151
1SL9147A00	1SL9147A00	49	1SL9895A00	1SL9895A00	151, 152	1SLM001020A0027	1SLM001020A0027	153
1SL9149A00	1SL9149A00	49	1SL9896A00	1SL9896A00	151, 152	1SLM001020A0028	1SLM001020A0028	155
1SL9151A00	1SL9151A00	49	1SL9897A00	1SL9897A00	151, 152	1SLM001020A0029	1SLM001020A0029	155
1SL9153A00	1SL9153A00	49	1SL9902A00	1SL9902A00	61	1SLM001020A0030	1SLM001020A0030	155
1SL9163A00	1SL9163A00	49	1SL9904A00	1SL9904A00	59	1SLM001020A0031	1SLM001020A0031	155
1SL9165A00	1SL9165A00	49	1SL9910A00	1SL9910A00	61	2CSK1625CH	2CSK1625CH	26
1SL9167A00	1SL9167A00	49	1SL9911A00	1SL9911A00	61	2CSK1626CH	2CSK1626CH	26
1SL9169A00	1SL9169A00	49	1SL9912A00	1SL9912A00	61	M078550002	M078550002	78
1SL9171A00	1SL9171A00	49	1SL9913A00	1SL9913A00	61	M999120000	M999120000	78
1SL9173A00	1SL9173A00	49	1SL9914A00	1SL9914A00	61	M999130000	M999130000	78
1SL9183A00	1SL9183A00	49	1SL9915A00	1SL9915A00	61	M999140000	M999140000	78
1SL9185A00	1SL9185A00	49	1SL9916A00	1SL9916A00	61	M999150000	M999150000	78
1SL9187A00	1SL9187A00	49	1SL9923A00	1SL9923A00	58	M999160000	M999160000	78
1SL9189A00	1SL9189A00	49	1SL9924A00	1SL9924A00	58	M999170000	M999170000	78
1SL9191A00	1SL9191A00	49	1SL9925A00	1SL9925A00	58	M999180000	M999180000	78
1SL9193A00	1SL9193A00	49	1SL9926A00	1SL9926A00	58	PF35X75X	1SLM001000A0001	57
1SL9822A00	1SL9822A00	57	1SL9927A00	1SL9927A00	58	PF35X100X	1SLM001000A0002	57

Appendix

Product ID index

Product ID	Order Code	Page	Product ID	Order Code	Page
PF35X150X	1SLM001000A0003	57	PF100X300X	1SLM001000A0023	60
PF35X200X	1SLM001000A0004	57	PF100X400EZ	7TFP000000R2186	60
PF35X300X	1SLM001000A0005	57	PF100X400X	1SLM001000A0024	60
PF50X75X	1SLM001000A0006	57	PF100X500EZ	7TFP000000R2181	60
PF50X100X	1SLM001000A0007	57	PF100X500X	1SLM001000A0025	60
PF50X150X	1SLM001000A0008	57	PF35X100EZ	7TFP000000R2187	57
PF50X200X	1SLM001000A0009	57	PF35X150EZ	7TFP000000R2188	57
PF50X300X	1SLM001000A0010	57	PF35X200EZ	7TFP000000R2189	57
PF50X400X	1SLM001000A0011	57	PF35X300EZ	7TFP000000R2190	57
PF50X500X	1SLM001000A0012	57	PF35X75EZ	7TFP000000R2191	57
PF75X75X	1SLM001000A0013	58	PF50X100EZ	7TFP000000R2192	57
PF75X100X	1SLM001000A0014	58	PF50X150EZ	7TFP000000R2193	57
PF75X150X	1SLM001000A0015	58	PF50X200EZ	7TFP000000R2194	57
PF75X200X	1SLM001000A0016	60	PF50X300EZ	7TFP000000R2195	57
PF75X300X	1SLM001000A0017	60	PF50X400EZ	7TFP000000R2196	57
PF75X400X	1SLM001000A0018	60	PF50X500EZ	7TFP000000R2197	57
PF75X500X	1SLM001000A0019	60	PF50X75EZ	7TFP000000R2198	57
PF100X100EZ	7TFP000000R2182	60	PF75X100EZ	7TFP000000R2199	58
PF100X100X	1SLM001000A0020	60	PF75X150EZ	7TFP000000R2961	58
PF100X150EZ	7TFP000000R2183	60	PF75X200EZ	7TFP000000R2201	58
PF100X150X	1SLM001000A0021	60	PF75X300EZ	7TFP000000R2202	58
PF100X200EZ	7TFP000000R2184	60	PF75X400EZ	7TFP000000R2203	58
PF100X200X	1SLM001000A0022	60	PF75X500EZ	7TFP000000R2962	58
PF100X300EZ	7TFP000000R2185	60	PF75X75EZ	7TFP000000R2205	58

Additional information

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.



—
Electrification business

ABB S.p.A.

Installation Products
Via Luciano Lama, 33
20099 Sesto San Giovanni (MI)
T. +39 0224141

new.abb.com/low-voltage