

Snap-in markers - UC-EM (17,5X7,5) - 0825495

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Snap-in markers, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: snapped into marker carrier, Lettering field: 17.5 x 7.5 mm



Why buy this product

- ✓ The UC-EM ... UniCard labeling range includes markers for devices and switching devices from a wide range of manufacturers
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The wide temperature range means that the labels can be used in control cabinets as well as the field
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 364263
Weight per Piece (excluding packing)	9.77 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	17.5 mm
Width (a)	7.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA

Snap-in markers - UC-EM (17,5X7,5) - 0825495

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	20
Number of individual labels per row	5
Printability	Inkjet printing
	Plotter
Device	5147888 BLUEMARK LED
	5147999 BLUEMARK CLED
	5144615 CMS-P1-PLOTTER
	5146121 P1 UC-MAG 6
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	snapped into marker carrier

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

Snap-in markers - UC-EM (17,5X7,5) - 0825495

Classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 5 - 5146118



Magazine, for CMS-P1-PLOTTER, for accommodating UC1-TM..., UC1U-TM...

Drawings

Pictogram

