

Magnifying lamp with 60 LEDs, 190x157 mm rectangular polished glass lens, 5 diopter magnification, clamp mounting, 26 watts



LUX177-5D60SMD

Introduction :

Magnifying lamp equipped with a 190x157 mm polished glass lens and 5 diopter magnification, offering high reliability thanks to its 80 cm articulated arm. It is equipped with 60 SMD technology LEDs, allowing it to also be used as a desk lamp. A switch and protective cover on the top allow the magnifying lamp to be used. The magnifying head can be easily adjusted to find the best working position. Ideal for model making, watchmaking, DIY, sewing, electronics, and more.

Hardware & Electrical specifications :

- Polished rectangular glass lens.
- Dimensions lens : 190x157 mm.
- Magnification: 5 diopters.
- Lens protection cover.
- Illumination by 60 SMD LEDs.
- Color temperature: 6000°K.
- Brightness: 650 lumens.
- 230Vac power supply.
- Adapter: 24Vdc 0.600A.
- Power consumption: 26W.
- On/off switch.
- 180° horizontal and vertical adjustment.
- Vise clamp mounting.
- Manually adjustable articulated arm.
- Arm length: 80 cm.
- Magnifying lamp weight: 3,980 kg.
- Packaging dimensions: 53 x 35 x 13 cm.
- Packaging weight: 4,640 kg.

Lens protection cover

Articulated arm



Vise clamp

