


FEATURES

- **Thermal Conductivity of 1.6 W/mK:** Provides effective heat transfer, enhancing device performance.
- **Operating Temperature Range of -60 °C to 240 °C:** Suitable for a wide range of environments.
- **Thickness of 0.25 mm:** Offers a low-profile solution for tight spaces.
- **Non-Adhesive:** Allows for easy repositioning and removal without residue.
- **Compliance with ANSI-ESD S20.20:2021, REACH, RoHS:** Meets key safety and environmental standards.

RS PRO 19 mm Thermal Conductive Pad, Brick Red

RS Stock No: 655-986



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO thermal conductive pad is designed to efficiently transfer heat between components and heat sinks, ensuring optimal thermal management in electronic devices. With a thermal conductivity of 1.6 W/mK, it is ideal for applications requiring reliable heat dissipation. The pad's brick red colour makes it easily identifiable during installation.

General Specifications

Colour	Brick Red
Product Type	Thermal Conductive Pad
Self-Adhesive	No

Mechanical Specifications

Length	19 mm
Thickness	0.25 mm
Width	25.4 mm

Operation Environment Specifications

Maximum Operating Temperature	240 °C
Minimum Operating Temperature	-60 °C

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH, RoHS
---------------------	-----------------------------------

Thermal Performance Specifications

Thermal Conductivity	1.6 W/mK
----------------------	----------