


Geberit Mapress Stainless Steel T-piece with female thread (silicone-free)



Example image



APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water $\leq 120\text{ }^{\circ}\text{C}$
- For saturated steam $\leq 120\text{ }^{\circ}\text{C}$
- For service water and process water
- For treated water
- For grey and black water with a pH value ≥ 5.5

- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- For technical building systems, industry and shipbuilding

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
81304	12 / 15 / 12	15	1/2	15	90	6.4	4	3.2	3.2	1.2	2.7	1.2
81305	15	18	1/2	18	90	6.8	4.2	3.4	3.4	1.4	2.9	1.4
81306	15 / 20 / 15	18	3/4	18	90	6.8	4.4	3.4	3.4	1.4	2.9	1.4
81307	20 / 15 / 20	22	1/2	22	90	7.4	4.3	3.7	3.7	1.6	3	1.6

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
81308	20	22	3/4	22	90	7.4	4.6	3.7	3.7	1.6	3.1	1.6
81309	25 / 15 / 25	28	1/2	28	90	8.4	4.6	4.2	4.2	1.9	3.3	1.9
81310	25 / 20 / 25	28	3/4	28	90	8.4	4.9	4.2	4.2	1.9	3.4	1.9
81311	25	28	1	28	90	8.4	5.3	4.2	4.2	1.9	3.6	1.9
81312	32 / 15 / 32	35	1/2	35	90	10	5	5	5	2.4	3.7	2.4
81313	32 / 20 / 32	35	3/4	35	90	10	5.3	5	5	2.4	3.8	2.4
81316	40 / 15 / 40	42	1/2	42	90	11.4	5.3	5.7	5.7	2.7	4	2.7
81317	40 / 20 / 40	42	3/4	42	90	11.4	5.6	5.7	5.7	2.7	4.1	2.7
81320	50 / 15 / 50	54	1/2	54	90	13.8	5.9	6.9	6.9	3.4	4.6	3.4
81321	50 / 20 / 50	54	3/4	54	90	13.8	6.2	6.9	6.9	3.4	4.7	3.4
81324	50	54	2	54	90	13.8	7.9	6.9	6.9	3.4	5.6	3.4
81326	65 / 20 / 65	76.1	3/4	76.1	90	23	7.4	11.5	11.5	6.2	5.9	6.2
81331	80 / 20 / 80	88.9	3/4	88.9	90	26	8	13	13	7	6.5	7

Art. no.	DN	d, ø mm	Rp "	d1, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
81334	80 / 50 / 80	88.9	2	88.9	90	26	9.7	13	13	7	7.4	7
81336	100 / 20 / 100	108	3/4	108	90	31	9	15.5	15.5	8	7.5	8
81339	100 / 50 / 100	108	2	108	90	31	10.7	15.5	15.5	8	8.4	8