

TX565


Single use glove, 100% nitrile, powder free, 240mm long, 0.14mm thick, AQL 0.65

Premium performance, powder-free, extended cuff, nitrile single-use glove with AQL 0.65. Dual certified (Industrial and Medical), extremely strong and high chemical and puncture resistance.

Features

- 100% premium quality nitrile
- Palm thickness 0.14mm (5.5 mil), weight 8.5g (size M), 240mm long
- High resistance to penetration and projections of many chemicals
- Chlorinated inside to offer more comfort and reduce friction when donning
- Approved for food handling
- Medical device compliant (MDD 93/42/EEC), conforms to EN455 (all parts)
- Tested to ASTM D6978-05 (2023) against 24 chemotherapy drugs
- Silicone free to allow usage in bonding/painting operations (paints, coatings, primers, adhesives)

Certifications



Suitable industries & applications

Industries

- Chemicals
- Food Production
- Healthcare
- Manufacturing
- Oil and Gas

Applications

- Chemical Handling and Containment
- Component and Product Assembly
- Food Preparation and Handling
- Handling Wet Oily or Greasy Materials
- Painting and Finishing

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

Sales@GlobalGlove.com
763-450-0110

TX565

Single use glove, 100% nitrile, powder free, 240mm long, 0.14mm thick, AQL 0.65

Product information

Materials	Liner:	Nitrile
	Coating:	Uncoated
Colour	Purple	
Cuff Style	Beaded	

Ordering information

6/XS	SKG00565IB	Items per Case 10 x Box of 100
7/S	SKG00565ID	
8/M	SKG00565IF	
9/L	SKG00565IH	
10/XL	SKG00565IJ	
11/XXL	SKG00565IL	

Additional information

Certification legend




or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

Sales@GlobalGlove.com
763-450-0110