



Technical data

NUKR90H/3AS

Cam follower with shaft

PRODUCT DEFINITION

Brand	NTN
D - External diameter	90 mm
d1 - Stud diameter	30 mm
C - Width of bearing, drawn cup or outer ring	35 mm
F - Under roller diameter	47,5 mm
B - Bearing/Inner ring width	37 mm
B1 - Total stud length	100 mm
B2 - Stud rod length	63 mm
G - Stud thread designation	M30X1.5
G1 - Thread length of the stud	32 mm
B3 - Distance between washer face and radial lub hole	15 mm
C1 - Distance between roller face and washer face	1 mm
n - Axial lubrication hole diameter	8 mm
a - Radial lubrication hole diameter	4 mm
e - Inlet diameter of roller or washer	51 mm
h - Hexagonal hole	8 mm
R - Track roller radius	500 mm
Maximum tightening torque	360 N-m
Bearing with/without cage	Sans



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Radial clearance class	CN
Precision class	P0
Mass	1,96 kg

PRODUCT PERFORMANCE

Cr - Dynamic load rating	101000000 mN
C0r - Static load rating	151000000 mN
Track load capacity spherical outer ring	11400000 mN
N lim - Grease lubrication limit speed	12600 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

