



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 202 – 810 CMA

Stud Size: #2, M2

Features

Product Type Features

|                                        |                             |
|----------------------------------------|-----------------------------|
| Ring Terminal Product Type             | Closed Ring Tongue Terminal |
| Stud Size                              | #2, M2                      |
| Sealable                               | No                          |
| Wire Insulation Support Retention Type | Non-Insulation Support      |

Configuration Features

|                 |   |
|-----------------|---|
| Number of Holes | 1 |
|-----------------|---|

Body Features

|                |        |
|----------------|--------|
| Product Weight | .115 g |
|----------------|--------|

Contact Features

|                           |          |
|---------------------------|----------|
| Barrel Type               | Closed   |
| Terminal Orientation      | Straight |
| Terminal Plating Material | Tin      |

Mechanical Attachment

|                         |         |
|-------------------------|---------|
| Wire Insulation Support | Without |
|-------------------------|---------|

Dimensions



|                        |                   |
|------------------------|-------------------|
| Wire Size              | 202 – 810 CMA     |
| Stud Diameter          | 2.36 mm[.093 in]  |
| Tongue Thickness       | .79 mm[.031 in]   |
| Product Length         | 10.64 mm[.419 in] |
| Barrel Inside Diameter | .89 mm[.035 in]   |

Usage Conditions

|                   |             |
|-------------------|-------------|
| Insulation Option | Uninsulated |
|-------------------|-------------|

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |         |
|--------------------|---------|
| Packaging Quantity | 1000    |
| Packaging Method   | Package |

Other

|      |        |
|------|--------|
| Line | Budget |
|------|--------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                            |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




REPRESENTATION ONLY

TE Part # 69363  
DAHT STRATO SOLIS 26-20 ASSY


Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)



Ring Terminals(106)



Spade Terminals(46)

Customers Also Bought



TE Part #6609047-5  
20VT1 J0=F7814



TE Part #1-6609031-3  
10ER1=F7189



TE Part #1-320551-3  
TERMINAL,PIDG R IR 20 8



TE Part #2271195-1  
RPC-M12X-FF-8CON-M16-LAU





TE Part #2118706-2  
1 PC STD SHIELD, CRS-13.66X12.70X2.54MM



TE Part #FTRA6171M5PW-001  
OMNI,Ph,PMT,617-7125MHz



TE Part #ASL206-05SN-HE  
RECEPT.ASSY.PCB. 2 HOLE MNT. MICRO MK3



TE Part #2081679-1  
SMA JACK RECEPTACLE,PCB,RIGHT ANGLE,6GHZ



TE Part #31423  
TERMINAL,BUDG R 26-22, 0



TE Part #T4131012021-000  
M12,REAR MOUNT,FEMALE,A,2P, SOLDER WIRE

Documents

Product Drawings  
TERMINAL,BUDG R 26-22 2

English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_322771\_L.2d\_dxf.zip

English

Customer View Model  
ENG\_CVM\_CVM\_322771\_L.3d\_igs.zip

English

Customer View Model  
ENG\_CVM\_CVM\_322771\_L.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.