

Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

High Speed Chain Oil
 Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against

Lubricants

1.3. Details of the supplier of the safety data sheet

CRC Industries Europe bvba
 Touwslagerstraat 1
 9240 Zele
 Belgium
 Tel.: +32(0)52/45.60.11
 Fax.: +32(0)52/45.00.34
 E-mail : hse@crcind.com

Subsidiaries		Tel	Fax
CRC Industries Finland Oy	Asemanrinne 13, 08500 Lohja	+358/(19)32.921	+358/(19)383.676
CRC Industries France	6, avenue du marais, C.S. 90028, 95102 Argenteuil Cedex	01.34.11.20.00	01.34.11.09.96
CRC Industries Deutschland GmbH	Südring 9, D-76473 Iffezheim	(07229) 303.0	(07229)30 32 66
CRC INDUSTRIES IBERIA S.L.U.	GREMIO DEL CUERO-PARC.96, POLIGONO INDUSTRI. DE HONTORIA, 40195 SEGOVIA	0034/921.427.546	0034/921.436.270
CRC Industries Sweden	Kryptogatan 14, 431 53 Mölndal	0046/31 706 84 80	0046/31 27 39 91

1.4. Emergency telephone number

CRC Industries Europe, Belgium: Tel.: +32(0)52/45.60.11 (office hours)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1
 Extremely flammable aerosol.
 Pressurised container: May burst if heated.

Health: Skin irritation, category 2



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

Environment: Causes skin irritation.
Hazardous to the aquatic environment, chronic category 3
Harmful to aquatic life with long lasting effects.

Other hazards : None

Classification according to 67/548/EEC or 1999/45/EC:

Health: Not classified
Physical: EXTREMELY FLAMMABLE
Environment: R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

Hazard pictogram(s):



Signal word: Danger

Hazard statement(s): H222 : Extremely flammable aerosol.
H229 : Pressurised container: May burst if heated.
H315 : Causes skin irritation.
H412 : Harmful to aquatic life with long lasting effects.

Precautionary statement(s): P102 : Keep out of reach of children.
P210 : Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 : Do not spray on an open flame or other ignition source.
P251 : Do not pierce or burn, even after use.
P280 : Wear protective gloves/protective clothing/eye protection/face protection.
P410/412 : Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
P501-2 : Dispose of contents/container to an authorised waste collection point.

Supplemental Hazard information: None

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	68512-91-4	270-990-9	50-75	F+	12	K,G
mineral oil (IP 346 DMSO extract < 3%)	-	-	10-25	-	-	B
Naphtha (petroleum), hydrotreated light	64742-49-0	921-024-6	<15	F,Xn,N	11-38-51/53-65-67	B
Phosphoric acid, C8-16-alkyl esters, reaction products with (Z)-N-9-octadecenyl-1,3-propanediamine	90506-47-1	291-909-3	1-5	Xi	36/38	
2,6-di-tert-butyl-p-cresol	128-37-0	204-881-4	<1	N	51/53	B
Phosphoric acid ester, amine salt	-	-	<1	N	51/53	
Explanation notes						
B : substance with national established workplace exposure limit						
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006						
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)						

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
Hydrocarbons,C3-4-rich, petroleum distillate Petroleumgas (1,3-butadiene < 0.1%)	-	68512-91-4	270-990-9	50-75	Press. Gas, Flam. Gas 1	H280,H220	K,G
mineral oil (IP 346 DMSO extract < 3%)	-	-	-	10-25	-	-	B
Naphtha (petroleum), hydrotreated light	01-2119475514-35	64742-49-0	921-024-6	<15	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2	H225,H315,H336,H304,H411	B
2,6-di-tert-butyl-p-cresol	01-2119555270-46	128-37-0	204-881-4	<1	Aquatic Acute 1, Aquatic Chronic 1	H400,H410	B
Explanation notes							
B : substance with national established workplace exposure limit							
G : exempted from the obligation to register in accordance with art.2(7)(a)of REACH Regulation No 1907/2006							
K : not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)							

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes :	If substance has got into eyes, immediately wash out with plenty of water Seek medical attention if irritation persists
Contact with skin :	Wash with water and soap. Seek medical attention if irritation persists
Inhalation :	Fresh air, keep warm and at rest. Seek medical attention if ill effects occur
Ingestion :	If swallowed do not induce vomiting because of risk of aspiration into the lungs. If aspiration is suspected obtain immediate medical attention

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
---------------------	--



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia. Symptoms : sore throat, abdominal pain, nausea, vomiting
Skin contact :	May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice : If you feel unwell, seek medical advice (show the label where possible)
If symptoms persist always call a doctor

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C
Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing and gloves.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep out of reach of children.

7.3. Specific end use(s)

Lubricants

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

No information available

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
inhalation :	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
hands and skin :	Wear suitable protective gloves against chemicals (nitrile)
eyes :	Wear safety goggles.



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

Apperance : physical state : Liquid under pressure.
colour : Blue.
odour : Solvent.
pH : Not applicable.
Boiling point/range : Not available.
Flash point : < 0 °C
Evaporation rate : Not available.
Explosion limits : upper limit : Not available.
lower limit : Not available.
Vapour pressure : Not available.
Relative density : 0, 81 (@ 20°C).
Solubility in water : Not available.
Auto-ignition : > 200 °C
Viscosity : Not available.

9.2. Other information

VOC: 485 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Strong oxidising agent

10.6. Hazardous decomposition products



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact :	Prolonged skin contact will result in defatting of the skin, leading to irritation, and in some cases, dermatitis Repeated exposure may cause skin dryness or cracking.
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrotreated light	64742-49-0	LD50 oral rat	> 5000 mg/kg
		LC50 inhal.rat	> 25000 mg/m3
		LD50 derm.rat	> 2000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
Naphtha (petroleum), hydrotreated light	64742-49-0	LC50 fish	> 10 mg/l
		EC50 daphnia	3 mg/l

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Insoluble in water



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No experimental data available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.

National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : 1950

14.2. UN proper shipping name

Proper shipping name: AEROSOLS

14.3. Transport hazard class(es)

Class: 2.1
ADR/RID - Classification code: 5F

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

ADR/RID - Tunnelcode: (D)
IMDG - Ems: F-D, S-U



Productname : High Speed Chain Oil
Ref.Nr.: BDS001477_3_20130911

Creationdate : 11.09.13 Version : 1.0
Replaces:

IATA/CAO - PAX: 203
IATA/CAO - CAO 203

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.
Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.
Regulation (EC) No 1907/2006 (REACH)
EU-directive 99/45/EC
Regulation (EC) No 1272/2008 (CLP)

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R11: Highly flammable.
R12: Extremely flammable.
R38: Irritating to skin.
R65: Harmful: may cause lung damage if swallowed.
R67: Vapours may cause drowsiness and dizziness.
R36/38: Irritating to eyes and skin.
R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

*Explanation hazard statements: - : -
H220 : Extremely flammable gas.
H225 : Highly flammable liquid and vapour.
H280 : Contains gas under pressure; may explode if heated.
H304 : May be fatal if swallowed and enters airways.
H315 : Causes skin irritation.
H336 : May cause drowsiness or dizziness.
H400 : Very toxic to aquatic life.
H410 : Very toxic to aquatic life with long lasting effects.
H411 : Toxic to aquatic life with long lasting effects.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.

