

Endress+Hauser Vibronic level switch FTM21-DN246A

Single rod probe with extension tube for point level detection in bulk solids, also for dust and hazardous areas.



Picture for reference only. Product appearance may vary based on configuration

Soliphant FTM21 is a point level switch for applications with fine-grained or coarse-grained, non-fluidized bulk solids. The various designs means the device has a wide range of applications. Certificates are also available for use in dust and hazardous areas.

- Easy commissioning (plug and play)
- No calibration required
- Measurement not affected by build-up or external vibration
- No mechanically moved parts, free of maintenance
- Not affected by flow noises

Configuration of FTM21-DN246A:

Approval:	D	FM DIP+CSA DIP Cl.II,III Div.1+2 Gr.E-G, zone 20,21
Process Connection:	N	Thread ANSI NPT1-1/2, 316L
Sensor Length:	2	500mm
Electronics; Output:	4	FEM24; relay DPDT, 19-253VAC/55VDC
Housing; Cable Entry:	6	F18 Alu IP66/67 NEMA4X; NPT3/4 thread
Additional Option:	A	Basic version

Alternative part number: FTM21-DN246A