

242.1693

**FLUSH MOUNTING APPLIANCE
INLET**
16A 2P+E 6h 200-250V 60Hz 50Hz
70X87MM Screw terminals



* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	EUREKA Series
Synthetical description	FLUSH MOUNTING APPLIANCE INLET
Description	
The flush mounting appliance inlet from the EUREKA Series is engineered for a rated voltage of 200-250V and a current of 16A. Featuring 2P+E poles and a 6h hour position, it operates efficiently at both 50Hz and 60Hz frequencies. With a protection degree of IP44, it offers reliable performance in various environments. The inlet is equipped with screw terminals and is compatible with 90° angled outlets. This design ensures secure connections and optimal functionality for professional applications.	
Mounting version	FLUSH/SURFACE MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	16A
Poles	2P+E
Hour position	6h
Rated voltage	200-250V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	FLUSH/SURFACE MOUNTING
Colour	BLUE
Material	THERMOPLASTIC
Protection degree	Splash proof
Protection degree IP	IP44
Protection degree IK	IK07
Types of available outlets	90° ANGLED
Contact material	CuZn (brass)
Surface treatment contacts	Nickel-plated
Cable entry	PG 16

■ DIMENSIONAL CHARACTERISTICS

Flange	70X87MM
--------	---------

■ DOWNLOAD

Technical drawing [PDF]
Technical drawing [STP]
Technical drawing [DWG]