

101.8 | 101 - Adjustable wrenches, fast adjustment, metal handle




Standards:

NF ISO 6787, ISO 6787, DIN 3117, ASME B107.100

Description:

- Time gain: easy and fast moving jaw tightening on the nut using the button. 3 steps: - pull the button to release the moving jaw instantly. - adjust the moving jaw to the dimension required by hand. - if necessary, use the button traditionally for fine adjustment. 2 to 3 times faster than a standard adjustable wrench.
- Slim profile jaws for better accessibility.
- Extra wide opening for higher versatility.
- Grading in mm on one face.
- Presentation: chromed body.



	101.8
A [mm]	33.0
A [in]	
Length L [mm]	200.0
Length L1 [mm]	0.0
Thickness E [mm]	6.7
Thickness E1 [mm]	14.2
Thickness E2 [mm]	0.0
Thickness E3 [mm]	9.9
Thickness E4 [mm]	0.0
Head Height C [mm]	18.0
Head Height C1 [mm]	24.0
Head Width B [mm]	65.4
Weight [Kg]	0.3