

ATA6571 Errata and Data Sheet Clarification

The functionality of the ATA6571 device you have received is described in the Device Data Sheet DS20006329 with the exception of the anomalies described in this document.

The NERR pin is pulled to GND under the following conditions, which are in addition to those described in the data sheet.

1. NERR pin is pulled to GND:

a. When VS drops below its undervoltage detection level $V_{VS_UV_CAN_Set}$ and the WAKE pin is externally pulled to VS

If V_{VS} drops below its undervoltage detection level $V_{VS_UV_CAN_Set}$ (see Section 5. Electrical Characteristics in the data sheet), the ATA6571 enters Standby Mode and the transceiver switches off and disengages from the bus until V_{VS} recovers. If at that time the WAKE pin is connected to VS, the NERR pin and the RXD pin will be pulled to GND.

Therefore, if the application circuit is used as depicted in the data sheet — i.e., with a switch to GND at the WAKE pin, the NERR pin additionally signals a VS-undervoltage event, which can be used to monitor the VS supply voltage. This is only the case if the WAKE pin is pulled up externally to VS when the WAKE switch is open.

In case VS drops below its undervoltage detection level $V_{VS_UV_CAN_Set}$ when the WAKE pin is externally pulled to GND, it will not be signaled at the NERR pin and the RXD pin.

b. When VS drops below its undervoltage detection level V_{VS_PWROFF} and the WAKE pin is externally pulled to GND

If the V_{VS} voltage drops further below the supply voltage Threshold for power-off detection V_{VS_PWROFF} (see section 5. Electrical Characteristics in the data sheet), the CAN driver is already switched off. If this occurs when the WAKE pin is externally pulled to GND, the INH output switches off, the ATA6571 enters Sleep mode and the NERR pin and the RXD pin are pulled to GND by an internal 500Ω resistor.

c. At VIO undervoltage

If V_{VIO} drops below its undervoltage detection level (V_{VIO_UV} , see section 5. Electrical Characteristics in the data sheet), the transceiver switches off and disengages from the bus until V_{VIO} recovers. The NERR pin and the RXD pin is pulled immediately to GND by an internal 500Ω resistor.

If the voltage on the VIO pin drops below V_{VIO_UV} for longer than the undervoltage detection time, $t_{VSUP_UV_set}$, the $UV_{VCC/VIO}$ flag is set and the transceiver enters Sleep mode to save power and to ensure that the bus is not disturbed. In Sleep mode the voltage regulators connected to the INH pin are disabled, avoiding any extra power consumption that might be caused by a short-circuit condition.

This can be used to detect a VIO undervoltage.

d. At V_{CC} undervoltage during data transmission

If V_{VCC} drops below its undervoltage detection level (V_{VCC_UV} , see Section 5. Electrical Characteristics in the data sheet) while the device is in Normal mode and transmits data, the transceiver switches off until V_{VCC} recovers. Additionally, the NERR pin is pulled to GND and the RXD pin is pulled to VIO.

This can be used to detect a VCC undervoltage.

If the voltage on the VCC pin drops below V_{VCC_UV} for longer than the undervoltage detection time, $t_{VSUP_UV_set}$, the $UV_{VCC/VIO}$ flag is set and the transceiver enters Sleep mode to save power. In Sleep mode the external voltage regulators connected to the INH pin are disabled, avoiding any extra power consumption that might be caused by a short-circuit condition.

The NERR pin is released when entering Sleep mode.

2. CAN Bus Wake-Up Detection

The device does not wake up via the CAN bus (WUP) under the following conditions:

- The supply voltage (V_{VS}) falls under the "Supply Voltage Threshold for CAN TRX undervoltage Detection" ($V_{VS_UV_CAN_SET}$)
- The supply voltage (V_{VS}) rises slowly with a rise rate of $dV/dt < 1V/s$ from undervoltage condition ($V_{VS} < 4.2V$) to CAN operation condition ($V_{VS} > 4.6V$)
- During this rise, V_{VCC} and/or V_{VIO} are below their respective Undervoltage thresholds.

The device can be brought back into an operating state via a Local Wake-up request via the Wake pin or a power on reset ($V_{VS} < 2.8V$).

Workaround:

None.

APPENDIX A: DOCUMENT REVISION HISTORY

Rev. A (November 2020)

- Initial release of this document. This Errata completes the Device Data Sheet DS20006329 with the following information:
 - Updated conditions where the NERR pin is pulled to GND.

Rev. B (July 2025)

- Added condition [2](#).

Microchip Information

Trademarks

The “Microchip” name and logo, the “M” logo, and other names, logos, and brands are registered and unregistered trademarks of Microchip Technology Incorporated or its affiliates and/or subsidiaries in the United States and/or other countries (“Microchip Trademarks”). Information regarding Microchip Trademarks can be found at <https://www.microchip.com/en-us/about/legalinformation/microchip-trademarks>.

ISBN: 979-8-3371-1527-6

Legal Notice

This publication and the information herein may be used only with Microchip products, including to design, test, and integrate Microchip products with your application. Use of this information in any other manner violates these terms. Information regarding device applications is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. Contact your local Microchip sales office for additional support or, obtain additional support at www.microchip.com/en-us/support/design-help/client-support-services.

THIS INFORMATION IS PROVIDED BY MICROCHIP "AS IS". MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION INCLUDING BUT NOT LIMITED TO ANY IMPLIED WARRANTIES OF NON-INFRINGEMENT, MERCHANTABILITY, AND FITNESS FOR A PARTICULAR PURPOSE, OR WARRANTIES RELATED TO ITS CONDITION, QUALITY, OR PERFORMANCE.

IN NO EVENT WILL MICROCHIP BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL, OR CONSEQUENTIAL LOSS, DAMAGE, COST, OR EXPENSE OF ANY KIND WHATSOEVER RELATED TO THE INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROCHIP HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROCHIP'S TOTAL LIABILITY ON ALL CLAIMS IN ANY WAY RELATED TO THE INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, THAT YOU HAVE PAID DIRECTLY TO MICROCHIP FOR THE INFORMATION.

Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip Devices Code Protection Feature

Note the following details of the code protection feature on Microchip products:

- Microchip products meet the specifications contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is secure when used in the intended manner, within operating specifications, and under normal conditions.
- Microchip values and aggressively protects its intellectual property rights. Attempts to breach the code protection features of Microchip product is strictly prohibited and may violate the Digital Millennium Copyright Act.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of its code. Code protection does not mean that we are guaranteeing the product is “unbreakable”. Code protection is constantly evolving. Microchip is committed to continuously improving the code protection features of our products.