


Aluminum Electrolytic Capacitors

Radial, Enhanced High Temperature, Low Impedance


RoHS
COMPLIANT

FEATURES

- Useful life: up to 2000 h at 150 °C
- High stability, high reliability
- Very low ESR
- AEC-Q200 qualified
- Excellent ripple current capability
- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Radial leads, cylindrical aluminum case with pressure relief, insulated with a blue PET sleeve
- Charge and discharge proof
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Power supplies (SMPS, DC/DC converters) for industrial, automotive, telecommunications and military
- Smoothing, filtering and buffering

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance (in μF)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for $\pm 20\%$)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- Code indicating factory of origin
- Logo of manufacturer
- Upper category temperature (150 °C)
- Negative terminal identification
- Series number (160)




Fig. 1

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes (\varnothing D x L in mm)	10 x 12 to 18 x 35
Rated capacitance range, C_R	33 μF to 3300 μF
Tolerance on C_R	$\pm 20\%$
Rated voltage range, U_R	16 V to 50 V
Category temperature range	-55 °C to +150 °C
Endurance test at 150 °C	1000 h to 1500 h
Useful life at 150 °C	1000 h to 2000 h
Useful life at 40 °C, 1.8 x I_R applied	200 000 h
Shelf life at 0 V, 150 °C	1000 h
Based on sectional specification	IEC 60384-4 / EN130300
Climatic category IEC 60068	55/150/56

SELECTION CHART FOR C_R , U_R , AND RELEVANT NOMINAL CASE SIZES (\varnothing D x L in mm)				
C_R (μF)	U_R (V)			
	16	25	35	50
33	→	→	→	10 x 12
47	→	→	10 x 12	10 x 12
100	→	10 x 12	10 x 16	10 x 16
220	10 x 16	12.5 x 20	12.5 x 20	10 x 20
330	10 x 20	12.5 x 25	12.5 x 25	12.5 x 20
470	12.5 x 20	16 x 25	18 x 20	12.5 x 25
680	12.5 x 25	→	16 x 31	16 x 25
1000	16 x 25	16 x 31	18 x 35	18 x 31
1500	18 x 20	18 x 31	-	-
2200	18 x 25	-	-	-
2700	18 x 31	-	-	-
3300	18 x 35	-	-	-


DIMENSIONS in millimeters AND AVAILABLE FORMS


Fig. 2 - Form CA: long leads




Fig. 3 - Form CB: cut leads




Fig. 4 - Form TFA: taped in box (ammopack)

Table 1

DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES									
NOMINAL CASE SIZE Ø D x L	CASE CODE	Ø d	Ø D _{max.}	L _{max.}	F	MASS (g)	PACKAGING QUANTITIES		
							FORM CA	FORM CB	FORM TFA
10 x 12	14	0.6	10.5	13.5	5.0 ± 0.5	≈ 1.6	1000	500	800
10 x 16	15	0.6	10.5	17.5	5.0 ± 0.5	≈ 1.9	500	500	800
10 x 20	16	0.6	10.5	22.0	5.0 ± 0.5	≈ 2.2	500	500	800
12.5 x 20	17	0.6	13.0	22.0	5.0 ± 0.5	≈ 4.0	500	500	500
12.5 x 25	18	0.6	13.0	27.0	5.0 ± 0.5	≈ 5.0	250	250	500
16 x 25	19	0.8	16.5	27.0	7.5 ± 0.5	≈ 8.0	250	250	250
16 x 31	20	0.8	16.5	33.5	7.5 ± 0.5	≈ 9.0	100	100	250
18 x 20	1820	0.8	18.5	22.0	7.5 ± 0.5	≈ 8.0	100	100	250
18 x 25	1825	0.8	18.5	27.0	7.5 ± 0.5	≈ 10.0	100	100	250
18 x 31	1831	0.8	18.5	33.5	7.5 ± 0.5	≈ 12.5	100	100	-
18 x 35	22	0.8	18.5	37.5	7.5 ± 0.5	≈ 14.5	100	100	-

ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C _R	Rated capacitance at 100 Hz, tolerance ± 20 %
I _R	Rated RMS ripple current at 100 kHz, 150 °C
I _{L2}	Maximum leakage current after 2 min at U _R
tan δ	Maximum dissipation factor at 100 Hz
Z	Maximum impedance at 100 kHz

Note

- Unless otherwise specified, all electrical values in Table 2 apply at T_{amb} = 20 °C, P = 86 kPa to 106 kPa, RH = 45 % to 75 %

ORDERING EXAMPLE

Electrolytic capacitor 160 RLA series

470 µF / 25 V; ± 20 %

Nominal case size: Ø 10 mm x 16 mm; Form TFA

Ordering code: MAL216036471E3



Table 2

ELECTRICAL DATA AND ORDERING INFORMATION										
U _R (V)	C _R 100 Hz (μF)	NOMINAL CASE SIZE Ø D x L (mm)	I _R 100 kHz 150 °C (mA)	I _{L2} 2 min (μA)	tan δ 100 Hz	Z 100 kHz +20 °C (Ω)	Z 100 kHz -40 °C (Ω)	ORDERING CODE MAL2160.....		
								BULK PACKAGING		TAPED
								FORM CA	FORM CB	FORM TFA
16	220	10 x 16	300	38	0.14	0.075	0.450	55221E3	65221E3	35221E3
	330	10 x 20	400	56	0.14	0.065	0.390	55331E3	65331E3	35331E3
	470	12.5 x 20	600	78	0.14	0.048	0.288	55471E3	65471E3	35471E3
	680	12.5 x 25	700	112	0.14	0.040	0.240	55681E3	65681E3	35681E3
	1000	16 x 25	800	163	0.16	0.029	0.174	55102E3	65102E3	35102E3
	1500	18 x 20	750	243	0.16	0.035	0.210	55152E3	65152E3	35152E3
	2200	18 x 25	1200	355	0.18	0.028	0.168	55222E3	65222E3	35222E3
	2700	18 x 31	1600	435	0.18	0.025	0.150	55272E3	65272E3	35272E3
3300	18 x 35	2000	531	0.20	0.023	0.132	55332E3	65332E3	-	
25	100	10 x 12	250	28	0.12	0.120	0.750	56101E3	66101E3	36101E3
	220	12.5 x 20	600	58	0.12	0.048	0.288	56221E3	66221E3	36221E3
	330	12.5 x 25	700	86	0.12	0.040	0.240	56331E3	66331E3	36331E3
	470	16 x 25	800	121	0.12	0.029	0.174	56471E3	66471E3	36471E3
	1000	16 x 31	1000	253	0.12	0.027	0.162	56102E3	66102E3	36102E3
	1500	18 x 31	1600	378	0.14	0.025	0.150	56152E3	66152E3	36152E3
35	47	10 x 12	250	19	0.10	0.120	0.750	50479E3	60479E3	30479E3
	100	10 x 16	400	38	0.10	0.075	0.450	50101E3	60101E3	30101E3
	220	12.5 x 20	600	80	0.10	0.048	0.288	50221E3	60221E3	30221E3
	330	12.5 x 25	700	119	0.10	0.040	0.240	50331E3	60331E3	30331E3
	470	18 x 20	750	168	0.10	0.035	0.210	50471E3	60471E3	30471E3
	680	16 x 31	1000	241	0.10	0.027	0.162	50681E3	60681E3	30681E3
	1000	18 x 35	1200	353	0.10	0.024	0.144	50102E3	60102E3	-
	50	33	10 x 12	160	20	0.10	0.380	2.280	51339E3	61339E3
47		10 x 12	180	27	0.10	0.360	2.160	51479E3	61479E3	31479E3
100		10 x 16	270	53	0.10	0.260	1.560	51101E3	61101E3	31101E3
220		10 x 20	360	113	0.10	0.170	1.020	51221E3	61221E3	31221E3
330		12.5 x 20	400	168	0.10	0.115	0.690	51331E3	61331E3	31331E3
470		12.5 x 25	600	238	0.10	0.095	0.570	51471E3	61471E3	31471E3
680		16 x 25	700	343	0.10	0.069	0.414	51681E3	61681E3	31681E3
1000		18 x 31	1000	503	0.10	0.062	0.372	51102E3	61102E3	31102E3

ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
Voltage		
Surge voltage		U _s ≤ 1.15 x U _R
Reverse voltage		U _{rev} ≤ 0.5 V
Current		
Leakage current	After 2 min at U _R	I _{L2} ≤ 0.01 C _R x U _R + 3 μA
Inductance		
Equivalent series inductance (ESL)	Case Ø D = 10 mm	Typ. 16 nH
	Case Ø D ≥ 12.5 mm	Typ. 18 nH
Resistance		
Equivalent series resistance (ESR)	Calculated from tan δ _{max.} and C _R (see Table 2)	ESR = tan δ/2 π f C _R



CAPACITANCE (C)




Fig. 5 - Typical multiplier of capacitance at 100 Hz as a function of temperature ($C_0 = C$ at 20 °C)




Fig. 6 - Typical multiplier of capacitance as a function of frequency at 20 °C ($C_0 = C$ at 100 Hz)

EQUIVALENT SERIES RESISTANCE (ESR)




Fig. 7 - Typical multiplier of ESR at 100 Hz as a function of temperature ($ESR_0 = ESR$ at 20 °C)




Fig. 8 - Typical multiplier of ESR at 20 °C as a function of frequency ($ESR_0 = ESR$ at 100 Hz)

IMPEDANCE (Z)




Fig. 9 - Typical multiplier of impedance at 100 kHz as a function of temperature ($Z_0 = Z$ at 20 °C)




Fig. 10 - Typical impedance Z at 20 °C as a function of frequency




Fig. 11 - Typical impedance Z at 20 °C as a function of frequency

Table 3

ENDURANCE TEST DURATION AND USEFUL LIFE AS A FUNCTION OF CASE SIZE			
NOMINAL CASE SIZE Ø D x L (mm)	CASE CODE	ENDURANCE AT 150 °C (h)	USEFUL LIFE AT 150 °C (h)
10 x 12	14	1000	1000
10 x 16	15	1000	1000
10 x 20	16	1000	1000
12.5 x 20	17	1000	1000
12.5 x 25	18	1000	1000
16 x 25	19	1500	2000
16 x 31	20	1500	2000
18 x 20	1820	1500	2000
18 x 25	1825	1500	2000
18 x 31	1831	1500	2000
18 x 35	22	1500	2000

RIPPLE CURRENT AND USEFUL LIFE

MBC245




Fig. 12 - Multiplier of useful life as a function of ambient temperature and ripple current load

Table 4

MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY			
FREQUENCY (Hz)	I_R MULTIPLIER		
	$U_R = 16\text{ V to }25\text{ V}$	$U_R = 35\text{ V}$	$U_R = 50\text{ V}$
50	0.60	0.50	0.35
100	0.70	0.65	0.50
300	0.85	0.80	0.65
1000	0.90	0.85	0.80
3000	0.95	0.90	0.90
10 000	1.00	0.95	0.90
100 000	1.00	1.00	1.00



Table 5

TEST PROCEDURES AND REQUIREMENTS			
TEST		PROCEDURE (quick reference)	REQUIREMENTS
NAME OF TEST	REFERENCE		
Endurance	IEC 60384-4 / EN130300 subclause 4.13	T _{amb} = 150 °C; U _R applied; for test duration see Table 3	ΔC/C: ± 15 % tan δ ≤ 1.3 x spec. limit I _{L2} ≤ spec. limit
Useful life	CECC 30301 subclause 1.8.1	T _{amb} = 150 °C; U _R and I _R applied; for test duration see Table 3	ΔC/C: ± 30 % tan δ ≤ 3 x spec. limit I _{L2} ≤ spec. limit no short or open circuit total failure percentage: ≤ 1 %
Shelf life	IEC 60384-4 / EN130300 subclause 4.17	T _{amb} = 150 °C; no voltage applied; 1000 h after test: U _R to be applied for 30 min, 24 h o 48 h before measurement	ΔC/C: ± 15 % tan δ ≤ 1.3 x spec. limit I _{L2} ≤ spec. limit



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.