




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
		2024.06.25	Initial Release	LENA
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

- Material:
- Item ① Terminal Body: PA66,
 - Item ② Terminal lever: PBT ,
 - Item ③ Terminal Cover: PA66 ,
 - Item ④ Spring: Stainless
 - Item ⑤ Terminal Contact: Copper alloy,
- Electrical:
- | | | | |
|--------------------------|------------------|---------|---------|
| UL1059 | Group B.G | Group D | Group F |
| ●Voltage rating: | 300 V | 300V | 250V |
| ●Current rating: | 16A | 10A | 16A |
| ●Wire range: | | | |
| Solid wire: | 24-12AWG | | |
| Stranded wire: | 24-12AWG | | |
| ●Wire strip length: | 11-13 mm | | |
| ●Withstanding Voltage: | 1.6KV AC | | |
| ●Insulation Resisance: | DV500V 500MΩ min | | |
| ●Operating temperature: | -20℃ to +105℃ | | |
| ●Assembling temperature: | -5℃ to +105℃ | | |
| ●Safety Approval: | CEus | | |

Part No. **QT xx A FI x x V xxxx G**

NO. OF POLES
02: 2 POLES
03: 3 POLES
... ..
24: 24 POLES

Body color
0: Black
1: Natural color
2: Red
3: Orange
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey (標準色)
9: White
C: Green (RAL 6018/U)

Lever color
0: Black
1: Natural color
2: Red
3: Orange (標準色)
4: Yellow
5: Green (RAL6018/T)
6: Blue
8: Grey
9: White
C: Green (RAL 6018/U)

RoHS compliant (lead<4%)
In copper Alloy
00x0: "@" Logo (Standard)
00xA: "ANYTEK" Mark
Any special item by customer request.
please contact sales department.

Amphenol ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	QT series 90D pitch 5.0mm.Front Foot near Side Cover Interlace Soldering Foot						
PART NO.	QTxxAFIxxVxxxxG			DWG NO.	8QT0012		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
Roy 2024.11.07	Roy 2024.11.07	Lena 2024.06.25	Lena 2024.06.25			UNIT: mm	X. ±0.50
						SCALE: 2:1	X.X ±0.30
				SHEET: 01/01		REV.: A0	X.XX ±0.10
							X* ±1°