


Geberit Mapress Stainless Steel ball valve with actuator lever, flanged



Example image

APPLICATION PURPOSES

- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For service water and process water
- For treated water (application range according to Technical Information „Treated water“)
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For compressed air (oil purity class 0–3)

CHARACTERISTICS

- Spindle caulk made of PTFE
- Section seal of flange and ball made of PTFE
- Fulfills requirements in accordance with TA Air VDI 2440
- Connecting flange for motor in accordance with EN ISO 5211 (only for d = 76.1–108 mm)
- Length-adjustable actuator lever (only for d = 108 mm)
- Lockable
- Pressing indicator
- Leaky if unpressed

- Seal ring made of CIIR, black
- Pressing socket with transparent protection plug

TECHNICAL DATA

Operating temperature	-20 – +120 °C
Product material	CrNiMo steel 1.4401 (EN 10088)

ACCESSORIES

- Actuator lever set, lockable, for Geberit Mapress ball valve, flanged

Art. no.	DN	DNV	d, ø mm	k mm	m mm	L cm	L1 cm	L2 cm	Z cm	PN bar
92100	12	15	15			12.2	5	9.3	4.1	40
92101	15	15	18			12.2	5	9.3	4.1	40
92102	20	20	22			13.3	5.6	10.3	4.5	40

<i>Art. no.</i>	<i>DN</i>	<i>DNV</i>	<i>d_ø</i> <i>mm</i>	<i>k</i> <i>mm</i>	<i>m</i> <i>mm</i>	<i>L</i> <i>cm</i>	<i>L1</i> <i>cm</i>	<i>L2</i> <i>cm</i>	<i>Z</i> <i>cm</i>	<i>PN</i> <i>bar</i>
92103	25	25	28			14.2	6.6	12.8	4.8	16
92104	32	32	35			17	7.5	12.8	5.9	16
92105	40	40	42			19.4	8.5	15.8	6.7	16
92106	50	50	54			22.1	9.6	15.8	7.5	16
92107	65	65	76.1	70	9	29.1	13.5	22.3	9.2	16
92108	80	80	88.9	70	9	33.3	14.5	35.8	10.6	16
92109	100	100	108	102	11	41.2	17.7	50	13.1	16