



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Jackscrew Kit**

Jackscrew Type: **Fixed**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware

Body Features

Material	Stainless Steel
Thread Lead Type	Double

Mechanical Attachment

Jackscrew Material	Stainless Steel
Jackscrew Plating Material	Zinc
Mounting Hardware	Nuts and Lockwashers
Screw & Hole Thread Size	4-40, 6-32 [M3.5 x .6]
Hardware Type	Jackscrew Kit
Jackscrew Type	Fixed

Dimensions

Height	5.6 mm[.22 in]
Length	21.51 mm[.847 in]
Width	5.6 mm[.22 in]

Operation/Application

For Use With	Mate with Any Turnable Jackscrew Rod
--------------	--------------------------------------

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Comment	Two required.
---------	---------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	欧洲化学品管理局最新发布的SvHCs候选清单: 2019年1月 (197) SvHCs候选清单的声明更新至: 2018年1月 (181)
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought



TE Part #1-225554-1
TNC-DUAL CMP R/ANGLE
PLUG-W/P



TE Part #2803-4-0000
CONT SOC ASSY



TE Part #1-225550-3
TNC PLUG



TE Part #201358-1
MALE BLOCK 50 PL. SER.
"M"



Documents

Product Drawings

SKT ASSY,M SERIES

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_200875-7_AD.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_200875-7_AD.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_200875-7_AD.2d_dxf.zip](#)

English

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English