

FEATURES

- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight.
- **High Tensile Strength:** Withstands up to 22 kg, ensuring robust cable management.
- **Wide Temperature Range:** Operates effectively from -40 °C to 85 °C, suitable for diverse environments.
- **RoHS Compliant:** Meets safety and environmental standards.
- **UL 94HB Rated:** Provides a standard level of flame retardancy.
- **83 mm Maximum Bundle Diameter:** Accommodates large cable bundles.
- **4.8 mm Width:** Offers a balance between strength and flexibility.

RS PRO 300mm Nylon Cable Tie, Non-Releasable

RS Stock No: 656-097



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO cable ties are designed for secure and reliable bundling of cables and wires. Made from durable nylon, they are ideal for use in various industrial and commercial settings. The non-releasable design ensures a permanent hold, making them suitable for applications where security is paramount.

General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	22 kg

Protection Category

Fire Behaviour	UL 94HB
UV Resistant	Yes

Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	83 mm
Width	4.8 mm

Operation Environment Specifications

Maximum Operating Temperature	85 °C
Minimum Operating Temperature	-40 °C

Approvals

Standards/Approvals	RoHS, UL94HB
---------------------	--------------