

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 843477-1
TOOL, EXTRACTION RESET



TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL
FRAME



TE Part # 58336-1
HEAD (IDC) MODU MTE W/O TL


Customers Also Bought



TE Part #66740-6
TYPE XII FEMALE CONT (L.P.)




TE Part #281695-3
HEADER HE14 STRAIGHT 3 P



TE Part #207470-1
CABLE CLAMP KIT,SZ 2



TE Part #5-1419111-8
PT271730



TE Part #207467-1
CABLE CLAMP KIT,SZ 1



TE Part #205163-1
RECEPT ASSY,15 POSN,AMPLIMITE



TE Part #5745172-1
SIZE 2 ASSY KIT



TE Part #206127-1
CPC SPECIAL ASSEMBLY SIZE 17

Documents

Product Drawings

5X3 MTE SHRD PIN SR POL .100

English

CAD Files

Customer View Model

ENG_CVM_103944-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_103944-2_K.3d_stp.zip

English

Customer View Model

ENG_CVM_103944-2_K.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
AMPMODU MTE INTERCONNECT SYSTEM

English

Product Specifications
Application Specification

English

Instruction Sheets
Instruction Sheet (U.S.)

English