



circuit breaker 3VA2 IEC Frame 1250 breaking capacity class M Icu=55 kA @ 415 V 4-pole line protection ETU330 LIG In=1250 A overload protection Ir=500 A ...1250 A short-circuit protection Ii=15...10 x In neutral conductor protection adjustable (OFF/50%/100%) ground-fault protection Ig=02... 1 x In tg=01/03 s circuit breaker with straight bus connectors extended

Model	
product brand name	SENTRON
product designation	Molded case circuit breaker
design of the product	Line protection
design of the overcurrent release	ETU330
protection function of the overcurrent release	LIG
number of poles	4
General technical data	
insulation voltage / rated value	800 V
operating voltage / at AC / rated value	690 V
power loss [W] / maximum	516 W
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	172 W
mechanical service life (operating cycles) / typical	10 000
electrical endurance (operating cycles) / at AC-1 / at 380/415 V	4 600
electrical endurance (operating cycles) / at AC-1 / at 690 V	3 200
product feature / for neutral conductors / upgradable/retrofitable / short-circuit and overload proof	No
ground-fault monitoring version	Summation current formation L + N conductor
product function	
• communication function	No
• other measurement function	No
Net Weight	28.6 kg
Current	
operational current	
• at 40 °C	1 250 A
• at 45 °C	1 250 A
• at 50 °C	1 250 A
• at 55 °C	1 187 A
• at 60 °C	1 125 A
• at 65 °C	1 000 A
• at 70 °C	875 A
Switching capacity according to IEC 60947	
switching capacity class of the circuit breaker	M
maximum short-circuit current breaking capacity (Icu)	
• at 240 V	85 kA
• at 415 V	55 kA
• at 440 V	55 kA
• at 500 V	36 kA
• at 690 V	25 kA
operating short-circuit current breaking capacity (Ics)	

• at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	85 kA 55 kA 55 kA 36 kA 19 kA
short-circuit current making capacity (I _{cm}) • at 240 V • at 415 V • at 440 V • at 500 V • at 690 V	187 kA 121 kA 121 kA 76 kA 52.5 kA
Adjustable parameters	
product feature / for L-tripping / can be switched on/off	No
adjustable response value setting current (I _r) / of the L-trip / with I _{2t} characteristic • minimum • maximum	500 A 1 250 A
adjustable response value delay time (t _r) / for L-tripping / with I _{2t} characteristic • minimum • maximum	0.5 s 17 s
adjustable response value setting current (I _l) / for I-tripping • minimum • maximum	1 875 A 12 500 A
adjustable current response value current / for G-tripping / with standard characteristic • initial value • full-scale value	250 A 1 250 A
adjustable response value delay time (t _g) / for G-tripping / with I _{0t} characteristic • minimum • maximum	0.1 s 0.3 s
adjustable setting current (I _{nN}) / for N-tripping • minimum • maximum	250 A 1 250 A
design of the N-conductor protection	adjustable OFF; 50%; 100%
product function / grounding protection	Yes
Mechanical Design	
product component • undervoltage release • voltage trigger • trip indicator	No No No
height [in]	12.6 in
height	320 mm
width [in]	11.02 in
width	280 mm
depth [in]	4.72 in
depth	120 mm
Connections	
arrangement of electrical connectors / for main current circuit	Front terminal
type of electrical connection / for main current circuit	busbar connection pieces extended on two sides
design of the surface / of the connections / on the top of the switch (N, 1, 3, 5)	silver
design of the surface / of the connections / on the bottom of the switch (N, 2, 4, 6)	silver
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
Accessories	
product extension / optional / motor drive	No
Environmental conditions	
protection class IP / on the front	IP40
ambient temperature	

- 25 °C
70 °C
-40 °C
80 °C

Q

General Product Approval	EMV	Test Certificates
--------------------------	-----	-------------------

Test Certificates




Dangerous goods


Transport Information

Environmental Con- firmations

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/100812875>

<http://www.siemens.com/specifications>





last modified:

4/3/2025

