

## USB 3.0 to VGA External Multi Monitor Graphics Adapter with 3-Port USB Hub – VGA and USB 3.0 Mini Dock – 1920x1200 / 1080p

Product ID: USB32VGAEH3



The USB32VGAEH3 USB 3.0 to VGA Adapter turns a USB 3.0 port into a VGA output port with 1920x1200/1080p video support. The adapter features a built-in 3-port USB 3.0 hub, which enables you to connect three different USB devices, along with the display adapter, to the same USB 3.0 port – an ideal workaround for Ultrabook™ or laptop computers that have a limited number of USB ports available.

Functioning as an external graphics card, this USB to VGA adapter provides a convenient way to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer. Leveraging the high-bandwidth (5 Gbps) USB 3.0 interface, the adapter delivers smooth, high-definition content to your VGA monitor / projector. The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

The USB32VGAEH3 also features a built-in 3-port USB 3.0 hub, which lets you use the device as a mini dock for connecting peripherals such as a mouse, printer and keyboard along with your monitor. Then, it's as easy as connecting your laptop to the adapter to sync each device at your work station – a versatile solution for making your laptop portable when you want it to be, and powerful when you need it to be.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

**Recommended System Requirements:**

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

Available USB 3.0 port



## Certifications, Reports and Compatibility



## Applications

- Add an extra VGA display and 3 additional USB devices to an Ultrabook or laptop computer with limited USB and video output ports
- Add a secondary VGA display and extend your desktop
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Run multiple applications on different screens - check your email on one display and search the web on the other
- Simultaneously view large or multiple spreadsheets across several displays
- Connect your PC to your VGA-equipped projector or display for viewing family pictures and movies
- Great for boosting productivity for researchers and writers, offering the ability to have reference material on one display and a working document copy on the other

## Features

- High-bandwidth USB 3.0 host connection, for reliable high-definition video playback
- Built in 3-Port USB 3.0 hub offers improved connectivity options on your slimline laptop or Ultrabook
- USB 3.0 (5 Gbps) Interface, backward compatible with USB 2.0
- Fast, easy installation
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation

<b>Hardware</b>	Warranty	2 Years
	Audio	No
	Chipset ID	MCT Trigger 5 T5-302
	Industry Standards	SuperSpeed USB 3.0, USB 2.0
	Memory	16MB DDR II
	USB Pass-Through	Yes
<b>Performance</b>	General Specifications	This USB video adapter uses a Trigger family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a DisplayLink or Fresco family chipset.
	Maximum Analog Resolutions	1920x1200
	Supported Resolutions	Widescreen(16/32 bit): 1920x1200, 1920x1080, 1680x1050, 1600x900, 1440x900, 1360x768, 1280x800, 1280x768, 1280x720  Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - USB Type-A (9 pin) USB 3.0 Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
		3 - USB Type-A (9 pin) USB 3.0 Female
<b>Software</b>	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows® 10 (32/64) Windows 8 / 8.1 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64)
<b>Special Notes / Requirements</b>	<b>Note</b>	Connect a maximum of five USB video adapters on a single PC - See manual for system requirements
	System and Cable Requirements	CPU: i3 Dual core 2.8GHz RAM: 2GB or higher  Full HD Video: CPU: Quad Core 2.4GHz or Higher (i5 recommended) RAM: 4GB or higher
<b>Power</b>	Power Source	USB-Powered
<b>Environmental</b>	Humidity	< 85% non-condensing

	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-10°C to 75°C (14°F to 167°F)
<b>Physical Characteristics</b>	Cable Length	152.5 mm [6 in]
	Color	Black
	Enclosure Type	Plastic
	Product Height	14 mm [0.6 in]
	Product Length	235 mm [9.3 in]
	Product Weight	212 g [7.5 oz]
	Product Width	44 mm [1.7 in]
<b>Packaging Information</b>	Shipping (Package) Weight	212 g [7.5 oz]
<b>What's in the Box</b>	Included in Package	1 - USB 3.0 to VGA Adapter w/ 3-Port USB 3.0 Hub
		1 - Software Installation Disc
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.