


Marker for terminal blocks - TMT (EX6,5)R - 0803064

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK X, THERMOMARK S1.1, Mounting type: Snap into universal marker groove, Snap into flat marker groove, Lettering field: 6.5 x 50,000 mm

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| GTIN |  4 046356 935531 |
| Weight per Piece (excluding packing) | 323.0 g |
| Custom tariff number | 39269097 |
| Country of origin | France |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|------------|--------|
| Length (b) | 50 m |
| Width (a) | 6.5 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -30 °C ... 80 °C |
| Recommended storage conditions | 10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing. |

General

| | |
|---|--------------------------------|
| Color | white |
| Components | Free from silicone and cadmium |
| Material | PVC |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 1 |
| Number of individual labels per row | 1 |
| RoHS compliant | Yes |
| Printability | Thermal transfer |
| Device | 5146477 THERMOMARK ROLL |
| Ink ribbon | 5145384 THERMOMARK-RIBBON 110 |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02 |

Marker for terminal blocks - TMT (EX6,5)R - 0803064

Technical data

General

| | |
|--|-------------------------------------|
| Result | Test passed |
| Test specification weathering-resistance | Following ISO 4892-2:2013-03 |
| Test duration | 96 h |
| Wipe resistance test result | Test passed |
| Salt spray test specification | DIN EN 60068-2-11:2000-02 |
| Test duration | 96 h |
| Salt spray testing result | Test passed |
| Alternating condensation climate with SO2 test specification | Following DIN 50018:2013-05 |
| Climate level | AHT 1.0 S |
| Cycles | 2 |
| Condensation test result | Test passed |
| Wipe resistance of test specification inscriptions | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result | Test passed |
| Marking mounting type | Snap into universal marker groove |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black