

Performance you can trust



FOODLUBE® Hi-Torque (with sups)

**High performance, food grade, synthetic gearbox fluids.
Non-toxic gearbox lubricants with the unique Start Up Protection System that
protects on start up as well as during use.**

Viscosity grades: ISO VG 150, 220, 320, 460

Features

- Temperature range –20°C to 150°C
- 320/460 grade ideal for high temperature chains up to 180°C
- Outstanding EP performance (FZG load stage 12)
- Highly resistant to water wash off
- Increased service intervals
- Excellent corrosion protection
- Do not contain: mineral hydrocarbons, animal derived materials, nut oils or genetically modified ingredients.
- FDA Group 21 CFR 178.3570
- NSF H1 registered -

Foodlube Hi-Torque 150 – 121604

Foodlube Hi-Torque 220 – 122073

Foodlube Hi-Torque 320 – 122072

Foodlube Hi-Torque 460 – 122071

Directions for Use

- For optimum performance drain & flush prior to filling with ROCOL.
- Additive packages are not required with FOODLUBE® Hi-Torque oils due to their inherent EP Performance.

T +44 (0) 113 232 2600

F +44 (0) 113 232 2740

E customer-service@rocol.com

www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of *ITW* Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

FOODLUBE® Hi-Torque (with sups)

Appearance	Pale yellow, almost colourless, fluid
Base type	Polyalphaolefin
Viscosities	
Foodlube Hi-Torque 150	40°C 150cSt 100°C 17.7cSt VI 130
Foodlube Hi-Torque 220	40°C 220cSt 100°C 24.9cSt VI 138
Foodlube Hi-Torque 320	40°C 320cSt 100°C 29.9cSt VI 143
Foodlube Hi-Torque 460	40°C 460cSt 100°C 38.5cSt VI 131
Temperature range	-20°C to 150°C
320/460 (high temp chain lubrication)	Up to 180°C
FZG load stage	12
Storage	Storage temperature should be controlled to between 1 and 40°C
Pack sizes – Part Codes	
Foodlube Hi-Torque 150	5L – p/c 15426 20L – p/c 15425 200L – p/c15429
Foodlube Hi-Torque 220	5L – p/c 15526 20L – p/c 15525 200L – p/c 15529
Foodlube Hi-Torque 320	5L – p/c 15766 20L – p/c 15765 200L – p/c 15769
Foodlube Hi-Torque 460	5L – p/c 15776 20L – p/c 15775 200L – p/c 15779

T +44 (0) 113 232 2600
F +44 (0) 113 232 2740
E customer-service@rocol.com
www.rocol.com

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of *ITW* Ltd



BS EN ISO 9001
Certificate No. FM 12448



BS EN ISO 14001
Certificate No. EMS 67596



OHSAS 18001
Certificate No. OHS 78173



INVESTOR IN PEOPLE

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.