




 LASER PRINT:



CODINGS 2:1



RETAINER FLAP OPEN VS CLOSED 2:1



NOTES:


- △1 AREA FOR LASER PRINT
- 2 USABLE CONTACTS MCON 1.2 LL
SEE TE-NO. 1452674
- 3 SEE PRODUCT SPECIFICATION NO.108-18782 FOR THE FOLLOWING PRODUCT PROPERTIES:
-MAX. WIRE SIZE RANGE PERMITTED
-PERMISSIBLE CURRENT CARRYING CAPACITY OF THE SINGLE CONTACT
-MAX OPERATING VOLTAGE
-VIBRATION RESISTANCE
-MAX OPERATING TEMPERATURE
- MAX OPERATING TEMPERATURE 130°C
- △4 SUPPLIER-MARK (ONLY FOR TE CONNECTIVITY INTERNAL TRACKING)
- △5 SPACE OF ACTIVITY
- △6 SUPPLY CONDITION: CPA (4) AND
RETAINER FLAP (1) IN PRELOCKED POSITION
- △7 WARPAGE PERMITTED TO MAX. -0.5mm
- △8 TE ORDER-NO.
- 9 ACCORDING TO INTERFACE DRAWING
SEE TE-NO. 114-18679-3
- △10 ASSEMBLY LINE SEGMENT IDENTIFICATION
- △11 DATE CODE (DDYY)
- △12 QR CODE:
FIRST ROW: MANUFACTURING INFORMATION ONLY FOR TE CONNECTIVITY
SECOND ROW: TE.COM ONLINE CATALOG LINK FOR CUSTOMER
- 14 THE MARKING ON THE COMPONENTS MAY VARY IN THE SAME BATCH TOO
IT DOES NOT SERVE ANY FUNCTION
IT IS ONLY USED FOR TE CONNECTIVITY INTERNAL TRACKING
FOR VALID CUSTOMER TRACKING PLEASE USE THE LASER PRINT - SEE NOTE △1
- △5 PLEASE CARRY OUT THE CLEARANCE TEST FOR THE SOCKET HOUSING
BASED ON THE WIRE SIZE USED
- 16 SECONDARY LOCK THAT HAVE BEEN CLOSED DURING TRANSPORT CAN BE MOVED BACK
TO PRE-LOCKED POSITION ACCORDING TO INSTRUCTIONS FOUND IN THE
APPLICATION SPEC. NO 114-94767

1-2441393-1 AS SHOWN



-	1	1	1	1	NEXTGEN+ MCON 1.2 LL CPA,SUST	PBT-GF30 BMB	GREEN	4
1	1	1	1	1	3POS MCON 1.2 - SEAL	SILOPREN LSR	BLUE	3
1	1	1	1	1	3POS,NEXTGEN+ MCON 1.2,PROTEC. COVER	PA6-GF15 BMB	BLACK	2
-	1	-	-	-	3POS,NEXTGEN+, MCON 1.2 LL REC,SLD - COD D	PBT-GF20 BMB	VIOLET	1
-	-	1	-	-	3POS,NEXTGEN+, MCON 1.2 LL REC,SLD - COD C	PBT-GF20 BMB	BLUE	1
-	-	-	1	-	3POS,NEXTGEN+, MCON 1.2 LL REC,SLD - COD B	PBT-GF20 BMB	BROWN	1
1	-	-	-	1	3POS,NEXTGEN+, MCON 1.2 LL REC,SLD - COD A	PBT-GF20 BMB	BLACK	1
1- -6	4- -13	- -12	- -11	- -1	DESCRIPTION	MATERIAL	COLOUR	ITEM NO
C	C	C	C	C	REVISION			
	QTY	REQD	PER	ASSY	PARTS LIST			

3D VIEW 2:1



TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-1400CENTRIC TO NOMINAL DIMENSION, EDITION 1992-11 SHALL APPLY.		DWN: 23APR2024			
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: SZEKELY LEHEL		 TE Connectivity	
DIMENSIONS:		APVD:	NAME:	3POS. NEXTGEN+, MCON 1.2 LL REC. SLD SUSTAINABLE	
mm		PRODUCT SPEC			
		109-94767			
0 P.LC ± 0.1		APPLICATION SPEC			
2 P.LC ± 0.01		114-94767			
0 P.LC ± 0.001		WEIGHT			
4 P.LC ± 0.0001					
ANGLES		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
FINISH		A	00779	C=2441393	-
MATERIAL		CUSTOMER DRAWING			
See: Parts List		SCALE 5:1 SHEET 1 OF 1 REV			