



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Holder**

Primary Product Color: **Ivory**

Primary Product Material: **PA 66**

Number of Positions: **18**

Operating Temperature (Max): **105 °C [221 °F]**

Features

Product Type Features

Connector Hardware Accessory Type	Holder
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	18
---------------------	----

Body Features

Primary Product Color	Ivory
Primary Product Material	PA 66

Housing Features

Centerline (Pitch)	2 mm[.079 in]
--------------------	---------------

Dimensions

Product Width	7.55 mm[.297 in]
Row-to-Row Spacing	6.6 mm
Product Length	22.3 mm[.878 in]
Product Height	6.65 mm[.261 in]
Wire Size	28 – 24 AWG

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Packaging Features



Packaging Method	Bag
Packaging Quantity	1000

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-292138-8
CT DOUBLE ROW ASSY H 18P HDR N



TE Part # 353918-1
CT 1.5MM REC CONT CRIMP TYPE



TE Part # CAT-3980700-DRWBSV
CT 2mm Dbl Row Assembly w/Boss: Vert.



TE Part # CAT-AM7017-H8172
AMP COMMON TERMINATION HOUSINGS



TE Part # 1-84580-8
2MM CT D/R HDR ASSY H/TEMP 18P

TE Part # CAT-AM7017-C7671
Common Termination Contacts —
POWER TRIPLE LOCK

Also in the Series | AMP CT

Connector Contacts(8)

Connector Hardware(46)

PCB Headers & Receptacles(756)

Rectangular Connector Housings(72)

Rectangular Power Connectors(906)

Standard Rectangular Connectors(158)

Wire-to-Board Connector Assemblies
& Housings(97)

Wire-to-Board Headers & Receptacles
(756)

Customers Also Bought

TE Part #1-1318115-9
DYNAMIC D-2100 TAB HSG 20P F/H

TE Part #61556-1
RING 22-16 AWG .0245 X .435 TPST

TE Part #179720-6
PL 187 (4.8 MM) HOUSING
RECEPTACLE

TE Part #2-175133-8
CT DOUBLE ROW 28P HOLDER
NATU.

TE Part #1565080-1
GRACE INERTIA 3.5 TAB CONTACT(L)

TE Part #350777-1
02P UMNL PLUG HSG

TE Part #CAT-D9934-A75B
Receptacle and Tab Housing: 5.08 mm
Pitch, 250-600V

TE Part #177900-1
POWER DBL LOCK PLUG HSG 4P



Documents

Product Drawings

CT DOUBLE ROW 18P HOLDER NATU.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-175133-8_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-175133-8_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-175133-8_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping of AMP 2.0mm Pitch, CT Crimp Typell Rec Contact

English

Application Specification

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English