



# Product data sheet

Power tools for trade & industry

Stirring Mechanism

## PRO GRW 18V-120



The compact alternative to a conventional mixer

### The most important data

Battery voltage	18.0 V
Weight	2.9 kg

**Order number** 0 601 1C2 000

## Technical data

### Additional data

Battery voltage	18.0 V
Weight	2.9 kg
Bit holder	M14
Stirrer basket diameter max	120 mm

## Noise/vibration information

### Total vibration values

Vibration emission value ah	1.1 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



**BOSCH**

Invented for life

# Product data sheet

Power tools for trade & industry

## Advantages:

- Compact and ergonomic design with highly adjustable handle and 13-cm extension piece
- Splash-free mixing thanks to 3 speed-adjustment options
- Superior mixing performance thanks to constant speed even under higher loads
- Reliable mixing of different materials due to powerful brushless motor
- Protection ensured with KickBack Control which switches off the tool to reduce the hazard of sudden torque reaction

**HEAVY  
DUTY**



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/ge/en/wac/>

