

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Solid-state relay, for signal amplification and isolation of the control and load circuits, can be plugged in the solderable plug-in bases SIM-AMS or with PCB connection for mounting directly onto the PCB, input: 4.25-32 V DC, output: 1-350 V DC/1 A

Your advantages

- Compact dimensions
- No electromagnetic interference
- High test voltage of up to 4 kV between control and load circuits
- No wear, even at high switching frequencies
- Electrically insulated housing
- No contact bounce – no movable parts
- Switching power of up to 350 V DC/1 A, 60 V DC/4 A or 480 V AC/5 A

Commercial data

Item number	2982634
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CK7
Product key	DK69L1
Catalog page	Page 558 (C-7-2013)
GTIN	4046356131988
Weight per piece (including packing)	25.35 g
Weight per piece (excluding packing)	23 g
Customs tariff number	85362010
Country of origin	CN

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Technical data

Product properties

Product type	Single solid-state relay
Operating mode	100% operating factor

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Data management status

Date of last data management	17.05.2024
------------------------------	------------

Electrical properties

Test voltage (Input/output)	4 kV (50 Hz, 1 min., input/output)
-----------------------------	------------------------------------

Input data

Nominal input voltage U_N	24 V DC
Input voltage range	4.25 V DC ... 32 V DC
Switching threshold "0" signal, voltage	< 1 V DC
Switching threshold "1" signal voltage	> 3.3 V DC
Typical input current at U_N	15 mA
Typical response time	< 100 μ s
Typical turn-off time	< 250 μ s
Transmission frequency	100 Hz

Output data

Design of digital output	electronic
Output voltage range	1 V DC ... 350 V DC
Limiting continuous current	1 A (see derating curve)
Min. load current	1 mA
Leakage current	100 μ A
Surge current	20 A ($t_p = 1$ s)
Voltage drop at max. limiting continuous current	0.5 V
Output circuit	2-conductor
Protective circuit	Reverse polarity protection; Polarity protection diode

Dimensions

Dimensional drawing	
Width	10.5 mm

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Height	43 mm
Depth	25.4 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations


Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 55011

Mounting


Assembly note	Can be aligned with > 9 mm spacing
Mounting position	any

Drawings

Diagram



Dimensional drawing




OV-24DC/350DC/1 - Semi-conductor relay

2982634

<https://www.phoenixcontact.com/in/products/2982634>



Circuit diagram



OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2982634>



cUL Recognized
Approval ID: FILE E 195083



UL Recognized
Approval ID: FILE E 195083



EAC
Approval ID: RU*C-DE.*08.B.00010

cULus Recognized

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Classifications

ECLASS

ECLASS-11.0	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604

ETIM

ETIM 9.0	EC001504
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/in/products/2982634>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in