MOSFET – Power, N-Channel, SUPERFET III, FRFET

650 V, 70 A, 33 mΩ

Description

SUPERFET III MOSFET is ON Semiconductor's brand-new high voltage super-junction (SJ) MOSFET family that is utilizing charge balance technology for outstanding low on-resistance and lower gate charge performance. This advanced technology is tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate.

Consequently, SUPERFET III MOSFET is very suitable for the various power system for miniaturization and higher efficiency.

SUPERFET III FRFET MOSFET's optimized reverse recovery performance of body diode can remove additional component and improve system reliability.

Features

- 700 V @ T_J = 150°C
- Typ. $R_{DS(on)} = 28 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. Q_g = 188 nC)
- Low Effective Output Capacitance (Typ. Coss(eff.) = 1568 pF)
- 100% Avalanche Tested
- These Devices are Pb-Free and are RoHS Compliant

Applications


- Telecom / Server Power Supplies
- Industrial Power Supplies
- EV Charger
- UPS / Solar



ON Semiconductor®

www.onsemi.com


V _{DSS}	R _{DS(ON)} MAX	I _D MAX
650 V	33 mΩ @ 10 V	70 A





TO-247 long leads CASE 340CX

MARKING DIAGRAM



\$Y = ON Semiconductor Logo &Z = Assembly Plant Code &3 = Data Code (Year & Week)

&K = Lot

NTHL033N65S3HF = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^{\circ}C$, Unless otherwise noted)

Symbol	Parameter	Value	Unit		
V _{DSS}	Drain to Source Voltage			V	
V _{GSS}	Gate to Source Voltage - DC		±30	V	
		- AC (f > 1 Hz)	±30		
I _D	Drain Current	– Continuous (T _C = 25°C)	70	Α	
		- Continuous (T _C = 100°C)	53		
I _{DM}	Drain Current	- Pulsed (Note 1)	175	Α	
E _{AS}	Single Pulsed Avalanche Energy (Note 2)	1250	mJ		
I _{AS}	Avalanche Current (Note 2)	12	Α		
E _{AR}	Repetitive Avalanche Energy (Note 1)	5.0	mJ		
dv/dt	dv/dt MOSFET dv/dt Peak Diode Recovery dv/dt (Note 3)		100	V/ns	
			50		
P_{D}	Power Dissipation	(T _C = 25°C)	500	W	
		- Derate Above 25°C	4.0	W/°C	
T _J , T _{STG}	Operating and Storage Temperature Range	-55 to +150	°C		
TL	Maximum Lead Temperature for Soldering, 1/8'	300	°C		

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected. 1. Repetitive rating: pulse–width limited by maximum junction temperature. 2. $I_{AS} = 12 \text{ A}$, $R_G = 25 \Omega$, starting $T_J = 25^{\circ}\text{C}$. 3. $I_{SD} \le 35 \text{ A}$, $di/dt \le 200 \text{ A/µs}$, $V_{DD} \le 400 \text{ V}$, starting $T_J = 25^{\circ}\text{C}$.

THERMAL CHARACTERISTICS

Symbol	Parameter	Value	Unit
$R_{ hetaJC}$	Thermal Resistance, Junction to Case, Max.	0.25	°C/W
$R_{ heta JA}$	R _{θJA} Thermal Resistance, Junction to Ambient, Max.		

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Marking	Package	Packing Method	Reel Size	Tape Width	Quantity
NTHL033N65S3HF	NTHL033N65S3HF	TO-247	Tube	N/A	N/A	30 Units

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
OFF CHARACT	ERISTICS		•	1		
BV _{DSS} Drain to Source Breakdown Volta		$V_{GS} = 0 \text{ V}, I_D = 1 \text{ mA}, T_J = 25^{\circ}\text{C}$	650			V
		V _{GS} = 0 V, I _D = 1 mA, T _J = 150°C	700			V
ΔBV _{DSS} /ΔT _J Breakdown Voltage Temperature Coefficient		I _D = 15 mA, Referenced to 25°C		0.63		V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 650 V, V _{GS} = 0 V			10	μΑ
		V _{DS} = 520 V, T _C = 125°C		263		
I _{GSS}	Gate to Body Leakage Current	V _{GS} = ±30 V, V _{DS} = 0 V			±100	nA
ON CHARACTE	RISTICS					
V _{GS(th)}	Gate Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 2.5 \text{ mA}$	3.0		5.0	V
R _{DS(on)}	Static Drain to Source On Resistance	V _{GS} = 10 V, I _D = 35 A		28	33	mΩ
9 _{FS}	Forward Transconductance	Transconductance $V_{DS} = 20 \text{ V}, I_D = 35 \text{ A}$		49		S
DYNAMIC CHA	RACTERISTICS			•		
C _{iss}	Input Capacitance	V 400 V V 0 V 6 4 MU		6720		pF
C _{oss}	Output Capacitance	$V_{DS} = 400 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		159		pF
C _{oss(eff.)}	Effective Output Capacitance	V _{DS} = 0 V to 400 V, V _{GS} = 0 V		1568		pF
C _{oss(er.)}	Energy Related Output Capacitance	V _{DS} = 0 V to 400 V, V _{GS} = 0 V		292		pF
Q _{g(tot)}	Total Gate Charge at 10V			188		nC
Q _{gs}	Gate to Source Gate Charge	$V_{DS} = 400 \text{ V}, I_D = 35 \text{ A}, V_{GS} = 10 \text{ V}$ (Note 4)		55		nC
Q _{gd}	Gate to Drain "Miller" Charge	(1000)		73		nC
ESR	Equivalent Series Resistance	f = 1 MHz		1.1		Ω
SWITCHING CH	IARACTERISTICS		-			
t _{d(on)}	Turn-On Delay Time			43		ns
t _r	Turn-On Rise Time	$V_{DD} = 400 \text{ V}, I_D = 35 \text{ A},$		35		ns
t _{d(off)}	Turn-Off Delay Time	$V_{GS} = 10 \text{ V, R}_{g} = 2.2 \Omega$ (Note 4)		110		ns
t _f	Turn-Off Fall Time			28		ns
SOURCE-DRAI	N DIODE CHARACTERISTICS					
I _S	Maximum Continuous Source to Drain Diode Forward Current				70	Α
I _{SM}	Maximum Pulsed Source to Drain Diode Forward Current				175	Α
V_{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _{SD} = 35 A			1.3	V
t _{rr}	Reverse Recovery Time	V _{DD} = 400 V, I _{SD} = 35 A,		173		ns
Q _{rr}	Reverse Recovery Charge	$dI_F/dt = 100 A/\mu s$		1003		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Essentially independent of operating temperature typical characteristics.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 3. On-Resistance Variation vs. Drain Current and Gate Voltage




Figure 5. Capacitance Characteristics




Figure 2. Transfer Characteristics




Figure 4. Body Diode Forward Voltage Variation vs. Source Current and Temperature




Figure 6. Gate Charge Characteristics

TYPICAL CHARACTERISTICS




Figure 7. Breakdown Voltage Variation vs. Temperature




Figure 9. Maximum Safe Operating Area




Figure 11. Eoss vs. Drain-to-Source Voltage




Figure 8. On–Resistance Variation vs. Temperature




Figure 10. Maximum Drain Current vs. Case Temperature

TYPICAL CHARACTERISTICS




Figure 12. Transient Thermal Response Curve




Figure 13. Gate Charge Test Circuit & Waveform




Figure 14. Resistive Switching Test Circuit & Waveforms





Figure 15. Unclamped Inductive Switching Test Circuit & Waveforms




Forward Voltage Drop

Figure 16. Peak Diode Recovery dv/dt Test Circuit & Waveforms

Body Diode

PACKAGE DIMENSIONS

TO-247-3LD CASE 340CX ISSUE O




NOTES: UNLESS OTHERWISE SPECIFIED.

- A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.

 B. ALL DIMENSIONS ARE IN MILLIMETERS.

- C. DRAWING CONFORMS TO ASME Y14.5 2009.
 D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
- E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.



DIM	MILLIMETERS					
DIM	MIN	NOM	MAX			
Α	4.58	4.70	4.82			
A 1	2.20	2.40	2.60			
A2	1.40	1.50	1.60			
D	20.32	20.57	20.82			
Е	15.37	15.62	15.87			
E2	4.96	5.08	5.20			
е	~	5.56	~			
L	19.75	20.00	20.25			
L1	3.69	3.81	3.93			
ØР	3.51	3.58	3.65			
Q	5.34	5.46	5.58			
S	5.34	5.46	5.58			
b	1.17	1.26	1.35			
b2	1.53	1.65	1.77			
b4	2.42	2.54	2.66			
С	0.51	0.61	0.71			
D1	13.08	~	~			
D2	0.51	0.93	1.35			
E1	12.81	~	~			
ØP1	6.60	6.80	7.00			

SUPERFET is a registered trademark of Semiconductor Components Industries, LLC. FRFET is a registered trademark of Semiconductor Components Industries, LLC (SCILLC) or its subsidiaries in the United States and/or other countries.

ON Semiconductor and ill are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative