

# LOCTITE<sup>®</sup> 638™

(TDS for the new formulation of LOCTITE® 638™) September 2013

#### PRODUCT DESCRIPTION

LOCTITE<sup>®</sup> 638™ provides the following product characteristics:

Technology	Acrylic
Chemical Type	Urethane methacrylate
Appearance (uncured)	Green liquid <sup>™S</sup>
Fluorescence	Positive under UV light <sup>LMS</sup>
Components	One component -
	requires no mixing
Viscosity	High
Cure	Anaerobic
Secondary Cure	Activator
Application	Retaining
Strength	High

# This Technical Data Sheet is valid for LOCTITE<sup>®</sup> 638™ manufactured from the dates outlined in the "Manufacturing Date Reference" section.

LOCTITE<sup>®</sup> 638<sup>™</sup> is designed for the bonding of cylindrical fitting parts, particularly where bond gaps can approach 0.25 mm and where maximum strength at room temperature is required. The product cures when confined in the absence of air between close fitting metal surfaces and prevents loosening and leakage from shock and vibration. Typical applications include locking bushings and sleeves into housings and on shafts. LOCTITE<sup>®</sup> 638<sup>™</sup> provides robust curing performance. It not only works on active metals (e.g. mild steel) but also on passive substrates such as stainless steel and plated surfaces. The product offers high temperature performance and oil tolerance. It tolerates minor surface contaminations from various oils, such as cutting, lubrication, anti-corrosion and protection fluids.

#### **NSF** International

Registered to NSF Category P1 for use as a sealant where there is no possibilty of food contact in and around food processing areas. Note: This is a regional approval. Please contact your local Technical Service Center for more information and clarification.

#### TYPICAL PROPERTIES OF UNCURED MATERIAL

Specific Gravity @ 25 °C 1.1
Flash Point - See MSDS
Viscosity, Brookfield - RVT, 25 °C, mPa·s (cP):

Spindle 3, speed 20 rpm, 2,000 to 3,000<sup>LMS</sup>


Viscosity, Cone & Plate, 25 °C, mPa·s (cP):

Shear rate 129 s<sup>-1</sup> 1,900 to 3,100

#### TYPICAL CURING PERFORMANCE


#### Cure Speed vs. Substrate

The rate of cure will depend on the substrate used. The graph below shows the shear strength developed with time on steel pins and collars compared to different materials and tested according to ISO 10123.



#### Cure Speed vs. Bond Gap


The rate of cure will depend on the bondline gap. The following graph shows shear strength developed with time on steel pins and collars at different controlled gaps and tested according to ISO 10123.






#### Cure Speed vs. Temperature

The rate of cure will depend on the temperature. The graph below shows the shear strength developed with time at different temperatures on steel pins and collars and tested according to ISO 10123.



#### **Cure Speed vs. Activator**

The graph below shows the shear strength developed with time on stainless steel pins and collars using Activator  $7471^{\text{TM}}$ ,  $7649^{\text{TM}}$  and  $7091^{\text{TM}}$  and tested according to ISO 10123.



#### TYPICAL PROPERTIES OF CURED MATERIAL

#### **Physical Properties:**

Glass Transition Temperature ISO 11359-2, °C 76 Coefficient of Thermal Expansion, ISO 11359-2, K<sup>-1</sup>:

Below Tg 96×10<sup>-06</sup> Above Tg 192×10<sup>-06</sup>

### TYPICAL PERFORMANCE OF CURED MATERIAL Adhesive Properties

After 15 minutes @ 22 °C

Compressive Shear Strength, ISO 10123:

Steel pins and collars  $N/mm^2 \ge 13.5^{LMS}$  (psi) (1,960)

After 24 hours @ 22 °C

Compressive Shear Strength, ISO 10123:

Steel pins and collars  $N/mm^2 \ge 25^{LMS}$  (psi) (3,625)

After 7 days @ 22 °C

Compressive Shear Strength, ISO 10123:

Steel pins and collars	N/mm <sup>2</sup> 29
	(psi) (4,200)
Stainless Steel pins and collars	N/mm <sup>2</sup> 28
	(psi) (3,990)
Aluminum pins and collars	N/mm <sup>2</sup> 17
•	(psi) (2,710)

After 24 hours @ 22 °C

Breakaway Torque, ISO 10964:

M10 black oxide bolts and mild	N·m	57
steel nuts	(lb.in.)	(505)
3/8 x 16 steel nuts (grade	N⋅m	25
2) and bolts (grade 5)	(lb.in.)	(220)

Prevail Torque, ISO 10964:

M10 black oxide bolts and mild steel nuts	N·m (lb.in.)	22 (195)
3/8 x 16 steel nuts (grade 2) and bolts (grade 5)	N·m (lb.in.)	9.4 (85)

Breakloose Torque, ISO 10964, Pre-torqued to 5 N·m: 3/8 x 16 steel nuts (grade N·m 23 2) and bolts (grade 5) (lb.in.) (205)


Prevail Torque, ISO 10964, Pre-torqued to 5 N·m: 3/8 x 16 steel nuts (grade N·m 12 2) and bolts (grade 5) (lb.in.) (105)

#### TYPICAL ENVIRONMENTAL RESISTANCE

Cured for 1 week @ 22 °C Compressive Shear Strength, ISO 10123: Steel pins and collars


#### **Hot Strength**

Tested at temperature



#### **Heat Aging**

Aged at temperature indicated and tested @ 22 °C



#### Chemical/Solvent Resistance

Aged under conditions indicated and tested @ 22 °C.

		% of initial strength			n
Environment	°C	500 h	1000 h	3000 h	5000 h
Motor oil (5W40 -Synthetic)	125	175	165	165	165
Unleaded Petrol	22	105	105	105	105
Brake fluid	22	120	115	115	115
Water/glycol 50/50	87	145	145	145	145
Ethanol	22	110	110	100	100
Acetone	22	105	105	105	105
B100 Bio-Diesel	22	115	115	115	115
DEF (AdBlue <sup>®</sup> )	22	115	105	105	105

#### Stainless Steel pins and collars

		% of initial strength			
Environment	°C	500 h	1000 h	3000 h	5000 h
Sodium Hydroxide, 20%	22	100	85	60	55
Phosphoric Acid, 10%	22	95	70	40	40

#### **GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Where aqueous washing systems are used to clean the surfaces before bonding, it is important to check for compatibility of the washing solution with the adhesive. In some cases these aqueous washes can affect the cure and performance of the adhesive.

This product is not normally recommended for use on plastics (particularly thermoplastic materials where stress cracking of the plastic could result). Users are recommended to confirm compatibility of the product with such substrates.

#### Directions for use:

#### For Assembly

- 1. For best results, clean all surfaces (external and internal) with a LOCTITE<sup>®</sup> cleaning solvent and allow to dry.
- 2. To accelerate cure speed or where large gaps are present, use activator and allow to dry.
- For Slip Fitted Assemblies, apply adhesive around the leading edge of the pin and the inside of the collar and use a rotating motion during assembly to ensure good coverage.
- For Press Fitted Assemblies, apply adhesive thoroughly to both bond surfaces and assemble at high press on rates.
- 5. For Shrink Fitted Assemblies, the adhesive should be coated onto the part to produce a smooth, even film of material. If heating the hub for assembly, coat the pin. If the pin is to be cooled for assembly, coat the hub. If both heating and cooling is to be done, apply material to cooled part. Avoid condensation on cooled parts.
- 6. Parts should not be disturbed until sufficient handling strength is achieved.

#### For Disassembly

- 1. Remove with standard hand tools.
- 2. If needed, apply localized heat to the assembly to approximately 250 °C. Disassemble while hot.
- 3. If this temperature is not possible, heat as much as possible and use mechanical aids.

#### For Cleanup

 Cured product can be removed with a combination of soaking in a Loctite solvent and mechanical abrasion such as a wire brush.

#### Loctite Material Specification<sup>LMS</sup>

LMS dated July 11, 2013. Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Quality.

#### Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

#### Conversions

(°C x 1.8) + 32 = °F kV/mm x 25.4 = V/mil mm / 25.4 = inches µm / 25.4 = mil N x 0.225 = lb N/mm x 5.71 = lb/in N/mm² x 145 = psi MPa x 145 = psi N·m x 8.851 = lb·in N·m x 0.738 = lb·ft N·mm x 0.142 = oz·in mPa·s = cP

#### Manufacturing Date Reference

This Technical Data Sheet is valid for LOCTITE<sup>®</sup> 638™ manufactured from the dates below:

First manufacturing data

<u>wade m</u> .	<u>rirst manufacturing date</u> .
U.S.A.	September 2013
EU	Pending
China	August 2013
Brazil	November 2013
India	Pending

#### Disclaimer

Mada in

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

### In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

## In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

#### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere.  $^{\otimes}$  denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.4