



Wire & Cable > Wire & Cable Accessories > Cable Ties



Cable Tie Style: **Heavy Duty**

Packaging Method: **Bag**

Tensile Strength: **533.78 Newton**

Product Length: **390 mm [15.25 in]**

Features

Product Type Features

Cable Tie Style	Heavy Duty
Tensile Strength	533.78 Newton

Body Features

Primary Product Color	Natural
Primary Product Material	Nylon

Dimensions

Compatible Cable Bundle Diameter Range	101.6 mm[4 in]
Product Length	390 mm[15.25 in]
Product Width	7.7 mm[.303 in]
Product Thickness	1.98 mm[.078 in]

Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2025 (247)
Candidate List Declared Against: JAN 2025 (247)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #1-604751-9
CABLE TIE,11-3/4" L, NAT,100PK




TE Part #1-604774-9
CABLE TIE,15-1/2" L, NAT,100PK




TE Part #1-1478762-5
METAL BACKSHELL 15 WAY TOP E




TE Part #100504L
CONT SOC ASSY




TE Part #36917
TERMINAL,SOLIS R 1/0 3/8



TE Part #2-604771-9
CABLE TIE, NATURAL, 4" (1000)



TE Part #35184
TERMINAL,SOLIS R 2 3/8



TE Part #2-603227-9
CABLE TIE, NAT, 6" L, 1000/PACK



TE Part #608036-1
SILICONE FUSION TAPE,1"X36'



TE Part #170362-3
MINI UNIVERSAL M-N-L SOCKET

Documents

Product Drawings

CABLE TIE HD,15-1/4" L, NAT,100PK

English

Datasheets & Catalog Pages

CABLE TIES

English