

Impact Wrench XGT®

TW003G

40Vmax, 1/2"

Model TW003G is a impact wrench powered by a 40Vmax XGT Li-Ion battery. The tip shape of the anvil has been changed to a 12.7mm (1/2") square drive and socket retention to a pin detent.

Suitable for tasks such as chassis maintenance and construction site work. Driving shank 12.7mm (1/2") Square, pintent. Max fastening/Nut-busting torque: 1,600Nm. 4 stage impact power selection. Automatic impact stop system in forward/reverse rotation. Trigger switch with full speed mode.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 800 / 1000 / 1200 / 1800 min ⁻¹
Max Fastening Torque Impact Drill	200 / 400 / 820 / 1360 Nm
Nut-busting torque	1600 Nm
Tightening Capacity Standard Bolt	M12 - M36
Tightening Capacity High Tensile Bolt	M10 - M27
Impacts per Minute (IPM)	0 - 1600 / 2000 / 2300 / 2400 min ⁻¹
Drive Square	1/2 "
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electronic 4 stage impact power selection for added versatility
- Automatic impact stop system for avoiding under- and over-tightening
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing