

Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

| APPLICABLE STANDARD | | | | |
|--|---------------------------------------|-----------------------|---------------------------|---|
| RATING | OPERATING TEMPERATURE RANGE | 1 -25 °C TO +105 °C | STORAGE TEMPERATURE RANGE | -10 °C TO +60 °C |
| | VOLTAGE | _____ | APPLICABLE CABLE | 22 mm ² or AWG #4 OUTER DIAMETER : φ12.4 max. |
| | CURRENT | 2 94 A | | |
| SPECIFICATIONS | | | | |
| ITEM | TEST METHOD | REQUIREMENTS | QT | AT |
| CONSTRUCTION | | | | |
| GENERAL EXAMINATION | VISUALLY AND BY MEASURING INSTRUMENT. | ACCORDING TO DRAWING. | X | X |
| | | | | |
| COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
| △ | | | | |
| REMARK | | APPROVED | SU. OBARA | 13.02.22 |
| NOTE 1 OPERATING TEMPERATURE RANGE INCLUDES THE TEMPERATURE RISE BY CURRENT CARRYING. | | CHECKED | YH. YAMADA | 13.02.22 |
| 2 RATING CURRENT SHALL BE TESTED UNDER MATED CONDITION WITH AN APPLICABLE CONNECTOR. | | DESIGNED | HS. KAWASHIMA | 13.02.22 |
| | | DRAWN | KN. IKEHARA | 13.02.22 |
| Unless otherwise specified, refer to JIS C 5402, IEC 60512. | | | | |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test | | DRAWING NO. | ELC4-118015-00 | |
| HRS | SPECIFICATION SHEET | PART NO. | EF1-38-22 | |
| | HIROSE ELECTRIC CO., LTD. | CODE NO. | CL142-0006-7-00 | △ 1/1 |